

Type code

Type code

**Type/process temperature/process pressure/enclosure rating**

- S Standard, -20 ... +100 °C, -1 ... 10 bar, IP65/IP67
- H Extended, -20 ... +150 °C, -1 ... 16 bar, IP68/IP69

**Process connection/material**


- B G ½" PN25, DIN3852-A / 316L
- G G ½" PN25, ISO0228-1, for hygienic thread adapter / 316L (RA < 0.76 µm)
- N ½" NPT PN25, ASME B1.20.1/316L

**Electrical output**

- T 2 digital outputs (PNP/NPN/push-pull switchable) with IO-Link, 12 ... 35 V DC

**Electrical connection**

- M M12 round connector x 1, 4-pin



Not all variants of the type code can be combined!