

Type code

Type code

Output signal

P	Output signal Pt100, 4-wire
A	Measuring transducer 4 ... 20 mA, 2-wire

Measuring range

A	-50 ... +150 °C
B	-50 ... +250 °C

Process connection

D2	Clamp, DIN 32676, DN 10, DN 15, DN 20
D4	Clamp, DIN 32676, DN 25, DN 32, DN 40
D5	Clamp, DIN 32676, DN 50
C2	Clamp, ISO 2852, DN 12, DN 12.7, DN 17.2, DN 21.3
C3	Clamp, ISO 2852, DN 25, DN 33.7, DN 38
C5	Clamp, ISO 2852, DN 40, DN 51
T5	Tri-Clamp ½", ¾"
T1	Tri-Clamp 1", 1 ½"
T2	Tri-Clamp 2"
VB	Varivent connection, form B, DN 10, DN15
VF	Varivent connection, form F, DN 25
VN	Varivent connection, form N, DN 40
51	Conical coupling, DIN 11851, DN 20, with grooved cap nut
52	Conical coupling, DIN 11851, DN 25, with grooved cap nut
53	Conical coupling, DIN 11851, DN 32, with grooved cap nut
54	Conical coupling, DIN 11851, DN 40, with grooved cap nut
55	Conical coupling, DIN 11851, DN 50, with grooved cap nut

Installation length / Diameter

0256	25 mm / 6 mm
0506	50 mm / 6 mm
0756	75 mm / 6 mm
1006	100 mm / 6 mm
1506	150 mm / 6 mm
2006	200 mm / 6 mm

THTS -	1					M	Z
--------	---	--	--	--	--	---	---