



Betriebsanleitung, Ergänzung DEUTSCH

Bitte lesen Sie die beiliegende Betriebsanleitung und diese Betriebsanleitungsergänzung sorgfältig durch.

Ergänzung/Abweichung der technischen Daten zur Betriebsanleitung WL12G-3:

Typ: **WL12G-3V2572S05**

Artikelnr.: **1069340**

WL12G-3V2572 mit zusätzlich			
Linienförmiger Lichtfleck			
Lichtfleckgröße / im Abstand 1,5mm x 9mm @ 60 mm			
25mm @ 1 m			
Schaltpegel Modus III = 40%			
Modus Einstellung durch Teach-In			
Modus	10%	18%	40%
Target Art	PET-Flasche / Folie	Glas	Farbige Glas
Flasche			
Teach time			
button / (s)	2...5	5...10 ☐	> 10
Teach time			
Extern (ET) / (ms)	30...99	100 ...199	> 200
Farbe der			
Status LED	Grün	Blau	Hell Blau

Operating Instruction, Supplement ENGLISH

Please read the enclosed operating instruction and this operating instruction supplement carefully.

Supplement/deviation of technical data of the operating instructions WL12G-3:

Model Name: **WL12G-3V2572S05**

Part No.: **1069340**

WL12G-3V2572 with modification as followed			
line shaped lights spot			
Light spot size / at a distance 1,5mm x 9mm @ 60 mm			
25mm @ 1 m			
Switching mode III = 40%			
Modus set-up via Teach-In			
Modus	10%	18%	40%
Target Type	PET-bottle / foil	Glass	Colored Glas bottle
Teach time			
button / (s)	2...5	5...10 ☐	> 10
Teach time			
Extern (ET) / (ms)	30...99	100 ...199	> 200
Color of			
Status LED	Green	Blue	Bright Blue