



# SICK

8016332

## Betriebsanleitung, Ergänzung DEUTSCH

Bitte lesen Sie die beiliegende Betriebsanleitung und diese Betriebsanleitungsergänzung sorgfältig durch.

### Ergänzung/Abweichung der technischen Daten zur Betriebsanleitung WT14-2:

Typ: **WT14-2P432S18**

Artikelnr.: **1057507**

|                                    |                         |
|------------------------------------|-------------------------|
| Lichtquelle                        | PinPoint-LED (Rotlicht) |
| Schaltabstand max.                 | 50 ... 1000 mm / 90%    |
|                                    | 50 ... 700 mm / 18%     |
|                                    | 50 ... 400 mm / 6%      |
| Lichtfleckdurchmesser / Entfernung | 7 mm / 300 mm           |

Irrtümer und Änderungen vorbehalten

SICK AG, D-79183 Waldkirch, Erwin-Sick-Str. 1, [www.sick.com](http://www.sick.com)

## Operating Instruction, Supplement ENGLISH

Please read the enclosed operating instruction and this operating instruction supplement carefully.

### Supplement/deviation of technical data of the operating instructions WT14-2:

Model Name: **WT14-2P432S18**

Part No.: **1057507**

|                                |                          |
|--------------------------------|--------------------------|
| Light source                   | PinPoint LED (red light) |
| Sensing range max.             | 50 ... 1000 mm / 90%     |
|                                | 50 ... 700 mm / 18%      |
|                                | 50 ... 400 mm / 6%       |
| Light spot diameter / distance | 7 mm / 300 mm            |

Subject to change without notice

SICK AG, D-79183 Waldkirch, Erwin-Sick-Str. 1, [www.sick.com](http://www.sick.com)