



SICK

8017208

Betriebsanleitung, Ergänzung DEUTSCH

Bitte lesen Sie die beiliegende Betriebsanleitung und diese Betriebsanleitungsergänzung sorgfältig durch.

Ergänzung/Abweichung der technischen Daten zur Betriebsanleitung WL12G-3:

Typ: **WL12G-3V2572S07**

Artikelnr.: **1069341**

WL12G-3V2572 mit zusätzlich

Schaltpegel Modus III = 40%

Modus Einstellung durch Teach-In

Modus	10%	18%	40%
Target Art Flasche	PET-Flasche / Folie	Glas	Farbige Glas
Teach time button / (s)	2...5	5...10	> 10
Teach time Extern (ET) / (ms)	30...99	100 ...199	> 200
Farbe der Status LED	Grün	Blau	Hell Blau

Irrtümer und Änderungen vorbehalten

SICK AG, D-79183 Waldkirch, Erwin-Sick-Str. 1, www.sick.com

Operating Instruction, Supplement ENGLISH

Please read the enclosed operating instruction and this operating instruction supplement carefully.

Supplement/deviation of technical data of the operating instructions WL12G-3:

Model Name: **WL12G-3V2572S07**

Part No.: **1069341**

WL12G-3V2572 with modification as followed

Switching mode III = 40%

Modus set-up via Teach-In

Modus	10%	18%	40%
Target Type	PET-bottle / foil	Glass	Colored Glas bottle
Teach time button / (s)	2...5	5...10	> 10
Teach time Extern (ET) / (ms)	30...99	100 ...199	> 200
Color of Status LED	Green	Blue	Bright Blue

Subject to change without notice.

SICK AG, D-79183 Waldkirch, Erwin-Sick-Str. 1, www.sick.com