



SICK

8016330

Betriebsanleitung, Ergänzung DEUTSCH

Bitte lesen Sie die beiliegende Betriebsanleitung und diese Betriebsanleitungsergänzung sorgfältig durch.

Ergänzung/Abweichung der technischen Daten zur Betriebsanleitung WT14-2:

Typ: **WT14-2P432S17**

Artikelnr.: **1053779**

Lichtquelle	PinPoint-LED (Rotlicht)
Schaltabstand max.	50 ... 1300 mm / 90%
Lichtfleckdurchmesser / Entfernung	7 mm / 300 mm
Schaltabstand voreingestellt auf Potentiometer durch Label versiegelt	680 mm / 18%

Irrtümer und Änderungen vorbehalten
SICK AG, D-79183 Waldkirch, Erwin-Sick-Str. 1, www.sick.com

Operating Instruction, Supplement ENGLISH

Please read the enclosed operating instruction and this operating instruction supplement carefully.

Supplement/deviation of technical data of the operating instructions WT14-2:

Model Name: **WT14-2P432S17**

Part No.: **1053779**

Light source	PinPoint LED (red light)
Sensing range max.	50 ... 1300 mm / 90%
Light spot diameter / distance	7 mm / 300 mm
Sensing range pre-adjusted to Potentiometer sealed by label	680 mm / 18%

Subject to change without notice
SICK AG, D-79183 Waldkirch, Erwin-Sick-Str. 1, www.sick.com