



SICK

8021246

Betriebsanleitung, Ergänzung DEUTSCH

Bitte lesen Sie die beiliegende Betriebsanleitung und diese Betriebsanleitungsergänzung sorgfältig durch.

Ergänzung/Abweichung der technischen Daten zur Betriebsanleitung 8018743 MLG-2 ProNet mit CANopen-Feldbus

Typ: MLG10N-3140C1S456

Artikelnr.: 1087271

Sonderausführung:

- Kreuzstrahlmodus „messend“ für 629 Strahlen. (Voreingestellt.)
- CANopen-Voreinstellungen:
 - o Node-ID: 11
 - o Baudrate: 500kBit/s
 - o Prozessdaten mit Strahlstatus. Details siehe EDS-Datei.
- SOPAS-Konfiguration mit spezieller SDD.
- CANopen-Integration mit spezieller EDS-Datei.

Irrtümer und Änderungen vorbehalten

SICK AG, D-79183 Waldkirch, Erwin-Sick-Str. 1, www.sick.com

Operating Instruction, Supplement ENGLISH

Please read the enclosed operating instruction and this operating instruction supplement carefully.

Supplement/deviation of technical data of the operating instructions 8018744 MLG-2 ProNet with CANopen fieldbus

Model Name: MLG10N-3140C1S456

Part No.: 1087271

Special version:

- Cross beam mode “measurement” for 629 beams. (Default setup)
- CANopen-Pre-Settings:
 - o Node-ID: 11
 - o Baud rate: 500kBit/s
 - o Process data with beam status. Details see EDS file.
- SOPAS configuration with special SDD.
- CANopen integration with special EDS file.

Subject to change without notice.

SICK AG, D-79183 Waldkirch, Erwin-Sick-Str. 1, www.sick.com