

ARS20

ABSOLUTE ENCODERS





Technical data overview

| Shaft type | Solid shaft, Servo flange Solid shaft |
|--|--|
| Shaft diameter | 3/8" |
| Connection type | Cable, radial Male connector, radial |
| Max. resolution (number of steps per revolution x number of revolutions) | 8.192 32.768 360 |

Ordering information

Other models and accessories → www.sick.com/ARS20

• Mechanical design: Solid shaft, Servo flange

• Shaft diameter: 3/8"

| Connection type | Туре | Part no. |
|----------------------|----------------|----------|
| Cable, radial, 1.5 m | ARS20-26K08192 | 7101940 |
| | ARS20-26K32768 | 7101941 |
| | ARS20-27K08192 | 7101964 |
| | ARS20-27K32768 | 7101965 |
| | ARS20-66K08192 | 7101942 |
| | ARS20-66K32768 | 7101943 |
| | ARS20-67K08192 | 7101966 |
| | ARS20-67K32768 | 7101967 |
| | ARS20-A6K08192 | 7101922 |
| | ARS20-A6K32768 | 7101923 |
| | ARS20-A7K08192 | 7101930 |
| | ARS20-A7K32768 | 7101931 |
| | ARS20-F6K08192 | 7101938 |
| | ARS20-F6K32768 | 7101939 |
| | ARS20-F7K08192 | 7101962 |
| | ARS20-F7K32768 | 7101963 |

| Connection type | Туре | Part no. |
|------------------------|----------------|----------|
| Male connector, radial | ARS20-26408192 | 7101952 |
| | ARS20-26432768 | 7101953 |
| | ARS20-27408192 | 7101976 |
| | ARS20-27432768 | 7101977 |
| | ARS20-66408192 | 7101954 |
| | ARS20-66432768 | 7101955 |
| | ARS20-67408192 | 7101978 |
| | ARS20-67432768 | 7101979 |
| | ARS20-A6A08192 | 7101918 |
| | ARS20-A6A32768 | 7101919 |
| | ARS20-A7A08192 | 7101926 |
| | ARS20-A7A32768 | 7101927 |
| | ARS20-F6408192 | 7101950 |
| | ARS20-F6432768 | 7101951 |
| | ARS20-F7408192 | 7101974 |
| | ARS20-F7432768 | 7101975 |

Mechanical design: Solid shaft
Shaft diameter: 3/8"

| Connection type | Туре | Part no. |
|----------------------|----------------|----------|
| Cable, radial, 1.5 m | ARS20-2FK08192 | 7101934 |
| | ARS20-2FK32768 | 7101935 |
| | ARS20-2GK08192 | 7101958 |
| | ARS20-2GK32768 | 7101959 |
| | ARS20-6FK08192 | 7101936 |
| | ARS20-6FK32768 | 7101937 |
| | ARS20-6GK08192 | 7101960 |
| | ARS20-6GK32768 | 7101961 |
| | ARS20-AFK08192 | 7101920 |
| | ARS20-AFK32768 | 7101921 |
| | ARS20-AGK08192 | 7101928 |
| | ARS20-AGK32768 | 7101929 |
| | ARS20-FFK08192 | 7101932 |
| | ARS20-FFK32768 | 7101933 |
| | ARS20-FGK08192 | 7101956 |
| | ARS20-FGK32768 | 7101957 |

| Connection type | Туре | Part no. |
|------------------------|----------------|----------|
| Male connector, radial | ARS20-2F408192 | 7101946 |
| | ARS20-2F432768 | 7101947 |
| | ARS20-2G408192 | 7101970 |
| | ARS20-2G432768 | 7101971 |
| | ARS20-6F408192 | 7101948 |
| | ARS20-6F432768 | 7101949 |
| | ARS20-6G408192 | 7101972 |
| | ARS20-6G432768 | 7101973 |
| | ARS20-AFA08192 | 7101916 |
| | ARS20-AFA32768 | 7101917 |
| | ARS20-AGA08192 | 7101924 |
| | ARS20-AGA32768 | 7101925 |
| | ARS20-FF408192 | 7101944 |
| | ARS20-FF432768 | 7101945 |
| | ARS20-FG408192 | 7101968 |
| | ARS20-FG432768 | 7101969 |
| | ARS20-G7500360 | 7102172 |

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

