KHU53-XXX01700 KH53

MAGNETIC LINEAR ENCODERS




•

KHU53-XXX01700 | KH53 MAGNETIC LINEAR ENCODERS

	Туре		Part no.
		KHU53-XXX01700	1030086
Illustration may differ	Other models and accessories → www.sick.com/KH53		
Detailed technical data			
Performance			
Measuring range		0 m 1,700 m	
Interfaces			
Code type		Universal configurable	
Mechanical data			
Weight		+ 0.5 kg, per meter	
Length of measuring element		1.9072 m (including distance)	
Material, measuring elements		AIMgSi0,5F22	
Description		Sector	y coded for measuring range up to 1700 m (not suit- n)
Ambient data			
Resistance to shocks		50 g, 10 ms (DIN EN 61000-2-27)	
Resistance to vibration		30 g, 20 Hz 250 Hz (DIN EN 61000-2-	6)
Classifications			
ECLASS 5.0		27270705	
ECLASS 5.1.4		27270705	
ECLASS 6.0		27270705	
ECLASS 6.2		27270705	
ECLASS 7.0		27270705	
ECLASS 8.0		27270705	
ECLASS 8.1		27270705	
ECLASS 9.0		27270705	
ECLASS 10.0		27270705	
ECLASS 11.0		27270705	
ECLASS 12.0		27274304	
ETIM 5.0		EC002544	
ETIM 6.0		EC002544	
ETIM 7.0		EC002544	
ETIM 8.0		EC002544	
UNSPSC 16.0901		41111613	


Dimensional drawing (Dimensions in mm (inch))

Measuring element




Position tolerance


End of measurement path



Start of measuring path



Assembly note




Only use non ferro-magnetic materials for the assembly base of the read head. A separation distance of 80 mm must be observed for ferro-magnetic materials (e.g., iron).

KHU53-XXX01700 | KH53

MAGNETIC LINEAR ENCODERS

Length of measuring element



SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

