




Flexi Link cable

SICK
Sensor Intelligence.



Ordering information

Type	Part no.
Flexi Link cable	6034249

Other models and accessories → www.sick.com/

Detailed technical data

Technical specifications

Accessory group	Plug connectors and cables
Accessory family	Cables (ready to assemble)
Connection type head A	Flying leads
Connection type head B	Flying leads
Cable	4-wire, twisted pair, PVC
Jacket material	PVC
Cable diameter	8.5 mm
Conductor cross-section	2 x 2 x 0.34 mm ²
Shielding	Shielded
Signal type	Flexi Link
Items supplied	By the meter

Classifications

ECl@ss 5.0	19030312
ECl@ss 5.1.4	19030312
ECl@ss 6.0	27061801
ECl@ss 6.2	27061801
ECl@ss 7.0	27061801
ECl@ss 8.0	27061801
ECl@ss 8.1	27061801
ECl@ss 9.0	27061801
ECl@ss 10.0	27061801
ECl@ss 11.0	27061801
ECl@ss 12.0	27061801
ETIM 5.0	EC000830
ETIM 6.0	EC000830
ETIM 7.0	EC003249
ETIM 8.0	EC003249
UNSPSC 16.0901	26121604

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com