



DSC-1205T000025KM0

SICK
Sensor Intelligence.



Illustration may differ

Ordering information

Type	Part no.
DSC-1205T000025KM0	6030664

Other models and accessories → www.sick.com/


Detailed technical data

Technical specifications


Accessory group	Distributors
Accessory family	T-junctions
Connection type head A	Female connector, M12, 5-pin, A-coded
Connection type head B	Male connector, M12, 5-pin, A-coded
Connector material	TPU
Connector color	Black
Locking nut material	CuZn, nickel-plated brass
Reference voltage	≤ 60 V
Current loading	4 A
Note	5-pin
Enclosure rating	IP67 ¹⁾
Description	T-piece for simultaneous connection to sender and receiver, splits the cable from the control cabinet to the sender and receiver

¹⁾ Only in fully locked position with its plugs.

Dimensional drawing (Dimensions in mm (inch))



PIN assignment



SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com