


MAGNETIC TAPE

SICK
Sensor Intelligence.



Ordering information

| Type | Part no. |
|---------------|----------|
| MAGNETIC TAPE | 5337613 |

Other models and accessories → www.sick.com/

Detailed technical data

Technical specifications

| | |
|--|--|
| Accessory group | Magnets |
| Description | Magnetic tape, North is top side, adhesive, width 25 mm, length 50 m |
| Dimensions (W x H x L) | 25 mm x 1.3 mm x 50 m |
| Maximum energy product | ≥ 9 kJ/m ³ |
| Remanence | < 220 mT |
| Coercivity of the mag. flow density | ≥ 170 kA/m |
| Coercivity of the mag. polarization | ≥ 280 kA/m |
| Field line thickness via LS | 150 g |
| Fire protection class | B2 nach DIN 4102 |
| Density | 3.7 g/cm ³ |
| Magnetization | Axial |
| Minimum bend radius | 2 mm ¹⁾ |
| Ambient operating temperature max. | ≤ +70 °C |

¹⁾ Vertical.

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com