



CDM420-0205

Connection Device Modular

4DPROCONNECTIVITY

SICK
Sensor Intelligence.



Illustration may differ



Ordering information

Type	Part no.
CDM420-0205	1029854

Other models and accessories → www.sick.com/Connection_Device_Modular

Detailed technical data

Features

Brief description	Modular connection module for one sensor with pre-mounted CMF400 PROFIBUS module (Interface 2 x M12) and integrated CMC parameter cloning module
Supported products	CLV61x - CLV65x
Cloning module support (CMC)	Yes
Supports display module (CMD)	Yes
Supports power supply module (CMP)	Yes
Supports fieldbus gateway (CMF)	Integrated (PROFIBUS DP)

Mechanics/electronics

Power consumption	Power consumption of the sensor + 0.5 W
Housing	Polycarbonate
Housing color	Blue (RAL 5012)
Enclosure rating	IP65 ¹⁾
Protection class	III
Weight	+ 800 g
Dimensions (L x W x H)	192 mm x 167 mm x 70 mm
Scanner connection	15-pin D-Sub HD female connector
Service plug	9-pin D-Sub plug (internal)

¹⁾ When using a standard connection cable for scanners by SICK.

Interfaces

Ethernet	✓, TCP/IP
Remark	Corresponding CMF fieldbus gateway additionally necessary
Serial	✓, RS-232, RS-422, RS-485
Remark	Depending on sensor connected
CAN	✓
Remark	Depending on sensor connected
PROFIBUS DP	✓
Remark	CMF400 PROFIBUS-Gateway already integrated

DeviceNet™	✓
Remark	Corresponding CMF fieldbus gateway additionally necessary
Digital inputs	Depending on sensor connected
Digital outputs	Depending on sensor connected
Optical indicators	5 LED
Configuration software	SOPAS ET

Ambient data



Ambient operating temperature	0 °C ... +40 °C
Storage temperature	-20 °C ... +70 °C
Permissible relative humidity	< 90 %, Non-condensing


Classifications

eCI@ss 5.0	27242208
eCI@ss 5.1.4	27242608
eCI@ss 6.0	27242608
eCI@ss 6.2	27242608
eCI@ss 7.0	27242608
eCI@ss 8.0	27242608
eCI@ss 8.1	27242608
eCI@ss 9.0	27242608
eCI@ss 10.0	27242608
eCI@ss 11.0	27242608
eCI@ss 12.0	27242608
ETIM 5.0	EC001604
ETIM 6.0	EC001604
ETIM 7.0	EC001604
ETIM 8.0	EC001604
UNSPSC 16.0901	32151705

Recommended accessories

Other models and accessories → www.sick.com/Connection_Device_Modular

	Brief description	Type	Part no.
Cloning module			
	External parameter memory for integration in CDB620/CDB650/CDM42x	CMC600-101	1042259
Plug connectors and cables			
	Head A: female connector, M12, 17-pin, straight Head B: male connector, D-Sub-HD, 15-pin, straight Cable: Power, serial, CAN, digital I/Os, shielded, 3 m	YF2Z1D-030XXXMHDAC	2055420

	Brief description	Type	Part no.
	Head A: female connector, D-Sub, 9-pin, straight Head B: female connector, D-Sub, 9-pin, straight Cable: serial, unshielded, 3 m For PC connection	YFHDA9-030XXXFHDA9	2103279

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com