


# MBR-065-KLB

Magnetic tapes

**MAGNETS**

**SICK**  
Sensor Intelligence.



### Ordering information

Description	Type	Part no.
Magnetic tape ring inner diameter: 65 mm, magnetic tape ring outer diameter: 81 mm, magnetic tape ring width: 10 mm, weight: ≤ 0.58 kg, <sup>☞</sup> magnetic tape material: 17410 hard ferrite 9/28 P, material ring: Aluminum, period length: 2 mm, operating temperature range: -30 °C ... 100 °C, <sup>☞</sup> storage temperature range: -30 °C ... 100 °C, temperature coefficient: (11 ± 1) µm/K/m	MBR-065-KLB	6079316

Magnetic tape for STS065

Other models and accessories → [www.sick.com/Magnetic\\_tapes](http://www.sick.com/Magnetic_tapes)

### Detailed technical data

#### Features

<b>Accessory group</b>	Magnetic tapes
<b>Description</b>	Magnetic tape ring inner diameter: 65 mm, magnetic tape ring outer diameter: 81 mm, magnetic tape ring width: 10 mm, weight: ≤ 0.58 kg, <sup>☞</sup> magnetic tape material: 17410 hard ferrite 9/28 P, material ring: Aluminum, period length: 2 mm, operating temperature range: -30 °C ... 100 °C, <sup>☞</sup> storage temperature range: -30 °C ... 100 °C, temperature coefficient: (11 ± 1) µm/K/m
<b>Material</b>	17410 Hard ferrite 9/28 P
<b>Temperature resistance min ... max:</b>	-30 °C +100 °C

#### Classifications

<b>ECLASS 5.0</b>	27279209
<b>ECLASS 5.1.4</b>	27279209
<b>ECLASS 6.0</b>	27279209
<b>ECLASS 6.2</b>	27279209
<b>ECLASS 7.0</b>	27279209
<b>ECLASS 8.0</b>	27279209
<b>ECLASS 8.1</b>	27279209
<b>ECLASS 9.0</b>	27272492
<b>ECLASS 10.0</b>	27272492
<b>ECLASS 11.0</b>	27272492
<b>ECLASS 12.0</b>	27274392
<b>ETIM 5.0</b>	EC002594
<b>ETIM 6.0</b>	EC002594
<b>ETIM 7.0</b>	EC002594
<b>ETIM 8.0</b>	EC002594
<b>UNSPSC 16.0901</b>	39122245

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

**For us, that is “Sensor Intelligence.”**

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)