



On-metal transponder (63 mm x 10 mm x 4 mm)

RFID transponders

RFID

SICK
Sensor Intelligence.



Ordering information

Type	Part no.
On-metal transponder (63 mm x 10 mm x 4 mm)	6053374

Other models and accessories → www.sick.com/RFID_transponders

Detailed technical data

Features

Frequency band	UHF (860 MHz ... 960 MHz)
Carrier frequency	902 MHz ... 928 MHz
RFID standard	EPCglobal UHF Class 1 Generation 2, ISO/IEC 18000-6 C
IC type	Alien Higgs 3
Memory capacity (UII / user memory)	96/512 Bit
IC write cycle	≤ 100,000
IC data retention time	< 10 years

Mechanics/electronics

Housing	Thermoplastic
Housing color	Black
Enclosure rating	IP68
Weight	2.1 g
Dimensions (L x W x H)	62.5 mm x 9.4 mm x 3.6 mm
Hole	5 mm

Ambient data

Ambient operating temperature	-40 °C ... +85 °C
Storage temperature	-40 °C ... +85 °C

Classifications

eCl@ss 5.0	27280402
eCl@ss 5.1.4	27280402
eCl@ss 6.0	27280402
eCl@ss 6.2	27280402
eCl@ss 7.0	27280402
eCl@ss 8.0	27280402
eCl@ss 8.1	27280402
eCl@ss 9.0	27280402
eCl@ss 10.0	27280402
eCl@ss 11.0	27280402
eCl@ss 12.0	27280402

ETIM 6.0	EC002998
ETIM 7.0	EC002998
ETIM 8.0	EC002998
UNSPSC 16.0901	52161523

Recommended services

Additional services → www.sick.com/RFID_transponders

	Type	Part no.
Maintenance		
<ul style="list-style-type: none"> Product area: RFID Range of services: Inspection, analysis and restoring of defined functions, Checking and adjustment of reading configuration, data processing, network, interfaces and inputs and outputs as well as operating data Duration: Additional work will be invoiced separately Travel expenses: The prices do not include travel costs such as hotel, flight, travel time and expenses. 	Maintenance RFU/RFH	1611424
Commissioning		
<ul style="list-style-type: none"> Product area: RFID Range of services: Inspection of connection, alignment, optimization of parameters of the RFU/RFH as well as tests, Setup of previously defined functions of reading configuration, data processing and network, interfaces and inputs and outputs Travel expenses: The prices do not include travel costs such as hotel, flight, travel time and expenses. Duration: Additional work will be invoiced separately 	Commissioning RFU/RFH	1610018

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com