

# RZT7-03ZVO-KWDS19

RZT7

**SENSORS FOR T-SLOT CYLINDERS** 



# Rico Rico Address

### Ordering information

Туре	Part no.
RZT7-03ZV0-KWDS19	1115151

Other models and accessories → www.sick.com/RZT7



#### Detailed technical data

#### **Features**

Cylinder type	T-slot
Cylinder types with adapter	Profile cylinder Tie rod cylinder Round body cylinder Dovetail groove cylinder SMC rail CDQ2 SMC rail ECDQ2
Housing length	32.5 mm
Switching output	Reed
Switching frequency	400 Hz
Output function	NC
Electrical wiring	AC/DC 2-wire
Enclosure rating	IP65 <sup>1)</sup> IP67

<sup>&</sup>lt;sup>1)</sup> According to EN 60529.

#### Mechanics/electronics

Supply voltage	5 V AC/DC 120 V AC/DC <sup>1)</sup>
Rated insulation voltage U <sub>i</sub>	230 V
Rated impulse with stand voltage $\mathbf{U}_{\mathrm{imp}}$	4 kV
Voltage drop	≤ 3.5 V
Continuous current I <sub>a</sub>	$\leq$ 100 mA $^{2)}$
Switching capacity	≤ 6 W
Protection class	II
Response sensitivity, typ.	3 mT
Overrun distance, typ.	10 mm

 $<sup>^{1)}</sup>$  Mains fuse F < 0.8 A IEC60127-2 sheet 1.

<sup>2)</sup> AC/DC.

 $<sup>^{\</sup>rm 3)}$  Supply voltage  $\rm U_B$  and constant ambient temperature Ta.

Reproducibility	$\leq 0.1  \text{mT}^{(3)}$
Status indicator LED	No
Ambient operating temperature	-30 °C +70 °C
Shock and vibration resistance	30 g, 11 ms / 10 55 Hz, 1 mm
EMC	According to EN 60947-5-2
Connection type	Cable, 2-wire, 10 m
Connection type Detail	
Conductor cross section	0.12 mm <sup>2</sup>
Cable diameter	Ø 2.9 mm
Bending radius	With fixed installation > $10 \times \text{cable diameter}$ For flexible use > $15 \times \text{cable diameter}$
Cable outlet	Axial
Material	
Housing	Plastic, Grilamid LVX-65H SST
Cable	PVC

 $<sup>^{1)}</sup>$  Mains fuse F < 0.8 A IEC60127-2 sheet 1.


#### Classifications

ECLASS 5.0	27270104
ECLASS 5.1.4	27270104
ECLASS 6.0	27270104
ECLASS 6.2	27270104
ECLASS 7.0	27270104
ECLASS 8.0	27270104
ECLASS 8.1	27270104
ECLASS 9.0	27270104
ECLASS 10.0	27270104
ECLASS 11.0	27270104
ECLASS 12.0	27274301
ETIM 5.0	EC002544
ETIM 6.0	EC002544
ETIM 7.0	EC002544
ETIM 8.0	EC002544
UNSPSC 16.0901	39122230

<sup>2)</sup> AC/DC

<sup>3)</sup> Supply voltage U<sub>B</sub> and constant ambient temperature Ta.


#### Installation note



Part number: 2077201

#### Dimensional drawing (Dimensions in mm (inch))

#### Cable



- ① Connection
- 2 Position sensor element
- ③ Fixing screw SW 2.5
- ④ Retaining ribs

		L	A	
1070866	RZT7-03ZVO-KW0	2 m	31.5	2
1115151	RZT7-03ZV0-KWDS19	10 m	31.5	2

#### Recommended accessories

Other models and accessories → www.sick.com/RZT7

	Brief description	Туре	Part no.	
Brackets for cylinder sensors				
	Mounting bracket for cylinder with dovetail slot, Aluminum, without mounting hardware	BEF-KHZ-ST1	2022703	
	Mounting bracket for integrated profile cylinder/tie-rod cylinder, zinc diecast, mounting hardware included	BEF-KHZ-PT1	2022702	
*	1 piece, Mounting bracket on round body cylinder with piston diameter of 12 mm, ambient temperature min 0 °C max 50 °C, plastic, Aluminum	BEF-KHZ-RT-12	2077681	
	1 piece, Mounting bracket on round body cylinder with piston diameter of 16 mm, ambient temperature min 0 °C max 50 °C, plastic, Aluminum	BEF-KHZ-RT-16	2077680	
	1 piece, Mounting bracket on round body cylinder with piston diameter of 20 mm, ambient temperature min 0 °C max 50 °C, plastic, Aluminum	BEF-KHZ-RT-20	2077679	
	1 piece, Mounting bracket on round body cylinder with piston diameter of 25 mm, ambient temperature min 0 °C max 50 °C, plastic, Aluminum	BEF-KHZ-RT-25	2077678	
	$1$ piece, Mounting bracket on round body cylinder with piston diameter of 32 mm, ambient temperature min 0 $^{\circ}$ C max 50 $^{\circ}$ C, plastic, Aluminum	BEF-KHZ-RT-32	2077677	
	$1$ piece, Mounting bracket on round body cylinder with piston diameter of 40 mm, ambient temperature min 0 $^{\circ}\text{C}$ max 50 $^{\circ}\text{C}$ , plastic, Aluminum	BEF-KHZ-RT-40	2077676	
	$1$ piece, Mounting bracket on round body cylinder with piston diameter of 50 mm, ambient temperature min 0 $^{\circ}$ C max 50 $^{\circ}$ C, plastic, Aluminum	BEF-KHZ-RT-50	2077675	
	$1$ piece, Mounting bracket on round body cylinder with piston diameter of 63 mm, ambient temperature min 0 $^{\circ}$ C max 50 $^{\circ}$ C, plastic, Aluminum	BEF-KHZ-RT-63	2077674	
	1 piece, Mounting bracket on round body cylinder with piston diameter of 8 mm 130 mm, ambient temperature min $-30~^\circ\text{C}$ max 80 $^\circ\text{C}$ , stainless steel, Zinc cast	BEF-KHZ-RT1-130	2077684	
R TEL	1 piece, Mounting bracket on round body cylinder with piston diameter of 8 mm 25 mm, ambient temperature min $-30$ °C max 80 °C, stainless steel, Zinc cast	BEF-KHZ-RT1-25	2077682	
	1 piece, Mounting bracket on round body cylinder with piston diameter of 8 mm 63 mm, ambient temperature min –30 °C max 80 °C, stainless steel, Zinc cast	BEF-KHZ-RT1-63	2077683	
	Mounting bracket for mounting on SMC rails CDQ2 (T-slot), Aluminum, without mounting hardware	BEF-KHZ-TT2	2046440	
0	Mounting bracket for mounting on SMC rails ECDQ2 (T-slot), Aluminum, without mounting hardware	BEF-KHZ-TT1	2046439	
Device protection (mechanical)				
	Protective adapter, die-cast zinc, mounting hardware included	BEF-SG-MRZT	2077201	

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

