

miniTwin



SICK
Sensor Intelligence.



Technical data overview

Safety level	PL c, SIL 1, Type 2 PL e, SIL 3, Type 4
Resolution	14 mm / 24 mm / 34 mm (depending on type)
Scanning range	8 m / 5 m (depending on type)
Protective field height	120 mm ... 1,200 mm (depending on type)
Enclosure rating	IP65
Ambient operating temperature	-20 °C ... +55 °C



Product description

For more than 10 years, SICK has been writing a success story with the miniTwin – the safety light curtain in miniature format – in hazardous point protection for finger and hand protection. Its two twin sticks, in which the sender and receiver are installed symmetrically in a compact housing for the first time, have received several awards. One of the Twin-Sticks is mounted opposite the other one and rotated by 180 degrees. This creates a safe protective field. The miniature design of the miniTwin, the option of cascading it and its different protective field heights save production space and enable small safety distances. At the same time, this mini device achieves great things: it functions perfectly, even when subjected to very strong shocks and vibrations and temperatures down to -20° Celsius.

At a glance

- Twin sticks: sender and receiver in a compact housing
- Different protective field heights, graduated to 60 mm each
- Diagnostics through protective field visualization
- Commissioning and alignment by means of color LEDs, configuration without software
- Cascading possible
- Application-specific brackets

Your benefits

- Benefit from optimum integration into your machine thanks to the miniature design
- Minimize your ordering, logistics, handling and maintenance work due to the small number of components, which are all standardized.
- Increase the productivity of your staff with optimal work ergonomics. With the miniTwin, work can be performed unhindered at machines, accelerating production processes.
- Take advantage of the benefits of quick diagnostics
- Save time and resources thanks to easy commissioning and configuration
- Eliminate blind zones
- Reduce mounting times

Fields of application

- Packaging industry
- Food and beverage industry
- Health care manufacturing
- Storage and conveyor
- Electronics industry
- Automotive and parts suppliers

Ordering information

Other models and accessories → www.sick.com/miniTwin

miniTwin2 as a standalone device

- **Mounting system type:** O-fix bracket
- **System connection:** male connector M12, 5-pin

Resolution	Length of cable	Protective field height	Type	Part no.
14 mm	160 mm	120 mm	C2MT-01214BBC03BB0	1207923
		180 mm	C2MT-01814BBC03BB0	1207924
	350 mm	240 mm	C2MT-02414BBC03DB0	1207925
		300 mm	C2MT-03014BBC03DB0	1207926
		360 mm	C2MT-03614BBC03DB0	1207927
		420 mm	C2MT-04214BBC03DB0	1207928
		480 mm	C2MT-04814BBC03DB0	1207929
		540 mm	C2MT-05414BBC03DB0	1207930
	700 mm	660 mm	C2MT-06614BBC03FB0	1207932
		720 mm	C2MT-07214BBC03FB0	1207933
		780 mm	C2MT-07814BBC03FB0	1207934
		840 mm	C2MT-08414BBC03FB0	1207935
		900 mm	C2MT-09014BBC03FB0	1207936
		960 mm	C2MT-09614BBC03FB0	1207937
		1,020 mm	C2MT-10214BBC03FB0	1207938
		1,080 mm	C2MT-10814BBC03FB0	1207939
	1,140 mm	C2MT-11414BBC03FB0	1207940	
	1,200 mm	C2MT-12014BBC03FB0	1207941	

Resolution	Length of cable	Protective field height	Type	Part no.
24 mm	160 mm	120 mm	C2MT-01224BBC03BB0	1207942
		180 mm	C2MT-01824BBC03BB0	1207943
	350 mm	240 mm	C2MT-02424BBC03DB0	1207944
		300 mm	C2MT-03024BBC03DB0	1207945
		360 mm	C2MT-03624BBC03DB0	1207946
		420 mm	C2MT-04224BBC03DB0	1207947
		480 mm	C2MT-04824BBC03DB0	1207948
		540 mm	C2MT-05424BBC03DB0	1207949
		600 mm	C2MT-06024BBC03FB0	1207950
	700 mm	660 mm	C2MT-06624BBC03FB0	1207951
		720 mm	C2MT-07224BBC03FB0	1207952
		780 mm	C2MT-07824BBC03FB0	1207953
		840 mm	C2MT-08424BBC03FB0	1207954
		900 mm	C2MT-09024BBC03FB0	1207955
		960 mm	C2MT-09624BBC03FB0	1207956
		1,020 mm	C2MT-10224BBC03FB0	1207957
		1,080 mm	C2MT-10824BBC03FB0	1207958
		1,140 mm	C2MT-11424BBC03FB0	1207959
		1,200 mm	C2MT-12024BBC03FB0	1207960
	34 mm	160 mm	120 mm	C2MT-01234BBC03BB0
180 mm			C2MT-01834BBC03BB0	1207962
350 mm		240 mm	C2MT-02434BBC03DB0	1207963
		300 mm	C2MT-03034BBC03DB0	1207964
		360 mm	C2MT-03634BBC03DB0	1207965
		420 mm	C2MT-04234BBC03DB0	1207966
		480 mm	C2MT-04834BBC03DB0	1207967
		540 mm	C2MT-05434BBC03DB0	1207968
		600 mm	C2MT-06034BBC03FB0	1207969
700 mm		660 mm	C2MT-06634BBC03FB0	1207970
		720 mm	C2MT-07234BBC03FB0	1207971
		780 mm	C2MT-07834BBC03FB0	1207972
		840 mm	C2MT-08434BBC03FB0	1207973
		900 mm	C2MT-09034BBC03FB0	1207974
		960 mm	C2MT-09634BBC03FB0	1207975
		1,020 mm	C2MT-10234BBC03FB0	1207976
		1,080 mm	C2MT-10834BBC03FB0	1207977
		1,140 mm	C2MT-11434BBC03FB0	1207978
		1,200 mm	C2MT-12034BBC03FB0	1207979

miniTwin2 as a standalone device, miniTwin2 as last guest for 2- or 3-device cascade

- **Mounting system type:** C-fix or L-fix bracket
- **System connection:** male connector M12, 5-pin

Resolution	Length of cable	Protective field height	Type	Part no.	
14 mm	160 mm	120 mm	C2MT-01214BBC03BE0	1207793	
		180 mm	C2MT-01814BBC03BE0	1207794	
	350 mm	240 mm	C2MT-02414BBC03DE0	1207795	
		300 mm	C2MT-03014BBC03DE0	1207796	
		360 mm	C2MT-03614BBC03DE0	1207797	
		420 mm	C2MT-04214BBC03DE0	1207798	
		480 mm	C2MT-04814BBC03DE0	1207799	
		540 mm	C2MT-05414BBC03DE0	1207800	
		600 mm	C2MT-06014BBC03FE0	1207801	
	700 mm	660 mm	C2MT-06614BBC03FE0	1207802	
		720 mm	C2MT-07214BBC03FE0	1207803	
		780 mm	C2MT-07814BBC03FE0	1207813	
		840 mm	C2MT-08414BBC03FE0	1207814	
		900 mm	C2MT-09014BBC03FE0	1207816	
		960 mm	C2MT-09614BBC03FE0	1207817	
		1,020 mm	C2MT-10214BBC03FE0	1207818	
		1,080 mm	C2MT-10814BBC03FE0	1207819	
	24 mm	160 mm	120 mm	C2MT-01224BBC03BE0	1207822
			180 mm	C2MT-01824BBC03BE0	1207823
350 mm		240 mm	C2MT-02424BBC03DE0	1207824	
		300 mm	C2MT-03024BBC03DE0	1207825	
		360 mm	C2MT-03624BBC03DE0	1207832	
		420 mm	C2MT-04224BBC03DE0	1207833	
		480 mm	C2MT-04824BBC03DE0	1207834	
		540 mm	C2MT-05424BBC03DE0	1207835	
		600 mm	C2MT-06024BBC03FE0	1207836	
700 mm		660 mm	C2MT-06624BBC03FE0	1207837	
		720 mm	C2MT-07224BBC03FE0	1207838	
		780 mm	C2MT-07824BBC03FE0	1207839	
		840 mm	C2MT-08424BBC03FE0	1207840	
		900 mm	C2MT-09024BBC03FE0	1207841	
		960 mm	C2MT-09624BBC03FE0	1207842	
		1,020 mm	C2MT-10224BBC03FE0	1207843	
		1,080 mm	C2MT-10824BBC03FE0	1207844	
		1,140 mm	C2MT-11424BBC03FE0	1207845	
		1,200 mm	C2MT-12024BBC03FE0	1207846	

Resolution	Length of cable	Protective field height	Type	Part no.
34 mm	160 mm	120 mm	C2MT-01234BBC03BE0	1207847
		180 mm	C2MT-01834BBC03BE0	1207848
	350 mm	240 mm	C2MT-02434BBC03DE0	1207849
		300 mm	C2MT-03034BBC03DE0	1207850
		360 mm	C2MT-03634BBC03DE0	1207851
		420 mm	C2MT-04234BBC03DE0	1207852
		480 mm	C2MT-04834BBC03DE0	1207853
		540 mm	C2MT-05434BBC03DE0	1207854
		600 mm	C2MT-06034BBC03FE0	1207855
	700 mm	660 mm	C2MT-06634BBC03FE0	1207856
		720 mm	C2MT-07234BBC03FE0	1207857
		780 mm	C2MT-07834BBC03FE0	1207858
		840 mm	C2MT-08434BBC03FE0	1207859
		900 mm	C2MT-09034BBC03FE0	1207860
		960 mm	C2MT-09634BBC03FE0	1207861
		1,020 mm	C2MT-10234BBC03FE0	1207862
		1,080 mm	C2MT-10834BBC03FE0	1207863
		1,140 mm	C2MT-11434BBC03FE0	1207864
		1,200 mm	C2MT-12034BBC03FE0	1207865

miniTwin2 as host for 2- or 3-device cascade, miniTwin2 as middle guest for 3-device cascade

- **Mounting system type:** C-fix or L-fix bracket
- **System connection:** male connector M12, 5-pin
- **Extension connection:** female connector M12, 5-pin

Resolution	Length of cable	Protective field height	Type	Part no.
14 mm	160 mm	120 mm	C2MT-01214BBC04BE0	1207866
		180 mm	C2MT-01814BBC04BE0	1207867
	350 mm	240 mm	C2MT-02414BBC04DE0	1207868
		300 mm	C2MT-03014BBC04DE0	1207869
		360 mm	C2MT-03614BBC04DE0	1207870
		420 mm	C2MT-04214BBC04DE0	1207871
		480 mm	C2MT-04814BBC04DE0	1207872
		540 mm	C2MT-05414BBC04DE0	1207873
		600 mm	C2MT-06014BBC04FE0	1207874
	700 mm	660 mm	C2MT-06614BBC04FE0	1207875
		720 mm	C2MT-07214BBC04FE0	1207876
		780 mm	C2MT-07814BBC04FE0	1207877
		840 mm	C2MT-08414BBC04FE0	1207878
		900 mm	C2MT-09014BBC04FE0	1207879
		960 mm	C2MT-09614BBC04FE0	1207880
		1,020 mm	C2MT-10214BBC04FE0	1207881
		1,080 mm	C2MT-10814BBC04FE0	1207882
	1,140 mm	C2MT-11414BBC04FE0	1207883	
	1,200 mm	C2MT-12014BBC04FE0	1207884	

Resolution	Length of cable	Protective field height	Type	Part no.
24 mm	160 mm	120 mm	C2MT-01224BBC04BE0	1207885
		180 mm	C2MT-01824BBC04BE0	1207886
	350 mm	240 mm	C2MT-02424BBC04DE0	1207887
		300 mm	C2MT-03024BBC04DE0	1207888
		360 mm	C2MT-03624BBC04DE0	1207889
		420 mm	C2MT-04224BBC04DE0	1207890
		480 mm	C2MT-04824BBC04DE0	1207891
		540 mm	C2MT-05424BBC04DE0	1207892
		600 mm	C2MT-06024BBC04FE0	1207893
	700 mm	660 mm	C2MT-06624BBC04FE0	1207894
		720 mm	C2MT-07224BBC04FE0	1207895
		780 mm	C2MT-07824BBC04FE0	1207896
		840 mm	C2MT-08424BBC04FE0	1207897
		900 mm	C2MT-09024BBC04FE0	1207898
		960 mm	C2MT-09624BBC04FE0	1207899
		1,020 mm	C2MT-10224BBC04FE0	1207900
		1,080 mm	C2MT-10824BBC04FE0	1207901
		1,140 mm	C2MT-11424BBC04FE0	1207902
		1,200 mm	C2MT-12024BBC04FE0	1207903
		34 mm	160 mm	120 mm
180 mm	C2MT-01834BBC04BE0			1207905
350 mm	240 mm		C2MT-02434BBC04DE0	1207906
	300 mm		C2MT-03034BBC04DE0	1207907
	360 mm		C2MT-03634BBC04DE0	1207908
	420 mm		C2MT-04234BBC04DE0	1207909
	480 mm		C2MT-04834BBC04DE0	1207910
	540 mm		C2MT-05434BBC04DE0	1207911
	600 mm		C2MT-06034BBC04FE0	1207912
700 mm	660 mm		C2MT-06634BBC04FE0	1207913
	720 mm		C2MT-07234BBC04FE0	1207914
	780 mm		C2MT-07834BBC04FE0	1207915
	840 mm		C2MT-08434BBC04FE0	1207916
	900 mm		C2MT-09034BBC04FE0	1207917
	960 mm		C2MT-09634BBC04FE0	1207918
	1,020 mm		C2MT-10234BBC04FE0	1207919
	1,080 mm		C2MT-10834BBC04FE0	1207920
	1,140 mm		C2MT-11434BBC04FE0	1207921
	1,200 mm		C2MT-12034BBC04FE0	1207922

miniTwin4 as a standalone device

- **Mounting system type:** O-fix bracket
- **System connection:** male connector M12, 5-pin

Resolution	Length of cable	Protective field height	Type	Part no.
14 mm	160 mm	120 mm	C4MT-01214ABB03BB0	1206951
		180 mm	C4MT-01814ABB03BB0	1206945
	350 mm	240 mm	C4MT-02414ABB03DB0	1206954
		300 mm	C4MT-03014ABB03DB0	1206953
		360 mm	C4MT-03614ABB03DB0	1206955
		420 mm	C4MT-04214ABB03DB0	1206956
		480 mm	C4MT-04814ABB03DB0	1206957
		540 mm	C4MT-05414ABB03DB0	1206958
		700 mm	C4MT-06014ABB03FB0	1206959
	700 mm	660 mm	C4MT-06614ABB03FB0	1206960
		720 mm	C4MT-07214ABB03FB0	1206961
		780 mm	C4MT-07814ABB03FB0	1206962
		840 mm	C4MT-08414ABB03FB0	1206963
		900 mm	C4MT-09014ABB03FB0	1206964
		960 mm	C4MT-09614ABB03FB0	1206965
		1,020 mm	C4MT-10214ABB03FB0	1206966
		1,080 mm	C4MT-10814ABB03FB0	1206967
		1,140 mm	C4MT-11414ABB03FB0	1206968
		1,200 mm	C4MT-12014ABB03FB0	1206969
24 mm	160 mm	120 mm	C4MT-01224ABB03BB0	1207318
		180 mm	C4MT-01824ABB03BB0	1207177
	350 mm	240 mm	C4MT-02424ABB03DB0	1207319
		300 mm	C4MT-03024ABB03DB0	1207320
		360 mm	C4MT-03624ABB03DB0	1207321
		420 mm	C4MT-04224ABB03DB0	1207322
		480 mm	C4MT-04824ABB03DB0	1207178
		540 mm	C4MT-05424ABB03DB0	1207323
		700 mm	C4MT-06024ABB03FB0	1207324
	700 mm	660 mm	C4MT-06624ABB03FB0	1207325
		720 mm	C4MT-07224ABB03FB0	1207326
		780 mm	C4MT-07824ABB03FB0	1207327
		840 mm	C4MT-08424ABB03FB0	1207328
		900 mm	C4MT-09024ABB03FB0	1207329
		960 mm	C4MT-09624ABB03FB0	1207330
		1,020 mm	C4MT-10224ABB03FB0	1207331
		1,080 mm	C4MT-10824ABB03FB0	1207332
		1,140 mm	C4MT-11424ABB03FB0	1207180
		1,200 mm	C4MT-12024ABB03FB0	1207333

Resolution	Length of cable	Protective field height	Type	Part no.
34 mm	160 mm	120 mm	C4MT-01234ABB03BB0	1207334
		180 mm	C4MT-01834ABB03BB0	1207335
	350 mm	240 mm	C4MT-02434ABB03DB0	1207336
		300 mm	C4MT-03034ABB03DB0	1207337
		360 mm	C4MT-03634ABB03DB0	1207338
		420 mm	C4MT-04234ABB03DB0	1207339
		480 mm	C4MT-04834ABB03DB0	1207340
		540 mm	C4MT-05434ABB03DB0	1207341
		600 mm	C4MT-06034ABB03FB0	1207342
	700 mm	660 mm	C4MT-06634ABB03FB0	1207343
		720 mm	C4MT-07234ABB03FB0	1207344
		780 mm	C4MT-07834ABB03FB0	1207345
		840 mm	C4MT-08434ABB03FB0	1207346
		900 mm	C4MT-09034ABB03FB0	1207347
		960 mm	C4MT-09634ABB03FB0	1207348
		1,020 mm	C4MT-10234ABB03FB0	1207349
		1,080 mm	C4MT-10834ABB03FB0	1207350
		1,140 mm	C4MT-11434ABB03FB0	1207351
		1,200 mm	C4MT-12034ABB03FB0	1207169

miniTwin4 as a standalone device, miniTwin4 as last guest for 2- or 3-device cascade

- **Mounting system type:** C-fix or L-fix bracket
- **System connection:** male connector M12, 5-pin

Resolution	Length of cable	Protective field height	Type	Part no.
14 mm	160 mm	120 mm	C4MT-01214ABB03BE0	1207094
		180 mm	C4MT-01814ABB03BE0	1207097
	350 mm	240 mm	C4MT-02414ABB03DE0	1207098
		300 mm	C4MT-03014ABB03DE0	1207099
		360 mm	C4MT-03614ABB03DE0	1207100
		420 mm	C4MT-04214ABB03DE0	1207101
		480 mm	C4MT-04814ABB03DE0	1207102
		540 mm	C4MT-05414ABB03DE0	1207103
	700 mm	600 mm	C4MT-06014ABB03FE0	1207104
		660 mm	C4MT-06614ABB03FE0	1207105
		720 mm	C4MT-07214ABB03FE0	1207106
		780 mm	C4MT-07814ABB03FE0	1207107
		840 mm	C4MT-08414ABB03FE0	1207108
		900 mm	C4MT-09014ABB03FE0	1207109
		960 mm	C4MT-09614ABB03FE0	1207110
		1,020 mm	C4MT-10214ABB03FE0	1207111
		1,080 mm	C4MT-10814ABB03FE0	1207112
		1,140 mm	C4MT-11414ABB03FE0	1207113
1,200 mm	C4MT-12014ABB03FE0	1207114		
24 mm	160 mm	120 mm	C4MT-01224ABB03BE0	1207222
		180 mm	C4MT-01824ABB03BE0	1207223
	350 mm	240 mm	C4MT-02424ABB03DE0	1207224
		300 mm	C4MT-03024ABB03DE0	1207225
		360 mm	C4MT-03624ABB03DE0	1207227
		420 mm	C4MT-04224ABB03DE0	1207228
		480 mm	C4MT-04824ABB03DE0	1207229
		540 mm	C4MT-05424ABB03DE0	1207230
	700 mm	600 mm	C4MT-06024ABB03FE0	1207231
		660 mm	C4MT-06624ABB03FE0	1207232
		720 mm	C4MT-07224ABB03FE0	1207233
		780 mm	C4MT-07824ABB03FE0	1207234
		840 mm	C4MT-08424ABB03FE0	1207235
		900 mm	C4MT-09024ABB03FE0	1207236
		960 mm	C4MT-09624ABB03FE0	1207237
		1,020 mm	C4MT-10224ABB03FE0	1207238
		1,080 mm	C4MT-10824ABB03FE0	1207239
		1,140 mm	C4MT-11424ABB03FE0	1207240
1,200 mm	C4MT-12024ABB03FE0	1207241		

Resolution	Length of cable	Protective field height	Type	Part no.
34 mm	160 mm	120 mm	C4MT-01234ABB03BE0	1207242
		180 mm	C4MT-01834ABB03BE0	1207243
	350 mm	240 mm	C4MT-02434ABB03DE0	1207244
		300 mm	C4MT-03034ABB03DE0	1207245
		360 mm	C4MT-03634ABB03DE0	1207246
		420 mm	C4MT-04234ABB03DE0	1207247
		480 mm	C4MT-04834ABB03DE0	1207248
		540 mm	C4MT-05434ABB03DE0	1207249
		600 mm	C4MT-06034ABB03FE0	1207250
	700 mm	660 mm	C4MT-06634ABB03FE0	1207251
		720 mm	C4MT-07234ABB03FE0	1207252
		780 mm	C4MT-07834ABB03FE0	1207253
		840 mm	C4MT-08434ABB03FE0	1207254
		900 mm	C4MT-09034ABB03FE0	1207255
		960 mm	C4MT-09634ABB03FE0	1207256
		1,020 mm	C4MT-10234ABB03FE0	1207257
		1,080 mm	C4MT-10834ABB03FE0	1207258
		1,140 mm	C4MT-11434ABB03FE0	1207259
		1,200 mm	C4MT-12034ABB03FE0	1207260

miniTwin4 as host for 2- or 3-device cascade, miniTwin4 as middle guest for 3-device cascade

- **Mounting system type:** C-fix or L-fix bracket
- **System connection:** male connector M12, 5-pin
- **Extension connection:** female connector M12, 5-pin

Resolution	Length of cable	Protective field height	Type	Part no.
14 mm	160 mm	120 mm	C4MT-01214ABB04BE0	1207115
		180 mm	C4MT-01814ABB04BE0	1207116
	350 mm	240 mm	C4MT-02414ABB04DE0	1207117
		300 mm	C4MT-03014ABB04DE0	1207118
		360 mm	C4MT-03614ABB04DE0	1207119
		420 mm	C4MT-04214ABB04DE0	1207120
		480 mm	C4MT-04814ABB04DE0	1207121
		540 mm	C4MT-05414ABB04DE0	1207122
		700 mm	600 mm	C4MT-06014ABB04FE0
	660 mm		C4MT-06614ABB04FE0	1207124
	720 mm		C4MT-07214ABB04FE0	1207125
	780 mm		C4MT-07814ABB04FE0	1207126
	840 mm		C4MT-08414ABB04FE0	1207127
	900 mm		C4MT-09014ABB04FE0	1207128
	960 mm		C4MT-09614ABB04FE0	1207129
	1,020 mm		C4MT-10214ABB04FE0	1207130
	1,080 mm		C4MT-10814ABB04FE0	1207131
	1,140 mm		C4MT-11414ABB04FE0	1207132
	1,200 mm	C4MT-12014ABB04FE0	1207133	

Resolution	Length of cable	Protective field height	Type	Part no.
24 mm	160 mm	120 mm	C4MT-01224ABB04BE0	1207168
		180 mm	C4MT-01824ABB04BE0	1207283
	350 mm	240 mm	C4MT-02424ABB04DE0	1207284
		300 mm	C4MT-03024ABB04DE0	1207285
		360 mm	C4MT-03624ABB04DE0	1207286
		420 mm	C4MT-04224ABB04DE0	1207287
		480 mm	C4MT-04824ABB04DE0	1207181
		540 mm	C4MT-05424ABB04DE0	1207288
		600 mm	C4MT-06024ABB04FE0	1207289
	700 mm	660 mm	C4MT-06624ABB04FE0	1207290
		720 mm	C4MT-07224ABB04FE0	1207291
		780 mm	C4MT-07824ABB04FE0	1207292
		840 mm	C4MT-08424ABB04FE0	1207293
		900 mm	C4MT-09024ABB04FE0	1207294
		960 mm	C4MT-09624ABB04FE0	1207295
		1,020 mm	C4MT-10224ABB04FE0	1207296
		1,080 mm	C4MT-10824ABB04FE0	1207297
		1,140 mm	C4MT-11424ABB04FE0	1207298
		1,200 mm	C4MT-12024ABB04FE0	1207299
34 mm	160 mm	120 mm	C4MT-01234ABB04BE0	1207300
		180 mm	C4MT-01834ABB04BE0	1207301
	350 mm	240 mm	C4MT-02434ABB04DE0	1207302
		300 mm	C4MT-03034ABB04DE0	1207303
		360 mm	C4MT-03634ABB04DE0	1207304
		420 mm	C4MT-04234ABB04DE0	1207305
		480 mm	C4MT-04834ABB04DE0	1207306
		540 mm	C4MT-05434ABB04DE0	1207307
	700 mm	600 mm	C4MT-06034ABB04FE0	1207308
		660 mm	C4MT-06634ABB04FE0	1207309
		720 mm	C4MT-07234ABB04FE0	1207310
		780 mm	C4MT-07834ABB04FE0	1207311
		840 mm	C4MT-08434ABB04FE0	1207312
		900 mm	C4MT-09034ABB04FE0	1207313
		960 mm	C4MT-09634ABB04FE0	1207314
		1,020 mm	C4MT-10234ABB04FE0	1207315
		1,080 mm	C4MT-10834ABB04FE0	1207316
		1,140 mm	C4MT-11434ABB04FE0	1207317
		1,200 mm	C4MT-12034ABB04FE0	1206993

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com