



# SICK

8024416

## Betriebsanleitung, Ergänzung DEUTSCH

Bitte lesen Sie die beiliegende Betriebsanleitung und diese Betriebsanleitungsergänzung sorgfältig durch.

### Ergänzung/Abweichung der technischen Daten zur Betriebsanleitung WL4SL(G)-3 (#8015555):

Typ: **WL4SLG-3N1162P01 / WL4SLG-3N1162S03**

Artikelnr.: **1101033**

- Lieferung inkl. Feintrippl-Reflektor P250F, 5308843
- Laserstrahl-Geometrie wie folgt:
  - o Laserstrahl ist in ca. 300 mm fokussiert
  - o Ø 20 mm in 4 m
- Maximale Reichweite 4 m
- Wir empfehlen, den Reflektor nicht im Fokusbereich von ca. 250 mm bis ca. 350 mm einzusetzen.

Irrtümer und Änderungen vorbehalten

SICK AG, D-79183 Waldkirch, Erwin-Sick-Str. 1, [www.sick.com](http://www.sick.com)

## Operating Instruction, Supplement ENGLISH

Please read the enclosed operating instruction and this operating instruction supplement carefully.

### Supplement/deviation of technical data of the operating instructions WL4SL(G)-3 (#8015555):

Model Name: **WL4SLG-3N1162P01 / WL4SLG-3N1162S03**

Part No.: **1101033**

- Scope of delivery incl. fine triple reflector P250F
- Light beam properties as follows:
  - o Laser beam is focused in approx. 300 mm
  - o Spot size Ø 20 mm in 4 m
- Maximum range on reflector 4 m
- We recommend not to install the reflector in the focus range of approx. 250 mm to 350 mm

Subject to change without notice.

SICK AG, D-79183 Waldkirch, Erwin-Sick-Str. 1, [www.sick.com](http://www.sick.com)