

SICK

8024685 1020
9310222 190D
WTB4F_DID8389197
8389197
3694269430
9310208 190D (1.1.0)

Australia Phone +61 3 9457 0800	Osterreich Phone +43 (0)22 36 62 28 8-0
Belgium/Luxembourg Phone +32 (0)2 468 55 66	Norge Phone +47 67 61 50 00
Brasil Phone +55 11 5215-4900	Polka Phone +49 22 837 40 50
Canada Phone +1 905 771 14 44	România Phone +40 356 171 120
China Phone +86 4000 121 000 +8622553 6300	Russia Phone +7 495 775 09 30
Danmark Phone +45 45 42 64 00	Schweden Phone +46 11 419 29 39
Deutschland Phone +49 211 5361 301	Sveits Phone +41 41 619 29 39
España Phone +34 93 480 31 00	South Korea Phone +82 2 786 6321/4
France Phone +33 1 64 42 39 00	Suomi Phone +358 9 25 15 800
Great Britain Phone +44 (0)1727 831521	Sverige Phone +46 10 110 10 00
India Phone +91-22-4033 8333	Taiwan Phone +886 2 2375 4288
Italy Phone +39 2 4681000	Türkiye Phone +90 (216) 528 50 00
Japan Phone +81 (03) 5309 2112	United Arab Emirates Phone +971 (0) 4 5855 878
Magnesium Phone +36 1 371 2680	USA/Mexico Phone +1 (952) 941 6780
Niederland Phone +31 (0)30 229 25 44	

SICK AG, Erwin-Sick-Strasse 1, D 79183 Waldkirch

Please find detailed addresses and additional representatives and agencies in all major industrial nations at www.sick.com

More representatives and agencies at www.sick.com - Subject to change without notice - The specified product features and technical data do not represent any guarantee.

Weitere Niederlassungen finden Sie unter www.sick.com - Irrtümer und Änderungen vorbehalten - Angegebene Produkteigenschaften und technische Daten stellen keine Garantieerklärung dar.

Plus de représentations et d'agences à l'adresse www.sick.com - Sujet à modification sans préavis - Les caractéristiques de produit et techniques indiquées ne constituent pas de déclaration de garantie.

Para mais representantes e agências, consulte www.sick.com - Alterações poderão ser feitas sem prévio aviso - As características do produto e os dados técnicos apresentados não constituem declaração de garantia.

Flere representanter og agenturer på www.sick.com - Med forbehold for ændringer og fejl - De angivne produktetskræb og tekniske data udgør ikke nogen garantiæklæring.

Altri rappresentanti ed agenzie si trovano su www.sick.com - Contenuti soggetti a modifiche senza preavviso - Le caratteristiche del prodotto e i dati tecnici non rappresentano una dichiarazione di garanzia.

Meer vestigingen en correcties voorbehouden - Aangegeven producteigenschaften en technische gegevens vormen geen garantieverklaring.

Más representantes y agencias en www.sick.com - Sujeto a cambio sin preaviso - Las características y los datos técnicos especificados no constituyen ninguna declaración de garantía.

欲了解更多代表机构和代理商信息, 请登录 www.sick.com - 如有更改, 不另行通知 - 对所给出的产品特性和技术参数 的正确性不予保证.



Please note the validity of the additional operating instructions for automation functions

1. Physical layer

Note: The IO-Link Device's max. current consumption (inclusive load current) shall not exceed the master port's max. output power current.

SIO Modus	yes
Min Cycle Time	2.3 ms
Baudrate ²	COM2
Process Data Length (IN)	2 Byte
IODD version	V1.26119
Valid for IO-Link version	1.1.0

2. Process data

Record³: 2 Byte

Bitoffset																
Byte 0	Current receive level (live)															
Type/Subindex	Unsigned Integer 14															
Bitoffset																
Byte 1	Current receive level (live)															
Type/Subindex	Unsigned Integer 14															

3. Service data

The following ISDUs will not be saved via Data-Storage: Profile characteristic, Teach-in channel, Teach-in state, Device specific tag, Sender configuration, Quality of teach, Temperature zone, Current receiver level (live), Find me and SLTI Version

Index dec (hex)	Name	Format (Offset)	Length	Access ¹	Default Value	Value / Range	Remark [Unit]
12 (0x0C)	Device Access Locks	Record ³	2 Byte	rw			
2 (0x02)	Data Storage Lock	Bit (1)	1 Bit	rw			
4 (0x04)	Local User Interface Lock	Bit (3)	1 Bit	rw			
16 (0x10)	Vendor Name	String	7 Byte	ro	SICK AG		
17 (0x11)	Vendor Text	String	64 Byte	ro			
18 (0x12)	Product Name	String	18 Byte	ro			
19 (0x13)	Product ID	String	7 Byte	ro			
20 (0x14)	Product Text	String	45 Byte	ro			
21 (0x15)	Serial Number	String	8 Byte	ro			
22 (0x16)	Hardware Version	String	4 Byte	ro			
23 (0x17)	Firmware Version	String	19 Byte	ro			
24 (0x18)	Application Specific Tag	String	32 Byte	rw	*****		
36 (0x24)	Device Status	UInt	8 Bit	ro		0 = Device is OK 1 = Maintenance required 2 = Out of specification 3 = Functional check 4 = Failure 5...255 = Reserved	
37 (0x25)	Detailed Device Status	Array ³	6 Byte	ro		Octet String [2]	
40 (0x28)	Process Data Input	PD In	2 Byte	ro			

Index dec (hex)	Name	Format (Offset)	Length	Access ¹	Default Value	Value / Range	Remark [Unit]
13 (0x0D)	Profile characteristic	Array ³	12 Byte	ro		Unsigned Integer16 [6]	
14 (0x0E)	PDInput descriptor	Array ³	6 Byte	ro		Octet String [2]	
15 (0x0F)	PDOOutput descriptor	Array ³	3 Byte	ro		Octet String [1]	
58 (0x3A)	Teach-in channel	UInt	8 Bit	rw	0	0 = default Qint. = Qint.1 1 = Qint.1 2 = Qint.2	
59 (0x3B)	Teach-in state	Record ³	1 Byte	ro			
1 (0x01)	Teach flags	Bit (4)	1 Bit	ro		false = Teachpoint 1 not taught true = Teachpoint 1 successfully taught	
2 (0x02)	Teach state	Bit (0)	4 Bit	ro		0 = IDLE 1 = SP1 SUCCESS 5 = BUSY 7 = ERROR	
60 (0x3C)	Qint.1 SP1 / SP2	Record	3 Byte	rw			

¹ ro = read only, wo = write only, rw = read/write

² COM values specify the bitrate (see IO-Link specification): COM1 (4,8 kbit/s), COM2 (38,4 kbit/s), COM3 (230,4 kbit/s)

³Subindex access not supported

SICK

8024685 1020
9310222 190D
WTB4F_DID8389197
8389197
3694269430
9310208 190D (1.1.0)

Australia Phone +61 3 9457 0800	Osterreich Phone +43 (0)22 36 62 28 8-0
Belgium/Luxembourg Phone +32 (0)2 468 55 66	Norge Phone +47 67 61 51 00
Brazil Phone +55 11 5215-4900	Polka Phone +48 22 837 40 50
Canada Phone +1 905 771 14 44	România Phone +40 356 171 120
China Phone +86 4000 121 000 +8623533 6300	Russia Phone +7 495 775 09 30
Denmark Phone +45 45 82 64 00	Schweiz Phone +41 41 619 29 39
Deutschland Phone +49 211 5301 301	Slovenija Phone +386 (0)147 69 990
España Phone +34 93 480 31 00	South Korea Phone +82 2 786 6321/4
France Phone +33 1 64 62 39 00	Suomi Phone +358 9 25 15 800
Great Britain Phone +44 (0)1727 831121	Sverige Phone +46 10 110 10 00
India Phone +91-22-4033 8333	Taiwan Phone +886 2 2375 6288
Italy Phone +39 02 27 43 41	Türkiye Phone +90 (216) 538 50 00
Japan Phone +81 (03) 5309 2112	United Arab Emirates Phone +971 (0)4 5665 878
Magyarország Phone +36 1 271 2680	USA/Mexico Phone +1 952 941 6780
Niederland Phone +31 (0)30 229 25 44	

SICK AG, Erwin-Sick-Strasse 1, D 79183 Waldkirch

Please find detailed addresses and additional representatives and agencies in all major industrial nations at www.sick.com

More representatives and agencies at www.sick.com - Subject to change without notice - The specified product features and technical data do not represent any guarantee.

Weitere Niederlassungen finden Sie unter www.sick.com - Irrtümer und Änderungen vorbehalten - Angegebene Produkteigenschaften und technische Daten stellen keine Garantieerklärung dar.

Plus de représentations et d'agences à l'adresse www.sick.com - Sujet à modification sans préavis - Les caractéristiques de produit et techniques indiquées ne constituent pas de déclaration de garantie.

Para mais representantes e agências, consulte www.sick.com - Alterações poderão ser feitas sem prévio aviso - As características do produto e os dados técnicos apresentados não constituem declaração de garantia.


Fiere representanter og agenturer på www.sick.com - Med forbehold for ændringer og fejl - De anførte produkttegnelser og tekniske data udgør ikke nogen garanti erklæring.

Altri rappresentanti ed agenzie si trovano su www.sick.com - Contenuti soggetti a modifiche senza preavviso - Le caratteristiche del prodotto e i dati tecnici non rappresentano una dichiarazione di garanzia.

Meer vestigingen en vertegenwoordigingen vindt u op www.sick.com - Wijzigingen en correcties voorbehouden - Aangegeven producteigenschappen en technische gegevens vormen geen garantieverklaring.

Más representantes y agencias en www.sick.com - Sujeto a cambio sin previo aviso - Las características y los datos técnicos especificados no constituyen ninguna declaración de garantía.

欲了解更多代表机构和代理商信息，请登录 www.sick.com - 如有更改，不另行通知 - 对所给出的产品特性和技术参数 的正确性不予保证。



Please note the validity of the additional operating instructions for automation functions

ENGLISH

SICK device specific							
Index dec (hex)	Name	Format (Offset)	Length	Access ¹	Default Value	Value / Range	Remark [Unit]
1 (0x01)	SP1 sensing range	Bit (8)	16 Bit	rw	14	0...65535	Device's effective value range: See device data sheet 'Sensing range max.' [mm]
2 (0x02)	SP2 sensing range	Bit (0)	8 Bit	rw	0	0 = SP2 not used	
61 (0x3D)	Qint.1 configuration	Record	4 Byte	rw			
1 (0x01)	Switchpoint logic	Bit (24)	8 Bit	rw	128	128 = Vendor specific	
2 (0x02)	Switchpoint mode	Bit (16)	8 Bit	rw	128	128 = Vendor specific	
3 (0x03)	Switchpoint hysteresis	Bit (0)	16 Bit	rw	0	0 = Autodefined hysteresis	
62 (0x3E)	Qint.2 SP1 / SP2	Record	3 Byte	rw			
1 (0x01)	SP1 sensing range	Bit (8)	16 Bit	rw	14	0...65535	Device's effective value range: See device data sheet 'Sensing range max.'
2 (0x02)	SP2 sensing range	Bit (0)	8 Bit	rw	0	0 = SP2 not used	
63 (0x3F)	Qint.2 configuration	Record	4 Byte	rw			
1 (0x01)	Switchpoint logic	Bit (24)	8 Bit	rw	128	128 = Vendor specific	
2 (0x02)	Switchpoint mode	Bit (16)	8 Bit	rw	128	128 = Vendor specific	
3 (0x03)	Switchpoint hysteresis	Bit (0)	16 Bit	rw	0	0 = Autodefined hysteresis	
64 (0x40)	Device specific tag	String	32 Byte	rw	*****		
90 (0x5A)	Teach-in offset	Int	8 Bit	rw	0	-50...50	[mm]
92 (0x5C)	Physical input / output type configuration pin2	UInt	8 Bit	rw	3	1 = PNP 2 = NPN 3 = Push/Pull	
97 (0x61)	Sender configuration	UInt	8 Bit	rw	0	0 = Sender active 1 = Sender not active	
114 (0x72)	Quality of teach	UInt	8 Bit	ro		0...100	[%]
121 (0x79)	Pin 2 configuration	UInt	8 Bit	rw	40	0 = Deactivated / no function 1 = External input (Smart Task) 16 = Sender off 17 = Teach-in 34 = Switching signal QL2 35 = Detection output Qint.1 39 = Switching signal QL1 40 = Switching signal QL1/	
154 (0x9A)	Temperature zone	UInt	8 Bit	ro		0 = Very cold 1 = Cold 2 = Moderate 3 = Warm 4 = Hot	Sensor-internal temperature
179 (0xB3)	Alarm thresholds for diagnostic parameters	Record	4 Byte	rw			
1 (0x01)	Operating hours threshold	Bit (0)	32 Bit	rw	40000	0...1000000	[h]
180 (0xB4)	Current receiver level (live)	UInt	16 Bit	ro		0...16383	
190 (0xBE)	Operating hours	Record	8 Byte	ro			
1 (0x01)	Total operating hours	Bit (32)	32 Bit	ro		0...1000000	[h]
2 (0x02)	Operating hours since last reset	Bit (0)	32 Bit	ro		0...1000000	[h]
204 (0xCC)	Find me	UInt	8 Bit	rw	0	0 = Find me deactivated 1 = Find me activated	
226 (0xE2)	System state	Record ³	2 Byte	ro			
1 (0x01)	Detection output Qint.1	Bit (0)	1 Bit	ro		false = No object detected true = Object detected	
6 (0x06)	Input signal state Pin 2	Bit (7)	1 Bit	ro		false = External input LOW true = External input HIGH	
227 (0xE3)	Notification handling	UInt	8 Bit	rw	0	0 = All enabled 1 = All disabled 2 = Events enabled, PD invalid flag disabled 3 = Events disabled, PD invalid flag enabled	
1080 (0x438)	SLTI Version	String	8 Byte	ro			
1083 (0x43B)	Logic 1	UInt	8 Bit	rw	0	0 = DIRECT 1 = AND 2 = OR	
1084 (0x43C)	Logic 2	UInt	8 Bit	rw	0	0 = DIRECT 1 = AND 2 = OR	

¹ro = read only, wo = write only, rw = read/write

²COM values specify the bitrate (see IO-Link specification): COM1 (4,8 kbit/s), COM2 (38,4 kbit/s), COM3 (230,4 kbit/s)

³Subindex access not supported

SICK

8024685 1020
9310222 190D
WTB4F_DID8389197
8389197
3694269430
9310208 190D (1.1.0)

Australia Phone +61 3 9457 0800	Osterreich Phone +43 (0)22 36 62 28 8-0
Belgium/Luxembourg Phone +32 (0)2 468 55 66	Norge Phone +47 67 61 50 00
Brasil Phone +55 11 5215-4900	Polka Phone +48 22 837 40 50
Canada Phone +1 905 771 14 44	România Phone +40 356 171 120
China Phone +86 400 121 000 +86 2163 6300	Russia Phone +7 495 775 09 30
Danmark Phone +45 45 82 64 00	Schweden Phone +46 18 41 619 29 39
Deutschland Phone +49 211 5361 301	Singapore Phone +65 6744 3732
España Phone +34 93 480 31 00	South Africa Phone +27 11 472 3733
France Phone +33 1 64 62 39 00	South Korea Phone +82 2 786 6321/4
Great Britain Phone +44 (0)1727 831121	Suomi Phone +358 9 25 15 800
India Phone +91 22 4033 8333	Sverige Phone +46 10 110 10 00
Israel Phone +972 4 6801000	Taiwan Phone +886 2 2375 6288
Italia Phone +39 02 27 43 41	Türkiye Phone +90 (216) 528 50 00
Japan Phone +81 (03) 5309 2112	United Arab Emirates Phone +971 (0) 4 5565 878
Magnetsverige Phone +36 1 371 2680	USA/Mexico Phone +1 950 941 6780
Nedertland Phone +31 (0)30 229 25 44	

SICK AG, Erwin-Sick-Strasse 1, D 79183 Waldkirch

Please find detailed addresses and additional representatives and agencies in all major industrial nations at www.sick.com

More representatives and agencies at www.sick.com - Subject to change without notice - The specified product features and technical data do not represent any guarantee.

Weitere Niederlassungen finden Sie unter www.sick.com - Irrtümer und Änderungen vorbehalten - Angegebene Produkteigenschaften und technische Daten stellen keine Garantieerklärung dar.

Plus de représentations et d'agences à l'adresse www.sick.com - Sujet à modification sans préavis - Les caractéristiques de produit et techniques indiquées ne constituent pas de déclaration de garantie.

Para mais representantes e agências, consulte www.sick.com - Alterações poderão ser feitas sem prévio aviso - As características do produto e os dados técnicos apresentados não constituem declaração de garantia.


Flere representanter og agenturer på www.sick.com - Med forbehold for ændringer og fejl - De anførte produktetskræber og tekniske data udgør ikke nogen garanti erklæring.

Altri rappresentanti ed agenzie si trovano su www.sick.com - Contenuti soggetti a modifiche senza preavviso - Le caratteristiche del prodotto e i dati tecnici non rappresentano una dichiarazione di garanzia.

Meer vestigingen en vertegenwoordigingen vindt u op www.sick.com - Wijzigingen en correcties voorbehouden - Aangegeven producteigenschappen en technische gegevens vormen geen garantieverklaring.

Más representantes y agencias en www.sick.com - Sujeto a cambio sin previo aviso - Las características y los datos técnicos especificados no constituyen ninguna declaración de garantía.

欲了解更多代表机构和代理商信息，请登录 www.sick.com - 如有更改，不另行通知 - 对所给出的产品特性和技术参数的正确性不予保证。



Please note the validity of the additional operating instructions for automation functions

ENGLISH

SICK device specific							
Index dec (hex)	Name	Format (Offset)	Length	Access ¹	Default Value	Value / Range	Remark [Unit]
1085 (0x43D)	Timer 1 Mode	UInt	8 Bit	rw	0	0 = deactivated 1 = T-on delay 2 = T-off delay 3 = T-on/T-off delay 4 = Impulse (one shot)	
1086 (0x43E)	Timer 2 Mode	UInt	8 Bit	rw	0	0 = deactivated 1 = T-on delay 2 = T-off delay 3 = T-on/T-off delay 4 = Impulse (one shot)	
1087 (0x43F)	Time 1 Setup	UInt	16 Bit	rw	1	1...30000	[ms]
1088 (0x440)	Time 2 Setup	UInt	16 Bit	rw	1	1...30000	[ms]
1089 (0x441)	Inverter 1	UInt	8 Bit	rw	0	0 = not inverted 1 = inverted	
1090 (0x442)	Inverter 2	UInt	8 Bit	rw	0	0 = not inverted 1 = inverted	
1093 (0x445)	Inverter Ext. Input	UInt	8 Bit	rw	0	0 = not inverted 1 = inverted	

Standard command							
Index dec (hex)		Access ¹		Value	Name		Remark [Unit]
2 (0x02)	Standard Command	wo		65	Single value teach		
				130	Restore Factory Settings		
				228	Reset diagnostics parameter		

Events			
Code dec (hex)	Name	Type	Remark [Unit]
36000 (0x8CA0)	Short Circuit on Qx	Warning	Short circuit on outputs
36001 (0x8CA1)	New parameters	Notification	Parameters have been changed
36005 (0x8CA5)	Teach / value out of specified range	Notification	Teach / distance value out of specified range
36011 (0x8CAB)	Alarm operating hours	Warning	Threshold for operating hours violated

Error			
Code dec (hex)	Additional Code	Name	Remark [Unit]
128 (0x80)	17 (0x11)	Index not available	Access occurs to a not existing index
128 (0x80)	18 (0x12)	Subindex not available	Access occurs to a not existing subindex
128 (0x80)	32 (0x20)	Service temporarily not available	Parameter is not accessible due to the current state of the device application
128 (0x80)	35 (0x23)	Access denied	Write access on a read-only parameter
128 (0x80)	48 (0x30)	Parameter value out of range	Written parameter value is outside its permitted value range
128 (0x80)	51 (0x33)	Parameter length overrun	Written parameter length is above its predefined length
128 (0x80)	52 (0x34)	Parameter length underrun	Written parameter length is below its predefined length
128 (0x80)	64 (0x40)	Invalid parameter set	Written single parameter collides with other actual parameter settings
128 (0x80)	65 (0x41)	Inconsistent parameter set	Parameter inconsistencies were found at the end of block parameter transfer, device plausibility check failed

¹ro = read only, wo = write only, rw = read/write
²COM values specify the bitrate (see IO-Link specification): COM1 (4,8 kbit/s), COM2 (38,4 kbit/s), COM3 (230,4 kbit/s)
³Subindex access not supported