

# SICK

8026766 0721  
9342719 1C8F  
**WTV4F\_DID8389299**  
8389299  
2177740402  
9342698 1C8F (1.1.0)

<b>Australia</b> Phone +61 3 9457 0800	<b>Osterreich</b> Phone +43 (0)22 36 62 28 8-0
<b>Belgium/Luxembourg</b> Phone +32 (0)2 468 55 66	<b>Norge</b> Phone +47 67 61 50 00
<b>Brasil</b> Phone +55 11 5215-4900	<b>Polka</b> Phone +48 22 837 40 50
<b>Canada</b> Phone +1 905 771 14 44	<b>România</b> Phone +40 356 171 120
<b>China</b> Phone +86 4000 121 000 +862025530300	<b>Russia</b> Phone +7 495 775 09 30
<b>Danmark</b> Phone +45 45 42 64 00	<b>Schweden</b> Phone +46 10 110 10 00
<b>Deutschland</b> Phone +49 211 5301 301	<b>Slovenija</b> Phone +386 (0)147 69 990
<b>España</b> Phone +34 93 480 31 00	<b>South Korea</b> Phone +82 2 786 6321/4
<b>France</b> Phone +33 1 64 62 39 00	<b>Suomi</b> Phone +358 9 25 15 800
<b>Great Britain</b> Phone +44 (0)1727 83121	<b>Sverige</b> Phone +46 10 110 10 00
<b>India</b> Phone +91-22-4033 8333	<b>Taiwan</b> Phone +886 2 2375 4288
<b>Israel</b> Phone +972 4 6801000	<b>Türkiye</b> Phone +90 (216) 528 50 00
<b>Italia</b> Phone +39 02 27 43 41	<b>United Arab Emirates</b> Phone +971 (0) 4 5855 878
<b>Japan</b> Phone +81 (03) 5309 2112	<b>USA/Mexico</b> Phone +1 (952) 941 6780
<b>Magnesium</b> Phone +36 1 371 2680	
<b>Niederland</b> Phone +31 (0)30 229 25 44	

SICK AG, Erwin-Sick-Strasse 1, D 79183 Waldkirch

Please find detailed addresses and additional representatives and agencies in all major industrial nations at [www.sick.com](http://www.sick.com)

More representatives and agencies at [www.sick.com](http://www.sick.com) - Subject to change without notice - The specified product features and technical data do not represent any guarantee.

Weitere Niederlassungen finden Sie unter [www.sick.com](http://www.sick.com) - Irrtümer und Änderungen vorbehalten - Angegebene Produkteigenschaften und technische Daten stellen keine Garantieerklärung dar.

Plus de représentations et d'agences à l'adresse [www.sick.com](http://www.sick.com) - Sujet à modification sans préavis - Les caractéristiques de produit et techniques indiquées ne constituent pas de déclaration de garantie.

Para mais representantes e agências, consulte [www.sick.com](http://www.sick.com) - Alterações poderão ser feitas sem prévio aviso - As características do produto e os dados técnicos apresentados não constituem declaração de garantia.

Flere representanter og agenturer på [www.sick.com](http://www.sick.com) - Med forbehold for ændringer og fejl - De angivne produktetskræber og tekniske data udgør ikke nogen garanti erklæring.

Altri rappresentanti ed agenzie si trovano su [www.sick.com](http://www.sick.com) - Contenuti soggetti a modifiche senza preavviso - Le caratteristiche del prodotto e i dati tecnici non rappresentano una dichiarazione di garanzia.

Meer vestigingen en correcties voorbehouden - Aangegeven producteigenschaften en technische gegevens vormen geen garantieverklaring.

Más representantes y agencias en [www.sick.com](http://www.sick.com) - Sujeto a cambio sin previo aviso - Las características y los datos técnicos especificados no constituyen ninguna declaración de garantía.

欲了解更多代表机构和代理商信息, 请登录 [www.sick.com](http://www.sick.com) - 如有更改, 不另行通知 - 对所给出的产品特性和技术参数 的正确性不予保证.



Please note the validity of the additional operating instructions for automation functions

## 1. Physical layer

Note: The IO-Link Device's max. current consumption (inclusive load current) shall not exceed the master port's max. output power current.

SIO Modus	yes
Min Cycle Time	2.3 ms
Baudrate <sup>2</sup>	COM2
Process Data Length (IN)	2 Byte
IODD version	V1.29083
Valid for IO-Link version	1.1.0

## 2. Process data

Record<sup>3</sup>: 2 Byte

Bitoffset																						
Byte 0	Current receive level (live)																					
Type/Subindex	Unsigned Integer 14																					
Bitoffset																						
Byte 1	Current receive level (live)												CL2				CL1					
Type/Subindex	Unsigned Integer 14												3		Boolean		2		Boolean		1	

## 3. Service data

The following ISDUs will not be saved via Data-Storage: Profile characteristic, Teach-in channel, Teach-in state, Device specific tag, Sender configuration, Quality of teach, Temperature zone, Current receiver level (live), Find me and SLTI Version

Index dec (hex)	Name	Format (Offset)	Length	Access <sup>1</sup>	Default Value	Value / Range	Remark [Unit]
12 (0x0C)	Device Access Locks	Record <sup>3</sup>	2 Byte	rw			
2 (0x02)	Data Storage Lock	Bit (1)	1 Bit	rw			
4 (0x04)	Local User Interface Lock	Bit (3)	1 Bit	rw			
16 (0x10)	Vendor Name	String	7 Byte	ro	SICK AG		
17 (0x11)	Vendor Text	String	64 Byte	ro			
18 (0x12)	Product Name	String	18 Byte	ro			
19 (0x13)	Product ID	String	7 Byte	ro			
20 (0x14)	Product Text	String	45 Byte	ro			
21 (0x15)	Serial Number	String	8 Byte	ro			
22 (0x16)	Hardware Version	String	4 Byte	ro			
23 (0x17)	Firmware Version	String	19 Byte	ro			
24 (0x18)	Application Specific Tag	String	32 Byte	rw	*****		
36 (0x24)	Device Status	UInt	8 Bit	ro		0 = Device is OK 1 = Maintenance required 2 = Out of specification 3 = Functional check 4 = Failure 5...255 = Reserved	
37 (0x25)	Detailed Device Status	Array <sup>3</sup>	6 Byte	ro		Octet String [2]	
40 (0x28)	Process Data Input	PD In	2 Byte	ro			

Index dec (hex)	Name	Format (Offset)	Length	Access <sup>1</sup>	Default Value	Value / Range	Remark [Unit]
13 (0x0D)	Profile characteristic	Array <sup>3</sup>	12 Byte	ro		Unsigned Integer16 [6]	
14 (0x0E)	PDInput descriptor	Array <sup>3</sup>	6 Byte	ro		Octet String [2]	
15 (0x0F)	PDOOutput descriptor	Array <sup>3</sup>	3 Byte	ro		Octet String [1]	
58 (0x3A)	Teach-in channel	UInt	8 Bit	rw	0	0 = default Qint. = Qint.1 1 = Qint.1 2 = Qint.2	
59 (0x3B)	Teach-in state	Record <sup>3</sup>	1 Byte	ro			
1 (0x01)	Teach flags	Bit (4)	1 Bit	ro		false = Teachpoint 1 not taught true = Teachpoint 1 successfully taught	
2 (0x02)	Teach state	Bit (0)	4 Bit	ro		0 = IDLE 1 = SP1 SUCCESS 5 = BUSY 7 = ERROR	
60 (0x3C)	Qint.1 SP1 / SP2	Record	3 Byte	rw			

<sup>1</sup> ro = read only, wo = write only, rw = read/write

<sup>2</sup> COM values specify the bitrate (see IO-Link specification): COM1 (4,8 kbit/s), COM2 (38,4 kbit/s), COM3 (230,4 kbit/s)

<sup>3</sup>Subindex access not supported

# SICK

8026766 0721  
9342719 1C8F  
**WTV4F\_DID8389299**  
8389299  
2177740402  
9342698 1C8F (1.1.0)

<b>Australia</b> Phone +61 3 9467 0800	<b>Osterreich</b> Phone +43 (0)22 36 62 28 8-0
<b>Belgium/Luxembourg</b> Phone +32 (0)2 468 55 66	<b>Norge</b> Phone +47 67 61 51 00
<b>Brazil</b> Phone +55 11 5215-4900	<b>Polka</b> Phone +48 22 837 40 50
<b>Canada</b> Phone +1 905 771 14 44	<b>România</b> Phone +40 356 171 120
<b>China</b> Phone +86 4000 121 000 +8623533 6300	<b>Russia</b> Phone +7 495 775 09 30 +7 495 6744 3732
<b>Denmark</b> Phone +45 45 82 64 00	<b>Schweden</b> Phone +386 (0)147 69 990
<b>Deutschland</b> Phone +49 211 5301 301	<b>Slovenija</b> Phone +386 (0)147 69 990
<b>España</b> Phone +34 93 480 31 00	<b>South Korea</b> Phone +82 2 786 6321/4
<b>France</b> Phone +33 1 64 62 39 00	<b>Suomi</b> Phone +358 9 25 15 800
<b>Great Britain</b> Phone +44 (0)1727 831121	<b>Sverige</b> Phone +46 10 110 10 00
<b>India</b> Phone +91 22 4033 8333	<b>Taiwan</b> Phone +886 2 2375 4288
<b>Italy</b> Phone +39 02 27 43 41	<b>Türkiye</b> Phone +90 (216) 538 50 00
<b>Japan</b> Phone +81 (03) 5309 2112	<b>United Arab Emirates</b> Phone +971 (0)4 5665 878
<b>Magyarország</b> Phone +36 1 271 2680	<b>USA/Mexico</b> Phone +1 952 941 6780
<b>Niederland</b> Phone +31 (0)30 229 25 44	

SICK AG, Erwin-Sick-Strasse 1, D 79183 Waldkirch

Please find detailed addresses and additional representatives and agencies in all major industrial nations at [www.sick.com](http://www.sick.com)

More representatives and agencies at [www.sick.com](http://www.sick.com) - Subject to change without notice - The specified product features and technical data do not represent any guarantee.

Weitere Niederlassungen finden Sie unter [www.sick.com](http://www.sick.com) - Irrtümer und Änderungen vorbehalten - Angegebene Produkteigenschaften und technische Daten stellen keine Garantieerklärung dar.

Plus de représentations et d'agences à l'adresse [www.sick.com](http://www.sick.com) - Sujet à modification sans préavis - Les caractéristiques de produit et techniques indiquées ne constituent pas de déclaration de garantie.

Para mais representantes e agências, consulte [www.sick.com](http://www.sick.com) - Alterações poderão ser feitas sem prévio aviso - As características do produto e os dados técnicos apresentados não constituem declaração de garantia.


Fiere representanter og agenturer på [www.sick.com](http://www.sick.com) - Med forbehold for ændringer og fejl - De anførte produkttegnelser og tekniske data udgør ikke nogen garanti erklæring.

Altri rappresentanti ed agenzie si trovano su [www.sick.com](http://www.sick.com) - Contenuti soggetti a modifiche senza preavviso - Le caratteristiche del prodotto e i dati tecnici non rappresentano una dichiarazione di garanzia.

Meer vestigingen en vertegenwoordigingen vindt u op [www.sick.com](http://www.sick.com) - Wijzigingen en correcties voorbehouden - Aangegeven producteigenschappen en technische gegevens vormen geen garantieverklaring.

Más representantes y agencias en [www.sick.com](http://www.sick.com) - Sujeto a cambio sin previo aviso - Las características y los datos técnicos especificados no constituyen ninguna declaración de garantía.

欲了解更多代表机构和代理商信息，请登录 [www.sick.com](http://www.sick.com) - 如有更改，不另行通知 - 对所给出的产品特性和技术参数 的正确性不予保证。



Please note the validity of the additional operating instructions for automation functions

## ENGLISH

SICK device specific							
Index dec (hex)	Name	Format (Offset)	Length	Access <sup>1</sup>	Default Value	Value / Range	Remark [Unit]
1 (0x01)	SP1 sensing range	Bit (8)	16 Bit	rw	14	0...65535	Device's effective value range: See device data sheet 'Sensing range max.' [mm]
2 (0x02)	SP2 sensing range	Bit (0)	8 Bit	rw	0	0 = SP2 not used	
61 (0x3D)	Qint.1 configuration	Record	4 Byte	rw			
1 (0x01)	Switchpoint logic	Bit (24)	8 Bit	rw	128	128 = Vendor specific	
2 (0x02)	Switchpoint mode	Bit (16)	8 Bit	rw	128	128 = Vendor specific	
3 (0x03)	Switchpoint hysteresis	Bit (0)	16 Bit	rw	0	0 = Autodefined hysteresis	
62 (0x3E)	Qint.2 SP1 / SP2	Record	3 Byte	rw			
1 (0x01)	SP1 sensing range	Bit (8)	16 Bit	rw	14	0...65535	Device's effective value range: See device data sheet 'Sensing range max.'
2 (0x02)	SP2 sensing range	Bit (0)	8 Bit	rw	0	0 = SP2 not used	
63 (0x3F)	Qint.2 configuration	Record	4 Byte	rw			
1 (0x01)	Switchpoint logic	Bit (24)	8 Bit	rw	128	128 = Vendor specific	
2 (0x02)	Switchpoint mode	Bit (16)	8 Bit	rw	128	128 = Vendor specific	
3 (0x03)	Switchpoint hysteresis	Bit (0)	16 Bit	rw	0	0 = Autodefined hysteresis	
64 (0x40)	Device specific tag	String	32 Byte	rw	*****		
90 (0x5A)	Teach-in offset	Int	8 Bit	rw	0	-50...50	[mm]
92 (0x5C)	Physical input / output type configuration pin2	UInt	8 Bit	rw	3	1 = PNP 2 = NPN 3 = Push/Pull	
97 (0x61)	Sender configuration	UInt	8 Bit	rw	0	0 = Sender active 1 = Sender not active	
114 (0x72)	Quality of teach	UInt	8 Bit	ro		0...100	[%]
121 (0x79)	Pin 2 configuration	UInt	8 Bit	rw	40	0 = Deactivated / no function 1 = External input (Smart Task) 16 = Sender off 17 = Teach-in 34 = Switching signal QL2 35 = Detection output Qint.1 39 = Switching signal QL1 40 = Switching signal QL1/	
154 (0x9A)	Temperature zone	UInt	8 Bit	ro		0 = Very cold 1 = Cold 2 = Moderate 3 = Warm 4 = Hot	Sensor-internal temperature
179 (0xB3)	Alarm thresholds for diagnostic parameters	Record	4 Byte	rw			
1 (0x01)	Operating hours threshold	Bit (0)	32 Bit	rw	40000	0...1000000	[h]
180 (0xB4)	Current receiver level (live)	UInt	16 Bit	ro		0...16383	
190 (0xBE)	Operating hours	Record	8 Byte	ro			
1 (0x01)	Total operating hours	Bit (32)	32 Bit	ro		0...1000000	[h]
2 (0x02)	Operating hours since last reset	Bit (0)	32 Bit	ro		0...1000000	[h]
204 (0xCC)	Find me	UInt	8 Bit	rw	0	0 = Find me deactivated 1 = Find me activated	
226 (0xE2)	System state	Record <sup>3</sup>	2 Byte	ro			
1 (0x01)	Detection output Qint.1	Bit (0)	1 Bit	ro		false = No object detected true = Object detected	
6 (0x06)	Input signal state Pin 2	Bit (7)	1 Bit	ro		false = External input LOW true = External input HIGH	
227 (0xE3)	Notification handling	UInt	8 Bit	rw	0	0 = All enabled 1 = All disabled 2 = Events enabled, PD invalid flag disabled 3 = Events disabled, PD invalid flag enabled	
1080 (0x438)	SLTI Version	String	8 Byte	ro			
1083 (0x43B)	Logic 1	UInt	8 Bit	rw	0	0 = DIRECT 1 = AND 2 = OR	
1084 (0x43C)	Logic 2	UInt	8 Bit	rw	0	0 = DIRECT 1 = AND 2 = OR	

<sup>1</sup>ro = read only, wo = write only, rw = read/write

<sup>2</sup>COM values specify the bitrate (see IO-Link specification): COM1 (4,8 kbit/s), COM2 (38,4 kbit/s), COM3 (230,4 kbit/s)

<sup>3</sup>Subindex access not supported

# SICK

8026766 0721  
9342719 1C8F  
**WTV4F\_DID8389299**  
8389299  
2177740402  
9342698 1C8F (1.1.0)

<b>Australia</b> Phone +61 3 9457 0800	<b>Osterreich</b> Phone +43 (0)22 36 62 28 8-0
<b>Belgium/Luxembourg</b> Phone +32 (0)2 468 55 66	<b>Norge</b> Phone +47 67 61 50 00
<b>Brasil</b> Phone +55 11 5215-4900	<b>Polka</b> Phone +48 22 837 40 50
<b>Canada</b> Phone +1 905 771 14 44	<b>România</b> Phone +40 356 171 120
<b>China</b> Phone +86 400 121 000 +86 2163 6300	<b>Russia</b> Phone +7 495 775 09 30
<b>Denmark</b> Phone +45 45 82 64 00	<b>Schweden</b> Phone +46 8 744 3732
<b>Deutschland</b> Phone +49 211 5361 301	<b>Sveits</b> Phone +386 (0)147 69 990
<b>España</b> Phone +34 93 480 31 00	<b>South Africa</b> Phone +27 11 472 3733
<b>France</b> Phone +33 1 64 62 39 00	<b>South Korea</b> Phone +82 2 786 6321/4
<b>Great Britain</b> Phone +44 (0)1727 831121	<b>Suomi</b> Phone +358 9 25 15 800
<b>India</b> Phone +91 22 4033 8333	<b>Sverige</b> Phone +46 10 110 10 00
<b>Israel</b> Phone +972 4 6801000	<b>Taiwan</b> Phone +886 2 2375 6288
<b>Italia</b> Phone +39 02 27 43 41	<b>Türkiye</b> Phone +90 (216) 528 50 00
<b>Japan</b> Phone +81 (03) 5309 2112	<b>United Arab Emirates</b> Phone +971 (0)4 5855 878
<b>Magnetsverige</b> Phone +36 1 371 2680	<b>USA/Mexico</b> Phone +1 950 941 6780
<b>Nedertland</b> Phone +31 (0)30 229 25 44	

SICK AG, Erwin-Sick-Strasse 1, D-79183 Waldkirch

Please find detailed addresses and additional representatives and agencies in all major industrial nations at [www.sick.com](http://www.sick.com)

More representatives and agencies at [www.sick.com](http://www.sick.com) - Subject to change without notice - The specified product features and technical data do not represent any guarantee.

Weitere Niederlassungen finden Sie unter [www.sick.com](http://www.sick.com) - Irrtümer und Änderungen vorbehalten - Angegebene Produkteigenschaften und technische Daten stellen keine Garantieerklärung dar.

Plus de représentations et d'agences à l'adresse [www.sick.com](http://www.sick.com) - Sujet à modification sans préavis - Les caractéristiques de produit et techniques indiquées ne constituent pas de déclaration de garantie.

Para mais representantes e agências, consulte [www.sick.com](http://www.sick.com) - Alterações poderão ser feitas sem prévio aviso - As características do produto e os dados técnicos apresentados não constituem declaração de garantia.

Flere representanter og agenturer på [www.sick.com](http://www.sick.com) - Med forbehold for ændringer og fejl - De arfbrte produktgenskaber og tekniske data udgår ikke nogen garantiærklæring.

Altri rappresentanti ed agenzie si trovano su [www.sick.com](http://www.sick.com) - Contenuti soggetti a modifiche senza preavviso - Le caratteristiche del prodotto e i dati tecnici non rappresentano una dichiarazione di garanzia.

Meer vestigingen en vertegenwoordigingen vindt u op [www.sick.com](http://www.sick.com) - Wijzigingen en correcties voorbehouden - Aangegeven producteigenschappen en technische gegevens vormen geen garantieverklaring.

Más representantes y agencias en [www.sick.com](http://www.sick.com) - Sujeto a cambio sin previo aviso - Las características y los datos técnicos especificados no constituyen ninguna declaración de garantía.

欲了解更多代表机构和代理商信息，请登录 [www.sick.com](http://www.sick.com) - 如有更改，不另行通知 - 对所给出的产品特性和技术参数的正确性不予保证。



Please note the validity of the additional operating instructions for automation functions

## ENGLISH

SICK device specific							
Index dec (hex)	Name	Format (Offset)	Length	Access <sup>1</sup>	Default Value	Value / Range	Remark [Unit]
1085 (0x43D)	Timer 1 Mode	UInt	8 Bit	rw	0	0 = deactivated 1 = T-on delay 2 = T-off delay 3 = T-on/T-off delay 4 = Impulse (one shot)	
1086 (0x43E)	Timer 2 Mode	UInt	8 Bit	rw	0	0 = deactivated 1 = T-on delay 2 = T-off delay 3 = T-on/T-off delay 4 = Impulse (one shot)	
1087 (0x43F)	Time 1 Setup	UInt	16 Bit	rw	1	1...30000	[ms]
1088 (0x440)	Time 2 Setup	UInt	16 Bit	rw	1	1...30000	[ms]
1089 (0x441)	Inverter 1	UInt	8 Bit	rw	1	0 = not inverted 1 = inverted	
1090 (0x442)	Inverter 2	UInt	8 Bit	rw	1	0 = not inverted 1 = inverted	
1093 (0x445)	Inverter Ext. Input	UInt	8 Bit	rw	0	0 = not inverted 1 = inverted	

Standard command							
Index dec (hex)		Access <sup>1</sup>		Value	Name		Remark [Unit]
2 (0x02)	Standard Command	wo		65	Single value teach		
				130	Restore Factory Settings		
				228	Reset diagnostics parameter		

Events			
Code dec (hex)	Name	Type	Remark [Unit]
36000 (0x8CA0)	Short Circuit on Qx	Warning	Short circuit on outputs
36001 (0x8CA1)	New parameters	Notification	Parameters have been changed
36005 (0x8CA5)	Teach / value out of specified range	Notification	Teach / distance value out of specified range
36011 (0x8CAB)	Alarm operating hours	Warning	Threshold for operating hours violated

Error			
Code dec (hex)	Additional Code	Name	Remark [Unit]
128 (0x80)	17 (0x11)	Index not available	Access occurs to a not existing index
128 (0x80)	18 (0x12)	Subindex not available	Access occurs to a not existing subindex
128 (0x80)	32 (0x20)	Service temporarily not available	Parameter is not accessible due to the current state of the device application
128 (0x80)	35 (0x23)	Access denied	Write access on a read-only parameter
128 (0x80)	48 (0x30)	Parameter value out of range	Written parameter value is outside its permitted value range
128 (0x80)	51 (0x33)	Parameter length overrun	Written parameter length is above its predefined length
128 (0x80)	52 (0x34)	Parameter length underrun	Written parameter length is below its predefined length
128 (0x80)	64 (0x40)	Invalid parameter set	Written single parameter collides with other actual parameter settings
128 (0x80)	65 (0x41)	Inconsistent parameter set	Parameter inconsistencies were found at the end of block parameter transfer, device plausibility check failed

<sup>1</sup>ro = read only, wo = write only, rw = read/write  
<sup>2</sup>COM values specify the bitrate (see IO-Link specification): COM1 (4,8 kbit/s), COM2 (38,4 kbit/s), COM3 (230,4 kbit/s)  
<sup>3</sup>Subindex access not supported