

Dx100 LEADING IN VERSATILITY AND FLEXIBILITY



Long Range Distance Sensors

Accurate distance sensors for precise positioning tasks – DL100 Pro



Laser-based distance sensors have their origins in the ingenuity of SICK engineers. Continuous development in response to customer requirements combined with the latest technology opens the door to new and increasingly innovative products.

But how can highly sophisticated distance sensors be improved even further? SICK set itself this challenge once again, and came up with the product family Dx100 – smaller, faster, more flexible and cost-effective to operate.





When positioning cranes and in automated storage and retrieval systems, accuracy, speed and minimal downtimes are the key to success. The product family Dx100 has been adapted to increasing drive speeds and now analyzes the signals in the control circuit even faster than before. The sensors feature preventive maintenance functions and send information to the control station if, for example, maintenance is required because of a contaminated working environment. Additional interfaces, bus capability and an innovative mounting concept improve the top performance of this product family even further.

Significantly smaller than comparable distance sensors

The housing dimensions of the Dx100 product family are 119.9 mm x 82.5 mm x 69.4 mm making them the smallest sensors in their performance class.


- New application possibilities.
- Low weight.
- Easy to mount.



Innovative mounting system

Because the housing of all Dx100 versions is identical, the mechanical interfaces and accessories are the same for all versions.

- Reduced logistic and storage costs.
- Fast mounting and simple replacement of equipment.
 Easy mounting:
 - 1 Mount the device in the precisely fitting plate.
 - 2 Tighten it using the black adjustment screw.
 - 3 Perform fine adjustment using 3 spring-loaded screws.



One housing, flexible content

The modular concept of the Dx100 platform means: one housing version with flexible content for different fields of application.


Because of this, performance can be tailored to, and selected on the basis of the application in question.

- Only the required interfaces.
- Only the required resolution.
- Only the required accuracy.
- → That means: only the costs for the required performance.



Increased performance and lower operating costs make the sensors of the Dx100 product family the optimal choice for your application.

Thermo Protection Cooling Case (TPCC) – keeps the sensor cool and inside the temperature operating range



The Thermo Protection Cooling Case (TPCC) from SICK cools and protects laser-based sensors. By extending the sensor service life, it also contributes to protecting your investment.

With a maintenance-free Peltier cooler (24 V/15 A), the TPCC offers efficient protection at ambient temperatures from -20 °C to +75 °C. The internal temperature is thermostat-controlled. If the temperature becomes too high, the TPCC shuts itself down automatically.

High temperature ranges, harsh environmental conditions

The use of the TPCC is particularly appropriate in locations with high ambient temperatures due to the process environment.

The TPCC is perfect for use:

- in the steel industry
- · in the paper industry
- in glass manufacturing
- on overhead cranes under the ceiling of industrial buildings
- in countries and locations where high ambient temperatures can be expected

The rugged fibre glass housing with protective front screen offers additional protection against mechanical damage and remains dimensionally stable up to +140 °C. This temperature is beyond the maximum value specified for the TPCC.

Increased sensor availability, extended service life

Due to physics of laser diodes , the service life of the laser halves for each 10 °C increase in temperature. By using the TPCC, the sensor is actively cooled by means of the Peltier effect. This extends the service life of the laser – and thus of your sensor: at 25 °C it will already be extended by 15 %, at 45 °C by 400 %.

In addition:

The low internal temperature of the TPCC also offers economic advantages. The constant conditions within the TPCC ensure that the measured values are more accurate. Sensor availability increases, and unexpected failures and system downtime can be avoided.

Benefit: replacement costs are reduced and productivity increases.

DME to Dx100 upgrade kit: Straightforward sensor replacement to ensure the availability of your system



Upgrade kits from SICK often provide a cost-effective alternative to purchasing a brand new drive and control system. These solutions enable quick and easy integration of the latest technology, in order to increase the productivity of existing systems.

In the event of upcoming modernization of systems, preventative replacement of DME distance sensors after years of use: SICK DME-Dx100 upgrade kits are designed for carrying out the conversion of the tried and tested DME distance sensors to the current Dx100 with the least possible cost and effort.

We will also be happy to assist you with conversion at your site. Contact us!

Tailor-made, easy to use

The DME-Dx100 upgrade kit is characterized by a range of special features:

- Upgrade kit specifically tailored to the application
- All accessories required at the site are included ¹)
- The enclosed upgrade instructions describe the detailed steps involved
- The Dx100 is mechanically mounted on DME hole pattern using an adapter plate
- Electrical connections are established with preassembled adapter cables

Early conversion, clear advantages

Decide to upgrade soon using the tailor-made DME-Dx100 upgrade kit – and you will enjoy all the economic benefits:

- Boost the productivity of your system by using the latest technology
- Maximum system availability combined with minimum downtime during conversion
- Avoid costly and unscheduled outage times by taking the precautionary step of converting your system to Dx100
- Convert your existing system cost-effectively in just a few steps




DME to Dx100 upgrade kit ordering information

Previously available in the system	Data interface	Model name Dx100	Upgrade kit model name	Upgrade kit part no.	
	SSI	Dx100-xxxxxx01	DME3-Dx100 SSI/RS-422	2065223	
DME3000	PROFIBUS	Dx100-xxxxxx02	DME3-Dx100 PROFIBUS	2065222	
	RS-422	Dx100-xxxxxx03	D-xxxxx03 DME3-Dx100 SSI/RS-422		
DME 4000 /	SSI	Dx100-xxxxx01	DME4/5-Dx100 SSI/RS-422	2065221	
DME4000/ DME5000	PROFIBUS	Dx100-xxxxxx02	DME4/5-Dx100 PROFIBUS	2065220	
DIVIESOOO	RS-422	Dx100-xxxxxx03	DME4/5-Dx100 SSI/RS-422	2065221	

5

 $^{^{\}rm 1)}$ The Dx100 distance sensor is not included in the upgrade kit and must be selected and ordered separately.

Reliable, fast, precise positioning





Additional information

Detailed technical data7
Ordering information8
Dimensional drawing9
Adjustments 10
Connection type and diagram 10
Recommended accessories 11

6



Product description

The DL100 Pro family combines leading edge technology with innovative design. The product's phase-shift measurement technology ensures the highest performance, which, in co-operation with drives manufacturers, has been optimized for perfect integration into closed control loops. Our innovative 3-axis bracket, the smallest housing in its sensor class, as well as the intelligent quick lock system with fast connectors, offers optimized handling and reduced costs of ownership.

At a glance

- Measuring range up to 300 m
- Numerous fieldbus interfaces
- Pre-failure notification and diagnostic data available
- Display with intuitive menu and easy to see status LEDs
- Small and rugged metal housing

3-axis alignment bracket with quick lock system

- Elongated holes for precise adjustment of sensor offset
- SPEEDCON™ and standard M12 electrical connections

Your benefits

- Enhanced closed-loop behavior offers highest performance and productivity
- Operating temperature down to -40
 °C ensures the highest reliability in cold storage warehouses and freezers
- Numerous fieldbus and Ethernetbased interfaces offer the highest flexibility and fast communication for maximum efficiency
- Pre-failure and extensive diagnostic data allow for preventive maintenance, ensuring the highest machine uptime
- Small, rugged metal housing and SpeedCon[™] compatible connectors ensure hassle-free installation – even in confined spaces
- 3-axis alignment bracket ensures fast alignment and easy exchange, reducing maintenance and setup costs
- Numerous accessories allow flexible use and guarantee high operation functionality

www.mysick.com/en/DL100_Pro

For more information, just enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples and much more.



Detailed technical data

Performance

Resolution	0.1 mm, 0.125 mm, 1 mm, 10 mm, 100 mm
Dead time	2 ms
Output rate	Synchronous to PLC request
Light source ¹⁾	Laser, red
Laser protection class	2 (EN 60825-1 / CDRH)
Typ. light spot size (distance)	5 mm (+ 2 mm x distance in m)
Max. movement speed	30 m/s
Acceleration (max.)	≤ 15 m/s²
Internal measurement cycle	1 ms

 $^{\scriptscriptstyle 1)}$ Average service life of 100,000 h at $T_{_A}$ = +25 °C .

Interfaces

Switching output ¹⁾	B (push/pull), MF1, MF2
Multifunctional input ²⁾	1 x MF1
¹⁾ HIGH > $V_s - 3 V / LOW < 2 V.$	

²⁾ HIGH > 12 V / LOW < 3 V.

Mechanics/electronics

Supply voltage V_s	DC 18 V 30 V, limit values
Ripple ¹⁾	5 V _{pp}
Initialization time ²⁾	Тур. 1.5 s
Housing material	Aluminum/zinc die-cast
Connection type	Connector M12, SPEEDCON™ compatible
Indication	6 digit 5 x 7 dot matrix display, LEDs
Weight ³⁾	Approx. 800 g 1,600 g
Output current I _A ⁴⁾	≤ 100 mA

 $^{\scriptscriptstyle 1)}$ May not fall short of or exceed $\rm V_S$ tolerances.

²⁾ After loss of reflector < 40 ms.

 $^{\scriptscriptstyle 3)}$ Without mounting bracket: approx. 800 g, with mounting bracket: approx. 1,600 g.

⁴⁾ Short circuit/overload protected. Max. 100 nF / 20 mH.

Ambient data

Enclosure rating	IP 65
Protection class	III
Electromagnetic compatibility (EMC) ¹⁾	EN 61000-6-2, EN 61000-6-4
Effect of air pressure	0.3 ppm/hPa
Effect of air temperature	1 ppm/K
Temperature drift	Typ. 0.1 mm/K
Mechanical load	Shock: EN 600 68-2-27 Sine: EN 600 68-2-6 Noise: EN 600 68-2-64


 $^{\scriptscriptstyle (1)}$ This is a Class A device. This device can cause radio interference in living quarters.

Ordering information

Ambient tempera- ture	Power con- sumption	Measuring range	Accuracy	Repeat- ability	Frequency coded	Interface	Model name	Part no.																								
					Yes	RS-422	DL100-21AB2103	1060953																								
						SSI	DL100-21AA2101	1052684																								
						PROFIBUS	DL100-21AA2102	1052686																								
		0.15 m 100 m	±2mm	0.5 mm		PROFINET	DL100-21AA2112	1058164																								
		100 111				RS-422	DL100-21AA2103	1052688																								
						CANopen	DL100-21AA2109	1060386																								
						EtherNet/IP	DL100-21AA2110	1066427																								
						SSI	DL100-22AA2101	1052690																								
						PROFIBUS	DL100-22AA2102	1052692																								
Operation		0.15 m	± 2.5 mm	1 mm	No	PROFINET	DL100-22AA2112	1058166																								
-20 °C +55 °C 1)		200 m	± 2.5 mm	T 11111	INU	RS-422	DL100-22AA2103	1052694																								
Operation with cooling case	At 24 V DC					CANopen	DL100-22AA2109	1060388																								
-20 °C +75 °C	< 250 mA					EtherNet/IP	DL100-22AA2110	1066428																								
Storage						SSI	DL100-23AA2101	1052696																								
–40 °C +75 °C						PROFIBUS	DL100-23AA2102	1052698																								
						PROFINET	DL100-23AA2112	1058168																								
						RS-422	DL100-23AA2103	1052700																								
		0.45				CANopen	DL100-23AA2109	1060390																								
		0.15 m 300 m	±3 mm	2 mm		EtherNet/IP	DL100-23AA2110	1066429																								
						SSI	DL100-23AB2101	1060948																								
						PROFIBUS	DL100-23AB2102	1060949																								
																													Yes	PROFINET	DL100-23AB2112	1060952
						RS-422	DL100-23AB2103	1060950																								
						CANopen	DL100-23AB2109	1060951																								
					Yes	PROFIBUS	DL100-21HB2102	1064835																								
						SSI	DL100-21HA2101	1052685																								
		0.45				PROFIBUS	DL100-21HA2102	1052687																								
		0.15 m 100 m	± 2 mm	0.5 mm		PROFINET	DL100-21HA2112	1058165																								
						RS-422	DL100-21HA2103	1052689																								
						CANopen	DL100-21HA2109	1060387																								
						EtherNet/IP	DL100-21HA2110	1066423																								
Operation with						SSI	DL100-22HA2101	1052691																								
heating -40 °C +55 °C						PROFIBUS	DL100-22HA2102	1052693																								
Operation with	At 24 V DC	0.15 m	± 2.5 mm	1 mm	No	PROFINET	DL100-22HA2112	1058167																								
cooling case -40 °C +75 °C	< 1000 mA	200 m	± 2.0 mm	1	NO	RS-422	DL100-22HA2103	1052695																								
Storage						CANopen	DL100-22HA2109	1060389																								
-40 °C +75 °C						EtherNet/IP	DL100-22HA2110	1066425																								
						SSI	DL100-23HA2101	1052697																								
						PROFIBUS	DL100-23HA2102	1052699																								
		0.45 m				PROFINET	DL100-23HA2112	1058169																								
		0.15 m 300 m	±3 mm	2 mm		RS-422	DL100-23HA2103	1052701																								
						CANopen	DL100-23HA2109	1060391																								
						EtherNet/IP	DL100-23HA2110	1066426																								
					Yes	EtherNet/IP	DL100-23HB2110	1066438																								

¹⁾ Temperatures < -10 °C require warm-up time of typ. 7 minutes

Dimensional drawing



1 Optical axis, sender


- 2 Optical axis, receiver
- 3 Zero level
- 4 Threaded mounting hole M5
- S Status LED [status]
- ⑥ Display
- ⑦ Control elements

dimensions in mm


DL100 Pro

Adjustments


DL100-xxXXxx02



(5) Status LED [status]
(6) Display
(7) Control elements



⑥ Display⑦ Control elements




Connection type and diagram

Please note: Since wire color on 8-pin connection cables are not normed, always check for a correct pin to wire color assignment when using connection cables other than specified here.


Dx100 Ethernet Socket M12, 4-pin, D-coded







Dx100 SSI, RS-422 Connector M12, 8-pin, A-coded






Dx100 PROFIBUS/ PROFINET/CANopen Connector M12, 4-pin, A-coded







Dx100 PROFIBUS IN Connector M12, 5-pin B-coded






DL100 Pro






① Not connected


Dx100 PROFINET, Port 1/ Port 2 Socket M12, 4-pin, D-coded



Dx100 CANopen Socket M12, 5-pin, CANout



Dx100 CANopen Socket M12, 5-pin, CANin



Recommended accessories

Plug connectors and cables

	Brief description	Model name	Part no.	Dx100 SSI	Dx100 PROFIBUS	Dx100 RS-422	Dx100 PROFINET	Dx100 CANopen	Dx100 EtherNet/IP
\sim	Female connector, M12, 4-pin, straight, 2 m, PVC	DOL-1204-G02M	6009382	-	•	-	•	•	•
	Female connector, M12, 4-pin, straight, 5 m, PVC	DOL-1204-G05M	6009866	-	•	-	•	•	•
Illustration may differ	Female connector, M12, 4-pin, straight, 10 m, PVC	DOL-1204-G10M	6010543	-	•	-	•	•	•
	Female connector, M12, 5-pin, straight, 5 m, PROFIBUS, shielded	DOL-1205-G05MQ	6026006	-	•	-	-	-	-
	Female connector, M12, 5-pin, straight, 10 m, PROFIBUS, shielded	DOL-1205-G10MQ	6026008	-	•	-	-	-	-
19 G	Female connector, M12, 5-pin, straight, 15 m, PROFIBUS, shielded	DOL-1205-G15MQ	6032637	-	•	-	-	-	-
	Female connector, M12, 8-pin., straight, 2 m, PUR halogen free, shielded	DOL-1208-G02MAH1	6032448	•	-	•	-	-	-
	Female connector, M12, 8-pin., straight, 5 m, PUR halogen free, shielded	DOL-1208-G05MAH1	6032449	•	-	•	-	-	-
• •	Female connector, M12, 8-pin., straight, 10 m, PUR halogen free, shielded	DOL-1208-G10MAH1	6032450	•	-	•	-	-	-
	Male connector, M12, 4-pin, straight, PROFIBUS, terminal resistor	PR-STE-END	6021156	-	•	-	-	-	-
	Connection cable, Ethernet patch cable, 2 m, straight, connector M12, 4-pin to connector RJ-45 $$	SSL-2J04-G02ME	6034414	•	•	•	-	•	-
	Connection cable, Ethernet patch cable, 5 m, straight, connector M12, 4-pin to connector RJ-45 $$	SSL-2J04-G05ME	6035389	•	•	•	-	•	-
	Connection cable, Ethernet patch cable, 10 m, straight, connector M12, 4-pin to connector RJ-45	SSL-2J04-G10ME	6030928	•	•	•	-	•	-

	Brief description	Model name	Part no.	Dx100 SSI	Dx100 PROFIBUS	Dx100 RS-422	Dx100 PROFINET	Dx100 CANopen	Dx100 EtherNet/IP
	Connecting cable, M12 male connector, straight, to open end, 2 \mbox{m}	SSL-1204-G02MZ90	6048247	-	-	-	•	-	-
	Connecting cable, M12 male connector, straight, to open end, 5 \mbox{m}	STL-1204-G05MZ90	6048248	-	-	-	•	-	-
	Connecting cable, M12 male connector, straight, to open end, 10 m	STL-1204-G10MZ90	6048249	-	-	-	•	-	-
	Male connector, M12, 5-pin, straight, 5 m, PROFIBUS, shielded	STL-1205-G05MQ	6026005	-	ullet	-	-	-	-
	Male connector, M12, 5-pin, straight, 10 m, PROFIBUS, shielded	STL-1205-G10MQ	6026007	-	•	-	-	-	-
<i>•</i>	Male connector, M12, 5-pin, straight, 15 m, PROFIBUS, shielded	STL-1205-G15MQ	6036898	-	•	-	-	-	-
	Male connector, M12, 4-pin, straight, 2 m, Ethernet/IP, shielded	STL-1204-G02ME90	6045284	-	-	-	-	-	•
The	Male connector, M12, 4-pin, straight, 5 m, Ethernet/IP, shielded	STL-1204-G05ME90	6045285	-	-	-	-	-	•
	Male connector, M12, 4-pin, straight, 10 m, Ethernet/IP, shielded	STL-1204-G10ME90	6045286	-	-	-	-	-	•

Reflectors

Brief description	Model name	Part no.	Dx100 SSI	Dx100 PROFIBUS	Dx100 RS-422	Dx100 PROFINET	Dx100 CANopen	Dx100 EtherNet/IP
Reflector plate, DG tape 665 mm x 665 mm, material: base plate aluminum, screw connection	PL560DG	1016806	•	•	•	•	•	•

Terminal and alignment brackets

	Brief description	Model name	Part no.	Dx100 SSI	Dx100 PROFIBUS	Dx100 RS-422	Dx100 PROFINET	Dx100 CANopen	Dx100 EtherNet/IP
R.	Alignment unit for Dx100, steel, zinc coated, incl. mounting material	BEF-AH-DX100	2058653	•	•	•	•	•	•

For additional accessories, please see page 13.

Accessories

Adapters/distributors

Brief description	Model name	Part no.	Dx100 SSI	Dx100 PROFIBUS	Dx100 RS-422	Dx100 PROFINET	Dx100 CANopen	Dx100 EtherNet/IP
Signal converter from SSI to analog signal (0 mA 20 mA $/$ 4 mA 20 mA $/$ 0 V 10 V)	HN.SK20.2	6021449	•	-	-	-	-	-

Device protection (mechanical)

	Brief description	Model name	Part no.	Dx100 SSI	Dx100 PROFIBUS	Dx100 RS-422	Dx100 PROFINET	Dx100 CANopen	Dx100 EtherNet/IP
,	Thermo protection cooling case DS/DT500, peltier cooling unit, fiber glass housing	TPCC Cooling Case Dx100	6048328	•	•	•	•	•	•

Mounting brackets/plates

	Brief description	Model name	Part no.	Dx100 SSI	Dx100 PROFIBUS	Dx100 RS-422	Dx100 PROFINET	Dx100 CANopen	Dx100 EtherNet/IP
	Adapter plate for DME3000 to Dx100	BEF-AP3-Dx100	2064250	ullet	ullet	•	٠	٠	•
	Adapter plate for DME4000 / DME5000 to Dx100	BEF-AP4/5-Dx100	2062704	•	•	•	•	•	•

Plug connectors and cables

	Brief description	Model name	Part no.	Dx100 SSI	Dx100 PROFIBUS	Dx100 RS-422	Dx100 PROFINET	Dx100 CANopen	Dx100 EtherNet/IP
No. 200	Data cable for Ethernet with 4-pin M12 plug, angled, 8-pin RJ45 plug, 5 m	Connection cable (plug-plug)	6039488	•	•	•	-	•	-
	Female connector, M12, 4-pin, straight, 2 m, PVC	DOL-1204-G02M	6009382	-	•	-	•	•	ullet
	Female connector, M12, 4-pin, straight, 5 m, PVC	DOL-1204-G05M	6009866	-	ullet	-	ullet	ullet	ullet
	Female connector, M12, 4-pin, straight, 10 m, PVC	DOL-1204-G10M	6010543	-	•	-	•	•	ullet
Illustration may differ	Female connector, M12, 4-pin, straight, 15 m, PVC	DOL-1204-G15M	6010753	-	ullet	-	ullet	٠	ullet
uner	Female connector, M12, 4-pin, straight, 20 m, PVC	DOL-1204-G20M	6034401	-	ullet	-	ullet	ullet	ullet
	Female connector, M12, 4-pin, straight, 5 m, PVC, shielded	DOL-1204-G05MA	6042100	-	•	-	•	•	•
	Female connector, M12, 4-pin, straight, 2 m, PUR halogen free	DOL-1204-G02MC	6025900	-	ullet	-	ullet	ullet	ullet
	Female connector, M12, 4-pin, straight, 5 m, PUR halogen free	DOL-1204-G05MC	6025901	-	•	-	•	•	ullet
	Female connector, M12, 4-pin, straight, 10 m, PUR halogen free	DOL-1204-G10MC	6025902	-	•	-	•	•	•
	Female connector, M12, 4-pin, straight, 15 m, PUR halogen free	DOL-1204-G15MC	6034749	-	•	-	•	•	•
fi F fi F	Female connector, M12, 4-pin, straight, 20 m, PUR halogen free	DOL-1204-G20MC	6034750	-	•	-	•	•	•
	Female connector, M12, 4-pin, straight, 25 m, PUR halogen free	DOL-1204-G25MC	6034751	-	•	-	•	•	•
	Female connector, M12, 4-pin, straight, 5 m, PUR halogen free, shielded	DOL-1204-G05MAC	6038621	-	•	-	•	•	•
No.	Female connector, M12, 4-pin, straight, 10 m, PUR halogen free, shielded	DOL-1204-G10MA	6041797	-	•	-	•	•	•
	Female connector, M12, 4-pin, angled, 2 m, PVC	DOL-1204-W02M	6009383	-	•	-	•	•	ullet
	Female connector, M12, 4-pin, angled, 5 m, PVC	DOL-1204-W05M	6009867	-	ullet	-	ullet	ullet	ullet
	Female connector, M12, 4-pin, angled, 10 m, PVC	DOL-1204-W10M	6010541	-	ullet	-	ullet	•	ullet
Illustration may differ	Female connector, M12, 4-pin, angled, 15 m, PVC	DOL-1204-W15M	6036474	-	ullet	-	ullet	ullet	ullet
diller	Female connector, M12, 4-pin, angled, 20 m, PVC	DOL-1204-W20M	6033559	-	ullet	-	ullet	ullet	ullet
	Female connector, M12, 4-pin, angled, 2 m, PUR halogen free	DOL-1204-W02MC	6025903	-	ullet	-	ullet	٠	ullet
	Female connector, M12, 4-pin, angled, 5 m, PUR halogen free	DOL-1204-W05MC	6025904	-	ullet	-	ullet	٠	ullet
\sim	Female connector, M12, 4-pin, angled, 10 m, PUR halogen free	DOL-1204-W10MC	6025905	-	ullet	-	ullet	٠	ullet
	Female connector, M12, 4-pin, angled, 15 m, PUR halogen free	DOL-1204-W15MC	6034752	-	•	-	•	•	•
	Female connector, M12, 4-pin, angled, 20 m, PUR halogen free	DOL-1204-W20MC	6034753	-	٠	-	٠	٠	ullet
	Female connector, M12, 4-pin, angled, 25 m, PUR halogen free	DOL-1204-W25MC	6034754	-	ullet	-	•	•	ullet
6	Female connector, M12, 4-pin, angled, 5 m, PVC, shielded	DOL-1204-W05MA	6042098	_	•	-	•	•	•

	Brief description	Model name	Part no.	Dx100 SSI	Dx100 PROFIBUS	Dx100 RS-422	Dx100 PROFINET	Dx100 CANopen	Dx100 EtherNet/IP
	Female connector, M12, 5-pin, straight, 5 m, PROFIBUS,	DOL-1205-G05MQ	6026006						
	shielded Female connector, M12, 5-pin, straight, 10 m, PROFIBUS, shielded	DOL-1205-G10MQ	6026008	-	•	-	-	-	-
~	Female connector, M12, 5-pin, straight, 12 m, PROFIBUS, shielded	DOL-1205-G12MQ	6032636	-	•	-	-	-	-
	Female connector, M12, 5-pin, straight, 15 m, PROFIBUS, shielded	DOL-1205-G15MQ	6032637	-	•	-	-	-	-
	Female connector, M12, 5-pin, straight, 20 m, PROFIBUS, shielded	DOL-1205-G20MQ	6032638	-	•	-	-	-	-
	Female connector, M12, 5-pin, straight, 30 m, PROFIBUS, shielded	DOL-1205-G30MQ	6032639	-	•	-	-	-	-
	Female connector, M12, 5-pin, straight, 50 m, PROFIBUS, shielded	DOL-1205-G50MQ	6032861	-	•	-	-	-	-
	Female connector, M12, 5-pin, straight, 5 m, CAN/CAN open, shielded on pin 1 $$	DOL-1205-G05M_ Can	6021166	-	-	-	-	•	-
/ c	Female connector, M12, 5-pin, straight, 10 m, CAN/CANopen, shielded on pin 1 $\ensuremath{\mathbbm 1}$	DOL-1205-G10M_ Can	6021175	-	-	-	-	•	-
No.	Female connector, M12, 5-pin, straight, 6 m, DeviceNet/CANopen, dropcable shielded	DOL-1205-G06MK	6028326	-	-	-	-	•	-
	Female connector, M12, 5-pin, angled, 10 m, PROFIBUS, shielded	DOL-1205-W10MQ	6041425	-	•	-	-	-	-
	Female connector, M12, 8-pin., straight, 2 m, PUR halogen free, shielded	DOL-1208-G02MAH1	6032448	•	-	•	-	-	-
	Female connector, M12, 8-pin., straight, 5 m, PUR halogen free, shielded	DOL-1208-G05MAH1	6032449	•	-	•	-	-	-
No /	Female connector, M12, 8-pin., straight, 10 m, PUR halogen free, shielded	DOL-1208-G10MAH1	6032450	•	-	•	-	-	-
	Female connector, M12, 8-pin, straight, 20 m, PUR halogen free, shielded,	DOL-1208-G20MAH1	6032451	•	-	•	-	-	-
So the	Profibus adapter cable DME4000 / DME5000 to DL100 Pro	DSC-1608-1204	2062595	-	•	-	-	-	-
	SSI / RS-422 adapter cable DME4000 / DME5000 to DL100 Pro	DSC-1608-1208	2062563	•	-	•	-	-	-
N 0	SSI / RS-422 adapter cable DME3000 to DL100 Pro	DSC-1612-1208	2061596	•	-	•	-	-	-
	Connection cable, M12, 5-pin, connector straight/socket straight, 2 m, CAN/CANopen, shielded	DSL-1205-G02MK	6028903	-	-	-	-	•	-
11	Connection cable, M12, 5-pin, connector straight/socket straight, 3 m, CAN/CANopen, shielded	DSL-1205-G03MK	6021165	-	-	-	-	•	-
To Co	Connection cable, M12, 5-pin, connector straight/socket straight, 5 m, CAN/CANopen, shielded	DSL-1205-G05MK	6021168	-	-	-	-	•	-
	Connection cable, M12, 5-pin, connector straight/socket straight, 6 m, CAN/CANopen, shielded	DSL-1205-G06MK	6028327	-	-	-	-	•	-
100 KG	Connection cable, M12, 5-pin, connector straight/socket straight, 10 m, PROFIBUS, shielded	DSL-1205-G10MQ	6032640	-	•	-	-	-	-
1. T.	Connection cable, M12, 5-pin, connector straight/socket straight, 1 m, CAN/CANopen, shielded	DSL1205-G01MK	6021164	-	-	-	-	•	-

	Brief description	Model name	Part no.	Dx100 SSI	Dx100 PROFIBUS	Dx100 RS-422	Dx100 PROFINET	Dx100 CANopen	Dx100 EtherNet/IP
	Female connector, M12, 5-pin, 2 m, PVC	DeviceNet cable	6030920	-	-	-	-		-
	Female connector, M12, 5-pin, 3 m, PVC	DeviceNet cable	6030739	-	-	-	-	•	-
	Female connector, M12, 5-pin, 4 m, PVC	DeviceNet cable	6030740	-	-	-	-	•	-
1 💞	Female connector, M12, 5-pin, 5 m, PVC	DeviceNet cable	6030741	-	-	-	-	ullet	-
	Female connector, M12, 5-pin, 6 m, PVC	DeviceNet cable	6030742	-	-	-	-	ullet	-
\mathcal{N}	Cable, by the meter, PROFIBUS, shielded	LTG-2102-MW	6021355	-	•	-	-	-	-
	Cable, by the meter, 8-pin, PUR halogen free, shielded, twinned wires	LTG-3108-MW	6032456	•	-	•	-	-	-
	Male connector, M12, 5-pin, straight, PROFIBUS, shielded	PR-STE-1205-G	6021354	-	•	-	-	-	-
	Male connector, M12, 4-pin, straight, PROFIBUS, terminal resistor	PR-STE-END	6021156	-	•	-	-	-	-
-	Connecting cable, M12 male connector, D-coded, angled, to M12 male connector, straight, 2 m	SSL-1204-F02MZ90	6048250	-	-	-	•	-	-
	Connecting cable, M12 male connector, D-coded, angled, to M12 male connector, straight, 5 m	SSL-1204-F05MZ90	6048251	-	-	-	•	-	-
	Connecting cable, M12 male connector, D-coded, angled, to M12 male connector, straight, 10 m	SSL-1204-F10MZ90	6048252	-	-	-	•	-	-
	Connecting cable, M12 male connector D-coded straight to M12 male connector straight, 2 m $$	SSL-1204-G02MZ90	6048241	-	-	-	•	-	-
	Connecting cable, M12 male connector, D-coded, straight, to M12 male connector, straight, 5 m	SSL-1204-G05MZ90	6048242	-	-	-	•	-	-
	Connecting cable, M12 male connector, D-coded, straight, to M12 male connector, straight, 10 m	SSL-1204-G10MZ90	6048243	-	-	-	•	-	-
	Connecting cable, M12 male connector, D-coded, angled, to RJ45, straight, 2 m	SSL-2J04-F02MZ	6048253	-	-	-	•	-	-
	Connecting cable, M12 male connector, D-coded, angled, to RJ45, straight, 5 \mbox{m}	SSL-2J04-F05MZ	6048254	-	-	-	•	-	-
	Connecting cable, M12 male connector, D-coded, angled, to RJ45, straight, 10 m	SSL-2J04-F10MZ	6048255	-	-	-	•	-	-
	Connection cable, Ethernet patch cable, 2 m, straight, connec- tor M12, 4-pin to connector RJ-45	SSL-2J04-G02ME	6034414	•	•	•	-	•	-
	Connection cable, Ethernet patch cable, 3 m, straight, connec- tor M12, 4-pin to connector RJ-45	SSL-2J04-G03ME	6029630	•	•	•	-	•	-
. The second	Connection cable, Ethernet patch cable, 5 m, straight, connector M12, 4-pin to connector RJ-45	SSL-2J04-G05ME	6035389	•	•	•	-	•	-
Illustration may differ	Connection cable, Ethernet patch cable, 10 m, straight, con- nector M12, 4-pin to connector RJ-45	SSL-2J04-G10ME	6030928	•	•	•	-	•	-
	Connection cable, Ethernet patch cable, 20 m, straight, con- nector M12, 4-pin to connector RJ-45	SSL-2J04-G20ME	6036158	•	•	•	-	•	-
	Connection cable, Ethernet patch cable, 25 m, straight, con- nector M12, 4-pin to connector RJ-45	SSL-2J04-G25ME	6033555	•	•	٠	-	•	-
	Connecting cable, M12 male connector, D-coded, straight, to RJ45, straight, 2 m	SSL-1204-G02MZ60	6048244	-	-	-	•	-	-
	Connecting cable, M12 male connector, D-coded, straight, to RJ45, straight, 5 m	SSL-1204-G05MZ60	6048245	-	-	-	•	-	-
	Connecting cable, M12 male connector, D-coded, straight, to RJ45, straight, 10 m	SSL-1204-G10MZ60	6048246	-	-	-	•	-	-

	Brief description	Model name	Part no.	Dx100 SSI	Dx100 PROFIBUS	Dx100 RS-422	Dx100 PROFINET	Dx100 CANopen	Dx100 EtherNet/IP
	Ethernet cable, M12, 4-pin, angled/RJ45, CAT5, 2 m	SSL-2J04-H02ME60	6047911	•	•	•	-	•	ullet
	Ethernet cable, M12, 4-pin, angled/RJ45, CAT5, 5 m	SSL-2J04-H05ME60	6045287	٠	•	٠	-	٠	\bullet
	Ethernet cable, M12, 4-pin, angled/RJ45, CAT5, 10 m	SSL-2J04-H10ME60	6045288	•	•	•	-	•	ullet
	Male connector, M12, 5-pin, straight, terminal resistor, De- viceNet and CANopen	STE-1205-GKEND	6037193	-	-	-	-	•	-
	Connecting cable, M12 male connector, straight, to open end, 2 m	STL-1204-G02MZ90	6048247	-	-	-	•	-	-
	Connecting cable, M12 male connector, straight, to open end, 5 m	STL-1204-G05MZ90	6048248	-	-	-	•	-	-
	Connecting cable, M12 male connector, straight, to open end, 10 \mbox{m}	STL-1204-G10MZ90	6048249	-	-	-	•	-	-
	Connecting cable, M12 male connector, angled, to open end, 2 m	STL-1204-W02MZ90	6048256	-	-	-	•	-	-
	Connecting cable, M12 male connector, angled, to open end, 5 m	STL-1204-W05MZ90	6048257	-	-	-	•	-	-
-	Connecting cable, M12 male connector, angled, to open end, 10 m $$	STL-1204-W10MZ90	6048258	-	-	-	•	-	-
	Connecting cable, M12 male connector, angled, to open end, 25 m	STL-1204-W25MZ90	6048259	-	-	-	•	-	-
	Male connector, M12, 5-pin, straight, 5 m, PROFIBUS, shielded	STL-1205-G05MQ	6026005	-	ullet	-	-	-	-
A	Male connector, M12, 5-pin, straight, 10 m, PROFIBUS, shielded	STL-1205-G10MQ	6026007	-	•	-	-	-	-
	Male connector, M12, 5-pin, straight, 12 m, PROFIBUS, shielded	STL-1205-G12MQ	6032635	-	•	-	-	-	-
	Male connector, M12, 5-pin, straight, 15 m, PROFIBUS, shielded	STL-1205-G15MQ	6036898	-	•	-	-	-	-
	Connection cable, DeviceNet drop cable, 10 m, straight, con- nector M12, 5-pin to open end, drag-chain compliant	STL-1205-G10M_CAN	6021293	-	-	-	-	•	-
\ \	Male connector, M12, 5-pin, angled, 5 m, PROFIBUS, shielded	STL-1205-W05MQ	6041426	-	•	-	-	-	-
	Male connector, M12, 5-pin, angled, 10 m, PROFIBUS, shielded	STL-1205-W10MQ	6041427	-	•	-	-	-	-
	Male connector, M12, 4-pin, straight, 2 m, Ethernet/IP, shielded	STL-1204-G02ME90	6045284	-	-	-	-	-	•
	Male connector, M12, 4-pin, straight, 5 m, Ethernet/IP, shielded	STL-1204-G05ME90	6045285	-	-	-	-	-	•
	Male connector, M12, 4-pin, straight, 10 m, Ethernet/IP, shielded	STL-1204-G10ME90	6045286	-	-	-	-	-	•

Power supply units/power cord connectors

Brief description	Model name	Part no.	Dx100 SSI	Dx100 PROFIBUS	Dx100 RS-422	Dx100 PROFINET	Dx100 CANopen	Dx100 EtherNet/IP
Power supply unit, DC 24 V / 10 A, 110 120, 210 240 VAC, 24 VDC, 10 A, for cap rail mounting and TPCC supply	Power supply unit	6020875	•	•	•	•	•	•

Reflectors

Brief description	Model name	Part no.	Dx100 SSI	Dx100 PROFIBUS	Dx100 RS-422	Dx100 PROFINET	Dx100 CANopen	Dx100 EtherNet/IP
Reflector plate, DG tape 1,200 mm x 1,200 mm, material: base plate aluminum, screw connection	PL1200DG	1051679	•	•	•	•	•	•
Reflector plate, DG tape 330 mm x 330 mm, material: base plate aluminum, screw connection	PL240DG	1017910	•	•	•	•	•	•
Reflector plate, DG tape 330 mm x 330 mm, material: base plate aluminum, screw connection, heated	PL240DG-H	1022926	•	•	•	•	•	•
Reflector plate, DG tape 665 mm x 665 mm, material: base plate aluminum, screw connection	PL560DG	1016806	•	•	•	•	•	•
Reflector plate, DG tape 665 mm x 665 mm, material: base plate aluminum, screw connection, heated	PL560DG-H	1023888	•	•	•	•	•	•
Reflector plate, DG tape 1,000 mm x 1,000 mm, material: base plate aluminum, screw connection	PL880DG	1018975	•	•	•	•	•	•
Diamond Grade reflective tape, sheet, 749 mm x 914 mm, self-adhesive	REF-DG	5320565	•	•	•	•	•	•
Diamond Grade reflective tape, customizable by sheet, self- adhesive	REF-DG-K	4019634	•	•	•	•	•	•

Sets

		Model name	Part no.	Dx100 SSI	Dx100 PROFIBUS	Dx100 RS-422	Dx100 PROFINET	Dx100 CANopen	Dx100 EtherNet/IP
	Accessory kit for retrofit from DME3000 PROFIBUS to Dx100 PROFIBUS	DME3000 Dx100 PROFIBUS retrofit kit	2065222	-	•	-	-	-	-
Var 10	Accessory kit for retrofit from DME3000 SSI/RS-422 to Dx100 SSI/RS-422	DME3000 Dx100 SSI/RS-422 retrofit kit	2065223	•	-	•	-	-	-
<u>IN</u>	Accessory kit for retrofit from DME4000/5000 PROFIBUS to Dx100 PROFIBUS	DME4000/5000 Dx100 PROFIBUS retrofit kit	2065220	-	•	-	-	-	-
	Accessory kit for retrofit from DME4000/5000 SSI/RS-422 to Dx100 SSI/RS-422	DME4000/5000 Dx100 SSI/RS-422 retrofit kit	2065221	•	-	•	-	-	-

Terminal and alignment brackets

	Brief description	Model name	Part no.	Dx100 SSI	Dx100 PROFIBUS	Dx100 RS-422	Dx100 PROFINET	Dx100 CANopen	Dx100 EtherNet/IP
R.	Alignment unit for Dx100, steel, zinc coated, incl. mounting material	BEF-AH-DX100	2058653	•	•	•	•	•	•

WWW.MYSICK.COM – SEARCH ONLINE AND ORDER

Search online quickly and safely - with the SICK "Finders"



Product Finder: We can help you to quickly target the product that best matches your application.

Applications Finder: Select the application description on the basis of the challenge posed, industrial sector, or product group.

Literature Finder: Go directly to the operating instructions, technical information, and other literature on all aspects of products from SICK.

These and other "Finders" at → www.mysick.com

Efficiency - with the e-commerce tools from SICK



Find out prices and availability: Determine the price and possible delivery date of your desired product simply and quickly at any time.

Request or view a quote: You can have a quote generated online here. Every quote is confirmed to you via e-mail.

Order online: You can go through the ordering process in just a few steps.

SERVICES FOR MACHINES AND SYSTEMS: SICK LifeTime Services

Our comprehensive and versatile LifeTime Services are the perfect addition to the comprehensive range of products from SICK. The services range from product-independent consulting to traditional product services.



SICK AT A GLANCE

SICK is a leading manufacturer of intelligent sensors and sensor solutions for industrial applications. With more than 6,500 employees and over 50 subsidiaries and equity investments as well as numerous representative offices worldwide, we are always close to our customers. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in various industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services round out our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

Worldwide presence:

Australia, Austria, Belgium/Luxembourg, Brazil, Czech Republic, Canada, China, Denmark, Finland, France, Germany, Great Britain, Hungary, India, Israel, Italy, Japan, Mexico, Netherlands, Norway, Poland, Romania, Russia, Singapore, Slovenia, South Africa, South Korea, Spain, Sweden, Switzerland, Taiwan, Turkey, United Arab Emirates, USA

Detailed addresses and additional representatives -> www.sick.com



