



8028721 0923
9382055 1L6P
WTB4S_DID8389429
8389429
1820200620
9382030 1L6P (1.1.0)

| | |
|--|---|
| Australia Phone +61 3 9467 0800 | Osterreich Phone +43 (0)22 36 62 28 8-0 |
| Belgium/Luxembourg Phone +32 (0)2 468 35 66 | Norge Phone +47 67 61 50 00 |
| Brasil Phone +55 11 5215-4900 | Polka Phone +48 22 837 40 50 |
| Canada Phone +1 905 771 14 44 | România Phone +40 356 171 120 |
| China Phone +86 4000 121 000 +86212633 6300 | Russia Phone +7 495 775 09 30 |
| Danmark Phone +45 45 82 64 00 | Schweiz Phone +41 41 619 29 39 |
| Deutschland Phone +49 211 5301 301 | Sverige Phone +46 744 37 32 |
| España Phone +34 93 480 31 00 | South Korea Phone +82 2 786 6321/4 |
| France Phone +33 1 64 62 39 00 | Sri Lanka Phone +94 11 472 3733 |
| Great Britain Phone +44 (0)1727 83121 | Taiwan Phone +886 2 2375 6288 |
| India Phone +91 22 4033 8333 | Türkiye Phone +90 (216) 528 50 00 |
| Israel Phone +972 4 6801000 | United Arab Emirates Phone +971 (0)4 5855 878 |
| Italy Phone +39 02 27 43 41 | USA/Mexico Phone +1 950 941 6780 |
| Japan Phone +81 (03) 5309 2112 | |
| Magnesium Phone +36 1 371 2680 | |
| Niederland Phone +31 (0)30 229 25 44 | |

SICK AG, Erwin-Sick-Strasse 1, D-79183 Waldkirch

Please find detailed addresses and additional representatives and agencies in all major industrial nations at www.sick.com

More representatives and agencies at www.sick.com - Subject to change without notice - The specified product features and technical data do not represent any guarantee.

Weitere Niederlassungen finden Sie unter www.sick.com - Irrtümer und Änderungen vorbehalten - Angegebene Produkteigenschaften und technische Daten stellen keine Garantieerklärung dar.

Plus de représentations et d'agences à l'adresse www.sick.com - Sujet à modification sans préavis - Les caractéristiques de produit et techniques indiquées ne constituent pas de déclaration de garantie.

Para mais representantes e agências, consulte www.sick.com - Alterações poderão ser feitas sem prévio aviso - As características do produto e os dados técnicos apresentados não constituem declaração de garantia.


Fiere representanter og agenturer på www.sick.com - Med forbehold for ændringer og fejl - De angivne produktetskræber og tekniske data udgør ikke nogen garantierklæring.

Altri rappresentanti ed agenzie si trovano su www.sick.com - Contenuti soggetti a modifiche senza preavviso - Le caratteristiche del prodotto e i dati tecnici non rappresentano una dichiarazione di garanzia.

Meer vestigingen en vertegenwoordigingen vindt u op www.sick.com - Wijzigingen en correcties voorbehouden - Aangegeven producteigenschaften en technische gegevens vormen geen garantieverklaring.

Más representantes y agencias en www.sick.com - Sujeto a cambio sin previo aviso - Las características y los datos técnicos especificados no constituyen ninguna declaración de garantía.

欲了解更多代表机构和代理商信息，请登录 www.sick.com - 如有更改，不另行通知 - 对所给出的产品特性和技术参数 的正确性不予保证。



Please note the validity of the additional operating instructions for automation functions

1. Device features

Data Storage class 2:

The configured Device supports Data Storage in such a manner that the replacement Device requires user manipulation such as teach-in prior to operation with the same performance.

| | |
|---|---|
| Supported Smart Sensor Profile Function Classes | Binary Data Channel, Teach Channel |
| Supported IO-Link Time Stamp Profile modes | none (IO-Link Time Stamp Profile not supported) |
| Block Parameter Transmission | supported |
| Data Storage functionality | supported |
| Access Locks (supported / modes) | Local User Interface |

2. Physical layer

Note: The IO-Link Device's max. current consumption (inclusive load current) shall not exceed the master port's max. output power current.

| | |
|---------------------------|----------|
| SIO Modus | yes |
| Min Cycle Time | 2.3 ms |
| Baudrate ² | COM2 |
| Process Data Length (IN) | 2 Byte |
| IODD version | V1.42249 |
| Valid for IO-Link version | 1.1 |

3. Process data

Record³: 2 Byte

| | | | | | | | | |
|---------------|---------------------|----|----|----|----|---------|---------|---------|
| Bitoffset | | | | | | | | |
| Byte 0 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 |
| Type/Subindex | Unsigned Integer 14 | | | | | | | |
| Bitoffset | | | | | | | | |
| Byte 1 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| Type/Subindex | Unsigned Integer 14 | | | | | | | |
| | | | | | | OL2 | OL1 | |
| | | | | | | 3 | 2 | 1 |
| | | | | | | Boolean | Boolean | Boolean |

4. Service data

The following ISDUs will not be saved via Data-Storage: Teach-in channel, Teach-in state, Quint.1 configuration, Quint.2 SP1 / SP2, Quint.2 configuration, Device specific tag, Sender configuration, Quality of teach, Temperature zone, Current receiver level (live), Find me and SLTI Version

| IO-Link specific | | | | | | | |
|------------------|--------------------------|---------------------|---------|---------------------|---------------|---|---|
| Index dec (hex) | Name | Format (Offset) | Length | Access ¹ | Default Value | Value / Range | Remark [Unit] |
| 12 (0x0C) | Device Access Locks | Record ³ | 2 Byte | rw | | | The access to the device parameters can be restricted by setting appropriate flags within this parameter. |
| 4 (0x04) | Local User Interface | Bool (3) | 1 Bit | rw | 0 | 0 = unlocked 1 = locked | |
| 16 (0x10) | Vendor Name | String | 7 Byte | ro | SICK AG | | The vendor name that is assigned to a Vendor ID. |
| 17 (0x11) | Vendor Text | String | 64 Byte | ro | | | Additional information about the vendor. |
| 18 (0x12) | Product Name | String | 18 Byte | ro | | | Complete product name. |
| 19 (0x13) | Product ID | String | 16 Byte | ro | | | Vendor-specific product or type identification (e.g., item number or model number). |
| 20 (0x14) | Product Text | String | 45 Byte | ro | | | Additional product information for the device. |
| 21 (0x15) | Serial Number | String | 8 Byte | ro | | | Unique, vendor-specific identifier of the individual device. |
| 22 (0x16) | Hardware Revision | String | 4 Byte | ro | | | Unique, vendor-specific identifier of the hardware revision of the individual device. |
| 23 (0x17) | Firmware Revision | String | 16 Byte | ro | | | Unique, vendor-specific identifier of the firmware revision of the individual device. |
| 24 (0x18) | Application-specific Tag | String | 32 Byte | rw | *** | | Possibility to mark a device with user- or application-specific information. |
| 36 (0x24) | Device Status | UInt | 8 Bit | ro | | 0 = Device is OK 1 = Maintenance required 2 = Out of specification 3 = Functional check 4 = Failure | Indicator for the current device condition and diagnosis state. |
| 37 (0x25) | Detailed Device Status | Array ³ | 6 Byte | ro | | Octet String [2] | List of all currently pending events in the device. |
| 37 (0x25) | Detailed Device Status | Array ³ | 6 Byte | ro | | Octet String [2] | List of all currently pending events in the device. |
| 40 (0x28) | PD Input | PD In | 2 Byte | ro | | | Last valid process input data of the device. |

¹ ro = read only, wo = write only, rw = read/write

² COM values specify the bitrate (see IO-Link specification): COM1 (4,8 kbit/s), COM2 (38,4 kbit/s), COM3 (230,4 kbit/s)

³ Subindex access not supported



8028721 0923
9382055 1L6P
WTB4S_DID8389429
8389429
1820200620
9382030 1L6P (1.1.0)

| | |
|--|---|
| <p>Australia Phone +61 3 9467 0800</p> <p>Belgium/Luxembourg Phone +32 (0)2 468 55 66</p> <p>Brazil Phone +55 11 5215-9900</p> <p>Canada Phone +1 905 771 14 44</p> <p>China Phone +86 4000 121 000 +852 2553 6300</p> <p>Denmark Phone +45 45 82 64 00</p> <p>Deutschland Phone +49 211 5361 301</p> <p>España Phone +34 93 480 31 00</p> <p>France Phone +33 1 64 62 39 00</p> <p>Great Britain Phone +44 (0)1277 831121</p> <p>India Phone +91 22 4033 8333</p> <p>Israel Phone +972 4 6801000</p> <p>Italia Phone +39 02 27 43 41</p> <p>Japan Phone +81 (03) 5309 2112</p> <p>Magnetsville Phone +36 1 371 2680</p> <p>Niederland Phone +31 (0)30 229 25 44</p> <p>SICK AG, Erwin-Sick-Strasse 1, D 79183 Waldkirch</p> | <p>Osterreich Phone +43 (0)32 36 62 28 8-0</p> <p>Norge Phone +47 67 61 50 00</p> <p>Polska Phone +49 22 837 40 50</p> <p>România Phone +40 356 171 120</p> <p>Russia Phone +7 495 775 09 30</p> <p>Schweiz Phone +41 41 619 29 39</p> <p>Singapore Phone +65 6744 3732</p> <p>South Africa Phone +27 11 472 3733</p> <p>South Korea Phone +82 2 786 6321/4</p> <p>Spain Phone +358 9 25 15 800</p> <p>Sverige Phone +46 10 110 10 00</p> <p>Taiwan Phone +886 2 2375 6288</p> <p>Türkiye Phone +90 (216) 538 50 00</p> <p>United Arab Emirates Phone +971 (0)4 5865 878</p> <p>USA/Mexico Phone +1 950 941 6780</p> |
|--|---|

Please find detailed addresses and additional representatives and agencies in all major industrial nations at www.sick.com

More representatives and agencies at www.sick.com - Subject to change without notice - The specified product features and technical data do not represent any guarantee.

Weitere Niederlassungen finden Sie unter www.sick.com - Irrtümer und Änderungen vorbehalten - Angegebene Produkteigenschaften und technische Daten stellen keine Garantieerklärung dar.

Plus de représentations et d'agences à l'adresse www.sick.com - Sujet à modification sans préavis - Les caractéristiques de produit et techniques indiquées ne constituent pas de déclaration de garantie.

Para mais representantes e agências, consulte www.sick.com - Alterações poderão ser feitas sem prévio aviso - As características do produto e os dados técnicos apresentados não constituem declaração de garantia.


Flere repræsentanter og agenturer på www.sick.com - Med forbehold for ændringer og fejl - De arfærte produktgenskaber og tekniske data udgør ikke nogen garantierklæring.

Altri rappresentanti ed agenzie si trovano su www.sick.com - Contenuti soggetti a modifiche senza preavviso - Le caratteristiche del prodotto e i dati tecnici non rappresentano una dichiarazione di garanzia.

Meer vestigingen en correcties voorbehouden - Aangegeven producteigenschappen en technische gegevens vormen geen garantieverklaring.

Más representantes y agencias en www.sick.com - Sujeto a cambio sin previo aviso - Las características y los datos técnicos especificados no constituyen ninguna declaración de garantía.

欲了解更多代表机构和代理商信息，请登录 www.sick.com - 如有更改，不另行通知 - 对所给出的产品特性和技术参数的正确性不予保证。



Please note the validity of the additional operating instructions for automation functions

ENGLISH

| SICK device specific | | | | | | | |
|----------------------|---|---------------------|---------|---------------------|---------------|---|-----------------------------|
| Index dec (hex) | Name | Format (Offset) | Length | Access ¹ | Default Value | Value / Range | Remark (Unit) |
| 25 (0x19) | Function Tag | String | 32 Byte | rw | *** | | |
| 26 (0x1A) | Location Tag | String | 32 Byte | rw | *** | | |
| 58 (0x3A) | Teach-in channel | UInt | 8 Bit | rw | 0 | 0 = default Quint. = Quint.1 1 = Quint.1 2 = Quint.2 | |
| 59 (0x3B) | Teach-in state | Record ³ | 1 Byte | ro | | | |
| 1 (0x01) | Teach flags | Bool (4) | 1 Bit | ro | | false = Teachpoint 1 not taught true = Teachpoint 1 successfully taught | |
| 2 (0x02) | Teach state | UInt (0) | 4 Bit | ro | | 0 = IDLE 1 = SP1 SUCCESS 5 = BUSY 7 = ERROR | |
| 60 (0x3C) | Qint.1 SP1 / SP2 | Record | 3 Byte | rw | | | |
| 1 (0x01) | SP1 sensing range | UInt (8) | 16 Bit | rw | 9 | 9...270 | [mm] |
| 2 (0x02) | SP2 sensing range | UInt (0) | 8 Bit | rw | 0 | 0 = SP2 not used | |
| 61 (0x3D) | Qint.1 configuration | Record | 4 Byte | rw | | | |
| 1 (0x01) | Switchpoint logic | UInt (24) | 8 Bit | rw | 128 | 128 = Vendor specific | |
| 2 (0x02) | Switchpoint mode | UInt (16) | 8 Bit | rw | 128 | 128 = Vendor specific | |
| 3 (0x03) | Switchpoint hysteresis | UInt (0) | 16 Bit | rw | 0 | 0 = Autodefined hysteresis | |
| 62 (0x3E) | Qint.2 SP1 / SP2 | Record | 3 Byte | rw | | | |
| 1 (0x01) | SP1 sensing range | UInt (8) | 16 Bit | rw | 9 | 9...270 | |
| 2 (0x02) | SP2 sensing range | UInt (0) | 8 Bit | rw | 0 | 0 = SP2 not used | |
| 63 (0x3F) | Qint.2 configuration | Record | 4 Byte | rw | | | |
| 1 (0x01) | Switchpoint logic | UInt (24) | 8 Bit | rw | 128 | 128 = Vendor specific | |
| 2 (0x02) | Switchpoint mode | UInt (16) | 8 Bit | rw | 128 | 128 = Vendor specific | |
| 3 (0x03) | Switchpoint hysteresis | UInt (0) | 16 Bit | rw | 0 | 0 = Autodefined hysteresis | |
| 64 (0x40) | Device specific tag | String | 32 Byte | rw | *** | | |
| 90 (0x5A) | Teach-in offset | Int | 8 Bit | rw | 0 | -100...100 | [mm] |
| 92 (0x5C) | Physical input / output type configuration pin2 | UInt | 8 Bit | rw | 3 | 1 = PNP 2 = NPN 3 = Push/Pull | |
| 97 (0x61) | Sender configuration | UInt | 8 Bit | rw | 0 | 0 = Sender active 1 = Sender not active | |
| 114 (0x72) | Quality of teach | UInt | 8 Bit | ro | | 0...100 | [%] |
| 121 (0x79) | Pin 2 configuration | UInt | 8 Bit | rw | 40 | 0 = Deactivated / no function 1 = External input (Smart Task) 16 = Sender off 17 = Teach-in 34 = Switching signal QL2 35 = Detection output Quint.1 39 = Switching signal QL1 40 = Switching signal QL1/ | |
| 154 (0x9A) | Temperature zone | UInt | 8 Bit | ro | | 0 = Very cold 1 = Cold 2 = Moderate 3 = Warm 4 = Hot | Sensor-internal temperature |
| 179 (0xB3) | Alarm thresholds for diagnostic parameters | Record | 4 Byte | rw | | | |
| 1 (0x01) | Operating hours threshold | UInt (0) | 32 Bit | rw | 40000 | 0...1000000 | [h] |
| 180 (0xB4) | Current receiver level (live) | UInt | 16 Bit | ro | | 0...16383 | |
| 190 (0xBE) | Operating hours | Record | 8 Byte | ro | | | |
| 1 (0x01) | Total operating hours | UInt (32) | 32 Bit | ro | | 0...1000000 | [h] |
| 2 (0x02) | Operating hours since last reset | UInt (0) | 32 Bit | ro | | 0...1000000 | [h] |
| 204 (0xCC) | Find me | UInt | 8 Bit | rw | 0 | 0 = Find me deactivated 1 = Find me activated | |
| 226 (0xE2) | System state | Record ³ | 2 Byte | ro | | | |
| 1 (0x01) | Detection output Quint.1 | Bool (0) | 1 Bit | ro | | false = No object detected true = Object detected | |
| 6 (0x06) | Input signal state Pin 2 | Bool (7) | 1 Bit | ro | | false = External input FALSE true = External input TRUE | |

¹ ro = read only, wo = write only, rw = read/write

² COM values specify the bitrate (see IO-Link specification): COM1 (4,8 kbit/s), COM2 (38,4 kbit/s), COM3 (230,4 kbit/s)

³ Subindex access not supported



8028721 0923
9382055 1L6P
WTB4S_DID8389429
8389429
1820200620
9382030 1L6P (1.1.0)

| | |
|---|---|
| Australia Phone +61 3 9457 0800 | Osterreich Phone +43 (0)22 36 62 28 8-0 |
| Belgium/Luxembourg Phone +32 (0)2 468 35 66 | Norge Phone +47 67 61 50 00 |
| Brazil Phone +55 11 3215-4900 | Polka Phone +48 22 837 40 50 |
| Canada Phone +1 905 771 14 44 | România Phone +40 356 171 120 |
| China Phone +86 4000 121 000 +852 2353 6300 | Russia Phone +7 495 775 05 30 |
| Denmark Phone +45 45 82 64 00 | Schweden Phone +41 41 619 29 39 |
| Deutschland Phone +49 211 5361 301 | Sveits Phone +43 6744 3732 |
| España Phone +34 93 480 31 00 | South Africa Phone +27 11 472 3733 |
| France Phone +33 1 64 62 39 00 | South Korea Phone +82 2 786 6321/4 |
| Great Britain Phone +44 (0)1727 831121 | Suomi Phone +358 9 25 15 800 |
| India Phone +91 22 4033 8333 | Sverige Phone +46 10 110 10 00 |
| Israel Phone +972 4 6801000 | Taiwan Phone +886 2 2375 6288 |
| Italia Phone +39 02 27 43 41 | Türkiye Phone +90 (216) 538 50 00 |
| Japan Phone +81 (03) 5309 2112 | United Arab Emirates Phone +971 (0) 4 5855 878 |
| Magnetsverige Phone +36 1 371 2680 | USA/Mexico Phone +1 952 941 6780 |
| Niederland Phone +31 (030) 229 25 44 | |

SICK AG, Erwin-Sick-Strasse 1, D-79183 Waldkirch

Please find detailed addresses and additional representatives and agencies in all major industrial nations at www.sick.com

More representatives and agencies at www.sick.com - Subject to change without notice - The specified product features and technical data do not represent any guarantee.

Weitere Niederlassungen finden Sie unter www.sick.com - Irrtümer und Änderungen vorbehalten! Angegebene Produkteigenschaften und technische Daten stellen keine Garantieerklärung dar.

Plus de représentations et d'agences à l'adresse www.sick.com - Sujet à modification sans préavis - Les caractéristiques de produit et techniques indiquées ne constituent pas de déclaration de garantie.

Para mais representantes e agências, consulte www.sick.com - Alterações poderão ser feitas sem prévio aviso - As características do produto e os dados técnicos apresentados não constituem declaração de garantia.

Flere repræsentanter og agenturer på www.sick.com - Med forbehold for ændringer og fejl - De anførte produktdata og tekniske data udgør ikke nogen garantierklæring.

Altri rappresentanti ed agenzie si trovano su www.sick.com - Contenuti soggetti a modifiche senza preavviso - Le caratteristiche del prodotto e i dati tecnici non rappresentano una dichiarazione di garanzia.

Meer vestigingen en vertegenwoordigingen vindt u op www.sick.com - Wijzigingen en correcties voorbehouden - Aangegeven producteigenschaften en technische gegevens vormen geen garantieverklaring.

Más representantes y agencias en www.sick.com - Sujeto a cambio sin preaviso - Las características y los datos técnicos especificados no constituyen ninguna declaración de garantía.

欲了解更多代表机构和代理商信息，请登录 www.sick.com - 如有更改，不另行通知 - 对所给出的产品特性和技术参数的正确性不予保证。



Please note the validity of the additional operating instructions for automation functions

ENGLISH

| SICK device specific | | | | | | | |
|----------------------|-----------------------|-----------------|--------|---------------------|---------------|---|---------------|
| Index dec (hex) | Name | Format (Offset) | Length | Access ¹ | Default Value | Value / Range | Remark [Unit] |
| 227 (0xE3) | Notification handling | UInt | 8 Bit | rw | 0 | 0 = All enabled 1 = All disabled 2 = Events enabled, PD invalid flag disabled 3 = Events disabled, PD invalid flag enabled | |
| 1080 (0x438) | SLTI Version | String | 8 Byte | ro | | | |
| 1083 (0x43B) | Logic 1 | UInt | 8 Bit | rw | 0 | 0 = DIRECT 1 = AND 2 = OR | |
| 1084 (0x43C) | Logic 2 | UInt | 8 Bit | rw | 0 | 0 = DIRECT 1 = AND 2 = OR | |
| 1085 (0x43D) | Timer 1 Mode | UInt | 8 Bit | rw | 0 | 0 = deactivated 1 = T-on delay 2 = T-off delay 3 = T-on/T-off delay 4 = Impulse (one shot) | |
| 1086 (0x43E) | Timer 2 Mode | UInt | 8 Bit | rw | 0 | 0 = deactivated 1 = T-on delay 2 = T-off delay 3 = T-on/T-off delay 4 = Impulse (one shot) | |
| 1087 (0x43F) | Time 1 Setup | UInt | 16 Bit | rw | 1 | 1...30000 | [ms] |
| 1088 (0x440) | Time 2 Setup | UInt | 16 Bit | rw | 1 | 1...30000 | [ms] |
| 1089 (0x441) | Inverter 1 | UInt | 8 Bit | rw | 0 | 0 = not inverted 1 = inverted | |
| 1090 (0x442) | Inverter 2 | UInt | 8 Bit | rw | 1 | 0 = not inverted 1 = inverted | |
| 1093 (0x445) | Inverter Ext. Input | UInt | 8 Bit | rw | 0 | 0 = not inverted 1 = inverted | |

| Standard command | | | | | | | |
|------------------|----------------|---------------------|-------|-----------------------------|---------------|--|--|
| Index dec (hex) | Name | Access ¹ | Value | Name | Remark [Unit] | | |
| 2 (0x02) | System Command | wo | 65 | Single value teach | | | |
| | | | 129 | Application Reset | | | |
| | | | 130 | Restore Factory Settings | | | |
| | | | 131 | Back-to-box | | | |
| | | | 228 | Reset diagnostics parameter | | | |

| Events | | | |
|----------------|--------------------------------------|--------------|---|
| Code dec (hex) | Name | Type | Remark [Unit] |
| 30480 (0x7710) | Short circuit | Error | Shortcut on outputs |
| 36001 (0x8CA1) | New parameters | Notification | Parameters have been changed |
| 36005 (0x8CA5) | Teach / value out of specified range | Notification | Teach / distance value out of specified range |
| 36011 (0x8CAB) | Alarm operating hours | Warning | Threshold for operating hours violated |

| Error | | | |
|----------------|-----------------|-----------------------------------|---|
| Code dec (hex) | Additional Code | Name | Remark [Unit] |
| 128 (0x80) | 17 (0x11) | Index not available | Read or write access attempt to a non-existing index. |
| 128 (0x80) | 18 (0x12) | Subindex not available | Read or write access attempt to a non-existing subindex of an existing index. |
| 128 (0x80) | 32 (0x20) | Service temporarily not available | Parameter not accessible due to the current state of the technology-specific application. |
| 128 (0x80) | 35 (0x23) | Access denied | Write access to a read-only parameter or read access to write-only parameter. |
| 128 (0x80) | 48 (0x30) | Parameter value out of range | Written parameter value is outside of the permitted value range. |
| 128 (0x80) | 51 (0x33) | Parameter length overrun | Written parameter is longer than specified. |
| 128 (0x80) | 52 (0x34) | Parameter length underrun | Written parameter is shorter than specified. |
| 128 (0x80) | 64 (0x40) | Invalid parameter set | Written single parameter value collides with other existing parameter settings. |
| 128 (0x80) | 65 (0x41) | Inconsistent parameter set | Parameter set inconsistencies at the end of block parameter transfer. Device plausibility check failed. |

¹ ro = read only, wo = write only, rw = read/write

² COM values specify the bitrate (see IO-Link specification): COM1 (4,8 kbit/s), COM2 (38,4 kbit/s), COM3 (230,4 kbit/s)

³ Subindex access not supported