



SICK

8028412 0323
9377070 0323

WTT4SLC_DID8389416

8389416

4074689436

9377064 0323 (1.1.0)

Australia Phone +61 3 9467 0800	Osterreich Phone +43 (0)22 36 62 28 8-0
Belgium/Luxembourg Phone +32 (0)2 468 35 66	Norge Phone +47 67 61 51 00
Brasil Phone +55 11 5215-4900	Polka Phone +48 22 837 40 50
Canada Phone +1 905 771 14 44	România Phone +40 356 171 120
China Phone +86 4000 121 000	Russia Phone +7 495 775 09 30
China Phone +86 21 5351 3300	Schweden Phone +46 18 41 619 29 39
Danmark Phone +45 45 82 64 00	Schwiz Phone +41 619 29 39
Deutschland Phone +49 211 5351 301	Slovenija Phone +386 (0)47 69 990
España Phone +34 93 480 31 00	South Korea Phone +82 2 786 632/4
France Phone +33 1 64 62 39 00	Spain Phone +358 9 25 15 800
Great Britain Phone +44 (0)1727 83121	Sri Lanka Phone +94 10 110 10 00
India Phone +91 22 4033 8333	Taiwan Phone +886 2 2375 4288
Israel Phone +972 4 6801000	Türkiye Phone +90 (216) 528 50 00
Italia Phone +39 02 27 43 41	United Arab Emirates Phone +971 (0) 4 5565 878
Japan Phone +81 (03) 5309 2112	USA/Mexico Phone +1 952 941 6780
Magnetsverige Phone +36 1 371 2680	
Niederland Phone +31 (0)30 229 25 44	

Please find detailed addresses and additional representatives and agencies in all major industrial nations at www.sick.com

8211463

More representatives and agencies at www.sick.com - Subject to change without notice - The specified product features and technical data do not represent any guarantee.

Weitere Niederlassungen finden Sie unter www.sick.com - Irrtümer und Änderungen vorbehalten - Angegebene Produkteigenschaften und technische Daten stellen keine Garantieerklärung dar.

Plus de représentations et d'agences à l'adresse www.sick.com - Sujet à modification sans préavis - Les caractéristiques de produit et techniques indiquées ne constituent pas de déclaration de garantie.

Para mais representantes e agências, consulte www.sick.com - Alterações poderão ser feitas sem prévio aviso - As características do produto e os dados técnicos apresentados não constituem declaração de garantia.


Flere repræsentanter og agenturer på www.sick.com - Med forbehold for ændringer og fejl - De angivne produktdata og tekniske data udgør ikke nogen garanti erklæring.

Altri rappresentanti ed agenzie si trovano su www.sick.com - Contenuti soggetti a modifiche senza preavviso - Le caratteristiche del prodotto e i dati tecnici non rappresentano una dichiarazione di garanzia.

Meer vestigingen en vertegenwoordigingen vindt u op www.sick.com - Wijzigingen en correcties voorbehouden - Aangegeven producteigenschappen en technische gegevens vormen geen garantieverklaring.

Más representantes y agencias en www.sick.com - Sujeto a cambio sin previo aviso - Las características y los datos técnicos especificados no constituyen ninguna declaración de garantía.

欲了解更多代表机构和代理商信息，请登录 www.sick.com - 如有更改，不另行通知 - 对所给出的产品特性和技术参数 的正确性不予保证。



Please note the validity of the additional operating instructions for automation functions

1. Physical layer

Note: The IO-Link Device's max. current consumption (inclusive load current) shall not exceed the master port's max. output power current.

SIO Modus	yes
Min Cycle Time	0.8 ms
Baudrate ²	COM3
Process Data Length (IN)	4 Byte
IODD version	V1.38954
Valid for IO-Link version	1.1.0

2. Process data

Record³: 4 Byte

Bitoffset																
Byte 0	31	30	29	28	27	26	25	24								
Type/Subindex	Unsigned Integer 16															
Bitoffset																
Byte 1	23	22	21	20	19	18	17	16								
Type/Subindex	Unsigned Integer 16															
Bitoffset																
Byte 2	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Type/Subindex	Boolean															
Bitoffset																
Byte 3	7	6	5	4	3	2	1	0	7	6	5	4	3	2	1	0
Type/Subindex	Boolean															

3. Service data

The following ISDUs will not be saved via Data-Storage: Profile characteristic, Teach-in channel, Teach-in state, Device / function name, Sender configuration, Temperature, Operating hours, Find me, System state, Distance to object and SLTI Version

IO-Link specific							
Index dec (hex)	Name	Format (Offset)	Length	Access ¹	Default Value	Value / Range	Remark [Unit]
0 (0x00)	Direct Parameters 1	Record	16 Byte	rw			
1 (0x01)	Direct Parameters 2	Record	16 Byte	rw			
12 (0x0C)	Device Access Locks	Record ³	2 Byte	rw			
2 (0x02)	Data Storage Lock	Bit (1)	1 Bit	rw			
4 (0x04)	Local User Interface Lock	Bit (3)	1 Bit	rw			
16 (0x10)	Vendor Name	String	7 Byte	ro	SICK AG		
18 (0x12)	Product Name	String	18 Byte	ro			
19 (0x13)	Product ID	String	13 Byte	ro			
20 (0x14)	Product Text	String	45 Byte	ro			
21 (0x15)	Serial Number	String	8 Byte	ro			
22 (0x16)	Hardware Version	String	4 Byte	ro			
23 (0x17)	Firmware Version	String	19 Byte	ro			
24 (0x18)	Application Specific Tag	String	32 Byte	rw	*****		
36 (0x24)	Device Status	UInt	8 Bit	ro		0 = Device is OK 1 = Maintenance required 2 = Out of specification 3 = Functional check 4 = Failure 5...255 = Reserved	
40 (0x28)	Process Data Input	PD In	4 Byte	ro			
SICK device specific							
Index dec (hex)	Name	Format (Offset)	Length	Access ¹	Default Value	Value / Range	Remark [Unit]
13 (0x0D)	Profile characteristic	Array ³	10 Byte	ro		Unsigned Integer16 [5]	
14 (0x0E)	PDInput descriptor	Array ³	6 Byte	ro		Octet String [2]	
15 (0x0F)	PDOutput Descriptor	Array ³	3 Byte	ro		Octet String [1]	

¹ ro = read only, wo = write only, rw = read/write

² COM values specify the bitrate (see IO-Link specification): COM1 (4,8 kbit/s), COM2 (38,4 kbit/s), COM3 (230,4 kbit/s)

³Subindex access not supported





SICK

8028412 0323
9377070 0323

WTT4SLC_DID8389416

8389416

4074689436

9377064 0323 (1.1.0)

Australia Phone +61 3 9457 0800	Osterreich Phone +43 (0)22 36 62 28 8-0
Belgium/Luxembourg Phone +32 (0)2 468 35 66	Norge Phone +47 67 61 51 50 00
Brasil Phone +55 11 5215-4900	Polka Phone +48 22 837 40 50
Canada Phone +1 905 771 14 44	România Phone +40 356 171 120
China Phone +86 4000 121 000	Russia Phone +7 495 775 05 30
Denmark Phone +45 45 82 64 00	Schweiz Phone +41 41 619 29 39
Deutschland Phone +49 211 5361 301	Sverige Phone +46 10 110 10 00
España Phone +34 93 480 31 00	Taiwan Phone +886 2 2375 6288
France Phone +33 1 64 62 39 00	Türkiye Phone +90 (216) 538 50 00
Great Britain Phone +44 (0)1727 831211	United Arab Emirates Phone +971 (0)4 5865 878
India Phone +91 22 4033 8333	USA/Mexico Phone +1 952 941 6780
Israel Phone +972 4 6801000	
Italy Phone +39 02 27 43 41	
Japan Phone +81 (03) 5309 2112	
Magyarország Phone +36 1 371 2680	
Niederland Phone +31 (0)30 229 25 44	

Please find detailed addresses and additional representatives and agencies in all major industrial nations at www.sick.com

8211463

More representatives and agencies at www.sick.com - Subject to change without notice - The specified product features and technical data do not represent any guarantee.

Weitere Niederlassungen finden Sie unter www.sick.com - Irrtümer und Änderungen vorbehalten! - Angegebene Produkteigenschaften und technische Daten stellen keine Garantieerklärung dar.

Plus de représentations et d'agences à l'adresse www.sick.com - Sujet à modification sans préavis - Les caractéristiques de produit et techniques indiquées ne constituent pas de déclaration de garantie.

Para mais representantes e agências, consulte www.sick.com - Alterações poderão ser feitas sem prévio aviso - As características do produto e os dados técnicos apresentados não constituem declaração de garantia.

Flere representanter og agenturer på www.sick.com - Med forbehold for ændringer og fejl - De arfærte produktagskaber og tekniske data udgør ikke nogen garantierklæring.

Altri rappresentanti ed agenzie si trovano su www.sick.com - Contenuti soggetti a modifiche senza preavviso - Le caratteristiche del prodotto e i dati tecnici non rappresentano una dichiarazione di garanzia.

Meer vestigingen en correcties voorbehouden - Aangegeven producteigenschappen en technische gegevens vormen geen garantieverklaring.

Más representantes y agencias en www.sick.com - Sujeto a cambio sin previo aviso - Las características y los datos técnicos especificados no constituyen ninguna declaración de garantía.

欲了解更多代表机构和代理商信息，请登录 www.sick.com - 如有更改，不另行通知 - 对所给出的产品特性和技术参数 的正确性不予保证。



Please note the validity of the additional operating instructions for automation functions

ENGLISH							
SICK device specific							
Index dec (hex)	Name	Format (Offset)	Length	Access ¹	Default Value	Value / Range	Remark [Unit]
58 (0x3A)	Teach-in channel	Uint	8 Bit	rw	0	0 = Qint1 1 = Qint1 2 = Qint2 3 = Qint3 4 = Qint4 5 = Qint5 6 = Qint6 7 = Qint7 8 = Qint8	
59 (0x3B)	Teach-in state	Record ³	1 Byte	ro			
1 (0x01)	Teach flag SP2	Bit (6)	1 Bit	ro		false = Teachpoint 1 not taught true = Teachpoint 1 successfully taught	
2 (0x02)	Teach flag SP1	Bit (4)	1 Bit	ro		false = Teachpoint 1 not taught true = Teachpoint 1 successfully taught	
3 (0x03)	Teach state	Bit (0)	4 Bit	ro		0 = IDLE 1 = SP1 SUCCESS 2 = SP2 SUCCESS 5 = BUSY 7 = ERROR	
60 (0x3C)	Qint.1 SP1 / SP2	Record	4 Byte	rw			
1 (0x01)	Qint.1 SP1 sensing range	Bit (16)	16 Bit	rw	400	0...65535	[mm]
2 (0x02)	Qint.1 SP2 sensing range	Bit (0)	16 Bit	rw	150	0...65535	[mm]
61 (0x3D)	Qint.1 configuration	Record	4 Byte	rw			
1 (0x01)	Qint.1 Switchpoint logic	Bit (24)	8 Bit	rw	0	0 = not inverted	
2 (0x02)	Qint.1 Switchpoint mode	Bit (16)	8 Bit	rw	1	0 = Deactivated 1 = Single point mode 2 = Window mode 3 = Two point mode	
3 (0x03)	Qint.1 Switchpoint hysteresis	Bit (0)	16 Bit	rw	0	0 = Vendor specific default	
62 (0x3E)	Qint.2 SP1 / SP2	Record	4 Byte	rw			
1 (0x01)	Qint.2 SP1 sensing range	Bit (16)	16 Bit	rw	200	0...65535	[mm]
2 (0x02)	Qint.2 SP2 sensing range	Bit (0)	16 Bit	rw	250	0...65535	[mm]
63 (0x3F)	Qint.2 configuration	Record	4 Byte	rw			
1 (0x01)	Qint.2 Switchpoint logic	Bit (24)	8 Bit	rw	0	0 = not inverted	
2 (0x02)	Qint.2 Switchpoint mode	Bit (16)	8 Bit	rw	1	0 = Deactivated 1 = Single point mode 2 = Window mode 3 = Two point mode	
3 (0x03)	Qint.2 Switchpoint hysteresis	Bit (0)	16 Bit	rw	0	0 = Vendor specific default	
64 (0x40)	Device / function name	String	32 Byte	rw	*****		
89 (0x59)	Measurement averaging	Uint	8 Bit	rw	0	0 = 1 1 = 2 2 = 4 3 = 8 4 = 16 5 = 32 6 = 64 7 = 128 8 = 256 9 = 512	
90 (0x5A)	Teach-in offset	Int	16 Bit	rw	0	-200...200	[mm]
97 (0x61)	Sender configuration	Uint	8 Bit	rw	0	0 = Sender active 1 = Sender not active	
121 (0x79)	Pin 2 configuration	Uint	8 Bit	rw	16	0 = Deactivated / no function 1 = External input (Smart Task) 16 = Sender off 17 = Teach-in 34 = Switching signal QL2 35 = Detection output Qint.1 36 = Detection output Qint.2 39 = Switching signal QL1 40 = Switching signal QL1/	
153 (0x99)	Temperature	Record ³	1 Byte	ro			
1 (0x01)	Current temperature	Bit (0)	8 Bit	ro		-127...127	Sensor-internal temperature [°C]
190 (0xBE)	Operating hours	Record ³	4 Byte	ro			
1 (0x01)	Total operating hours	Bit (0)	32 Bit	ro		0...1000000	[h]

¹ro = read only, wo = write only, rw = read/write
²COM values specify the bitrate (see IO-Link specification): COM1 (4,8 kbit/s), COM2 (38,4 kbit/s), COM3 (230,4 kbit/s)
³Subindex access not supported





SICK

8028412 0323
9377070 0323

WTT4SLC_DID8389416

8389416

4074689436

9377064 0323 (1.1.0)

Australia Phone +61 3 9457 0800	Osterreich Phone +43 (0)22 36 62 28 9-0
Belgium/Luxembourg Phone +32 (0)2 468 55 66	Norge Phone +47 67 61 50 00
Brasil Phone +55 11 5215-4900	Polka Phone +48 22 837 40 50
Canada Phone +1 905 771 14 44	România Phone +40 356 171 120
China (peoples) Phone +86 4000 121 000 +852 2553 6300	Russia Phone +7 495 775 09 30
Denmark Phone +45 45 82 64 00	Schweden Phone +46 8 744 3732
Deutschland Phone +49 211 5361 301	Slovenija Phone +386 (0)147 69 990
España Phone +34 93 480 31 00	South Korea Phone +82 2 786 6321/4
France Phone +33 1 64 62 39 00	Spain Phone +358 9 25 15 800
Great Britain Phone +44 (0)1727 831121	Sverige Phone +46 10 110 10 00
India Phone +91 22 4033 8333	Taiwan Phone +886 2 2375 4288
Israel Phone +972 4 6801000	Türkiye Phone +90 (216) 538 50 00
Italy Phone +39 02 27 43 41	United Arab Emirates Phone +971 (0)4 5855 878
Japan Phone +81 (03) 5309 2112	USA/Mexico Phone +1 952 941 6780
Magnesium Phone +36 1 371 2680	
Niederland Phone +31 (0)30 229 25 44	

SICK AG, Erwin-Sick-Strasse 1, D.79183 Waldkirch

Please find detailed addresses and additional representatives and agencies in all major industrial nations at www.sick.com

8211483

More representatives and agencies at www.sick.com - Subject to change without notice - The specified product features and technical data do not represent any guarantee.

Weitere Niederlassungen finden Sie unter www.sick.com - Irrtümer und Änderungen vorbehalten - Angegebene Produkteigenschaften und technische Daten stellen keine Garantieerklärung dar.

Plus de représentations et d'agences à l'adresse www.sick.com - Sujet à modification sans préavis - Les caractéristiques de produit et techniques indiquées ne constituent pas de déclaration de garantie.

Para mais representantes e agências, consulte www.sick.com - Alterações poderão ser feitas sem prévio aviso - As características do produto e os dados técnicos apresentados não constituem declaração de garantia.

Flere repræsentanter og agenturer på www.sick.com - Med forbehold for ændringer og fejl - De angivne produkttegnelser og tekniske data udgør ikke nogen garantierklæring.

Altri rappresentanti ed agenzie si trovano su www.sick.com - Contenuti soggetti a modifiche senza preavviso - Le caratteristiche del prodotto e i dati tecnici non rappresentano una dichiarazione di garanzia.

Meer vestigingen en correcties voorbehouden - Aangegeven producteigenschappen en technische gegevens vormen geen garantieverklaring.

Más representantes y agencias en www.sick.com - Sujeto a cambio sin previo aviso - Las características y los datos técnicos especificados no constituyen ninguna declaración de garantía.

欲了解更多代表机构和代理商信息，请登录 www.sick.com - 如有更改，不另行通知 - 对所给出的产品特性和技术参数正确性不予保证。



Please note the validity of the additional operating instructions for automation functions

ENGLISH

SICK device specific							
Index dec (hex)	Name	Format (Offset)	Length	Access ¹	Default Value	Value / Range	Remark [Unit]
204 (0xCC)	Find me	UInt	8 Bit	rw	0	0 = Find me deactivated 1 = Find me activated	
205 (0xCD)	SICK profile version	String	4 Byte	ro			
219 (0xDB)	Article No.	Record	7 Byte	ro			
1 (0x01)	Article No. IO-Link Device	Bit (0)	7 Byte	ro			
226 (0xE2)	System state	Record ³	2 Byte	ro			
1 (0x01)	Input signal state Pin 2	Bit (7)	1 Bit	ro		false = External input LOW true = External input HIGH	
227 (0xE3)	Notification handling	UInt	8 Bit	rw	0	0 = All enabled 1 = All disabled 2 = Events enabled, PD invalid flag disabled 3 = Events disabled, PD invalid flag enabled	
229 (0xE5)	Distance to object	Record ³	3 Byte	ro			
1 (0x01)	Distance	Bit (8)	16 Bit	ro		0...30000	[mm]
2 (0x02)	Distance qualifier	Bit (0)	2 Bit	ro		0 = Distance in range 1 = Distance over-run 2 = Distance under-run 3 = No distance information	
1080 (0x438)	SLTI Version	String	8 Byte	ro			
1081 (0x439)	Input selector 1	UInt	8 Bit	rw	0	0 = Qint.1 1 = Qint.2 2 = Qint.3 3 = Qint.4 4 = Qint.5 5 = Qint.6 6 = Qint.7 7 = Qint.8 64 = Ext.input 1	
1082 (0x43A)	Input selector 2	UInt	8 Bit	rw	1	0 = Qint.1 1 = Qint.2 2 = Qint.3 3 = Qint.4 4 = Qint.5 5 = Qint.6 6 = Qint.7 7 = Qint.8 64 = Ext.input 1	
1083 (0x43B)	Logic 1	UInt	8 Bit	rw	0	0 = DIRECT 1 = AND 2 = OR 3 = Window Mode 4 = Hysteresis	
1084 (0x43C)	Logic 2	UInt	8 Bit	rw	0	0 = DIRECT 1 = AND 2 = OR 3 = Window Mode 4 = Hysteresis	
1085 (0x43D)	Timer 1 Mode	UInt	8 Bit	rw	0	0 = deactivated 1 = T-on delay 2 = T-off delay 3 = T-on/T-off delay 4 = Impulse (one shot)	
1086 (0x43E)	Timer 2 Mode	UInt	8 Bit	rw	0	0 = deactivated 1 = T-on delay 2 = T-off delay 3 = T-on/T-off delay 4 = Impulse (one shot)	
1087 (0x43F)	Time 1 Setup	UInt	16 Bit	rw	1	1...30000	[ms]
1088 (0x440)	Time 2 Setup	UInt	16 Bit	rw	1	1...30000	[ms]
1089 (0x441)	Inverter 1	UInt	8 Bit	rw	1	0 = not inverted 1 = inverted	
1090 (0x442)	Inverter 2	UInt	8 Bit	rw	0	0 = not inverted 1 = inverted	
1093 (0x445)	Inverter Ext.input	UInt	8 Bit	rw	0	0 = not inverted 1 = inverted	
16384 (0x4000)	Qint.3 SP1 / SP2	Record	4 Byte	rw			
1 (0x01)	Qint.3 SP1 sensing range	Bit (16)	16 Bit	rw	300	0...65535	[mm]
2 (0x02)	Qint.3 SP2 sensing range	Bit (0)	16 Bit	rw	350	0...65535	[mm]
16385 (0x4001)	Qint.3 configuration	Record	4 Byte	rw			

¹ro = read only, wo = write only, rw = read/write

²COM values specify the bitrate (see IO-Link specification): COM1 (4,8 kbit/s), COM2 (38,4 kbit/s), COM3 (230,4 kbit/s)

³Subindex access not supported





SICK

8028412 0323
9377070 0323

WTT4SLC_DID8389416

8389416

4074689436

9377064 0323 (1..1.0)

Australia Phone +61 3 9457 0800	Osterreich Phone +43 (0)22 36 62 28 8-0
Belgium/Luxembourg Phone +32 (0)2 468 35 66	Norge Phone +47 67 61 50 00
Brasil Phone +55 11 3215-9900	Polka Phone +48 22 837 40 50
Canada Phone +1 905 771 14 44	România Phone +40 356 171 120
China Phone +86 4000 121 000	Russia Phone +7 495 775 05 30
China Phone +86 21 57 91 18 50	Schweiz Phone +41 41 619 29 39
China Phone +86 21 57 91 18 50	Singapore Phone +65 6744 3732
Danmark Phone +45 45 82 64 00	Slovenija Phone +386 (0)147 69 990
Deutschland Phone +49 211 5361 301	South Korea Phone +82 2 786 6321/4
España Phone +34 93 480 31 00	Spain Phone +358 9 25 15 800
France Phone +33 1 64 62 39 00	Sri Lanka Phone +91 10 110 10 00
Great Britain Phone +44 (0)1277 83121	Taiwan Phone +886 2 2375 6288
India Phone +91 22 4033 8333	Türkiye Phone +90 (216) 538 50 00
Italy Phone +39 02 27 43 41	United Arab Emirates Phone +971 (0)4 5855 878
Japan Phone +81 (03) 5309 2112	USA/Mexico Phone +1 950 941 61780
Magnetsville Phone +36 1 371 2680	
Niederland Phone +31 (0)30 229 25 44	
SICK AG, Erwin-Sick-Strasse 1, D.79183 Waldkirch	

Please find detailed addresses and additional representatives and agencies in all major industrial nations at www.sick.com

8211463

More representatives and agencies at www.sick.com - Subject to change without notice - The specified product features and technical data do not represent any guarantee.

Weitere Niederlassungen finden Sie unter www.sick.com - Irrtümer und Änderungen vorbehalten! - Angegebene Produkteigenschaften und technische Daten stellen keine Garantieerklärung dar.

Plus de représentations et d'agences à l'adresse www.sick.com - Sujet à modification sans préavis - Les caractéristiques de produit et techniques indiquées ne constituent pas de déclaration de garantie.

Para mais representantes e agências, consulte www.sick.com - Alterações poderão ser feitas sem prévio aviso - As características do produto e os dados técnicos apresentados não constituem declaração de garantia.

Flere representanter og agenturer på www.sick.com - Med forbehold for ændringer og fejl - De angivne produktdata og tekniske data udgør ikke nogen garantierklæring.

Altri rappresentanti ed agenzie si trovano su www.sick.com - Contenuti soggetti a modifiche senza preavviso - Le caratteristiche del prodotto e i dati tecnici non rappresentano una dichiarazione di garanzia.

Meer vestigingen en vertegenwoordigingen vindt u op www.sick.com - Wijzigingen en correcties voorbehouden - Aangegeven producteigenschappen en technische gegevens vormen geen garantieverklaring.

Más representantes y agencias en www.sick.com - Sujeto a cambio sin previo aviso - Las características y los datos técnicos especificados no constituyen ninguna declaración de garantía.

欲了解更多代表机构和代理商信息，请登录 www.sick.com - 如有更改，不另行通知 - 对所给出的产品特性和技术参数，其正确性不予保证。



Please note the validity of the additional operating instructions for automation functions

ENGLISH

SICK device specific							
Index dec (hex)	Name	Format (Offset)	Length	Access ¹	Default Value	Value / Range	Remark [Unit]
1 (0x01)	Qint.3 Switchpoint logic	Bit (24)	8 Bit	rw	0	0 = not inverted	
2 (0x02)	Qint.3 Switchpoint mode	Bit (16)	8 Bit	rw	1	0 = Deactivated 1 = Single point mode 2 = Window mode 3 = Two point mode	
3 (0x03)	Qint.3 Switchpoint hysteresis	Bit (0)	16 Bit	rw	0	0 = Vendor specific default	
16386 (0x4002)	Qint.4 SP1 / SP2	Record	4 Byte	rw			
1 (0x01)	Qint.4 SP1 sensing range	Bit (16)	16 Bit	rw	400	0...65535	[mm]
2 (0x02)	Qint.4 SP2 sensing range	Bit (0)	16 Bit	rw	450	0...65535	[mm]
16387 (0x4003)	Qint.4 configuration	Record	4 Byte	rw			
1 (0x01)	Qint.4 Switchpoint logic	Bit (24)	8 Bit	rw	0	0 = not inverted	
2 (0x02)	Qint.4 Switchpoint mode	Bit (16)	8 Bit	rw	1	0 = Deactivated 1 = Single point mode 2 = Window mode 3 = Two point mode	
3 (0x03)	Qint.4 Switchpoint hysteresis	Bit (0)	16 Bit	rw	0	0 = Vendor specific default	
16388 (0x4004)	Qint.5 SP1 / SP2	Record	4 Byte	rw			
1 (0x01)	Qint.5 SP1 sensing range	Bit (16)	16 Bit	rw	500	0...65535	[mm]
2 (0x02)	Qint.5 SP2 sensing range	Bit (0)	16 Bit	rw	550	0...65535	[mm]
16389 (0x4005)	Qint.5 configuration	Record	4 Byte	rw			
1 (0x01)	Qint.5 Switchpoint logic	Bit (24)	8 Bit	rw	0	0 = not inverted	
2 (0x02)	Qint.5 Switchpoint mode	Bit (16)	8 Bit	rw	1	0 = Deactivated 1 = Single point mode 2 = Window mode 3 = Two point mode	
3 (0x03)	Qint.5 Switchpoint hysteresis	Bit (0)	16 Bit	rw	0	0 = Vendor specific default	
16390 (0x4006)	Qint.6 SP1 / SP2	Record	4 Byte	rw			
1 (0x01)	Qint.6 SP1 sensing range	Bit (16)	16 Bit	rw	600	0...65535	[mm]
2 (0x02)	Qint.6 SP2 sensing range	Bit (0)	16 Bit	rw	650	0...65535	[mm]
16391 (0x4007)	Qint.6 configuration	Record	4 Byte	rw			
1 (0x01)	Qint.6 Switchpoint logic	Bit (24)	8 Bit	rw	0	0 = not inverted	
2 (0x02)	Qint.6 Switchpoint mode	Bit (16)	8 Bit	rw	1	0 = Deactivated 1 = Single point mode 2 = Window mode 3 = Two point mode	
3 (0x03)	Qint.6 Switchpoint hysteresis	Bit (0)	16 Bit	rw	0	0 = Vendor specific default	
16392 (0x4008)	Qint.7 SP1 / SP2	Record	4 Byte	rw			
1 (0x01)	Qint.7 SP1 sensing range	Bit (16)	16 Bit	rw	700	0...65535	[mm]
2 (0x02)	Qint.7 SP2 sensing range	Bit (0)	16 Bit	rw	750	0...65535	[mm]
16393 (0x4009)	Qint.7 configuration	Record	4 Byte	rw			
1 (0x01)	Qint.7 Switchpoint logic	Bit (24)	8 Bit	rw	0	0 = not inverted	
2 (0x02)	Qint.7 Switchpoint mode	Bit (16)	8 Bit	rw	1	0 = Deactivated 1 = Single point mode 2 = Window mode 3 = Two point mode	
3 (0x03)	Qint.7 Switchpoint hysteresis	Bit (0)	16 Bit	rw	0	0 = Vendor specific default	
16394 (0x400A)	Qint.8 SP1 / SP2	Record	4 Byte	rw			
1 (0x01)	Qint.8 SP1 sensing range	Bit (16)	16 Bit	rw	800	0...65535	[mm]
2 (0x02)	Qint.8 SP2 sensing range	Bit (0)	16 Bit	rw	850	0...65535	[mm]
16395 (0x400B)	Qint.8 configuration	Record	4 Byte	rw			
1 (0x01)	Qint.8 Switchpoint logic	Bit (24)	8 Bit	rw	0	0 = not inverted	
2 (0x02)	Qint.8 Switchpoint mode	Bit (16)	8 Bit	rw	1	0 = Deactivated 1 = Single point mode 2 = Window mode 3 = Two point mode	
3 (0x03)	Qint.8 Switchpoint hysteresis	Bit (0)	16 Bit	rw	0	0 = Vendor specific default	

¹ro = read only, wo = write only, rw = read/write
²COM values specify the bitrate (see IO-Link specification): COM1 (4,8 kbit/s), COM2 (38,4 kbit/s), COM3 (230,4 kbit/s)
³Subindex access not supported





SICK

8028412 0323
9377070 0323
WTT4SLC_DID8389416
8389416
4074689436
9377064 0323 (1.1.0)

Australia Phone +61 3 9457 0800	Osterreich Phone +43 (0)22 36 62 28 8-0
Belgium/Luxembourg Phone +32 (0)2 468 55 66	Norge Phone +47 67 61 50 00
Brasil Phone +55 11 5215-4900	Polka Phone +48 22 837 40 50
Canada Phone +1 905 771 14 44	România Phone +40 356 171 120
China Phone +86 4000 121 000 +8622353 6300	Russia Phone +7 495 775 09 30
Denmark Phone +45 45 82 64 00	Schweiz Phone +41 41 619 29 39
Deutschland Phone +49 211 5301 301	Slovenija Phone +386 (0)147 69 990
España Phone +34 93 480 31 00	South Korea Phone +82 2 786 6321/4
France Phone +33 1 64 62 39 00	Suomi Phone +358 9 25 15 800
Great Britain Phone +44 (0)1727 831521	Sverige Phone +46 10 110 10 00
India Phone +91 22 4033 8333	Taiwan Phone +886 2 2375 6288
Israel Phone +972 4 6801000	Türkiye Phone +90 (216) 528 50 00
Italy Phone +39 02 27 43 41	United Arab Emirates Phone +971 (0)4 5865 878
Japan Phone +81 (03) 5309 2112	USA/Mexico Phone +1 950 941 6780
Magyarország Phone +36 1 371 2680	
Niederland Phone +31 (0)30 229 25 44	

SICK AG, Erwin-Sick-Strasse 1, D 79183 Waldkirch

Please find detailed addresses and additional representatives and agencies in all major industrial nations at www.sick.com

8211463

More representatives and agencies at www.sick.com - Subject to change without notice - The specified product features and technical data do not represent any guarantee.

Weitere Niederlassungen finden Sie unter www.sick.com - Irrtümer und Änderungen vorbehalten - Angegebene Produkteigenschaften und technische Daten stellen keine Garantieerklärung dar.

Plus de représentations et d'agences à l'adresse www.sick.com - Sujet à modification sans préavis - Les caractéristiques de produit et techniques indiquées ne constituent pas de déclaration de garantie.

Para mais representantes e agências, consulte www.sick.com - Alterações poderão ser feitas sem prévio aviso - As características do produto e os dados técnicos apresentados não constituem declaração de garantia.

Flere repræsentanter og agenturer på www.sick.com - Med forbehold for ændringer og fejl - De anførte produktdata og tekniske data udgør ikke nogen garantierklæring.

Altri rappresentanti ed agenzie si trovano su www.sick.com - Contenuti soggetti a modifiche senza preavviso - Le caratteristiche del prodotto e i dati tecnici non rappresentano una dichiarazione di garanzia.

Meer vestigingen en vertegenwoordigingen vindt u op www.sick.com - Wijzigingen en correcties voorbehouden - Aangegeven producteigenschappen en technische gegevens vormen geen garantieverklaring.

Más representantes y agencias en www.sick.com - Sujeto a cambio sin previo aviso - Las características y los datos técnicos especificados no constituyen ninguna declaración de garantía.

欲了解更多代表机构和代理商信息，请登录 www.sick.com - 如有更改，不另行通知 - 对所给出的产品特性和技术参数的正确性不予保证。



Please note the validity of the additional operating instructions for automation functions

ENGLISH

Standard command					
Index dec (hex)		Access ¹	Value	Name	Remark [Unit]
2 (0x02)	Standard Command	wo	65	Single value teach SP1	
			66	Single value teach SP2	
			130	Restore Factory Settings	

Events					
Code dec (hex)	Name	Type		Remark [Unit]	
16912 (0x4210)	Device temperature over-run	Warning		Temperature is over specification	
16928 (0x4220)	Device temperature under-run	Warning		Temperature is under specification	
36000 (0x8CA0)	Short Circuit on Qx	Notification		Short circuit on outputs	
36001 (0x8CA1)	New parameters	Notification		Parameters have been changed	
36005 (0x8CA5)	Teach / value out of specified range	Notification		Teach / distance value out of specified range	
36006 (0x8CA6)	Value out of specified range	Notification		Setup value out of specified range	

Error					
Code dec (hex)	Additional Code	Name		Remark [Unit]	
128 (0x80)	17 (0x11)	Index not available		Access occurs to a not existing index	
128 (0x80)	18 (0x12)	Subindex not available		Access occurs to a not existing subindex	
128 (0x80)	32 (0x20)	Service temporarily not available		Parameter is not accessible due to the current state of the device application	
128 (0x80)	35 (0x23)	Access denied		Write access on a read-only parameter	
128 (0x80)	48 (0x30)	Parameter value out of range		Written parameter value is outside its permitted value range	
128 (0x80)	51 (0x33)	Parameter length overrun		Written parameter length is above its predefined length	
128 (0x80)	52 (0x34)	Parameter length underrun		Written parameter length is below its predefined length	
128 (0x80)	64 (0x40)	Invalid parameter set		Written single parameter collides with other actual parameter settings	
128 (0x80)	65 (0x41)	Inconsistent parameter set		Parameter inconsistencies were found at the end of block parameter transfer, device plausibility check failed	