

ARS60 Reliable and established







Technical data overview

Technical data overview	
Encoder design	Singleturn
Shaft type	Solid shaft, Servo flange Solid shaft, face mount flange Blind hollow shaft Through hollow shaft
Shaft diameter	
Solid shaft, Servo flange	6 mm
Solid shaft, face mount flange	10 mm
Blind hollow shaft	15 mm ¹⁾
Through hollow shaft	12 mm ²⁾
Connection type	Male connector, M23, 12-pin, radial Male connector, M23, 12-pin, axial Cable, 11-wire, radial Cable, 11-wire, axial Male connector, M23, 21-pin, radial Male connector, M23, 21-pin, axial Cable, 22-wire, radial Cable, 22-wire, axial
Communication interface	SSI / parallel data world (depending on type)
Number of steps per revolution (max. resolution) SSI, non programmable	360 2,880 720 1,024 (10 bit) 1,892 2,048 (11 bit) 3,600 4,096 (12 bit) 5,000 7,200 8,129 8,192 (13 bit) 10,000 16,384 (14 bit) 18,000 21,600 32,767 32,768 (15 bit) 512 (9 bit) 256 (8 bit) 72 1,000 1,440 4,000 14,400 2,000 8,640 9,192 9,360 12,800 18,080 28,800 32,000

 $^{^{1)}}$ Collets for 6, 8, 10, 12, 14 mm and 1/4", 3/8" and 1/2" as accessories, separate order item. For 15 mm shaft diameter collet is not needed. $^{2)}$ 12 mm requires the corresponding collet, this and other collets for 6, 8, 10 mm as well as 1/4", 3/8" and 1/2" need to be ordered separately as accessories.

 $^{^{}m 3)}$ With mating connector fitted.

```
32,400
                                   32,766
                                   500
                                   6,000
                                   7,400
                                   200
                                   4,320
                                   10
                                   1,576
                                   30,000
                                   8,196
                                   36
                                   25,000
                                   1,638
                                   4,086
                                   9,000
                                   24,576
                                   28,672
                                   22,528
Parallel data world, non programmable
                                   800
                                   2,880
                                   9
                                   360
                                   256 (8 bit)
                                   1,024 (10 bit)
                                   512 (9 bit)
                                   2,000
                                   4,096 (12 bit)
                                   500
                                   5,000
                                   720
                                   8,192 (13 bit)
                                   32,768 (15 bit)
                                   2,048 (11 bit)
                                   3,600
                                   10,000
                                   32,767
                                   15
                                   16,384 (14 bit)
                                   64 (6 bit)
                                   1,000
                                   7,200
                                   860
                                   2,500
                                   18,000
                                   8 (3 bit)
                                   12
                                   6,017
                                   1,440
                                   1,375
                                   18
                                   48
                                   24
                                   120
                                   34
                                   128 (7 bit)
                                   100
                                   180
                                   400
                                   454
                                   452
                                   8,100
                                   11,520
```

 $^{^{1)}}$ Collets for 6, 8, 10, 12, 14 mm and $^{1/4}$ ", $^{3/8}$ " and $^{1/2}$ " as accessories, separate order item. For 15 mm shaft diameter collet is not needed.

 $^{^{2)}}$ 12 mm requires the corresponding collet, this and other collets for 6, 8, 10 mm as well as $^{1/4}$ ", $^{3/8}$ " and $^{1/2}$ " need to be ordered separately as accessories.

³⁾ With mating connector fitted.

	1,360 4,090 7,920 576 3,621 2,534 4,000 14,400 10,240 19 200 72 232 8,000 8 7,999 40 16 42 2,280 2,400 24,000 36 5,760 5,808 21,600
Max. resolution (number of steps per revolu-	49 144 900 60 54 78 1,924 22,800
tion x number of revolutions)	-20 °C +85 °C
Operating temperature range Enclosure rating	-20 °C +85 °C
Enclosure fatting	(IEC 60529) Male connector ³⁾ IP66 (IEC 60529) Cable IP64 (IEC 60529) Male connector ³⁾ IP64 (IEC 60529) Cable

 $^{^{1)}}$ Collets for 6, 8, 10, 12, 14 mm and $^{1/4}$ ", $^{3/8}$ " and $^{1/2}$ " as accessories, separate order item. For 15 mm shaft diameter collet is not needed.

Product description

The modular setup of its CoreTech technology enables the compact ARS60 absolute singleturn encoder to provide a customized solution for all applications. All common mechanical variants are available with any number of increments between 2 and 32,768 and are either equipped with an SSI or parallel output, making the ARS60 a universal solution for nearly any application requirements

 $^{^{2)}}$ 12 mm requires the corresponding collet, this and other collets for 6, 8, 10 mm as well as $^{1/4}$ ", $^{3/8}$ " and $^{1/2}$ " need to be ordered separately as accessories.

³⁾ With mating connector fitted.

At a glance

- Absolute singleturn encoder
- Resolution: up to 15 bits (32,768 increments)
- Electrical interface: SSI with gray code type or gray capped
- Electrical interface: Parallel with gray, gray capped, binary, BCD code type
- · Zero-set function
- Mechanical interfaces: face mount flange, servo flange, blind and through hollow shaft
- Enclosure rating: Up to IP66

Your benefits

- Freely programmable resolution (up to 15 bits)
- Easy zero adjustment directly on the encoder by pressing a button or via sub cable (cable version)
- Suitable for all mounting methods thanks to the individual mechanical interfaces
- A versatile base model thanks to the easily exchangeable collets for the blind hollow shaft and through hollow shaft
- Versions with cable and M23 connector connection in axial and radial designs available


Fields of application

- · Electronics and solar industries
- · Textile machinery
- · Packaging industry
- · High-bay warehouses
- · Woodworking machines
- · Machine construction
- · Automotive industry
- · Material handling

Type code


Other models and accessories → www.sick.com/ARS60

Solid shaft



 $^{^{1)}}$ Communication interface J: Increments per revolution 2 \dots 7999 possible.

Hollow shaft



 $^{^{2)}}$ Communication interface A, B, F, G and H: Increments per revolution 2 ... 32768 possible.

¹⁾ Order collets for 6, 8, 10, 12 and 14 mm as well as 1/4", 3/8" and 1/2" extra as accessories (see recommended accessories). No collets are necessary for 15 mm shaft diameter.

²⁾ Order collets for 6, 8, 10 and 12 mm as well as 1/4", 3/8" and 1/2" extra as accessories (see recommended accessories). No collets are necessary for 15 mm shaft diameter.

 $^{^{}m 3)}$ Only for blind hollow shaft mechanical version.

 $^{^{\}rm 4)}$ Communication interface J: Increments per revolution 2 ... 7,999 possible.

 $^{^{5)}}$ Communication interface A, B, F, G and H: Increments per revolution 2 \dots 32768 possible.

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

