

IMC

Four times the switching capability with inductive intelligence





Technical data overview

recrimed data overview	
Housing	Cylindrical thread design / rectangular (depending on type)
Thread size	M8 x 1 M12 x 1 M18 x 1 M30 x 1.5
Dimensions	10 mm x 28 mm x 16 mm 12 mm x 40 mm x 26 mm
Diameter	Ø 8 mm Ø 30 mm (depending on type)
Sensing range S _n	2 mm 20 mm (depending on type)
Housing material	Stainless steel V2A / plastic (depending on type)
Enclosure rating	IP68 / IP69K / IP68 (depending on type)

Product description

The inductive, intelligent, and, thanks to IO-Link 1.1, communication-enabled IMC proximity sensors offer a whole host of new options to make handling applications easier and more reliable in every industry. Up to four individual switching points or windows including the hysteresis can be set. Equipped with two freely programmable switching end stages, an IMC can therefore replace several conventional devices. Adjustable switch-on and switch-off delays help to reliably suppress unwanted switching pulses in harsh environments. The additional on-board functions, such as logic modules, temperature measurement, counters, or time measurement enable complex tasks to be completed with ease directly in the sensor.

At a glance

- Types: M8 to M30; IQ10 and IQ12
- Four programmable switching points or windows at an Sn of up to 20 mm
- Freely programmable output function
- Enclosure rating: IP 68, IP 69K
- Temperature range: -40 °C to +75 °C
- Rugged stainless-steel or VISTAL housing
- · Logic, counter, time measurement, or temperature monitoring function
- IO-Link 1.1

Your benefits

- Advanced diagnostic options ensure stable processes
- Programmable switching thresholds and windows make predictive maintenance easier and reduce machine downtimes
- · Switching point teaching enables precise object positioning without the need for time-consuming adjustment
- Reduced costs as fewer sensors or sensor variants are required
- Stable signals thanks to integrated debounce function
- Reduced project planning and cabling work as complex tasks are easy to implement directly in the process
- Future-proof thanks to IO-Link 1.1 communication

Fields of application

- · Open and closed position on valves and grippers with just one sensor
- · Component wear monitoring
- · Distinguishing between materials in the machine tools industry
- Distinguishing between objects in the handling industry
- · Monitoring of industrial brakes
- · Precise stopping in the handling industry
- · Quality control in mechanical production

Ordering information

Other models and accessories → www.sick.com/IMC

• Sub product family: IMC08

• Sensing range S_n: 0 mm ... 2 mm (Adjustable.)

Cylindrical thread design: M8
Switching output: PNP
Installation type: flush
Output function: NC, NO

• Special features: Smart Task, Resistant against coolant lubricants, IO-Link

• Electrical wiring: DC 4-wire

• Connection type: male connector M12, 4-pin (With gold plated contact pins.)

Smart Sensor	Туре	Part no.
Enhanced Sensing (Counter + debouncing) Efficient communication Diagnosis Smart Task	IMC08-02BP- PVC0SA71	1079282
Enhanced Sensing (Time measurement + debouncing) Efficient communication Diagnosis Smart Task	IMC08-02BP- PVC0SA70	1079281
Enhanced Sensing (base logics) Efficient communication Diagnosis Smart Task	IMC08-02BP- PVC0SA00	1079280

• Sub product family: IMC08

• Sensing range S_n: 0 mm ... 4 mm (Adjustable.)

Cylindrical thread design: M8
Switching output: PNP
Installation type: non-flush
Output function: NC, NO

• Special features: Smart Task, Resistant against coolant lubricants, IO-Link

• Electrical wiring: DC 4-wire

• Connection type: male connector M12, 4-pin (With gold plated contact pins.)

Smart Sensor	Туре	Part no.
Enhanced Sensing (Counter + debouncing) Efficient communication Diagnosis Smart Task	IMC08- 04NPPVC0SA71	1079285
Enhanced Sensing (Time measurement + debouncing) Efficient communication Diagnosis Smart Task	IMCO8- 04NPPVCOSA70	1079284
Enhanced Sensing (base logics) Efficient communication Diagnosis Smart Task	IMC08- 04NPPVC0SA00	1079283

• Sensing range S_n : 0 mm ... 4 mm (Adjustable, with fixed offset.)

• Cylindrical thread design: M12

• Switching output: PNP

lr	stallation type	Output function	Special features	Electrical wiring	Connection type	Туре	Part no.
	Flush	NO	IO-Link	DC 4-wire	Male connector M12, 4-pin ¹⁾	IMC12-04BP- PVC0SB02	1097434

 $^{^{1)}}$ With gold plated contact pins.

• Sub product family: IMC12

• Sensing range S_n: 0 mm ... 4 mm (Adjustable.)

• Cylindrical thread design: M12

Switching output: PNP
Installation type: flush
Output function: NC, NO

• Special features: Smart Task, Resistant against coolant lubricants, IO-Link

• Electrical wiring: DC 4-wire

• Connection type: male connector M12, 4-pin (With gold plated contact pins.)

Smart Sensor	Туре	Part no.
Enhanced Sensing (Counter + debouncing) Efficient communication Diagnosis Smart Task	IMC12-04BP- PVC0SA71	1079288
Enhanced Sensing (Time measurement + debouncing) Efficient communication Diagnosis Smart Task	IMC12-04BP- PVC0SA70	1079287
Enhanced Sensing (base logics) Efficient communication Diagnosis Smart Task	IMC12-04BP- PVCOSA00	1079286

• Sub product family: IMC12

• Sensing range S_n: 0 mm ... 8 mm (Adjustable.)

Cylindrical thread design: M12Switching output: PNP

Installation type: non-flushOutput function: NC, NO

• Special features: Smart Task, Resistant against coolant lubricants, IO-Link

• Electrical wiring: DC 4-wire

• Connection type: male connector M12, 4-pin (With gold plated contact pins.)

Smart Sensor	Туре	Part no.
Enhanced Sensing (Counter + debouncing) Efficient communication Diagnosis Smart Task	IMC12- 08NPPVC0SA71	1079291
Enhanced Sensing (Time measurement + debouncing) Efficient communication Diagnosis Smart Task	IMC12- 08NPPVC0SA70	1079290

Smart Sensor	Туре	Part no.
Enhanced Sensing (base logics) Efficient communication	IMC12- 08NPPVC0SB00	1093141
Diagnosis Smart Task	IMC12- 08NPPVC0SA00	1079289

• Sensing range S_n : 0 mm ... 8 mm (Adjustable.)

• Cylindrical thread design: M18

Switching output: PNP
Installation type: quasi-flush
Output function: NC, NO

• Special features: Smart Task, Resistant against coolant lubricants, IO-Link

• Electrical wiring: DC 4-wire

• Connection type: male connector M12, 4-pin (With gold plated contact pins.)

Smart Sensor	Туре	Part no.
Enhanced Sensing (Counter + debouncing) Efficient communication Diagnosis Smart Task	IMC18-08BP- PVC0SA71	1079294
Enhanced Sensing (Time measurement + debouncing) Efficient communication Diagnosis Smart Task	IMC18-08BP- PVC0SA70	1079293
Enhanced Sensing (base logics) Efficient communication Diagnosis Smart Task	IMC18-08BP- PVC0SA00	1079292

 $\bullet \ \, \textbf{Sub product family:} \ \, \textbf{IMC18}$

• Sensing range S_n: 0 mm ... 12 mm (Adjustable. Teaching outside of the value range is not permitted since hysteresis and temperature drift can no longer be kept.)

• Cylindrical thread design: M18

Switching output: PNP
 Installation type: non-flush
 Output function: NC, NO

Special features	Electrical wiring	Connection type	Smart Sensor	Туре	Part no.
Smart Task, Resistant against coolant lubricants, IO-Link	DC 4-wire	Male connector M12, 4-pin ¹⁾	Enhanced Sens- ing (base logics) Efficient communication Diagnosis Smart Task	IMC18- 12NPPVC0SB00	1093167

 $^{^{1)}}$ With gold plated contact pins.

• Sensing range S_n: 0 mm ... 12 mm (Adjustable.)

• Cylindrical thread design: M18

Switching output: PNP
 Installation type: non-flush
 Output function: NC, NO

• Special features: Smart Task, Resistant against coolant lubricants, IO-Link

• Electrical wiring: DC 4-wire

• Connection type: male connector M12, 4-pin (With gold plated contact pins.)

Smart Sensor	Туре	Part no.
Enhanced Sensing (Counter + debouncing) Efficient communication Diagnosis Smart Task	IMC18- 12NPPVCOSA71	1079297
Enhanced Sensing (Time measurement + debouncing) Efficient communication Diagnosis Smart Task	IMC18- 12NPPVC0SA70	1079296
Enhanced Sensing (base logics) Efficient communication Diagnosis Smart Task	IMC18- 12NPPVCOSA00	1079295

• Sub product family: IMC30

• Sensing range S_n : 0 mm ... 15 mm (Adjustable.)

• Cylindrical thread design: M30

Switching output: PNP
Installation type: flush
Output function: NC, NO

• Special features: Smart Task, Resistant against coolant lubricants, IO-Link

• Electrical wiring: DC 4-wire

• Connection type: male connector M12, 4-pin (With gold plated contact pins.)

Smart Sensor	Туре	Part no.
Enhanced Sensing (Counter + debouncing) Efficient communication Diagnosis Smart Task	IMC30-15BP- PVC0SA71	1079300
Enhanced Sensing (Time measurement + debouncing) Efficient communication Diagnosis Smart Task	IMC30-15BP- PVCOSA70	1079299
Enhanced Sensing (base logics) Efficient communication Diagnosis Smart Task	IMC30-15BP- PVC0SA00	1079298

• Sensing range S_n: 0 mm ... 20 mm (Adjustable.)

• Cylindrical thread design: M30

Switching output: PNP
Installation type: non-flush
Output function: NC, NO

• Special features: Smart Task, Resistant against coolant lubricants, IO-Link

• Electrical wiring: DC 4-wire

• Connection type: male connector M12, 4-pin (With gold plated contact pins.)

Smart Sensor	Туре	Part no.
Enhanced Sensing (Counter + debouncing) Efficient communication Diagnosis Smart Task	IMC30- 20NPPVC0SA71	1079303
Enhanced Sensing (Time measurement + debouncing) Efficient communication Diagnosis Smart Task	IMC30- 20NPPVC0SA70	1079302
Enhanced Sensing (base logics) Efficient communication Diagnosis Smart Task	IMC30- 20NPPVC0SA00	1079301

• Sub product family: IQC10

• Sensing range S_n: 0 mm ... 3 mm (Adjustable.)

• Cuboid shape (W x H x D): 10 mm x 28 mm x 16 mm

Switching output: PNP
Installation type: flush
Output function: NC, NO

• Special features: Smart Task, IO-Link

• Electrical wiring: DC 4-wire

• Connection type: Cable with M12 male connector, 4-pin, 0.2 m (With gold plated contact pins.)

Smart Sensor	Туре	Part no.
Enhanced Sensing (Counter + debouncing) Efficient communication Diagnosis Smart Task	IQC10-03BPP- KQ8SA71	1083795
Enhanced Sensing (Time measurement + debouncing) Efficient communication Diagnosis Smart Task	IQC10-03BPP- KQ8SA70	1083794
Enhanced Sensing (base logics) Efficient communication Diagnosis Smart Task	IQC10-03BPP- KQ8SA00	1083793

IMC

• Sub product family: IQC12

• Cuboid shape (W x H x D): 12 mm x 40 mm x 26 mm

Switching output: PNP
Installation type: flush
Output function: NC, NO

• Special features: Smart Task, IO-Link

• Electrical wiring: DC 4-wire

• Connection type: Cable with M12 male connector, 4-pin, 0.2 m (With gold plated contact pins.)

Smart Sensor	Туре	Part no.
Enhanced Sensing (Counter + debouncing) Efficient communication Diagnosis Smart Task	IQC12-04BPP- KQ8SA71	1083798
Enhanced Sensing (Time measurement + debouncing) Efficient communication Diagnosis Smart Task	IQC12-04BPP- KQ8SA70	1083797
Enhanced Sensing (base logics) Efficient communication Diagnosis Smart Task	IQC12-04BPP- KQ8SA00	1083796

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

