

TR110 Lock

RFID-monitored safety locking device with high manipulation protection



TR110 Lock





Technical data overview

| Туре | Type 4, RFID (EN ISO 14119) | | | |
|-------------------------------|--|--|--|--|
| Actuator coding level | High coding level (EN ISO 14119) | | | |
| Type of output | Self-monitoring semiconductor outputs (OSSDs) | | | |
| Locking principle | Power to lock / power to release (depending on type) | | | |
| Locking monitoring | ✓ | | | |
| Door monitoring | ✓ | | | |
| Locking force F _{Zh} | 3,000 N (EN ISO 14119) 1,100 N (EN ISO 14119) 2,000 N (EN ISO 14119) | | | |
| Escape release | - / 🗸 (depending on type) | | | |
| Connection type | Plug connector, M12, 8-pin Plug connector, M12, 5-pin (depending on type) | | | |
| LED | 1 | | | |

Product description

The TR110 Lock safety locking device unites the advantages of proven technologies: high manipulation protection of the RFID technology for monitoring the actuator and the ruggedness and reliability of the mechanical locking device. The self-monitoring semiconductor outputs (OSSDs) with PL e (EN ISO 13849) result in a high level of safety, both for the door and for the locking monitoring. The optional escape release enables unlocking of the locking device from the hazardous area. The variants with two illuminable pushbuttons make it possible to trigger control signals such as door requests or resets directly on the safety switch.

At a glance

- PL e for door and locking monitoring (EN ISO 13849)
- Locking force: up to 3,900 N
- Actuator with high coding level (EN ISO 14119)
- Enclosure rating: IP67, IP69K
- · Power to lock or power to release variants
- Three actuation directions
- Optional emergency release
- Variants with two illuminable pushbuttons

Your benefits

- · Highest level of safety for door and locking monitoring with just one device
- High level of machine availability due to a rugged metal locking head and high locking force
- High coding level of the actuator fulfills the requirements of EN ISO 14119 on manipulation protection without additional mea-
- suresEasy mounting thanks to three actuation directions
- The escape release enables use of the locking device in applications in which the hazardous area is not completely visible
- Illuminable pushbuttons make triggering of control signals directly on the device possible
- · Additional application diagnostic outputs simplify diagnostics

Fields of application

- Hazardous areas with fully body access
- Hazardous areas with partial body access
- · Protection of persons in the event of the machine making dangerous overrun movements
- Applications requiring a high level of manipulation protection
- Applications requiring a high locking force

Ordering information

Other models and accessories → www.sick.com/TR110_Lock

| Locking principle | Connection type Detail | Safe series connection | Escape release | Pushbuttons | Туре | Part no. |
|-------------------|--|---|----------------|-------------|---------------|----------|
| Power to lock | Plug connec- tor, M12, 8-pin | None, only in- dividual wiring (with diagnostics) | - | - | TR110-SLUSABO | 6082945 |
| | | With Flexi Loop (with diagnostics) | - | - | TR110-SLUFLB0 | 6082948 |
| | Plug connec- tor, M12, 8- pin, plug connec- tor, M12, 5-pin | None, only in- dividual wiring (with diagnostics) | - | √ | TR110-SLU2BB0 | 6082954 |
| | | With T-connec- tor (without diagnostics) | - | - | TR110-SLUCABO | 6082951 |
| Power to release | Plug connec- tor, M12, 8-pin | None, only in- dividual wiring (with diagnostics) | 1 | - | TR110-SRUSAB1 | 6082946 |
| | | | - | - | TR110-SRUSAB0 | 6082944 |
| | | With Flexi Loop (with diagnostics) | 1 | - | TR110-SRUFLB1 | 6082949 |
| | | | - | - | TR110-SRUFLB0 | 6082947 |
| | Plug connec- tor, M12, 8- pin, plug connec- tor, M12, 5-pin | None, only in- dividual wiring (with diagnostics) | 1 | √ | TR110-SRU2BB1 | 6082955 |
| | | | - | √ | TR110-SRU2BB0 | 6082953 |
| | | With T-connec- tor (without diagnostics) | 1 | - | TR110-SRUCAB1 | 6082952 |
| | | | - | - | TR110-SRUCABO | 6082950 |

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

