



# SAPPC2D-08XS002

Safe Robotics Area Protection

SAFETY SYSTEMS FOR ROBOTS

**SICK**  
Sensor Intelligence.



### Ordering information

#### sBot Speed CIP

Variant	Robot type	Product type	Type	Part no.
sBot Speed CIP – FA	FANUC: R-30iB Plus	Software	SAPPC2D-08XS002	1614143

The software only has to be purchased separately if the associated safety system hardware is already available.

With purchase, you accept the product description available under Downloads > Documentation in connection with the General Terms and Conditions for the Supply of Software Products (AVB Software SICK).

Other models and accessories → [www.sick.com/Safe\\_Robotics\\_Area\\_Protection](http://www.sick.com/Safe_Robotics_Area_Protection)

### Detailed technical data

#### Features

<b>Variant</b>	sBot Speed CIP
<b>Product type</b>	Software
<b>Robot controller</b>	FANUC: R-30iB Plus
<b>Stopping process of the robot</b>	With speed reduction
<b>Robot restart</b>	Automatic
<b>Interfaces</b>	
Communication interface	EtherNet/IP™ CIP Safety™
<b>Safe state in the event of a fault</b>	The safety outputs via the network are logic 0.
<b>Safety task</b>	Hazardous area protection
<b>Safety controller included</b>	
Safety controller type	Programmable
<b>Performance level</b>	PL d (ISO 13849-1)
<b>Items supplied</b>	Software (Safety Designer project file with functional logic, pre-configuration file for microScan3 Core EFI-pro, CIP Safety communication setting and FANUC-specific settings) as well as operating instructions, connection diagram and SISTEMA file

#### Functions

<b>Emergency stop</b>	
Shut down in the event of an emergency situation	✓
Prevent unexpected restarting after an emergency stop	✓
<b>Initiate a safety stop</b>	
Automated reset and restart with safe sequence monitoring	✓
Optional manual reset	✓
<b>Safety-rated monitored speed</b>	
Trigger safety-rated monitored speed	✓
<b>Operating mode</b>	
Operating mode selection (implemented in robot control)	✓

Enabling device - manual operating mode (implemented in robot control)



## Classifications

<b>ECLASS 5.0</b>	27279090
<b>ECLASS 5.1.4</b>	27279090
<b>ECLASS 6.0</b>	27279090
<b>ECLASS 6.2</b>	27279090
<b>ECLASS 7.0</b>	27279090
<b>ECLASS 8.0</b>	27279090
<b>ECLASS 8.1</b>	27279090
<b>ECLASS 9.0</b>	27279090
<b>ECLASS 10.0</b>	27279090
<b>ECLASS 11.0</b>	27279090
<b>ECLASS 12.0</b>	27279090
<b>ETIM 5.0</b>	EC001449
<b>ETIM 6.0</b>	EC001449
<b>ETIM 7.0</b>	EC001449
<b>ETIM 8.0</b>	EC001449
<b>UNSPSC 16.0901</b>	32151705

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)