



INDUCTIVE PROXIMITY SENSORS



INDUCTIVE PROXIMITY SENSORS





Ordering information

| Туре | Part no. |
|----------------|----------|
| IH06-04NPO-VTK | 6025884 |

Other models and accessories -> www.sick.com/IMM

Detailed technical data

Features

| Housing | Cylindrical |
|-----------------------------------|---------------------|
| Housing | Short-body |
| Diameter | Ø 6.5 mm |
| Sensing range S _n | 4 mm |
| Safe sensing range S _a | 3.24 mm |
| Installation type | Non-flush |
| Switching frequency | 2,500 Hz |
| Connection type | Connector M8, 3-pin |
| Switching output | PNP |
| Output function | NC |
| Electrical wiring | DC 3-wire |
| Enclosure rating | IP67 ¹⁾ |

 $^{\mbox{1})}$ According to EN 60529.

Mechanics/electronics

| Supply voltage | 10 V DC 30 V DC |
|--|--|
| Ripple | < 10 % ¹⁾ |
| Voltage drop | $\leq 2 V^{2}$ |
| Time delay before availability | ≤ 50 ms |
| Hysteresis | 1 % 20 % |
| Reproducibility | ≤ 5 % ^{3) 4)} |
| Temperature drift (of S _r) | ± 10 % |
| EMC | EN 60947-5-2 IEC 61000-4-2: (Testlevel 2) |

 $^{1)}$ Of $V_{\mbox{S}}.$

 $^{2)}$ With Ia = 200 mA.

 $^{\rm 3)}$ Supply voltage U_B and constant ambient temperature Ta.

⁴⁾ Of Sr.

INDUCTIVE PROXIMITY SENSORS

| | IEC 61000-4-4: (Testlevel 3) |
|-----------------------------------|--|
| Continuous current I _a | ≤ 200 mA |
| Short-circuit protection | ✓ |
| Power-up pulse protection | ✓ |
| Shock and vibration resistance | 30 g, 11 ms / 10 55 Hz, 1 mm |
| Ambient operating temperature | -25 °C +70 °C |
| Housing material | Stainless steel V2A, DIN 1.4305 / AISI 303 |
| Sensing face material | Plastic, POM |
| Housing length | 40 mm |
| UL File No. | NMFT2.E175606 |

 $^{1)}$ Of V_S.

 $^{2)}$ With Ia = 200 mA.

 $^{3)}\,\mbox{Supply voltage U}_B$ and constant ambient temperature Ta.

 $^{4)}$ Of Sr.

Reduction factors

| Note | The values are reference values which may vary |
|----------------------------|--|
| Stainless steel (V2A, 304) | Approx. 0.77 |
| Aluminum (AI) | Approx. 0.47 |
| Copper (Cu) | Approx. 0.42 |
| Brass (Br) | Approx. 0.52 |

Installation note

| Remark | Associated graphic see "Installation" |
|--------|---------------------------------------|
| A | 6.5 mm |
| В | 13 mm |
| с | 6.5 mm |
| D | 12 mm |
| E | 8 mm |
| F | 32 mm |

Classifications


| ECLASS 5.0 | 27270101 |
|--------------|----------|
| ECLASS 5.1.4 | 27270101 |
| ECLASS 6.0 | 27270101 |
| ECLASS 6.2 | 27270101 |
| ECLASS 7.0 | 27270101 |
| ECLASS 8.0 | 27270101 |
| ECLASS 8.1 | 27270101 |
| ECLASS 9.0 | 27270101 |
| ECLASS 10.0 | 27270101 |
| ECLASS 11.0 | 27270101 |
| ECLASS 12.0 | 27274001 |
| ETIM 5.0 | EC002714 |

INDUCTIVE PROXIMITY SENSORS

| ETIM 6.0 | EC002714 |
|----------------|----------|
| ETIM 7.0 | EC002714 |
| ETIM 8.0 | EC002714 |
| UNSPSC 16.0901 | 39122230 |


Installation note

Non-flush installation




Connection diagram

Cd-004



Dimensional drawing (Dimensions in mm (inch))

Short-body, non-flush, connector







INDUCTIVE PROXIMITY SENSORS

Recommended accessories

Other models and accessories -> www.sick.com/IMM

| | Brief description | Туре | Part no. | |
|--------------|---|------------------------|----------|--|
| Terminal and | Ferminal and alignment brackets | | | |
| | Plastic (PA6), without mounting hardware | BEF-KH-M06 | 2101067 | |
| Others | | | | |
| R e | Connection type head A: Female connector, M8, 3-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 3-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals | YF8U13- 020VA1XLEAX | 2095860 | |
| · · · | Connection type head A: Female connector, M8, 3-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 3-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals | YF8U13- 050VA1XLEAX | 2095884 | |
| ×. | Connection type head A: Female connector, M8, 3-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 10 m, 3-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals | YF8U13- 100VA1XLEAX | 2095885 | |
| 3 | Connection type head A: Female connector, M8, 3-pin, angled, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 3-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals | YG8U13- 020VA1XLEAX | 2096165 | |
| | Connection type head A: Female connector, M8, 3-pin, angled, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 3-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals | YG8U13- 050VA1XLEAX | 2096166 | |
| > | Connection type head A: Female connector, M8, 3-pin, angled, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 10 m, 3-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals | YG8U13- 100VA1XLEAX | 2096209 | |
| | Connection type head A: Male connector, M8, 3-pin, straight, A-coded Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: 0.14 mm² 0.5 mm² | STE-0803-G | 6037322 | |
| | Connection type head A: Female connector, M8, 3-pin, straight, A-coded Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: 0.14 mm² 0.5 mm² | DOS-0803-G | 7902077 | |
| ×. | Connection type head A: Female connector, M8, 3-pin, angled, A-coded Description: Unshielded Connection systems: Solder connection Permitted cross-section: ≤ 0.25 mm² | DOS-0803-W | 7902078 | |

INDUCTIVE PROXIMITY SENSORS

| | Brief description | Туре | Part no. |
|-------|---|------------------------|----------|
| 10 Kg | Connection type head A: Female connector, M8, 3-pin, straight, A-coded Connection type head B: Male connector, M12, 3-pin, straight, A-coded Signal type: Sensor/actuator cable Cable: 2 m, 3-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals | YF8U13- 020VA1M2A13 | 2096605 |
| 10 Kg | Connection type head A: Female connector, M8, 3-pin, straight, A-coded Connection type head B: Male connector, M12, 3-pin, straight, A-coded Signal type: Sensor/actuator cable Cable: 5 m, 3-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals | YF8U13- 050VA1M2A13 | 2096606 |

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

