



**INDUCTIVE PROXIMITY SENSORS** 



INDUCTIVE PROXIMITY SENSORS



# Ordering information

Туре	Part no.
IM18-08NNP-ZC1	7902934

Other models and accessories → www.sick.com/IM\_Standard



#### Detailed technical data

#### Features

Housing	Metric
Housing	Standard design
Thread size	M18 x 1
Diameter	Ø 18 mm
Sensing range S <sub>n</sub>	8 mm
Safe sensing range S <sub>a</sub>	6.48 mm
Installation type	Non-flush
Switching frequency	1,000 Hz
Connection type	Male connector M12, 4-pin
Switching output	NPN
Output function	Complementary
Electrical wiring	DC 4-wire
Enclosure rating	IP68 <sup>1)</sup>

<sup>1)</sup> According to EN 60529.

#### Mechanics/electronics

Supply voltage	10 V DC 30 V DC
Ripple	≤ 10 %
Voltage drop	$\leq 0.8 V^{(1)}$
Time delay before availability	≤ 100 ms
Hysteresis	2 % 10 %
Reproducibility	≤ 5 % <sup>2) 3)</sup>
Temperature drift (of S <sub>r</sub> )	± 10 %

#### $^{1)}$ At I<sub>a</sub> max.

 $^{2)}$  Supply voltage  $U_{B}$  and constant ambient temperature Ta.

<sup>&</sup>lt;sup>3)</sup> Of Sr.

INDUCTIVE PROXIMITY SENSORS

EMC	According to EN 60947-5-2
Continuous current l <sub>a</sub>	≤ 400 mA
Short-circuit protection	✓
Power-up pulse protection	✓
Shock and vibration resistance	30 g, 11 ms / 10 55 Hz, 1 mm
Ambient operating temperature	-25 °C +70 °C
Housing material	Brass, Nickel-plated brass
Sensing face material	Plastic
Housing length	63 mm
Thread length	27 mm
Tightening torque, max.	40 Nm

 $^{1)}$  At I<sub>a</sub> max.

 $^{2)}$  Supply voltage  $\mathrm{U}_{\mathrm{B}}$  and constant ambient temperature Ta.

<sup>3)</sup> Of Sr.

#### Safety-related parameters

MTTF <sub>D</sub>	88 years
DC <sub>avg</sub>	0 %
Reduction factors	

St37 steel (Fe)	1
Stainless steel (V2A, 304)	Approx. 0.8
Aluminum (Al)	Approx. 0.45
Copper (Cu)	Approx. 0.4
Brass (Br)	Approx. 0.4

#### Installation note

Remark	Associated graphic see "Installation"
A	18 mm
В	36 mm
c	18 mm
D	24 mm
E	12 mm
F	64 mm

#### Classifications


ECLASS 5.0	27270101
ECLASS 5.1.4	27270101
ECLASS 6.0	27270101
ECLASS 6.2	27270101
ECLASS 7.0	27270101
ECLASS 8.0	27270101
ECLASS 8.1	27270101
ECLASS 9.0	27270101

INDUCTIVE PROXIMITY SENSORS

ECLASS 10.0	27270101
ECLASS 11.0	27270101
ECLASS 12.0	27274001
ETIM 5.0	EC002714
ETIM 6.0	EC002714
ETIM 7.0	EC002714
ETIM 8.0	EC002714
UNSPSC 16.0901	39122230

#### Installation note


Non-flush installation



#### Connection type




**Connection diagram** 



Cd-006



Dimensional drawing (Dimensions in mm (inch))



① Connection

② Display LED

③ Fastening nuts (2x); width across 24, metal

INDUCTIVE PROXIMITY SENSORS

#### **Recommended accessories**

Other models and accessories -> www.sick.com/IM\_Standard

	Brief description	Туре	Part no.
Nounting brackets and plates			
	Mounting plate for M18 sensors, steel, zinc coated, without mounting hardware	BEF-WG-M18	5321870
40	Mounting bracket for M18 sensors, steel, zinc coated, without mounting hardware	BEF-WN-M18	5308446
Terminal and	l alignment brackets		
Cor Cor	Clamping block for round sensors M18, without fixed stop, plastic (PA12), glass-fiber re- inforced, mounting hardware included	BEF-KH-M18	2051481
Others			
e contra	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled, A-coded</li> <li>Description: Unshielded, Head A: female connector, M12, 4-pin, angled, unshielded, for power supply, for cable diameter 3 mm 6.5 mm Head B: -</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: ≤ 0.75 mm<sup>2</sup></li> </ul>	DOS-1204-W	6007303
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight, A-coded</li> <li>Description: Unshielded, Head A: female connector, M12, 4-pin, straight, unshielded, for power supply, for cable diameter 4 mm 6 mm Head B: -</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: ≤ 0.75 mm<sup>2</sup></li> </ul>	DOS-1204-G	6007302
	<ul> <li>Connection type head A: Male connector, M12, 4-pin, straight, A-coded</li> <li>Description: Unshielded</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: ≤ 0.75 mm<sup>2</sup></li> </ul>	STE-1204-G	6009932
	<ul> <li>Connection type head A: Male connector, M12, 4-pin, angled, A-coded</li> <li>Description: Unshielded</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: ≤ 0.75 mm<sup>2</sup></li> </ul>	STE-1204-W	6022084
<b>\$</b>	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 2 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YF2A14- 020VB3XLEAX	2096234
<b>\$</b> 0	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YF2A14- 050VB3XLEAX	2096235
3	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 2 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YG2A14- 020VB3XLEAX	2095895
*	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YG2A14- 050VB3XLEAX	2095897

# IM18-08NNP-ZC1 | IM Standard INDUCTIVE PROXIMITY SENSORS

	Brief description	Туре	Part no.
6ED	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 2 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded, LED function display</li> <li>Note: Only suitable for PNP sensors</li> <li>Application: Zones with chemicals</li> </ul>	YI2A14- 020VB3XLEAX	2096222
(F)	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded, LED function display</li> <li>Note: Only suitable for PNP sensors</li> <li>Application: Zones with chemicals</li> </ul>	YI2A14- 050VB3XLEAX	2096223

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

