



WL160-P440

SICK
Sensor Intelligence.



Illustration may differ



Ordering information

Type	Part no.
WL160-P440	6008816

Other models and accessories → www.sick.com/

Detailed technical data

Features

Functional principle	Photoelectric retro-reflective sensor
Dimensions (W x H x D)	11 mm x 38 mm x 38 mm
Housing design (light emission)	Rectangular
Sensing range max.	3 m ¹⁾
Type of light	Visible red light
Light source	LED
Wave length	680 nm

¹⁾ Reflector PL80A.

Mechanics/electronics

Ripple	± 10 %
Current consumption	30 mA ¹⁾
Switching output	PNP
Switching mode	Light/dark switching
Switching mode selector	Selectable via light/dark rotary switch
Response time	≤ 0.9 ms ²⁾
Connection type	Male connector M8, 4-pin
Housing material	Plastic, ABS
Optics material	Plastic, PMMA
Ambient operating temperature	-25 °C ... +55 °C
Ambient temperature, storage	-40 °C ... +70 °C
UL File No.	NRNT2.E128350 & NRNT8.E128350

¹⁾ Without load.

²⁾ Signal transit time with resistive load.

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com