

Ø

**TEMPERATURE SENSORS** 



## TBT-1AAG11006GZ | TBT

TEMPERATURE SENSORS



#### Detailed technical data

#### Features

| Measuring range                   | -50 °C +150 °C   |
|-----------------------------------|--|
| Sensor element                    | Pt100  |
| Output signal                     | 4 mA 20 mA, 2-wire                                     |
| Maximum ohmic load R <sub>A</sub> | $R_A \le (L^+ - 10 \text{ V}) / 0.028 \text{ A [Ohm]}$ |

### Mechanics/electronics

| Process connection                 | Thread G ¼ B  |
|------------------------------------|---|
| Insertion length/diameter of probe | 100 mm / 6 mm   |
| Wetted parts                       | Stainless steel 1.4571  |
| Pressure resistance                | Max. 120 bar  |
| Housing material                   | Aluminum  |
| Connection type                    | Cable gland M16 x 1.5 $^{(1)}$  |
| Enclosure rating                   | IP65 <sup>2)</sup>  |
| Measuring current                  | 0.3 mA 1 mA   |
| Supply voltage                     | 10 V DC 35 V DC   |
| Maximum current consumption        | Ca. 28 mA   |
| Electrical safety                  | Protection class: III, insulation voltage: 100 V, reverse polarity protection of variant with measuring transducer 4 mA 20 mA: L+ to M $$ |
| Protection class III               | ✓   |
| CE-conformity                      | 2004/108/EC, EN 61326-2-3   |
| RoHS certificate                   | ✓   |
| Weight                             | Ca. 155 g (depending on configuration)  |
| Initialization time                | < 1 ms  |

<sup>1)</sup> The enclosure rating classes specified only apply while the thermometer is connected with female connectors that provide the corresponding enclosure rating. <sup>2)</sup> IP enclosure rating as per IEC 60529.

#### Performance

| Accuracy of sensor element | Class A according to IEC 60751 |
|----------------------------|--------------------------------|
|                            |                                |

 $^{1)}$  Depending on sensor configuration, according to IEC 60751.

# TBT-1AAG11006GZ | TBT

TEMPERATURE SENSORS

| Transmitter accuracy  | ≤ ± 0.1 % of span   |
|-----------------------|---|
| Transmitter linearity | ≤ 0.1 % of span   |
| Response time         | Response time $t_{50}$ : $\leq 5.8 \text{ s}^{-1}$<br>Response time $t_{90}$ : $\leq 15.5 \text{ s}^{-1}$ |

 $^{\mbox{\ 1)}}$  Depending on sensor configuration, according to IEC 60751.

#### Ambient data

| Ambient temperature                         | -40 °C +85 °C |
|---|---------------|
| Storage and transport temperature           | -40 °C +60 °C |
| Shock resistance according to IEC 60751     | 500 g         |
| Vibration resistance according to IEC 60751 | 3 g           |

#### Classifications

| ECLASS 5.0     | 27200208 |
|----------------|----------|
| ECLASS 5.1.4   | 27200208 |
| ECLASS 6.0     | 27200208 |
| ECLASS 6.2     | 27200208 |
| ECLASS 7.0     | 27200208 |
| ECLASS 8.0     | 27200208 |
| ECLASS 8.1     | 27200208 |
| ECLASS 9.0     | 27200208 |
| ECLASS 10.0    | 27200208 |
| ECLASS 11.0    | 27200208 |
| ECLASS 12.0    | 27200208 |
| ETIM 5.0       | EC002994 |
| ETIM 6.0       | EC002994 |
| ETIM 7.0       | EC002994 |
| ETIM 8.0       | EC002994 |
| UNSPSC 16.0901 | 41112211 |

## TBT-1AAG11006GZ | TBT

TEMPERATURE SENSORS

#### Dimensional drawing (Dimensions in mm (inch))


### Dimensional drawing: zylindrical threads

#### Thread, up to 150 °C

#### °C

Thread, up to 250 °C

#### Compression fitting



Dimensional drawing: conical threads


Thread, up to 150 °C


Thread, up to 250 °C

Compression fitting


**Å** <sup>14</sup> (0.55)

**X** (1.06)






Dimensional drawing: housing, without process connection



### Connection type

Cable entry M16 x 1.5, cable cross-section up to 0.75 mm2, output signal 4 mA  $\dots$  20 mA



# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

