

IM30-15NNS-ZC1

IM Standard

INDUCTIVE PROXIMITY SENSORS





Ordering information

| Туре | Part no. |
|----------------|----------|
| IM30-15NNS-ZC1 | 6020287 |

Other models and accessories → www.sick.com/IM_Standard

Illustration may differ



Detailed technical data

Features

| Housing | Metric |
|------------------------------|---------------------------|
| Housing | Standard design |
| Thread size | M30 x 1.5 |
| Diameter | Ø 30 mm |
| Sensing range S _n | 15 mm |
| Installation type | Non-flush |
| Switching frequency | 200 Hz |
| Connection type | Male connector M12, 4-pin |
| Switching output | NPN |
| Output function | NO |
| Electrical wiring | DC 3-wire |
| Enclosure rating | IP67 ¹⁾ |

¹⁾ According to EN 60529.

Mechanics/electronics

| Supply voltage | 10 V DC 30 V DC |
|--|------------------------|
| Ripple | ≤ 10 % ¹⁾ |
| Voltage drop | \leq 1 V $^{2)}$ |
| Time delay before availability | ≤ 100 ms |
| Hysteresis | 2 % 10 % |
| Reproducibility | ≤ 2 % ^{3) 4)} |
| Temperature drift (of S _r) | ± 10 % |

 $^{^{1)}}$ Of V_{S} .

²⁾ At I_a max.

 $^{^{\}rm 3)}$ Supply voltage U_B and constant ambient temperature Ta.

⁴⁾ Of Sr.

| EMC | According to EN 60947-5-2 |
|-----------------------------------|------------------------------|
| Continuous current I _a | ≤ 400 mA |
| Short-circuit protection | ✓ |
| Power-up pulse protection | ✓ |
| Shock and vibration resistance | 30 g, 11 ms / 10 55 Hz, 1 mm |
| Ambient operating temperature | -25 °C +70 °C |
| Housing material | Brass, Nickel-plated brass |
| Sensing face material | Plastic |
| Housing length | 76 mm |
| Thread length | 38 mm |
| Tightening torque, max. | 60 Nm |

 $^{^{1)}}$ Of V_{S} .

Installation note

| Remark | Associated graphic see "Installation" |
|--------|---------------------------------------|
| Α | 15 mm |
| В | 45 mm |
| c | 30 mm |
| D | 45 mm |
| E | 18 mm |
| F | 120 mm |

Classifications

| ECLASS 5.0 | 27270101 |
|----------------|----------|
| ECLASS 5.1.4 | 27270101 |
| ECLASS 6.0 | 27270101 |
| ECLASS 6.2 | 27270101 |
| ECLASS 7.0 | 27270101 |
| ECLASS 8.0 | 27270101 |
| ECLASS 8.1 | 27270101 |
| ECLASS 9.0 | 27270101 |
| ECLASS 10.0 | 27270101 |
| ECLASS 11.0 | 27270101 |
| ECLASS 12.0 | 27274001 |
| ETIM 5.0 | EC002714 |
| ETIM 6.0 | EC002714 |
| ETIM 7.0 | EC002714 |
| ETIM 8.0 | EC002714 |
| UNSPSC 16.0901 | 39122230 |


²⁾ At I_a max.


 $^{^{\}rm 3)}$ Supply voltage $\rm U_B$ and constant ambient temperature Ta.

⁴⁾ Of Sr.

Installation note

Non-flush installation







Connection type




Connection diagram



Cd-007



Dimensional drawing (Dimensions in mm (inch))



- ① Connection
- ② Display LED
- 3 Fastening nuts (2x); width across 36, metal

Recommended accessories

Other models and accessories → www.sick.com/IM_Standard

| | Brief description | Туре | Part no. | |
|-----------------------------|--|-------------|----------|--|
| Universal bar clamp systems | | | | |
| | Plate N10 for universal clamp bracket, M30, Zinc plated steel (sheet), Zinc die cast (clamping bracket), Universal clamp (5322626), mounting hardware | BEF-KHS-N10 | 2062372 | |
| Mounting brad | Mounting brackets and plates | | | |
| | Mounting plate for M30 sensors, steel, zinc coated, without mounting hardware | BEF-WG-M30 | 5321871 | |
| 40 | Mounting bracket for M30 sensors, steel, zinc coated, without mounting hardware | BEF-WN-M30 | 5308445 | |
| Others | | | | |
| | Connection type head A: Female connector, M12, 4-pin, angled, A-coded Description: Unshielded, Head A: female connector, M12, 4-pin, angled, unshielded, for power supply, for cable diameter 3 mm 6.5 mm Head B: - Connection systems: Screw-type terminals Permitted cross-section: ≤ 0.75 mm² | DOS-1204-W | 6007303 | |
| | Connection type head A: Female connector, M12, 4-pin, straight, A-coded Description: Unshielded, Head A: female connector, M12, 4-pin, straight, unshielded, for power supply, for cable diameter 4 mm 6 mm Head B: - Connection systems: Screw-type terminals Permitted cross-section: ≤ 0.75 mm² | DOS-1204-G | 6007302 | |

| | Brief description | Туре | Part no. |
|---|--|------------------------|----------|
| | Connection type head A: Male connector, M12, 4-pin, straight, A-coded Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: ≤ 0.75 mm² | STE-1204-G | 6009932 |
| | Connection type head A: Male connector, M12, 4-pin, angled, A-coded Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: ≤ 0.75 mm² | STE-1204-W | 6022084 |
| | Connection type head A: Female connector, M12, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals | YF2A14- 020VB3XLEAX | 2096234 |
| | Connection type head A: Female connector, M12, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals | YF2A14- 050VB3XLEAX | 2096235 |
| | Connection type head A: Female connector, M12, 4-pin, angled, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals | YG2A14- 020VB3XLEAX | 2095895 |
| 3 | Connection type head A: Female connector, M12, 4-pin, angled, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals | YG2A14- 050VB3XLEAX | 2095897 |
| | Connection type head A: Female connector, M12, 4-pin, angled, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded, LED function display Note: Only suitable for PNP sensors Application: Zones with chemicals | YI2A14- 020VB3XLEAX | 2096222 |
| | Connection type head A: Female connector, M12, 4-pin, angled, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded, LED function display Note: Only suitable for PNP sensors Application: Zones with chemicals | YI2A14- 050VB3XLEAX | 2096223 |

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

