

R Der

Sick Sensor Intelligence.

TEMPERATURE SENSORS

TBS-1ASG11506NM | TBS

TEMPERATURE SENSORS



Ordering information

Туре	Part no.
TBS-1ASG11506NM	6048663

Other models and accessories -> www.sick.com/TBS

Illustration may differ



Detailed technical data

Features

Temperature measuring range	-20 °C +80 °C
Sensor element	Pt1000, 2-wire, class A according to IEC 60751
Output signals	2 x PNP
Switching output	Transistor
Switching voltage	Supply voltage [V DC] - 1 V DC
Maximum switching current	≤ 250 mA
Switching delay	0 s 50 s, programmable
Setting accuracy of switching outputs	+0.1 °C
Switching output	Transistor
Number	2
Switching voltage	Supply voltage [V DC] - 1 V DC
Maximum switching current	≤ 250 mA
Switching delay	0 s 50 s, programmable
Setting accuracy of switching outputs	+0.1 °C
Temperature offset	±3°C
Scaling of measuring range	Zero point: max. +25 % of span Full scale: max25 % of span
Scaling of measuring range	Max. +25 % of span, max25 % of span
Display	14-segment LED, blue, 4-digits, height 9 mm, Display electronically turnable by 180 °, update: 200 ms
Rotatable housing	Display against housing with electrical connection: 330 $^\circ$ Housing against process connection: 320 $^\circ$

Mechanics/electronics

Process connection	Thread G ¼ A according to DIN 3852-E
Insertion length/diameter of probe	150 mm / 6 mm
Seal	NBR
Wetted parts	Stainless steel 1.4571 (AISI 316Ti)

 $^{1)}\ensuremath{\,\text{At}}$ room temperature and when connected through thread.

²⁾ IP enclosure rating as per IEC 60529.

TBS-1ASG11506NM | TBS

TEMPERATURE SENSORS

Maximum process pressure	≤ 150 bar ¹⁾	
Housing material	Lower body: stainless steel 1.4301 (AISI 304) Plastic head: PC + ABS Input keypad: TPE-E Display window: PC	
Connection type	M12 round connector x 1, 4-pin	
Enclosure rating	IP65 ²⁾ IP67 ²⁾	
Maximum ohmic load R _A	\leq 100 k Ω (Switching outputs)	
Supply voltage	15 V DC 35 V DC	
Maximum current consumption	45 mA	
Total current consumption	570 mA (incl. switching current) 320 mA	
Protection class	III	
Isolation voltage	500 V DC	
Overvoltage protection	40 V DC	
Short-circuit protection	Outputs Q_A , Q_1 , Q_2 towards M	
Reverse polarity protection	L ⁺ towards M	
Electrical safety		
Protection class	III	
Isolation voltage	500 V DC	
Overvoltage protection	40 V DC	
Short-circuit protection	Outputs Q_A , Q_1 , Q_2 towards M	
Reverse polarity protection	L ⁺ towards M	
CE-conformity	2004/108/EC, EN 61326-1 emission (group 1, class B) and interference immunity (industrial application)	
RoHS certificate	✓	
MTTF	325 years	

 $^{\left(1\right) }$ At room temperature and when connected through thread.

²⁾ IP enclosure rating as per IEC 60529.

Performance

Accuracy of sensor element	$\leq \pm (0.15 \text{ °C} + 0.002 t)^{(1)}$
Accuracy of switching output	≤ ± 0.8 % of span
Display accuracy	\leq ± 0.8 % of span ± 1 digit
Response time t ₅₀	≤ 5 s ²)
Response time t ₉₀	< 10 s ²⁾

 $^{(1)}$ [t] is the absolute value of the temperature in °C.

²⁾ Depending on sensor configuration, according to IEC 60751.

Ambient data

Ambient temperature	-20 °C +80 °C
Storage and transport temperature	-20 °C +80 °C
Relative humidity	45 % 75 %


TBS-1ASG11506NM | TBS

TEMPERATURE SENSORS


Classifications

ECLASS 5.0	27200208
ECLASS 5.1.4	27200208
ECLASS 6.0	27200208
ECLASS 6.2	27200208
ECLASS 7.0	27200208
ECLASS 8.0	27200208
ECLASS 8.1	27200208
ECLASS 9.0	27200208
ECLASS 10.0	27200208
ECLASS 11.0	27200208
ECLASS 12.0	27200208
ETIM 5.0	EC002994
ETIM 6.0	EC002994
ETIM 7.0	EC002994
ETIM 8.0	EC002994
UNSPSC 16.0901	41112211

Dimensional drawing (Dimensions in mm (inch)) TBS with connection G ¼ A according to DIN 3852-E



Connection type



Recommended accessories

Other models and accessories -> www.sick.com/TBS

	Brief description	Туре	Part no.
Others			
N	 Connection type head A: Female connector, M12, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 4-wire, PUR, halogen-free Description: Sensor/actuator cable, unshielded Application: Zones with oils and lubricants, Drag chain operation, Robot 	YF2A14- 020UB3XLEAX	2095607
	 Connection type head A: Female connector, M12, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PUR, halogen-free Description: Sensor/actuator cable, unshielded Application: Zones with oils and lubricants, Drag chain operation, Robot 	YF2A14- 050UB3XLEAX	2095608
\$	 Connection type head A: Female connector, M12, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF2A14- 020VB3XLEAX	2096234
•	 Connection type head A: Female connector, M12, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF2A14- 050VB3XLEAX	2096235

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

