

# KHK53-AXT00038

KH53

**MAGNETIC LINEAR ENCODERS** 





## Ordering information

Туре	Part no.
KHK53-AXT00038	1030050

Illustration may differ

Other models and accessories → www.sick.com/KH53



### Detailed technical data

#### Performance

Measuring range	0 m 38 m
Resolution	0.1 mm
Traversing speed	6.6 m/s <sup>1)</sup>
Repeatability	0.3 mm
Measurement accuracy	$\pm$ 1000 + ME (Tu-25 °C) Tk $\mu$ m $^{2)}$

<sup>1)</sup> If the max. traversing speed is exceeded or if the measuring elements are left, the corresponding error message is triggered (with SSI: FF FF FE hex).

### Interfaces

Communication interface	SSI
Position forming time	+ 0.8 ms
Interface, digital serial	SSI, 24 Bit, gray
Interface for parametrization	RS-422 Default OFF Four wire transmission, asynchrony, full duplex Data format: 1 start bit, 8 data bits, 1 stop bit, no parity Data protocol: ASCII, Baud rate 9600 RS-422

## Electrical data

Initialization time	2 s
Supply voltage	10 V 32 V
Current consumption	250 mA
Connection type	Cable, 12-wire, 5 m
MTTFd: mean time to dangerous failure	45 years (EN ISO 13849) <sup>1)</sup>

<sup>1)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of components, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

## Mechanical data

Weight	2.4 kg
Length of measuring element	See calculation example
Position tolerance	± 10 mm, see positional tolerances diagram
Read head material	AlMgSiPbF28

 $<sup>^{2)}</sup>$  If a positional tolerance of  $\pm$  1 mm is observed relative to the nominal distance in the N and Y directions within a measuring element relative to the starting point of this element ME = length of measuring element Tu = ambient temperature in °C. Tk = coefficient of thermal expansion (28  $\mu$ m/°C/m).

## Ambient data

EMC	According to EN 61000-6-2 and EN 61000-6-4 <sup>1)</sup>
Enclosure rating	IP66 (IEC 60529)
Operating temperature range	-20 °C +60 °C
Storage temperature range	-40 °C +85 °C
Resistance to shocks	30 g, 10 ms (DIN EN 60 068-2-27)
Resistance to vibration	10 g, 20 Hz 250 Hz (EN 60068-2-6)


 $<sup>^{1)}\,\</sup>mathrm{EMC}$  according to the standards quoted is achieved if shielded cables are used.

## Classifications

eCl@ss 5.0	27270705
eCl@ss 5.1.4	27270705
eCl@ss 6.0	27270705
eCl@ss 6.2	27270705
eCl@ss 7.0	27270705
eCl@ss 8.0	27270705
eCl@ss 8.1	27270705
eCl@ss 9.0	27270705
eCl@ss 10.0	27270705
eCl@ss 11.0	27270705
eCl@ss 12.0	27274304
ETIM 5.0	EC002544
ETIM 6.0	EC002544
ETIM 7.0	EC002544
ETIM 8.0	EC002544
UNSPSC 16.0901	41111613


## Dimensional drawing (Dimensions in mm (inch))

## SSI read head



### Position tolerance

KH53




All dimensions in mm (inch)


The operating reliability and accuracy of the measuring system depends on (amongst other things) compliance with the position tolerances. Magnetic or magnetizable materials are not permitted within 80 mm of the encoder or the measuring element.

- ① Read head
- ② Measuring element


End of measurement path



Start of measuring path




## Assembly note



Only use non ferro-magnetic materials for the assembly base of the read head. A separation distance of 80 mm must be observed for ferro-magnetic materials (e.g., iron).

## Length of measuring element

KH53 SSI



Measring range up to	Read head length	Length of measuring ele- ment including distance	Mounting systems per mea- suring element (suggestion)
39.90 m	0.866 m	2.304 m Identification letters A1 ≤ A18	4 clamp holders or 8 mounting brackets
107.40 m	1.051 m	1.8688 m Identification letters B1 ≤ B58	3 clamp holders or 6 mounting brackets
351.20 m	1.376 m	2.5088 m Identification letters C1 ≤ C141	4 clamp holders or 8 mounting brackets
1676.40 m	2.026 m	1.9072 m Identification letters D1 ≤ D880	3 clamp holders or 6 mounting brackets
The dimensions given are slightly rounded.			

## Recommended accessories

Other models and accessories → www.sick.com/KH53

	Brief description	Туре	Part no.	
Programming	Programming and configuration tools			
	Programming tool for ATM60, ATM90, and KH53	PGT-01-S	1030111	
Mounting brad	ckets and plates			
	Mounting bracket for KH53 measuring elements, without mounting hardware for the background	BEF-WK-KHT53	2029159	
Plug connecto	ors and cables			
	Head A: cable Head B: Flying leads Cable: SSI, Incremental, PUR, halogen-free, shielded	LTG-2512-MW	6027531	
<b>**</b>	Head A: cable Head B: Flying leads Cable: SSI, TTL, HTL, Incremental, PUR, halogen-free, shielded	LTG-2612-MW	6028516	
->	Head A: female connector, M23, 12-pin, straight Head B: Flying leads Cable: SSI, RS-422, TTL, HTL, PUR, halogen-free, shielded, 3 m	DOL-2312- G03MMA1	2029201	
	Head A: female connector, M23, 12-pin, straight Head B: Flying leads Cable: SSI, RS-422, TTL, HTL, PUR, halogen-free, shielded, 5 m	DOL-2312- G05MMA1	2029202	
	Head A: female connector, M23, 12-pin, straight Head B: Flying leads Cable: SSI, RS-422, TTL, HTL, PUR, halogen-free, shielded, 10 m	DOL-2312- G10MMA1	2029203	
	Head A: female connector, M23, 12-pin, straight Head B: Flying leads Cable: SSI, RS-422, TTL, HTL, PUR, halogen-free, shielded, 1.5 m	DOL-2312- G1M5MA1	2029200	

## MAGNETIC LINEAR ENCODERS

	Brief description	Туре	Part no.
	Head A: female connector, M23, 12-pin, straight Head B: Flying leads Cable: SSI, RS-422, PUR, halogen-free, shielded, 20 m	DOL-2312- G20MMA1	2029204
	Head A: female connector, M23, 12-pin, straight Head B: Flying leads Cable: SSI, RS-422, PUR, halogen-free, shielded, 30 m	DOL-2312- G30MMA1	2029205
	Head A: female connector, M23, 9-pin, straight Cable: HIPERFACE <sup>®</sup> , SSI, Incremental, shielded	DOS-2309-G	6028533
	Head A: female connector, M23, 12-pin, straight Cable: HIPERFACE <sup>®</sup> , SSI, Incremental, shielded	DOS-2312-G	6027538
(H=0)	Head A: female connector, M23, 12-pin, angled Cable: HIPERFACE <sup>®</sup> , SSI, Incremental, shielded	DOS-2312-W01	2072580
	Head A: male connector, M23, 12-pin, straight Cable: HIPERFACE <sup>®</sup> , SSI, Incremental, RS-422, shielded	STE-2312-G	6027537
Terminal and	alignment brackets		
	Spacer for KHT53, without mounting hardware for the background	BEF-KHA-KHT53	2042468
Magnetic linea	ar encoders		
	• System part: Mounting gauge • Measuring range: 0 m 38 m	KHM53-XXX00038	1030057
	<ul> <li>System part: Measuring element</li> <li>Measuring range: 0 m 38 m</li> <li>Code type: Coded</li> </ul>	KHT53-XXX00038	1030055
	<ul> <li>System part: Measuring element</li> <li>Measuring range: 0 m 38 m</li> <li>Code type: Universal configurable</li> </ul>	KHU53-XXX00038	1030056

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

