

WSE4FP-1G312100ZZZ w4

MINIATURE PHOTOELECTRIC SENSORS





Ordering information

Туре	Part no.
WSE4FP-1G312100ZZZ	1120403

Other models and accessories → www.sick.com/W4

Illustration may differ



Detailed technical data

Features

Functional principle	Through-beam photoelectric sensor
Sensing range	
Sensing range min.	0 m
Sensing range max.	10 m
Maximum distance range from receiver to sender (operating reserve 1)	0 m 10 m
Recommended distance range from receiver to sender (operating reserve 2)	0 m 7.5 m
Recommended sensing range for the best per- formance	0 m 7.5 m
Emitted beam	
Light source	PinPoint LED
Type of light	Visible red light
Shape of light spot	Point-shaped
Light spot size (distance)	Ø 40 mm (1,000 mm)
Maximum dispersion of the emitted beam around the standardized transmission axis (squint angle)	< +/- 1.5° (at Ta = +23 °C)
Key LED figures	
Normative reference	EN 62471:2008-09 IEC 62471:2006, modified
LED risk group marking	Free group
Wave length	635 nm
Average service life	100,000 h at $T_a = +25 ^{\circ}\text{C}$

Adjustment	
Wire/pin	For deactivation of the sender and execution of test logic
Indication	
LED blue	BluePilot: Alignment aid
LED green	Operating indicator Static on: power on
LED yellow	Status of received light beam Static on: object not present Static off: object present
Part number of individual components	WS04FP-1G3ZZ1A0ZZZ, 2121133 WE04FP-1G312100ZZZ, 2121134

Safety-related parameters

MTTF _D	574 years
DC _{avg}	0 %
T _M (mission time)	20 years

Electrical data

Ripple \$\(5 \) Vpp \\ \text{DC-12 (According to EN 60947-5-2)} \\ \text{DC-13 (According to EN 60947-5-2)} \\ \text{Current consumption} \\ \text{S O mA, without load. At U}_B = 24 \text{V} \\ \text{Protection class} \\ \text{Digital output} \\ \text{Number Type} \\ \text{Signal voltage PNP HIGH/LOW} \\ \text{Signal voltage PNP HIGH/LOW} \\ \text{Approx. U}_B \cdot 2.5 \text{V} \text{O V} \\ \text{Approx. U}_B \cdot 2.5 \text{V} \\ \text{O UmA} \\ \text{Approx. U}_B \cdot 2.5 \text{V} \\ \text{O Umaker of the current I}_{max.} \\ \text{Circuit protection outputs} \\ \text{Response time} \\ \text{Switching frequency} \\ \text{Switching frequency} \\ \text{Input, sender off, LOW active} \\ \text{Pin/Wire assignment, receiver} \end{array} \text{Input, sender off, LOW active} \end{array}		
Usage category DC-12 (According to EN 60947-5-2) DC-13 (According to EN 60947-5-2) DC-13 (According to EN 60947-5-2) Current consumption S 20 mA, without load. At U _B = 24 V Protection class III Number Type Push-pull: PNP/NPN Signal voltage PNP HIGH/LOW Approx. U _B -2.5 V / 0 V Signal voltage NPN HIGH/LOW Approx. U _B / < 2.5 V Output current I _{max} . Circuit protection outputs Reverse polarity protected Overcurrent protected Short-circuit protected Overcurrent protected Short-circuit protected Shor	Supply voltage U _B	10 V DC 30 V DC ¹⁾
DC-13 (According to EN 60947-5-2) Current consumption Protection class III Number Type Push-pull: PNP/NPN Signal voltage PNP HIGH/LOW Signal voltage NPN HIGH/LOW Output current I _{max.} Circuit protection outputs Response time Switching frequency Function of pin 4/black (BK) Pin/Wire assignment, receiver III 1 Push-pull: PNP/NPN Approx. U _B / 2.5 V / 0 V App	Ripple	≤ 5 V _{pp}
Protection class Digital output Number Type Push-pull: PNP/NPN Signal voltage PNP HIGH/LOW Signal voltage NPN HIGH/LOW Output current I _{max} . Circuit protection outputs Reverse polarity protected Overcurrent protected Short-circuit protecte	Usage category	, ,
Number Type Push-pull: PNP/NPN Signal voltage PNP HIGH/LOW Signal voltage NPN HIGH/LOW Output current I _{max} Circuit protection outputs Response time Switching frequency Function of pin 4/black (BK) Pin/Wire assignment, receiver Number 1 Approx. U _B / 2.5 V / 0 V Approx. U _B / 2.5 V \$\frac{2}{100 \text{ mA}}\$ Reverse polarity protected Overcurrent protected Short-circuit protected	Current consumption	\leq 20 mA, without load. At U _B = 24 V
Number Type Push-pull: PNP/NPN Signal voltage PNP HIGH/LOW Approx. U _B -2.5 V / 0 V Signal voltage NPN HIGH/LOW Approx. U _B / < 2.5 V Output current I _{max.} ≤ 100 mA Circuit protection outputs Reverse polarity protected Overcurrent protected Short-circuit protected Short-circuit protected Switching frequency Switching frequency 1,000 Hz ²) Pin/Wire assignment, sender Function of pin 4/black (BK) Input, sender off, LOW active	Protection class	III
Type Signal voltage PNP HIGH/LOW Approx. U _B -2.5 V / 0 V Approx. U _B / < 2.5 V Output current I _{max} . ≤ 100 mA Circuit protection outputs Response time Switching frequency Function of pin 4/black (BK) Push-pull: PNP/NPN Approx. U _B -2.5 V / 0 V Approx. U _B / < 2.5 V ≤ 100 mA Reverse polarity protected Overcurrent protected Short-circuit protected	Digital output	
Signal voltage PNP HIGH/LOW Signal voltage NPN HIGH/LOW Approx. $U_B / 2.5 \text{ V} / 0 \text{ V}$ Approx. $U_B / 2.5 \text{ V} / 0 \text{ V}$ Output current I_{max} . Circuit protection outputs Reverse polarity protected Overcurrent protected Short-circuit protected Fin/Wire assignment, sender Function of pin 4/black (BK) Input, sender off, LOW active	Number	1
Signal voltage NPN HIGH/LOW Output current I_{max} . $\leq 100 \text{ mA}$ Circuit protection outputs Reverse polarity protected Overcurrent protected Short-circuit protected $\leq 500 \mu \text{ switching frequency}$ Pin/Wire assignment, sender Function of pin 4/black (BK) Input, sender off, LOW active	Туре	Push-pull: PNP/NPN
Output current I _{max.} ≤ 100 mA Circuit protection outputs Reverse polarity protected Overcurrent protected Short-circuit protected Input Switching frequency Input Switching fr	Signal voltage PNP HIGH/LOW	Approx. U_B -2.5 V / 0 V
Circuit protection outputs Reverse polarity protected Overcurrent protected Short-circuit protected Short-circuit protected Response time ≤ 500 µs 1,000 Hz ²⁾ Pin/Wire assignment, sender Function of pin 4/black (BK) Input, sender off, LOW active Pin/Wire assignment, receiver	Signal voltage NPN HIGH/LOW	Approx. $U_B / < 2.5 V$
Overcurrent protected Short-circuit protected Short-circuit protected Response time Switching frequency 1,000 Hz ²⁾ Pin/Wire assignment, sender Function of pin 4/black (BK) Input, sender off, LOW active Pin/Wire assignment, receiver	Output current I _{max.}	≤ 100 mA
Switching frequency 1,000 Hz ²⁾ Pin/Wire assignment, sender Function of pin 4/black (BK) Input, sender off, LOW active Pin/Wire assignment, receiver	Circuit protection outputs	Overcurrent protected
Pin/Wire assignment, sender Function of pin 4/black (BK) Input, sender off, LOW active Pin/Wire assignment, receiver	Response time	≤ 500 µs
Function of pin 4/black (BK) Input, sender off, LOW active Pin/Wire assignment, receiver	Switching frequency	1,000 Hz ²⁾
Pin/Wire assignment, receiver	Pin/Wire assignment, sender	
	Function of pin 4/black (BK)	Input, sender off, LOW active
Function of pin 4/black (BK) Digital output, light switching, object present → output 0 LOW 3)	Pin/Wire assignment, receiver	
	Function of pin 4/black (BK)	Digital output, light switching, object present \rightarrow output Q LOW $^{3)}$

¹⁾ Limit values.

Mechanical data

Housing	Rectangular
Design detail	Flat
Dimensions (W x H x D)	16 mm x 40.1 mm x 12.1 mm

²⁾ With light/dark ratio 1:1.

³⁾ This switching output must not be connected to another output.

Connection	Cable, 3-wire, 2 m
Connection detail	
Deep-freeze property	Do not bend below 0 °C
Conductor size	0.14 mm ²
Cable diameter	Ø 3.4 mm
Length of cable (L)	2 m
Material	
Housing	Plastic, VISTAL®
Front screen	Plastic, PMMA
Cable	PVC
Weight	Approx. 30 g
Maximum tightening torque of the fixing screws	0.4 Nm

Ambient data

Enclosure rating	IP66 (EN 60529) IP67 (EN 60529)
Ambient operating temperature	-40 °C +60 °C
Ambient temperature, storage	-40 °C +75 °C
Typ. Ambient light immunity	Artificial light: $\leq 15,000 \text{ lx}$ Sunlight: $\leq 50,000 \text{ lx}$
Shock resistance	30 g, 11 ms (3 positive and 3 negative shocks along X, Y, Z axes, 18 total shocks (EN60068-2-27))
Vibration resistance	10 Hz 1,000 Hz (Amplitude 1 mm, 3 x 30 min (EN60068-2-6))
Air humidity	35 % 95 %, Relative humidity (no condensation)
Electromagnetic compatibility (EMC)	EN 60947-5-2
Resistance to cleaning agent	ECOLAB
UL File No.	NRKH.E181493 & NRKH7.E181493

Classifications


ECLASS 5.0	27270901
ECLASS 5.1.4	27270901
ECLASS 6.0	27270901
ECLASS 6.2	27270901
ECLASS 7.0	27270901
ECLASS 8.0	27270901
ECLASS 8.1	27270901
ECLASS 9.0	27270901
ECLASS 10.0	27270901
ECLASS 11.0	27270901
ECLASS 12.0	27270901
ETIM 5.0	EC002716
ETIM 6.0	EC002716
ETIM 7.0	EC002716
ETIM 8.0	EC002716

UNSPSC 16.0901

39121528

Adjustments

Display and adjustment elements



- ① LED blue
- ② LED green
- 3 LED yellow

Connection type

Cable, 3-wire






- ① Sender
- ② Receiver

Connection diagram


Cd-519




- ① Sender
- ② Receiver

Truth table


Push-pull: PNP/NPN - dark switching Q




Push-pull: PNP/NPN - light switching Q




Characteristic curve



Light spot size





Sensing range diagram



- A = Sensing range min. in m
- B = Sensing range max. in m
- C = Maximum distance range from receiver to sender
- D = Recommended distance range from receiver to sender
- Recommended sensing range for the best performance

Dimensional drawing (Dimensions in mm (inch))





- ① Center of optical axis
- ② M3 mounting hole
- 3 Connection
- ④ Display and adjustment elements

Recommended accessories

Other models and accessories → www.sick.com/W4

	Brief description	Туре	Part no.	
Mounting bra				
h.c	Mounting bracket for wall mounting, Stainless steel 1.4571, mounting hardware included	BEF-W4-A	2051628	
Plug connecto	Plug connectors and cables			
	 Connection type head A: Male connector, M8, 3-pin, straight Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: 0.14 mm² 0.5 mm² 	STE-0803-G	6037322	

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

