


Ø

TEMPERATURE SENSORS



TBT-1PAS10253PZ | TBT

TEMPERATURE SENSORS



Detailed technical data

Features

Measuring range	-50 °C +150 °C
Sensor element	Pt100
Output signal	Pt100, 4-wire

Mechanics/electronics

Process connectionCompression fitting G ¼ B, CrNi stainless steel ferruleInsertion length/diameter of probe25 mm / 3 mmWetted partsStainless steel 1.4571Pressure resistanceMax. 100 bar with supplied compression fitting with stainless steel ferruleHousing materialAluminumConnection typecable gland M16 x 1.5 ¹)Enclosure ratingIP67 ²)Measuring current0.3 mA 1 mAElectrical safetyProtection class III, dielectric strength: 100 VProtection class IIICentorificateWeightCa. 155 g (depending on configuration)		
Wetted partsStainless steel 1.4571Pressure resistanceMax. 100 bar with supplied compression fitting with stainless steel ferruleHousing materialAluminumConnection typeCable gland M16 x 1.5 ¹⁾ Enclosure ratingIP67 ²⁾ Measuring current0.3 mA 1 mAElectrical safetyProtection class: III, dielectric strength: 100 VProtection class IIIQ004/108/EC, EN 61326-2-3RoHS certificateIWeightCa. 155 g (depending on configuration)	Process connection	Compression fitting G 1/4 B, CrNi stainless steel ferrule
Pressure resistanceMax. 100 bar with supplied compression fitting with stainless steel ferruleHousing materialAluminumConnection typeCable gland M16 x 1.5 ¹⁾ Enclosure ratingIP67 ²⁾ Measuring current0.3 mA 1 mAElectrical safetyProtection class III, dielectric strength: 100 VProtection class IIIJCE-conformity2004/108/EC, EN 61326-2-3RoHS certificateIWeightCa 155 g (depending on configuration)	Insertion length/diameter of probe	25 mm / 3 mm
Housing materialAluminumConnection typeCable gland M16 x 1.5 ¹⁾ Enclosure ratingIP67 ²⁾ Measuring current0.3 mA 1 mAElectrical safetyProtection class: III, dielectric strength: 100 VProtection class IIIGE-conformity2004/108/EC, EN 61326-23RoHS certificateWeightCa. 155 g (depending on configuration)	Wetted parts	Stainless steel 1.4571
Connection typeCable gland M16 x 1.5 ¹)Enclosure ratingIP67 ²)Measuring current0.3 mA 1 mAElectrical safetyProtection class: III, dielectric strength: 100 VProtection class III✓CE-conformity2004/108/EC, EN 61326-23RoHS certificate✓WeightCa. 155 g (depending on configuration)	Pressure resistance	Max. 100 bar with supplied compression fitting with stainless steel ferrule
Enclosure ratingIP67 ² Measuring current0.3 mA 1 mAElectrical safetyProtection class: III, dielectric strength: 100 VProtection class III✓CE-conformity2004/108/EC, EN 61326-2-3RoHS certificate✓WeightCa. 155 g (depending on configuration)	Housing material	Aluminum
Measuring current0.3 mA 1 mAElectrical safetyProtection class: III, dielectric strength: 100 VProtection class III✓CE-conformity2004/108/EC, EN 61326-2-3RoHS certificate✓WeightCa. 155 g (depending on configuration)	Connection type	Cable gland M16 x 1.5 $^{1)}$
Electrical safety Protection class: III, dielectric strength: 100 V Protection class III ✓ CE-conformity 2004/108/EC, EN 61326-2-3 RoHS certificate ✓ Weight Ca. 155 g (depending on configuration)	Enclosure rating	IP67 ²⁾
Protection class III ✓ CE-conformity 2004/108/EC, EN 61326-2-3 RoHS certificate ✓ Weight Ca. 155 g (depending on configuration)	Measuring current	0.3 mA 1 mA
CE-conformity 2004/108/EC, EN 61326-2-3 RoHS certificate ✓ Weight Ca. 155 g (depending on configuration)	Electrical safety	Protection class: III, dielectric strength: 100 V
RoHS certificate ✓ Weight Ca. 155 g (depending on configuration)	Protection class III	✓
Weight Ca. 155 g (depending on configuration)	CE-conformity	2004/108/EC, EN 61326-2-3
	RoHS certificate	✓
In the section of the	Weight	Ca. 155 g (depending on configuration)
initialization time < 1 ms	Initialization time	< 1 ms

¹⁾ The enclosure rating classes specified only apply while the thermometer is connected with female connectors that provide the corresponding enclosure rating. ²⁾ IP enclosure rating as per IEC 60529.

Performance

Accuracy of sensor element	Class A according to IEC 60751
Transmitter accuracy	≤ ± 0.1 % of span
Transmitter linearity	≤ 0.1 % of span
Response time	Response time t_{50} : \leq 5.8 s ¹⁾ Response time t_{90} : \leq 15.5 s ¹⁾

¹⁾ Depending on sensor configuration, according to IEC 60751.

TBT-1PAS10253PZ | TBT

TEMPERATURE SENSORS

Ambient data


Ambient temperature	-40 °C +125 °C
Storage and transport temperature	-40 °C +60 °C
Shock resistance according to IEC 60751	500 g
Vibration resistance according to IEC 60751	3 g

Classifications

ECLASS 5.0	27200208
ECLASS 5.1.4	27200208
ECLASS 6.0	27200208
ECLASS 6.2	27200208
ECLASS 7.0	27200208
ECLASS 8.0	27200208
ECLASS 8.1	27200208
ECLASS 9.0	27200208
ECLASS 10.0	27200208
ECLASS 11.0	27200208
ECLASS 12.0	27200208
ETIM 5.0	EC002994
ETIM 6.0	EC002994
ETIM 7.0	EC002994
ETIM 8.0	EC002994
UNSPSC 16.0901	41112211

Dimensional drawing (Dimensions in mm (inch))


Dimensional drawing: zylindrical threads




TBT-1PAS10253PZ | TBT

TEMPERATURE SENSORS

Dimensional drawing: conical threads




Dimensional drawing: housing, without process connection



Connection type

Cable entry M16 x 1.5, cable cross-section up to 0.75 mm2, output signal Pt100



SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

