

DBS60E-S4CA00S87

DBS60

**INCREMENTAL ENCODERS** 



Illustration may differ

### Ordering information

Туре	Part no.
DBS60E-S4CA00S87	1092607

Other models and accessories → www.sick.com/DBS60



#### Detailed technical data

#### **Features**

Special device	✓
Specialty	Shaft 10 x 19 mm round Face mount flange with M3 & M4 Connector M23, 12-pin, radial with customer specific pin allocation
Standard reference device	DBS60E-S4CA05000, 1075365

#### Performance

Pulses per revolution	5,000
Measuring step	≤ 90°, electric/pulses per revolution
Measuring step deviation	± 36° / pulses per revolution
Error limits	Measuring step deviation x 3
Duty cycle	≤ 0.5 ± 10 %

#### Interfaces

Communication interface	Incremental
Communication Interface detail	TTL / RS-422
Number of signal channels	6-channel
Initialization time	< 5 ms <sup>1)</sup>
Output frequency	+ 300 kHz <sup>2)</sup>
Load current	≤ 30 mA, per channel
Power consumption	≤ 0.5 W (without load)

 $<sup>^{1)}</sup>$  Valid signals can be read once this time has elapsed.

#### Electrical data

Connection type	Male connector, M23, 12-pin, radial, Customer-specific pin assignment	
Supply voltage	10 30 V	
Reference signal, number	1	
Reference signal, position	90°, electric, logically gated with A and B	
Reverse polarity protection	<b>√</b>	

 $<sup>^{1)}</sup>$  Short-circuit opposite to another channel or GND permissible for max. 60 s. No protection signal against U<sub>S</sub>.

 $<sup>^{2)}</sup>$  Up to 450 kHz on request.

<sup>2)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of components, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

Short-circuit protection of the outputs	<b>√</b> ¹)
MTTFd: mean time to dangerous failure	500 years (EN ISO 13849-1) <sup>2)</sup>

 $<sup>^{1)}</sup>$  Short-circuit opposite to another channel or GND permissible for max. 60 s. No protection signal against U<sub>S</sub>.

#### Mechanical data

Mechanical design	Solid shaft, face mount flange
Shaft diameter	10 mm Round
Shaft length	19 mm
Flange type / stator coupling	Flange with 3 x M3 and 3 x M4
Weight	$+ 0.3 \ kg^{\ 1)}$
Shaft material	Stainless steel
Flange material	Aluminum
Housing material	Aluminum
Start up torque	+ 1.2 Ncm (+20 °C)
Operating torque	1.1 Ncm (+20 °C)
Permissible shaft loading	100 N (radial) $^{2)}$ 50 N (axial) $^{2)}$
Operating speed	6,000 min <sup>-1 3)</sup>
Maximum operating speed	9,000 min <sup>-1</sup> <sup>4)</sup>
Moment of inertia of the rotor	33 gcm <sup>2</sup>
Bearing lifetime	3.6 x 10 <sup>9</sup> revolutions
Angular acceleration	≤ 500,000 rad/s²

 $<sup>^{1)}</sup>$  Based on encoder with male connector or cable with male connector.

#### Ambient data

EMC	According to EN 61000-6-2 and EN 61000-6-3	
Enclosure rating	IP67, housing side (IEC 60529) <sup>1)</sup> IP65, shaft side (IEC 60529)	
Permissible relative humidity	90 % (Condensation not permitted)	
Operating temperature range	-30 °C +85 °C, at more than 3,000 pulses per revolution <sup>2)</sup>	
Storage temperature range	-40 °C +100 °C, without package	
Resistance to shocks	250 g, 3 ms (EN 60068-2-27)	
Resistance to vibration	30 g, 10 Hz 2,000 Hz (EN 60068-2-6)	

 $<sup>^{1)}</sup>$  With mating connector fitted.

#### Classifications

ECLASS 5.0	27270501
------------	----------

<sup>2)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of components, average ambient temperature 40°C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

 $<sup>^{2)}</sup>$  Higher values are possible using limited bearing life.

 $<sup>^{3)}</sup>$  Allow for self-heating of 3.2 K per 1,000 rpm when designing the operating temperature range.

<sup>&</sup>lt;sup>4)</sup> Maximum speed which does not cause mechanical damage to the encoder. Impact on the service life and signal quality is possible. Please note the maximum output frequency.


 $<sup>^{2)}</sup>$  These values relate to all mechanical versions including recommended accessories unless otherwise noted.

# DBS60E-S4CA00S87 | DBS60

INCREMENTAL ENCODERS

ECLASS 5.1.4	27270501
ECLASS 6.0	27270590
ECLASS 6.2	27270590
ECLASS 7.0	27270501
ECLASS 8.0	27270501
ECLASS 8.1	27270501
ECLASS 9.0	27270501
ECLASS 10.0	27270501
ECLASS 11.0	27270501
ECLASS 12.0	27270501
ETIM 5.0	EC001486
ETIM 6.0	EC001486
ETIM 7.0	EC001486
ETIM 8.0	EC001486
UNSPSC 16.0901	41112113

## Dimensional drawing (Dimensions in mm (inch))



## PIN assignment


View of M23 device connector on cable



Pin, 12-pin, M23		
connector	TTI/HTL signal	Explanation
1	A	Signal cable
2	· A	Signal cable
3	N.C.	Not assigned
4	В	Signal cable
5	•в	Signal cable
6	N.C.	Not assigned
7	Z	Signal cable
8	·z	Signal cable
9	N.C.	Not assigned
10	N.C.	Not assigned
11	+U <sub>S</sub>	Supply voltage (volt-free to housing)
12	GND	Ground connection of the encoder
Shield	Shield	Shield connected to housing on side of encoder. Connected to ground on side of control.

## Diagrams





#### Recommended accessories

Other models and accessories → www.sick.com/DBS60

	Brief description	Туре	Part no.
Flanges			
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 50 mm servo flange, aluminum, including 3 flat head screws M4 x 10, Aluminum, including 3 countersunk screws M3 x 10	BEF-FA-036-050	2029160
6	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 60 mm square mounting plate, aluminum, including 3 flat head screws M4 x 8, Aluminum, including 3 countersunk screws M4 x 8	BEF-FA-036-060REC	2029162
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 58 mm square mounting plate with shock absorbers, aluminum, Aluminum	BEF-FA-036-060RSA	2029163

	Brief description	Туре	Part no.
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 63 mm square mounting plate, aluminum, including 3 flat head screws M4 x 10, Aluminum, including 3 countersunk screws M3 x 10	BEF-FA-036-063REC	2034225
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 100 mm servo flange with 60 mm centering hub, aluminum, Aluminum	BEF-FA-036-100	2029161
Mounting bra	ckets and plates		
4.	Mounting bracket for encoder with spigot 36 mm for face mount flange, mounting kit included	BEF-WF-36	2029164
	Mounting angle spring-loaded, for flange with centerring collar 36 mm, working temperature range –40 $^{\circ}$ +120 $^{\circ}$ C, Aluminum	BEF-WF36F	4084775
Other mounti	ng accessories		
	Aluminium measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 200 mm $$	BEF-MR010020R	2055224
	Aluminium measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 300 mm $$	BEF-MR010030R	2049278
	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 500 mm	BEF-MR010050R	2055227
	Aluminum measuring wheel with cross-knurled surface for 10 mm solid shaft, circumference 200 mm	BEF-MR10200AK	4084737
	Aluminum measuring wheel with smooth polyurethane surface for 10 mm solid shaft, circumference 200 mm	BEF-MR10200AP	4084738
	Aluminum measuring wheel with ridged polyurethane surface for 10 mm solid shaft, circumference 200 mm	BEF-MR10200APG	4084740
	Aluminum measuring wheel with studded polyurethane surface for 10 mm solid shaft, circumference 200 mm	BEF-MR10200APN	4084739
	Aluminum measuring wheel with cross-knurled surface for 10 mm solid shaft, circumference 500 mm	BEF-MR10500AK	4084733
	Aluminum measuring wheel with smooth polyurethane surface for 10 mm solid shaft, circumference 500 mm	BEF-MR10500AP	4084734
	Aluminum measuring wheel with ridged polyurethane surface for 10 mm solid shaft, circumference 500 mm	BEF-MR10500APG	4084736
	Aluminum measuring wheel with studded polyurethane surface for 10 mm solid shaft, circumference 500 mm	BEF-MR10500APN	4084735
	O-ring for measuring wheels (circumference 200 mm)	BEF-OR-053-040	2064061
	0-ring for measuring wheels (circumference 300 mm), 2x 0-ring	BEF-OR-083-050	2064076
	0-ring for measuring wheels (circumference 500 mm)	BEF-OR-145-050	2064074
3-8-6-8	SICK modular measuring wheel system for face mount flange encoder with S4 mechanical design (10 mm x 19 mm solid shaft), e.g., DFS60-S4: with 0-ring measuring wheel, circumference 200 mm	BEF-MRS-10-U	2085714

	Brief description	Туре	Part no.
	Flange adapter (adapts size 60 face mount flange encoder to bearing block with part. no. 2044591)	BEF-FA-036-050-019	2063378
	Bearing block for servo and face mount flange encoder. The heavy-duty bearing block is used to absorb very large radial and axial shaft loads. Particularly when using belt pulleys, chain sprockets, friction wheels. Operating speed max. 4,000 rpm^-1, axial shaft load 150 N, radial shaft load 250 N, bearing service life 3.6 x 10^9 revolutions	BEF-FA-LB1210	2044591
	Mounting kit for servo flange encoder on the bearing block, 1 bar coupling SKPS 1520 06/06 1 hexagon socket wrench SW1.5 DIN 911, 3 mounting eccentric BEMN 1242 49 3 screws M4 x 10 DIN 912,1 hexagon socket wrench SW3 DIN 911, 1 bar coupling SKPS 1520 06/06 1 hexagon socket wrench SW1.5 DIN 911, 3 mounting eccentric BEMN 1242 49 3 screws M4 x 10 DIN 912, 1 hexagon socket wrench SW3 DIN 911	BEF-MK-LB	5320872
Shaft adaptat	ion		
	Bellows coupling, shaft diameter 6 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular +/- 4°; max. speed 10,000 rpm, -30 °C to +120 °C, max. torque 120 Ncm; material: stainless steel bellows, aluminum hub	KUP-0610-B	5312982
10	Double loop coupling, shaft diameter 6 mm $/$ 10 mm, max. shaft offset: radially +/- 2,5 mm, axially +/-3 mm, angle +/- 10 degrees;max. speed 3.000 rpm, -30 to +80 degrees Celsius, torsional spring stiffness of 25 Nm/rad	KUP-0610-D	5326697
(,°	Spring washer coupling, shaft diameter 6 mm $/$ 10 mm, Maximum shaft offset: radial +/- 0.3 mm, axial +/- 0.4 mm, angular +/- 2.5°; max. speed 12,000 rpm, $-10^\circ$ to +80 °C, max. torque 60 Ncm; material: aluminum flange, glass fiber-reinforced polyamide membrane and hardened steel coupling pin	KUP-0610-F	5312985
	Bar coupling, shaft diameter 6 mm / 10 mm, max. shaft offset: radial $\pm$ 0,3 mm, axial $\pm$ 0,3 mm, angular $\pm$ 3°; max. speed 10.000 rpm, $-10^\circ$ to $+80^\circ$ C, max. torque: 80 Ncm, material: fiber-glass reinforced polyamide, aluminum hub	KUP-0610-S	2056407
10	Double loop coupling, shaft diameter 8 mm $/$ 10 mm, max. shaft offset: radially +/-0,25 mm, axially +/-0,4 mm, angle +/- 4 degrees;max. speed 10.000 rpm, -30 to +120 degrees Celsius, torsional spring stiffness of 150 Nm/rad	KUP-0810-D	5326704
	Claw coupling, shaft diameter 8 mm / 10 mm, damping element 80 shore blue, maximum shaft offset: radial $\pm$ 0.22 mm, axial $\pm$ 1 mm angular $\pm$ 1.3°, max. speed 19,000 rpm, angle of twist max. 10°, –30 °C to +80 °C, max. torque 800 Ncm, tightening torque of screws: ISO 4029 150 Ncm, material: aluminum flange, damping element: polyurethane	KUP-0810-J	2128267
	Bar coupling, shaft diameter 8 mm / 10 mm, max. shaft offset: radial $\pm$ 0,3 mm, axial $\pm$ 0,3 mm, angular $\pm$ 3°; max. speed 10.000 rpm, $-10^\circ$ to $+80^\circ$ C, max. torque: 80 Ncm, material: fiber-glass reinforced polyamide, aluminum hub	KUP-0810-S	5314178
	Bellows coupling, shaft diameter 10 mm/10 mm; maximum shaft offset: radial +/- $0.25$ mm, axial +/- $0.4$ mm, angular +/- $4^\circ$ ; max. revolutions 10,000 rpm, -30° to +120°C, max. torque 120 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1010-B	5312983
	Double loop coupling, shaft diameter 10 mm / 10 mm, Maximum shaft offset: radial +/- 2.5 mm, axial +/- 3 mm, angular +/- $10^\circ$ ; max. speed 3,000 rpm, -30° to +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1010-D	5326703
	Spring washer coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset, radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angle $\pm$ 2.5°, torsion spring stiffness 30 Nm/rad; material: aluminum flange, glass-fiber reinforced polyamide membrane and hardened steel coupling pin	KUP-1010-F	5312986
	Claw coupling, shaft diameter 10 mm / 10 mm, damping element 80 shore blue, maximum shaft offset: radial $\pm$ 0.22 mm, axial $\pm$ 1 mm angular $\pm$ 1.3°, max. speed 19,000 rpm, angle of twist max. 10°, $-30$ °C to +80°C, max. torque 800 Ncm, tightening torque of screws: ISO 4029 150 Ncm, material: aluminum flange, damping element: polyurethane	KUP-1010-J	2127054

	Brief description	Туре	Part no.
0	Bar coupling, shaft diameter 10 mm / 10 mm; maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; speed 10,000 rpm, $-10$ ° to $+80$ ° Celsius, max. torque 80 Ncm; material: glass fiber-reinforced polyamide, aluminum hub	KUP-1010-S	2056408
	Spring coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset: radial $\pm$ 1.5 mm, axial $\pm$ 1.0 mm, angular $\pm$ 5°, max. speed 3,000 rpm, -30° to +120 °Celsius, nominal torque 150 Ncm, rotational angle at half nominal torque, direction of rotation right viewed on driving shaft 40°, left viewed on driving shaft 60°, material: spring steel 1.0600 nickel plated, zinc die cast hubs	KUP-1010-W	5319914
	10~mm/12~mm; maximum shaft offset: radial +/- 0.25 mm, axial +/- 0.4 mm, angular +/- 4°; max. revolutions 10,000 rpm, -30° to +120 °C, max. torque 120 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1012-B	5312984
Others			
	<ul> <li>Connection type head A: Female connector, M23, 12-pin, straight, A-coded</li> <li>Signal type: HIPERFACE<sup>®</sup>, SSI, Incremental</li> <li>Description: HIPERFACE<sup>®</sup>, SSI, Incremental, shielded, Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: -40 °C +125 °C</li> <li>Connection systems: Solder connection</li> </ul>	DOS-2312-G02	2077057
	<ul> <li>Connection type head A: Female connector, M23, 12-pin, angled, A-coded</li> <li>Signal type: HIPERFACE<sup>®</sup>, SSI, Incremental</li> <li>Description: HIPERFACE<sup>®</sup>, SSI, Incremental, shielded, Head A: female connector, M23, 12-pin, angled, shielded, for cable diameter 4.2 mm 6.6 mm Head B: - Operating temperature: -20 °C +130 °C</li> <li>Connection systems: Solder connection</li> </ul>	DOS-2312-W01	2072580
	<ul> <li>Connection type head A: Female connector, M23, 12-pin, straight</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Incremental</li> <li>Cable: 2 m, 11-wire, PUR</li> <li>Description: Incremental, shielded, Head A: female connector, M23, 12-pin, straight Head B: cable Cable: incremental, PUR, shielded, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 1 x 0.14 mm², Ø 7.8 mm</li> </ul>	DOL-2312-G02MLA3	2030682
	<ul> <li>Connection type head A: Female connector, M23, 12-pin, straight</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Incremental</li> <li>Cable: 7 m, 11-wire, PUR</li> <li>Description: Incremental, shielded, Head A: female connector, M23, 12-pin, straight Head B: cable Cable: incremental, PUR, shielded, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 1 x 0.14 mm², Ø 7.8 mm</li> </ul>	DOL-2312-G07MLA3	2030685
	<ul> <li>Connection type head A: Female connector, M23, 12-pin, straight</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Incremental</li> <li>Cable: 10 m, 11-wire, PUR</li> <li>Description: Incremental, shielded, Head A: female connector, M23, 12-pin, straight Head B: cable Cable: incremental, PUR, shielded, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 1 x 0.14 mm², Ø 7.8 mm</li> </ul>	DOL-2312-G10MLA3	2030688
	<ul> <li>Connection type head A: Female connector, M23, 12-pin, straight</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Incremental</li> <li>Cable: 15 m, 11-wire, PUR</li> <li>Description: Incremental, shielded, Head A: female connector, M23, 12-pin, straight Head B: cable Cable: incremental, PUR, shielded, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 1 x 0.14 mm², Ø 7.8 mm</li> </ul>	DOL-2312-G15MLA3	2030692
	<ul> <li>Connection type head A: Female connector, M23, 12-pin, straight</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Incremental</li> <li>Cable: 20 m, 11-wire, PUR</li> <li>Description: Incremental, shielded, Head A: female connector, M23, 12-pin, straight Head B: cable Cable: incremental, PUR, shielded, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 1 x 0.14 mm², Ø 7.8 mm</li> </ul>	DOL-2312-G20MLA3	2030695

	Brief description	Туре	Part no.
	<ul> <li>Connection type head A: Female connector, M23, 12-pin, straight</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Incremental</li> <li>Cable: 25 m, 11-wire, PUR</li> <li>Description: Incremental, shielded, Head A: female connector, M23, 12-pin, straight Head B: cable Cable: incremental, PUR, shielded, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 1 x 0.14 mm², Ø 7.8 mm</li> </ul>	DOL-2312-G25MLA3	2030699
	<ul> <li>Connection type head A: Female connector, M23, 12-pin, straight</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Incremental</li> <li>Cable: 30 m, 11-wire, PUR</li> <li>Description: Incremental, shielded, Head A: female connector, M23, 12-pin, straight Head B: cable Cable: incremental, PUR, shielded, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 1 x 0.14 mm², Ø 7.8 mm</li> </ul>	DOL-2312-G30MLA3	2030702
	Connection type head A: Flying leads Connection type head B: Flying leads Signal type: SSI, Incremental, HIPERFACE® Cable: 8-wire, PUR, halogen-free Description: SSI, Incremental, HIPERFACE®, shielded Items supplied: By the meter	LTG-2308-MWENC	6027529
/	<ul> <li>Connection type head A: Flying leads</li> <li>Connection type head B: Flying leads</li> <li>Signal type: SSI, Incremental</li> <li>Cable: 11-wire, PUR</li> <li>Description: SSI, Incremental, shielded</li> <li>Items supplied: By the meter</li> </ul>	LTG-2411-MW	6027530
<b>\</b>	<ul> <li>Connection type head A: Flying leads</li> <li>Connection type head B: Flying leads</li> <li>Signal type: SSI, Incremental</li> <li>Cable: 12-wire, PUR, halogen-free</li> <li>Description: SSI, Incremental, shielded</li> <li>Items supplied: By the meter</li> </ul>	LTG-2512-MW	6027531
	<ul> <li>Connection type head A: Flying leads</li> <li>Connection type head B: Flying leads</li> <li>Signal type: SSI, TTL, HTL, Incremental</li> <li>Cable: 12-wire, UV and saltwater-resistant, PUR, halogen-free</li> <li>Description: SSI, TTL, HTL, Incremental, shielded, Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, UV and saltwater resistant, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 2 x 0.14 mm², Ø 7.8 mm</li> <li>Items supplied: By the meter</li> </ul>	LTG-2612-MW	6028516

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

