

IMB08-02BDSVU5K

IMB

INDUCTIVE PROXIMITY SENSORS



INDUCTIVE PROXIMITY SENSORS

Ordering information

Туре	Part no.
IMB08-02BDSVU5K	1082062

Included in delivery: BEF-MU-M08N (1)

Other models and accessories → www.sick.com/IMB

Illustration may differ



Detailed technical data

Features

Housing	Metric	
Housing	Short-body	
Thread size	M8 x 1	
Diameter	Ø 8 mm	
Sensing range S _n	2 mm	
Safe sensing range S _a	1.62 mm	
Installation type	Flush	
Switching frequency	4,000 Hz	
Connection type	Cable, 2-wire, 5 m	
Output function	NO	
Electrical wiring	DC 2-wire	
Enclosure rating	IP68 ¹⁾ IP69K ²⁾	
Special features	Resistant against coolant lubricants, Visual adjustment indicator, Temperature resistance	
Special applications	Zones with coolants and lubricants, Mobile machines, Difficult application conditions	
Items supplied	Mounting nut, V2A stainless steel, with locking teeth (2x)	

¹⁾ According to EN 60529.

Mechanics/electronics

Supply voltage	10 V DC 30 V DC
Ripple	≤ 10 %

 $^{^{1)}}$ At I_a = 30 mA.

²⁾ According to ISO 20653:2013-03.

 $^{^{2)}\,\}mathrm{At}\,\mathrm{I}_{\mathrm{a}}\,\mathrm{max}.$

 $^{^{\}rm 3)}$ Supply voltage ${\rm U}_{\rm B}$ and constant ambient temperature Ta.

⁴⁾ Of Sr

 $^{^{5)}}$ When using the non-toothed side of the nut.

 $^{^{6)}}$ Valid if toothed side of nut is used.

Voltage drop	\leq 4 V $^{1)}$ \leq 4.5 V $^{2)}$
Time delay before availability	≤ 100 ms
Hysteresis	3 % 20 %
Reproducibility	≤ 2 % ^{3) 4)}
Temperature drift (of S _r)	± 10 %
ЕМС	According to EN 60947-5-2
Continuous current I _a	≤ 100 mA
Off-state current	Typ. 0.8 mA (\leq 1.2 mA at Ub max and 100 $^{\circ}$ C)
Minimum load current	≥ 3 mA
Cable material	PUR
Conductor size	0.14 mm ²
Cable diameter	Ø 3 mm
Short-circuit protection	✓
Power-up pulse	≤ 5 ms
Shock and vibration resistance	$100\mathrm{g}/11\mathrm{ms}/1000$ cycles; $150\mathrm{g}/1$ Mio cycles; 10 Hz 55 Hz, $1\mathrm{mm}/55$ Hz 500 Hz / $15\mathrm{g}$
Ambient operating temperature	-40 °C +100 °C
Housing material	Stainless steel V2A, DIN 1.4305 / AISI 303
Sensing face material	Plastic, LCP
Housing length	32 mm
Thread length	28 mm
Tightening torque, max.	Typ. 7 Nm ⁵⁾ Typ. 14 Nm ⁶⁾
Protection class	III
UL File No.	E181493

 $^{^{1)}}$ At I_a = 30 mA.

Safety-related parameters

MTTF _D	1,030 years
DC _{avg}	0 %
T _M (mission time)	20 years

Reduction factors

Note	The values are reference values which may vary	
St37 steel (Fe)	1	
Stainless steel (V2A, 304)	Approx. 0.74	
Aluminum (AI)	Approx. 0.43	
Copper (Cu)	Approx. 0.33	

²⁾ At I_a max.

 $^{^{\}rm 3)}$ Supply voltage $\rm U_B$ and constant ambient temperature Ta.

⁴⁾ Of Sr

⁵⁾ When using the non-toothed side of the nut.

⁶⁾ Valid if toothed side of nut is used.

Brass (Br)	Approx. 0.46
------------	--------------

Installation note


Remark	Associated graphic see "Installation"
В	6.5 mm
C	8 mm
D	6 mm
F	16 mm


Classifications

ECLASS 5.0	27270101
ECLASS 5.1.4	27270101
ECLASS 6.0	27270101
ECLASS 6.2	27270101
ECLASS 7.0	27270101
ECLASS 8.0	27270101
ECLASS 8.1	27270101
ECLASS 9.0	27270101
ECLASS 10.0	27270101
ECLASS 11.0	27270101
ECLASS 12.0	27274001
ETIM 5.0	EC002714
ETIM 6.0	EC002714
ETIM 7.0	EC002714
ETIM 8.0	EC002714
UNSPSC 16.0901	39122230

Installation note

Flush installation





Connection diagram


Cd-012



Response diagram


Response diagram

Distance in mm (inch)




Functional principle

Installation aid



Dimensional drawing (Dimensions in mm (inch))

IMB08 Short-body housing, cable, flush



- ① Connection
- ② Display LED
- ③ Fastening nuts (2 x); width across 13, stainless steel V2A

Recommended accessories

Other models and accessories → www.sick.com/IMB

	Brief description	Туре	Part no.
Mounting brackets and plates			
	Mounting plate for M8 sensors, steel, zinc coated, without mounting hardware	BEF-WG-M08	5321722
	Mounting bracket for M8 sensors, steel, zinc coated, without mounting hardware	BEF-WN-M08	5321721
Others			
	Connection type head A: Female connector, M12, 4-pin, straight, A-coded Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: ≤ 0.75 mm² Application: Hygienic and washdown zones	DOS-1204-GN	6028357
	Connection type head A: Female connector, M12, 4-pin, angled, A-coded Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: ≤ 0.75 mm² Application: Hygienic and washdown zones	DOS-1204-WN	6028358
	Connection type head A: Male connector, M12, 4-pin, straight, A-coded Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: ≤ 0.75 mm² Application: Hygienic and washdown zones	STE-1204-GN	6028359
	Connection type head A: Male connector, M12, 4-pin, straight, A-coded Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: ≤ 0.75 mm² Note: For 2 cable connections Application: Hygienic and washdown zones	STE-1204-TN	6028360

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

