



SICK Sensor Intelligence.

**LEVEL SENSORS** 

LEVEL SENSORS



#### Ordering information

Туре	Part no.
LFP0500-A4BMB	1071078

2077391 included in delivery

Other models and accessories → www.sick.com/LFP\_Cubic





#### Detailed technical data

#### Features

Medium	Fluids
Measurement	Switch, Continuous
Design	Remote amplifier, length of cable 1 m
Probe type	Rod probe
Probe length	500 mm
Process pressure	-1 bar 10 bar
Process temperature	-20 °C +100 °C
RoHS certificate	✓
IO-Link	✓
cULus certificate	✓
Performance	
Feriormance	
Accuracy of sensor element	± 5 mm <sup>1)</sup>
	± 5 mm <sup>1)</sup> ≤ 2 mm
Accuracy of sensor element	
Accuracy of sensor element Reproducibility	≤ 2 mm
Accuracy of sensor element Reproducibility Resolution	≤ 2 mm < 2 mm
Accuracy of sensor element Reproducibility Resolution Response time	≤ 2 mm < 2 mm < 400 ms ≥ 5 for rod probe / cable probe
Accuracy of sensor element Reproducibility Resolution Response time Dielectricity constant	<pre>≤ 2 mm</pre> < 2 mm < 400 ms ≥ 5 for rod probe / cable probe ≥ 1.8 with coaxial tube
Accuracy of sensor element Reproducibility Resolution Response time Dielectricity constant Conductivity	<pre>≤ 2 mm &lt; 2 mm &lt; 400 ms &gt; 5 for rod probe / cable probe ≥ 1.8 with coaxial tube No limitation</pre>
Accuracy of sensor element Reproducibility Resolution Response time Dielectricity constant Conductivity Maximum level change	≤ 2 mm < 2 mm < 400 ms ≥ 5 for rod probe / cable probe ≥ 1.8 with coaxial tube No limitation ≤ 500 mm/s

 $^{\mbox{1)}}$  With water under reference conditions.

 $^{2)}\ensuremath{\,\text{With}}\xspace$  parameterized container with water under reference conditions, otherwise 40 mm.

1

Display

### Electronics

2.000.01.000	
Communication interface	IO-Link
Supply voltage	12 V DC 30 V DC <sup>1)</sup>
Power consumption	$\leq$ 100 mA at 24 V DC without output load
Initialization time	≤5s
Protection class	III
Connection type	Round connector M12 x 1, 5-pin
Length of cable	1 m
Output signal	1 x PNP + 1 x PNP/NPN + 4 mA 20 mA / 0 V 10 V
Output load	4 mA 20 mA < 500 Ohm at Uv > 15 V, 4 mA 20 mA < 350 Ohm at Uv > 12 V, 0 V 10 V > 750 Ohm at Uv 14 $\geq$ V
Hysteresis	Min. 2 mm, free adjustable
Output current	< 100 mA
Inductive load	<1H
Capacitive load	100 nF
Enclosure rating	IP67: EN 60529
Temperature drift	< 0.1 mm/K
Lower signal level	3.8 mA 4 mA
Upper signal level	20 mA 20.5 mA
EMC	EN 61326-2-3, 2014/30/EU

 $^{\left( 1\right) }$  All connections are polarity protected. All outputs are overload and short-circuit protected.

#### Mechanics

Wetted parts1.4404, PTFE FKMProcess connectionG ¾ AHousing materialPlastic PBTMax. probe load≤ 6 NmMaterial coaxial cablePVCLength coaxial cable1 m	
Housing materialPlastic PBTMax. probe load≤ 6 NmMaterial coaxial cablePVC	
Max. probe load≤ 6 NmMaterial coaxial cablePVC	
Material coaxial cable PVC	
Length coaxial cable 1 m	
Ambient data	
Ambient operating temperature -20 °C +60 °	2
Ambient temperature, storage -40 °C +80 °	2
Ambient temperature coaxial cable-20 °C +60 °	2
Classifications	
ECLASS 5.0 27200513	
ECLASS 5.1.4 27200513	
ECLASS 6.0 27200513	
ECLASS 6.2 27200513	
ECLASS 7.0 27200513	
ECLASS 8.0 27200513	
ECLASS 8.1 27200513	
ECLASS 5.1.4         27200513           ECLASS 6.0         27200513	

LEVEL SENSORS

ECLASS 9.0	27200513
ECLASS 10.0	27200513
ECLASS 11.0	27200513
ECLASS 12.0	27200513
ETIM 5.0	EC001447
ETIM 6.0	EC001447
ETIM 7.0	EC001447
ETIM 8.0	EC001447
UNSPSC 16.0901	41113710

#### Type code

#### Type code


#### Probe length in mm Without probe 0025 200 mm (rod probe in 10 mm increments; cable probe in 1,000 mm 0200 increments) 4000 4,000 mm Process connection / probe version G 3/4 A / rod probe 1.4404 interchangeable, 100 °C; 10 bar Α 3/4" NPT / rod probe 1.4404 interchangeable, 100 °C; В 10 bar Е G 3/4 A / 3 mm cable probe, 1.4404 interchangeable, 100 °C; 10 bar F $^{3}\!4"$ NPT / 3 mm cable probe, 1.4404 interchangeable, 100 °C; 10 bar Housing / display / device connection Plastic housing with display / 1 x M12 male connec-4 tor / 5-pin 5 Plastic housing with display / 1 x M12 male connector / 8-pin Application type / design N Standard В Remote amplifier; length of cable 1 m C Remote amplifier; length of cable 2 m D Remote amplifier; length of cable 3.3 m Signal output M 4 ... 20 mA / 0 ... 10 V switchable Switching output B 1 x PNP + 1 x PNP/NPN С 1 x PNP + 3 x PNP/NPN Device type Standard LABS-free L LFP М

Not all variants of the type code can be combined!


Dependence between length of coaxial cable and probe length

Length of coaxial cable (mm)	Max. probe length (mm) foam mode deactivated	Max. probe length (mm) foam mode active
1000	4,000	2000
2000	3,000	1500
3300	1,000	500

#### Dimensional drawing (Dimensions in mm (inch))




#### Connection type




- ① L<sup>+</sup>: Supply voltage, brown
- O Q<sub>A</sub>: Analog current-/voltage output, white
- ③ M: Ground, reference ground for current-/voltage output, blue
- ④ C/Q1: Switching output 1, PNP/IO-Link-communication, black
- $\bigcirc$  Q<sub>2</sub>: Switching output 2, PNP/NPN, grey

LEVEL SENSORS

#### Instruction for installation




Installation in a metal immersion tube or metal bypass



LEVEL SENSORS

Installation in a metal tank



#### **Recommended accessories**

Other models and accessories → www.sick.com/LFP\_Cubic

	Brief description	Туре	Part no.
Spare parts			
	Spare probe for LFP Cubic, probe length 1000 mm, material 1.4404/316L, diameter 7 mm	BEF-ER- SN1000-LFPC	2065700
	Spare probe for LFP Cubic, probe length 2000 mm, material 1.4404/316L, diameter 7 mm	BEF-ER- SN2000-LFPC	2065701
and and	Spare coaxial cable for LFP Cubic, separate amplifier, length 1 m $$	CBL-CX-001000-LFPC	2077792

LEVEL SENSORS

	Brief description	Туре	Part no.		
Device protec	Device protection (mechanical)				
	Coaxial tube for LFP with process connection G $^{3}\!$	LFPCT-0200G1	2068141		
	Coaxial tube for LFP with process connection G 3/4, process connection of coaxial tube G 3/4, material 1.4571/316TI, for probe length 300 mm	LFPCT-0300G1	2068142		
	Coaxial tube for LFP with process connection G 3/4, process connection of coaxial tube G 3/4, material 1.4571/316TI, for probe length 400 mm	LFPCT-0400G1	2068143		
	Coaxial tube for LFP with process connection G 3/4, process connection of coaxial tube G 3/4, material 1.4571/316TI, for probe length 500 mm	LFPCT-0500G1	2068144		
	Coaxial tube for LFP with process connection G 3/4, process connection of coaxial tube G 3/4, material 1.4571/316TI, for probe length 600 mm	LFPCT-0600G1	2068145		
	Coaxial tube for LFP with process connection G 3/4, process connection of coaxial tube G 3/4, material 1.4571/316TI, for probe length 640 mm	LFPCT-0640G1	2087877		
	Coaxial tube for LFP with process connection G 3/4, process connection of coaxial tube G 3/4, material 1.4571/316TI, for probe length 700 mm	LFPCT-0700G1	2068146		
	Coaxial tube for LFP with process connection G 3/4, process connection of coax probe G 3/4, material 1.4571/316TI, for probe length 800 mm	LFPCT-0800G1	2068147		
	Coaxial probe for LFP with process connection G 3/4, process connection of coaxial tube G 3/4, material 1.4571/316Tl, for probe length 900 mm	LFPCT-0900G1	2067507		
	Coaxial tube for LFP with process connection G 3/4, process connection of coaxial tube G 3/4, material 1.4571/316TI, for probe length 1000 mm	LFPCT-1000G1	2065702		
	Coaxial tube for LFP with process connection G 3/4, process connection of coaxial tube G 3/4, material 1.4571/316TI, for probe length 1100 mm	LFPCT-1100G1	2068148		
	Coaxial tube for LFP with process connection G 3/4, process connection of coaxial tube G 3/4, material 1.4571/316TI, for probe length 1200 mm	LFPCT-1200G1	2068149		
	Coaxial tube for LFP with process connection G 3/4, process connection of coaxial tube G 3/4, material 1.4571/316TI, for probe length 1270 mm	LFPCT-1270G1	2142066		
	Coaxial tube for LFP with process connection G 3/4, process connection of coaxial tube G 3/4, material 1.4571/316TI, for probe length 1300 mm	LFPCT-1300G1	2068150		
	Coaxial tube for LFP with process connection G 3/4, process connection of coaxial tube G 3/4, material 1.4571/316TI, for probe length 1400 mm	LFPCT-1400G1	2068151		
	Coaxial tube for LFP with process connection G 3/4, process connection of coaxial tube G 3/4, material 1.4571/316TI, for probe length 1500 mm	LFPCT-1500G1	2068152		
	Coaxial tube for LFP with process connection G 3/4, process connection of coaxial tube G 3/4, material 1.4571/316TI, for probe length 1600 mm	LFPCT-1600G1	2068153		
	Coaxial tube for LFP with process connection G 3/4, process connection of coaxial tube G 3/4, material 1.4571/316TI, for probe length 1700 mm	LFPCT-1700G1	2068154		
	Coaxial tube for LFP with process connection G 3/4, process connection of coaxial tube G 3/4, material 1.4571/316TI, for probe length 1800 mm	LFPCT-1800G1	2068155		
	Coaxial tube for LFP with process connection G 3/4, process connection of coax probe G 3/4, material 1.4571/316TI, for probe length 1900 mm	LFPCT-1900G1	2068156		
	Coaxial tube for LFP with process connection G 3/4, process connection of coaxial tube G 3/4, material 1.4571/316TI, for probe length 2000 mm	LFPCT-2000G1	2065703		
Flanges					
	Process connection adapter G <sup>3</sup> / <sub>4</sub> to G1	BEF-HA- G1BSP1-LFP1	2067603		
	Weld-in flange G 3/4"	BEF-FL- GEWG34-LFP1	2082150		

LEVEL SENSORS

	Brief description	Туре	Part no.
Mounting bra	ackets and plates		
	Mounting bracket, stainless steel 1.4301 (AISI 304), mounting hardware included	BEF-FL-304LFP-HLDR	2077391
Others			
3	<ul> <li>Connection type head A: Female connector, M12, 5-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 2 m, 5-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals, Uncontaminated zones</li> </ul>	YG2A15- 020VB5XLEAX	2096215
3	<ul> <li>Connection type head A: Female connector, M12, 5-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 5-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals, Uncontaminated zones</li> </ul>	YG2A15- 050VB5XLEAX	2096216
	<ul> <li>Connection type head A: Female connector, M12, 5-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 10 m, 5-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals, Uncontaminated zones</li> </ul>	YG2A15- 100VB5XLEAX	2096217
<b>N</b> 0	<ul> <li>Connection type head A: Female connector, M12, 5-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 2 m, 5-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Uncontaminated zones, Zones with oils and lubricants, Robot, Drag chain operation</li> </ul>	YF2A15- 020UB5XLEAX	2095617
	<ul> <li>Connection type head A: Female connector, M12, 5-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 5-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Uncontaminated zones, Zones with oils and lubricants, Robot, Drag chain operation</li> </ul>	YF2A15- O5OUB5XLEAX	2095618
×.	<ul> <li>Connection type head A: Female connector, M12, 5-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 10 m, 5-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Uncontaminated zones, Zones with oils and lubricants, Robot, Drag chain operation</li> </ul>	YF2A15- 100UB5XLEAX	2095619
>	<ul> <li>Connection type head A: Female connector, M12, 5-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 2 m, 5-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Uncontaminated zones, Zones with oils and lubricants, Robot, Drag chain operation</li> </ul>	YG2A15- 020UB5XLEAX	2095772
	<ul> <li>Connection type head A: Female connector, M12, 5-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 5-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Uncontaminated zones, Zones with oils and lubricants, Robot, Drag chain operation</li> </ul>	YG2A15- 050UB5XLEAX	2095773

LEVEL SENSORS

	Brief description	Туре	Part no.
>	<ul> <li>Connection type head A: Female connector, M12, 5-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 10 m, 5-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Uncontaminated zones, Zones with oils and lubricants, Robot, Drag chain operation</li> </ul>	YG2A15- 100UB5XLEAX	2095774
<b>N</b> .0	<ul> <li>Connection type head A: Female connector, M12, 5-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 2 m, 5-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals, Uncontaminated zones</li> </ul>	YF2A15- 020VB5XLEAX	2096239
<b>N</b> O	<ul> <li>Connection type head A: Female connector, M12, 5-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 5-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals, Uncontaminated zones</li> </ul>	YF2A15- 050VB5XLEAX	2096240
<b>N</b> .0	<ul> <li>Connection type head A: Female connector, M12, 5-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 10 m, 5-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals, Uncontaminated zones</li> </ul>	YF2A15- 100VB5XLEAX	2096241

#### **Recommended services**

Additional services -> www.sick.com/LFP\_Cubic

	Туре	Part no.
Function Block Factory		
<ul> <li>Description: The Function Block Factory is an engineering tool for creating device and environment-specific function blocks that enable IO-Link sensors to be integrated into programmable logic controllers. The Function Block Factory supports common programmable logic controllers (PLCs) of various manufacturers such as Siemens, Beckhoff, Rockwell Automation B&amp;R and more. More information on the FBF can be found <a href="https://fbf.cloud.sick.com" target="_blank">here </a>.</li> <li>Provision: Customers can obtain access to the Function Block Factory and the license via <a href="https://fbf.cloud.sick.com" target="_blank">https://fbf.cloud.sick.com</a>.</li> </ul>	Function Block Factory	On request

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

