

# LL3-TH08S01

Fiber-optic cables

**FIBERS** 





#### Ordering information

| Туре        | Part no. |
|-------------|----------|
| LL3-TH08S01 | 5337056  |

Other models and accessories → www.sick.com/Fiber-optic\_cables

#### Detailed technical data

#### **Features**

| Device type                       | Fiber-optic cables                          |
|-----------------------------------|---|
| Functional principle              | Through-beam system                         |
| Fiber-optic head design           | Threaded sleeve                             |
| Application                       | Standard                                    |
| Compatible fiber-optic amplifiers | WLL80, WLL180, GLL170(T)                    |
| Sensing range max.                | Depending on the fiber optic amplifier used |
| Minimal object diameter           | 0.04 mm <sup>1)</sup>                       |
| Optical fiber head                |   |
| Angle of dispersion               | 60°   |
| Integrated lens                   | No  |
| Compatibility tip adapters        | Yes   |
| Optical fiber                     |   |
| Compatibility with infrared light | Yes <sup>2)</sup>                           |
| Adapter end sleeves required      | No  |

 $<sup>^{1)}</sup>$  Minimum detectable object was determined at optimum measuring distance and optimum setting.

#### Mechanics

| Optical fiber head                               |                      |
|--|----------------------|
| Light emission                                   | Axial                |
| Thread diameter (housing)                        | M4                   |
| Optical fiber taper diameter                     | ≥ 2.6 mm             |
| Optical fiber taper length after 2 mm            | ≥ 3 mm               |
| Optical fiber                                    |                      |
| Fiber length                                     | 195 mm, 545 mm       |
| Bending radius                                   | 25 mm                |
| Dynamic flexibility (robotics)                   | No                   |
| Outside diameter, optical fiber cable connection | 2.2 mm               |
| Fiber arrangement                                | Singlefiber          |
| Core structure                                   | Ø 1,2 mm Singlefiber |
| Material   |                      |
| Optical fiber head                               | Stainless steel      |
| Sheath   | Stainless steel      |

 $<sup>^{\</sup>rm 2)}$  Reduced sensing ranges possible when using a fiber-optic amplifier with infrared light.

| Fibers                        | Glass   |
|-------------------------------|---|
| Weight                        | 70 g  |
| Ambient data                  |   |
| Ambient operating temperature | -30 °C +350 °C  |
| Classifications               |   |
| ECLASS 5.0                    | 27270905  |
| ECLASS 5.1.4                  | 27270905  |
| ECLASS 6.0                    | 27270905  |
| ECLASS 6.2                    | 27270905  |
| ECLASS 7.0                    | 27270905  |
| ECLASS 8.0                    | 27270905  |
| ECLASS 8.1                    | 27270905  |
| ECLASS 9.0                    | 27270905  |
| ECLASS 10.0                   | 27270905  |
| ECLASS 11.0                   | 27270905  |
| ECLASS 12.0                   | 27270905  |
| ETIM 5.0                      | EC002651  |
| ETIM 6.0                      | EC002651  |
| ETIM 7.0                      | EC002651  |
| ETIM 8.0                      | EC002651  |
| UNSPSC 16.0901                | 39121528  |
| Sensing ranges with WLL180T   |   |
| Operating mode 16 µs          | 150 mm  |
| Operating mode 70 µs          | 480 mm  |
| Operating mode 250 µs         | 790 mm  |
| Operating mode 2 ms           | 1,500 mm  |
| Operating mode 8 ms           | 1,600 mm  |
| Note                          | Sensing ranges related to fiber-optic sensors with type of light: visible red light |
| Sensing ranges with GLL170    |   |
| Operating mode 250 µs         | 560 mm  |
| Sensing ranges with GLL170T   |   |

470 mm

680 mm


Operating mode 50 µs

Operating mode 250  $\mu s$ 


**FIBERS** 

#### Dimensional drawing (Dimensions in mm (inch))

#### 1 x 195 mm



#### 1 x 545 mm



### SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

## **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

