

# MPS-200CLTP0 MPS-C

**POSITION SENSORS** 





# Ordering information

Туре	Part no.
MPS-200CLTP0	1079364

Other models and accessories → www.sick.com/MPS-C



#### Detailed technical data

#### **Features**

Cylinder type	C-slot
Cylinder types with adapter	Round body cylinder Profile cylinders and tie-rod cylinders SMC rail CDQ2 SMC rail ECDQ2
Measuring range	200 mm <sup>1)</sup>
Housing length	215 mm
Switching output	Push-pull: PNP/NPN
Output function	Analog, IO-Link, Switching output
Electrical wiring	DC 4-wire
Analog output (voltage)	0 V 10 V
Analog output (current)	4 mA 20 mA
Enclosure rating	IP67 <sup>2)</sup>
Adjustment	
Teach-in control panel	Teaching in analog outputs Selecting the current/voltage output Inverting the analog output Teaching in digital switching outputs
IO-Link	Teaching in 4 switching points Pin 2 configuration (0 V-10 V, 4 mA-20 mA) Measuring range (mm) teach-in (analog output) Disabling teach-in pushbutton Teach-in modes per output via IO-Link (cylinder switch mode, two point mode, window mode, and single point mode)

 $<sup>^{1)}</sup>$  ± 1 mm.

 $<sup>^{2)}</sup>$  According to EN 60529.

# Mechanics/electronics

Supply voltage	12 V DC 30 V DC
Power consumption	42 mA, without load
Voltage drop	≤ 2 V
Continuous current I <sub>a</sub>	$\leq$ 100 mA $^{1)}$
Max. load resistance	≤ 500 $\Omega$ Power Output, at 24 V
Min. load resistance	$\geq 2 k\Omega^{2}$
Protection class	III
Time delay before availability	0.15 s
Required magnetic field sensitivity, typ.	3 mT 12 mT
Resolution, typ.	≥ 50 µm
Linearity error, typ.	0.3 mm <sup>3)</sup>
Repeat accuracy, typ.	0.1 mm <sup>4)</sup>
Sampling rate, typ.	1 ms
Reverse polarity protection	Yes
Short-circuit protection	Yes
Status indicator LED	Yes
Digital switching output	Yes
Teach-in	Yes
Ambient operating temperature	-20 °C +70 °C
Shock and vibration resistance	30 g, 11 ms / 10 55 Hz, 1 mm
EMC	According to EN 60947-5-7 <sup>5)</sup>
Connection type	Cable with M8 male connector, 4-pin, 0.3 m
Connection type Detail	
Deep-freeze property	Do not bend below 0 °C
Conductor cross section	0.08 mm <sup>2</sup>
Cable diameter	Ø 2.6 mm
Bending radius	With fixed installation > 5 x cable diameter For flexible use > 10 x cable diameter
Cable outlet	Axial
Material	
Housing	Plastic
Cable	PUR
UL File No.	NRKH.E181493 & NRKH7.E181493

 $<sup>^{1)} \</sup>le 100 \text{ mA (PUSH)}; \ge -100 \text{ mA (PULL)}.$ 

# Safety-related parameters

MTTF <sub>D</sub>	72 years
<b>DC</b> <sub>avg</sub>	0 %

<sup>&</sup>lt;sup>2)</sup> Voltage output.

 $<sup>^{3)}</sup>$  At 25  $\,^{\circ}$  C, linearity error (maximum deviation) depending on response curve and minimal deviation function.

 $<sup>^{\</sup>rm 4)}$  At 25  $^{\rm \circ}$  C, repeatability magnet movement in one direction.

 $<sup>^{5)}\,\</sup>mathrm{The}$  analog measured value can deviate under transient conditions.

# MPS-200CLTP0 | MPS-C

# **POSITION SENSORS**

T <sub>M</sub> (mission time)	20 years


#### Communication interface

Communication interface	IO-Link V1.1
Communication Interface detail	COM3
Cycle time	1 ms
Process data length	16 Bit
Process data structure	Bit 0 = switching signal $Q_{L1}$ Bit 1 = switching signal $Q_{L2}$ Bit 2 = switching signal $Q_{L3}$ Bit 3 = switching signal $Q_{L4}$ Bit 4 15 = position (in 50 µm)

#### Classifications


ECLASS 5.0 27270104 ECLASS 5.1.4 27270104 ECLASS 6.0 27270104 ECLASS 6.2 27270104 ECLASS 7.0 27270104 ECLASS 8.0 27270104 ECLASS 8.1 27270104 ECLASS 9.0 27270104 ECLASS 11.0 27270104 ECLASS 11.0 27270104 ECLASS 11.0 27270104 ECLASS 11.0 27270104 ECLASS 12.0 27274301 ETIM 5.0 EC002544 ETIM 6.0 EC002544 ETIM 7.0 EC002544 ETIM 8.0 UNSPSC 16.0901 39122230		
ECLASS 6.0 27270104 ECLASS 6.2 27270104 ECLASS 7.0 27270104 ECLASS 8.0 27270104 ECLASS 8.1 27270104 ECLASS 9.0 27270104 ECLASS 10.0 27270104 ECLASS 10.0 27270104 ECLASS 11.0 27270104 ECLASS 11.0 27270104 ECLASS 12.0 27274301 ETIM 5.0 EC002544 ETIM 6.0 EC002544 ETIM 7.0 EC002544 ETIM 8.0 EC002544	ECLASS 5.0	27270104
ECLASS 6.2 27270104 ECLASS 7.0 27270104 ECLASS 8.0 27270104 ECLASS 8.1 27270104 ECLASS 9.0 27270104 ECLASS 10.0 27270104 ECLASS 11.0 27270104 ECLASS 11.0 27270104 ECLASS 12.0 27274301 ETIM 5.0 EC002544 ETIM 6.0 EC002544 ETIM 7.0 EC002544 ETIM 8.0 EC002544	ECLASS 5.1.4	27270104
ECLASS 7.0 27270104 ECLASS 8.0 27270104 ECLASS 8.1 27270104 ECLASS 9.0 27270104 ECLASS 10.0 27270104 ECLASS 11.0 27270104 ECLASS 12.0 27274301 ETIM 5.0 EC002544 ETIM 6.0 EC002544 ETIM 7.0 EC002544 ETIM 8.0 EC002544	ECLASS 6.0	27270104
ECLASS 8.0 27270104 ECLASS 8.1 27270104 ECLASS 9.0 27270104 ECLASS 10.0 27270104 ECLASS 11.0 27270104 ECLASS 12.0 27274301 ETIM 5.0 EC002544 ETIM 6.0 EC002544 ETIM 7.0 EC002544 ETIM 8.0 EC002544	ECLASS 6.2	27270104
ECLASS 8.1 27270104 ECLASS 9.0 27270104 ECLASS 10.0 27270104 ECLASS 11.0 27270104 ECLASS 12.0 27274301 ETIM 5.0 EC002544 ETIM 6.0 EC002544 ETIM 7.0 EC002544 ETIM 8.0 EC002544	ECLASS 7.0	27270104
ECLASS 9.0 27270104 ECLASS 10.0 27270104 ECLASS 11.0 27270104 ECLASS 12.0 27274301 ETIM 5.0 EC002544 ETIM 6.0 EC002544 ETIM 7.0 EC002544 ETIM 8.0 EC002544	ECLASS 8.0	27270104
ECLASS 10.0 27270104 ECLASS 11.0 27270104 ECLASS 12.0 27274301 ETIM 5.0 EC002544 ETIM 6.0 EC002544 ETIM 7.0 EC002544 ETIM 8.0 EC002544	ECLASS 8.1	27270104
ECLASS 11.0       27270104         ECLASS 12.0       27274301         ETIM 5.0       EC002544         ETIM 6.0       EC002544         ETIM 7.0       EC002544         ETIM 8.0       EC002544	ECLASS 9.0	27270104
ECLASS 12.0 27274301 ETIM 5.0 EC002544 ETIM 6.0 EC002544 ETIM 7.0 EC002544 ETIM 8.0 EC002544	ECLASS 10.0	27270104
ETIM 5.0 EC002544  ETIM 6.0 EC002544  ETIM 7.0 EC002544  ETIM 8.0 EC002544	ECLASS 11.0	27270104
ETIM 6.0 EC002544 ETIM 7.0 EC002544 ETIM 8.0 EC002544	ECLASS 12.0	27274301
ETIM 7.0 EC002544 ETIM 8.0 EC002544	ETIM 5.0	EC002544
ETIM 8.0 EC002544	ETIM 6.0	EC002544
	ETIM 7.0	EC002544
UNSPSC 16.0901 39122230	ETIM 8.0	EC002544
	UNSPSC 16.0901	39122230

# Installation note




# Connection diagram

#### Cd-357



# Dimensional drawing (Dimensions in mm (inch))

Cable with connector M8



	Total length (L1) mm	Measuring rang (L2) mm
/IPS-xxx	40.6	25
/IPS-xxx	64.9	50
/IPS-xxx	114.9	100
/IPS-xxx	214.7	200

- ① Teach-in button
- ② Status LEDs
- ③ Operating LEDs
- ④ Fixing screw SW 1.5
- ⑤ Connection

#### Recommended accessories

Other models and accessories → www.sick.com/MPS-C

	Brief description	Туре	Part no.	
Connection m	Connection modules			
	IO-Link V1.1 Class A port, USB2.0 port, optional external power supply 24V $/$ 1A	IOLA2US-01101 (SiLink2 Master)	1061790	
	PROFINET IO-Link Master, IO-Link V1.1, Port Class A, power supply via $7/8$ " cable 24 V / 8 A, fieldbus connection via M12 cable	IOLG2PN-03208R01 (IO-Link Master)	6053253	
Brackets for c	Brackets for cylinder sensors			
Sall in	Mounting bracket for integrated profile cylinder/tie-rod cylinder, zinc diecast, mounting hardware included	BEF-KHZ-PC1	2076170	

	Brief description	Туре	Part no.
	1 piece, Mounting bracket on round body cylinder with piston diameter of 1 mm 130 mm, ambient temperature min –30 °C max 80 °C, stainless steel, Aluminum	BEF-KHZ-RC1-130	2077686
and a	1 piece, Mounting bracket on round body cylinder with piston diameter of 1 mm 25 mm, ambient temperature min –30 °C max 80 °C, stainless steel, Aluminum	BEF-KHZ-RC1-25	2077685
Other mounti	ng accessories		
80	10 pieces, Label Holder, 2.5 mm to 3.5 mm, 10 pcs., TPU	LABEL HOLDER	2086019
	<ul> <li>Connection type head A: Male connector, M8, 4-pin, straight, A-coded</li> <li>Description: Unshielded</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: 0.14 mm² 0.5 mm²</li> </ul>	STE-0804-G	6037323
	<ul> <li>Connection type head A: Female connector, M8, 4-pin, straight, A-coded</li> <li>Description: Unshielded</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: 0.14 mm² 0.5 mm²</li> </ul>	DOS-0804-G	6009974
	<ul> <li>Connection type head A: Female connector, M8, 4-pin, angled, A-coded</li> <li>Description: Unshielded</li> <li>Connection systems: Solder connection</li> <li>Permitted cross-section: ≤ 0.25 mm²</li> </ul>	DOS-0804-W	6009975
	<ul> <li>Connection type head A: Female connector, M8, 4-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 2 m, 4-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with oils and lubricants, Drag chain operation, Robot</li> </ul>	YF8U14- 020UA3XLEAX	2094791
	<ul> <li>Connection type head A: Female connector, M8, 4-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with oils and lubricants, Drag chain operation, Robot</li> </ul>	YF8U14- 050UA3XLEAX	2094792
	<ul> <li>Connection type head A: Female connector, M8, 4-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 2 m, 4-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with oils and lubricants, Drag chain operation, Robot</li> </ul>	YG8U14- 020UA3XLEAX	2095589
3	<ul> <li>Connection type head A: Female connector, M8, 4-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with oils and lubricants, Drag chain operation, Robot</li> </ul>	YG8U14- 050UA3XLEAX	2095590
10	<ul> <li>Connection type head A: Female connector, M8, 4-pin, straight, A-coded</li> <li>Connection type head B: Male connector, M12, 4-pin, straight, A-coded</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 0.6 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YF8U14- C60VA3M2A14	2096607

#### Recommended services

Additional services → www.sick.com/MPS-C

	Туре	Part no.
Function Block Factory		
<ul> <li>Description: The Function Block Factory supports common programmable logic controllers (PLCs) from various manufacturers, such as Siemens, Beckhoff, Rockwell Automation and B&amp;R. More information on the FBF can be found <a href="https://fbf.cloud.sick.com" target="_blank">here</a>.</li> <li>Note: You can configure your function block at <a href="https://fbf.cloud.sick.com" target="_blank">Function Block Factory.</a> As a login please use your SICK ID.</li> </ul>	Function Block Factory	On request

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

