

# IMF30-20NNSNCOS

IMF

**INDUCTIVE PROXIMITY SENSORS** 





## Ordering information

Туре	Part no.
IMF30-20NNSNC0S	1076661

Included in delivery: BEF-MU-M30N1(1)

Other models and accessories → www.sick.com/IMF

Illustration may differ



#### Detailed technical data

#### **Features**

Housing	Metric
Housing	Standard design
Thread size	M30 x 1.5
Diameter	Ø 30 mm
Sensing range S <sub>n</sub>	20 mm
Safe sensing range S <sub>a</sub>	16.2 mm
Installation type	Non-flush
Switching frequency	500 Hz
Connection type	Male connector M12, 4-pin <sup>1)</sup>
Switching output	NPN
Output function	NO
Electrical wiring	DC 3-wire
Enclosure rating	IP68 <sup>2)</sup> IP69K <sup>3)</sup>
Special features	Resistant to cleaning agents, Visual adjustment indicator, Temperature resistance
Special applications	Hygienic and washdown zones, Difficult application conditions
Items supplied	Mounting nut, V4A stainless steel (2x)

 $<sup>^{1)}</sup>$  With gold plated contact pins.

<sup>&</sup>lt;sup>2)</sup> According to EN 60529.

 $<sup>^{3)}</sup>$  According to ISO 20653:2013-03.

## Mechanics/electronics

Supply voltage	10 V DC 30 V DC
Ripple	≤ 10 %
Voltage drop	$\leq$ 2 V $^{1)}$
Hysteresis	3 % 20 %
Reproducibility	≤ 2 % <sup>2) 3)</sup>
Temperature drift (of S <sub>r</sub> )	± 10 %
EMC	According to EN 60947-5-2
Continuous current I <sub>a</sub>	≤ 200 mA
No load current	≤ 10 mA
Short-circuit protection	✓
Power-up pulse protection	✓
Shock and vibration resistance	$100~{\rm g}/2~{\rm ms}/500$ cycles; $150~{\rm g}/1$ Mio cycles; $10~{\rm Hz}55~{\rm Hz}/1~{\rm mm};55~{\rm Hz}500~{\rm Hz}/60~{\rm g}$
Ambient operating temperature	-40 °C +100 °C
Housing material	Stainless steel V4A, DIN 1.4404 / AISI 316L
Sensing face material	Plastic, LCP
Housing length	70 mm
Thread length	40 mm
Tightening torque, max.	Typ. 100 Nm
Protection class	III
UL File No.	E181493

<sup>1)</sup> At Ia max

# Safety-related parameters

MTTF <sub>D</sub>	1,971 years
DC <sub>avg</sub>	0 %
T <sub>M</sub> (mission time)	20 years

## Reduction factors

Note	The values are reference values which may vary
Stainless steel (V2A, 304)	Approx. 0.78
Aluminum (AI)	Approx. 0.44
Copper (Cu)	Approx. 0.36
Brass (Br)	Approx. 0.46

#### Installation note

Remark	Associated graphic see "Installation"
A	20 mm
В	62 mm
c	30 mm
D	60 mm

 $<sup>^{\</sup>rm 2)}$  Supply voltage  $\rm U_B$  and constant ambient temperature Ta.

<sup>&</sup>lt;sup>3)</sup> Of Sr.

# IMF30-20NNSNC0S | IMF

## INDUCTIVE PROXIMITY SENSORS


E	20 mm
F	160 mm


## Classifications

ECLASS 5.0	27270101
ECLASS 5.1.4	27270101
ECLASS 6.0	27270101
ECLASS 6.2	27270101
ECLASS 7.0	27270101
ECLASS 8.0	27270101
ECLASS 8.1	27270101
ECLASS 9.0	27270101
ECLASS 10.0	27270101
ECLASS 11.0	27270101
ECLASS 12.0	27274001
ETIM 5.0	EC002714
ETIM 6.0	EC002714
ETIM 7.0	EC002714
ETIM 8.0	EC002714
UNSPSC 16.0901	39122230

#### Installation note

Non-flush installation






## Connection diagram

Cd-007


## Response diagram

#### Response diagram




## Functional principle

#### Installation aid



## Dimensional drawing (Dimensions in mm (inch))

IMF30, non flush



#### Recommended accessories

Other models and accessories → www.sick.com/IMF

	Brief description	Туре	Part no.
Universal bar	clamp systems		
	Plate N10 for universal clamp bracket, M30, Zinc plated steel (sheet), Zinc die cast (clamping bracket), Universal clamp (5322626), mounting hardware	BEF-KHS-N10	2062372
Nounting bra	ckets and plates		
	Mounting plate for M30 sensors, steel, zinc coated, without mounting hardware	BEF-WG-M30	5321871
40	Mounting bracket for M30 sensors, steel, zinc coated, without mounting hardware	BEF-WN-M30	5308445
Others			
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 2 m, 4-wire, PP</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Connection systems: Flying leads</li> <li>Note: This product is generally resistant to chemical cleaning agents (see ECOLAB) and other chemical compounds such as H2O2 and CH2O2. Before permanent installation is carried out, the material's resistance to the cleaning agent being used must be checked., Resistant against lactic acid &amp; hydrogen peroxide (H2O2)</li> <li>Application: Hygienic and washdown zones, Drag chain operation</li> </ul>	DOL-1204-G02MRN	6058291
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PP</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Connection systems: Flying leads</li> <li>Note: This product is generally resistant to chemical cleaning agents (see ECOLAB) and other chemical compounds such as H202 and CH202. Before permanent installation is carried out, the material's resistance to the cleaning agent being used must be checked., Resistant against lactic acid &amp; hydrogen peroxide (H202)</li> <li>Application: Hygienic and washdown zones, Drag chain operation</li> </ul>	DOL-1204-G05MRN	6058476
8	Connection type head A: Female connector, M12, 4-pin, angled Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 4-wire, PP Description: Sensor/actuator cable, unshielded Connection systems: Flying leads Note: This product is generally resistant to chemical cleaning agents (see ECOLAB) and other chemical compounds such as H202 and CH202. Before permanent installation is carried out, the material's resistance to the cleaning agent being used must be checked., Resistant against lactic acid & hydrogen peroxide (H202) Application: Hygienic and washdown zones, Drag chain operation	DOL-1204-W02MRN	6058474
6	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PP</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Connection systems: Flying leads</li> <li>Note: This product is generally resistant to chemical cleaning agents (see ECOLAB) and other chemical compounds such as H2O2 and CH2O2. Before permanent installation is carried out, the material's resistance to the cleaning agent being used must be checked., Resistant against lactic acid &amp; hydrogen peroxide (H2O2)</li> <li>Application: Hygienic and washdown zones, Drag chain operation</li> </ul>	DOL-1204-W05MRN	6058477

	Brief description	Туре	Part no.
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 2 m, 4-wire, PP</li> <li>Description: Sensor/actuator cable, unshielded, LED function display</li> <li>Connection systems: Flying leads</li> <li>Note: This product is generally resistant to chemical cleaning agents (see ECOLAB) and other chemical compounds such as H2O2 and CH2O2. Before permanent installation is carried out, the material's resistance to the cleaning agent being used must be checked., Resistant against lactic acid &amp; hydrogen peroxide (H2O2), only suitable for PNP sensors</li> <li>Application: Hygienic and washdown zones, Drag chain operation</li> </ul>	DOL-1204-L02MRN	6058482
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PP</li> <li>Description: Sensor/actuator cable, unshielded, LED function display</li> <li>Connection systems: Flying leads</li> <li>Note: This product is generally resistant to chemical cleaning agents (see ECOLAB) and other chemical compounds such as H2O2 and CH2O2. Before permanent installation is carried out, the material's resistance to the cleaning agent being used must be checked., Resistant against lactic acid &amp; hydrogen peroxide (H2O2), only suitable for PNP sensors</li> <li>Application: Hygienic and washdown zones, Drag chain operation</li> </ul>	DOL-1204-L05MRN	6058483
60	Connection type head A: Female connector, M12, 4-pin, straight Connection type head B: Male connector, M12, 4-pin, straight Signal type: Sensor/actuator cable Cable: 2 m, 4-wire, PP Description: Sensor/actuator cable, unshielded Note: This product is generally resistant to chemical cleaning agents (see ECOLAB) and other chemical compounds such as H202 and CH202. Before permanent installation is carried out, the material's resistance to the cleaning agent being used must be checked., Resistant against lactic acid & hydrogen peroxide (H202) Application: Hygienic and washdown zones, Drag chain operation	DSL-1204-G02MRN	6058499
6	Connection type head A: Female connector, M12, 4-pin, straight Connection type head B: Male connector, M12, 4-pin, straight Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PP Description: Sensor/actuator cable, unshielded Note: This product is generally resistant to chemical cleaning agents (see ECOLAB) and other chemical compounds such as H202 and CH202. Before permanent installation is carried out, the material's resistance to the cleaning agent being used must be checked., Resistant against lactic acid & hydrogen peroxide (H202) Application: Hygienic and washdown zones, Drag chain operation	DSL-1204-G05MRN	6058500
8	Connection type head A: Female connector, M12, 4-pin, angled Connection type head B: Male connector, M12, 4-pin, straight Signal type: Sensor/actuator cable Cable: 2 m, 4-wire, PP Description: Sensor/actuator cable, unshielded Note: This product is generally resistant to chemical cleaning agents (see ECOLAB) and other chemical compounds such as H202 and CH202. Before permanent installation is carried out, the material's resistance to the cleaning agent being used must be checked., Resistant against lactic acid & hydrogen peroxide (H202) Application: Hygienic and washdown zones, Drag chain operation	DSL-1204-B02MRN	6058502
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled</li> <li>Connection type head B: Male connector, M12, 4-pin, straight</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PP</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Note: This product is generally resistant to chemical cleaning agents (see ECOLAB) and other chemical compounds such as H2O2 and CH2O2. Before permanent installation is carried out, the material's resistance to the cleaning agent being used must be checked., Resistant against lactic acid &amp; hydrogen peroxide (H2O2)</li> <li>Application: Hygienic and washdown zones, Drag chain operation</li> </ul>	DSL-1204-B05MRN	6058503

# IMF30-20NNSNCOS | IMF

# INDUCTIVE PROXIMITY SENSORS

	Brief description	Туре	Part no.
6	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight</li> <li>Connection type head B: Male connector, M12, 4-pin, straight</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 20 m, 4-wire, PP</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Note: This product is generally resistant to chemical cleaning agents (see ECOLAB) and other chemical compounds such as H2O2 and CH2O2. Before permanent installation is carried out, the material's resistance to the cleaning agent being used must be checked., Resistant against lactic acid &amp; hydrogen peroxide (H2O2)</li> <li>Application: Hygienic and washdown zones, Drag chain operation</li> </ul>	YF2AP4- 020PA2M2AP4	2143765

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

