

# IMR18-15NPSTCOS

IMR

**INDUCTIVE PROXIMITY SENSORS** 





# Ordering information

Туре	Part no.
IMR18-15NPSTC0S	6069278

Other models and accessories → www.sick.com/IMR



#### Detailed technical data

#### **Features**

i catules	
Housing	Metric
Housing	Standard design
Thread size	M18 x 1
Diameter	Ø 18 mm
Sensing range S <sub>n</sub>	15 mm
Safe sensing range S <sub>a</sub>	12.1 mm
Installation type	Non-flush
Switching frequency	1,500 Hz
Connection type	Male connector M12, 4-pin
Switching output	PNP
Output function	NO
Electrical wiring	DC 3-wire
Enclosure rating	IP68
Special features	Reduction factor 1, Weld immune
Special applications	Welding range, Difficult application conditions
Items supplied	Mounting nut, brass, PTFE coating (2x) Washer, brass, PTFE coating, with locking teeth (2x)

### Mechanics/electronics

,	
Supply voltage	10 V DC 30 V DC
Ripple	≤ 10 %
Voltage drop	$\leq$ 1.8 V $^{1)}$
Hysteresis	3 % 15 %
Reproducibility	≤ 2 % <sup>2) 3)</sup>
Temperature drift (of S <sub>r</sub> )	$\leq \pm 10 \% \leq \pm 15 \%^{4}$

<sup>1)</sup> At I may

 $<sup>^{2)}\,\</sup>mbox{Supply voltage}\,\,\mbox{U}_{\mbox{\footnotesize B}}$  and constant ambient temperature Ta.

<sup>&</sup>lt;sup>3)</sup> Of Sr.

<sup>&</sup>lt;sup>4)</sup> -25 °C ... +70 °C.

<sup>&</sup>lt;sup>5)</sup> Reference voltage: 50 V DC.

Continuous current I <sub>a</sub>	≤ 200 mA
No load current	≤ 15 mA
Off-state current	≤ 0.1 mA
Short-circuit protection	✓
Magnetic field strength	≤ 100 mT
Shock and vibration resistance	30 g, 11 ms / 10 55 Hz, 1 mm
Ambient operating temperature	-30 °C +85 °C
Housing material	PTFE coating, brass
Sensing face material	Plastic, PTFE coating
Housing length	52 mm
Thread length	26 mm
Tightening torque, max.	Typ. 15 Nm
Protection class	II <sup>5)</sup>
UL File No.	E191603

<sup>1)</sup> At I<sub>a</sub> max.

# Safety-related parameters

MTTF <sub>D</sub>	139 years
DC <sub>avg</sub>	0%
T <sub>M</sub> (mission time)	20 years

#### **Reduction factors**

Note	The values are reference values which may vary
Reduction factor	Reduction factor 1
Stainless steel (V2A, 304)	1
Aluminum (AI)	1
Copper (Cu)	1
Brass (Br)	1

#### Installation note

Remark	Associated graphic see "Installation"
A	18 mm
В	54 mm
С	18 mm
D	45 mm
E	10 mm
F	90 mm
G	54 mm

### Classifications

CLASS 5.0	27270101
-----------	----------

 $<sup>^{\</sup>rm 2)}$  Supply voltage  $\rm U_B$  and constant ambient temperature Ta.

<sup>3)</sup> Of Sr

<sup>&</sup>lt;sup>4)</sup> -25 °C ... +70 °C.


<sup>5)</sup> Reference voltage: 50 V DC.

# IMR18-15NPSTCOS | IMR

# INDUCTIVE PROXIMITY SENSORS


ECLASS 5.1.4	27270101
ECLASS 6.0	27270101
ECLASS 6.2	27270101
ECLASS 7.0	27270101
ECLASS 8.0	27270101
ECLASS 8.1	27270101
ECLASS 9.0	27270101
ECLASS 10.0	27270101
ECLASS 11.0	27270101
ECLASS 12.0	27274001
ETIM 5.0	EC002714
ETIM 6.0	EC002714
ETIM 7.0	EC002714
ETIM 8.0	EC002714
UNSPSC 16.0901	39122230

### Installation note




# Connection diagram

Cd-007




# Response diagram





### Dimensional drawing (Dimensions in mm (inch))



- ① M12 x 1
- ② LED output state, yellow
- ③ Fastening nuts (2x); width across 24, metal

## Recommended accessories

Other models and accessories  $\rightarrow$  www.sick.com/IMR

	Brief description	Туре	Part no.	
Mounting bra	Mounting brackets and plates			
40	Mounting bracket for M18 sensors, steel, zinc coated, without mounting hardware	BEF-WN-M18	5308446	
Others				
No.	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Uncontaminated zones, Zones with oils and lubricants, Robot, Drag chain operation</li> </ul>	YF2A14- 050UB3XLEAX	2095608	

# IMR18-15NPSTC0S | IMR

# INDUCTIVE PROXIMITY SENSORS

	Brief description	Туре	Part no.
No.	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 2 m, 4-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Uncontaminated zones, Zones with oils and lubricants, Robot, Drag chain operation, weld-spark resistant</li> </ul>	YF2A14- 020UW1XLEAX	2104883
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Uncontaminated zones, Zones with oils and lubricants, Robot, Drag chain operation, weld-spark resistant</li> </ul>	YF2A14- 050UW1XLEAX	2104884
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 2 m, 4-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Uncontaminated zones, Zones with oils and lubricants, Robot, Drag chain operation, weld-spark resistant</li> </ul>	YG2A14- 020UW1XLEAX	2104886
7	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Uncontaminated zones, Zones with oils and lubricants, Robot, Drag chain operation, weld-spark resistant</li> </ul>	YG2A14- 050UW1XLEAX	2104887

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

