

INDUCTIVE PROXIMITY SENSORS



INDUCTIVE PROXIMITY SENSORS



Ordering information

Туре	Part no.
IM30-40NNS-NC1	6027585

Included in delivery: BEF-MU-M30N1(1)

Other models and accessories → www.sick.com/IMI



Detailed technical data

Features

Housing	Metric
Thread size	M30 x 1.5
Diameter	Ø 30 mm
Sensing range S _n	40 mm
Safe sensing range S _a	32.4 mm
Installation type	Non-flush
Switching frequency	90 Hz
Connection type	Male connector M12, 4-pin
Switching output	NPN
Output function	NO
Electrical wiring	DC 3-wire
Enclosure rating	IP68, IP69K ¹⁾
Special features	Sensing face made of stainless steel V4A, Resistant to cleaning agents, triple sensing range, Visual adjustment indicator
Special applications	Hygienic and washdown zones, Difficult application conditions
Items supplied	Mounting nut, V4A stainless steel (2x) Washer, V4A stainless steel, with locking teeth (2x)

 $^{\mbox{1)}}$ According to EN 60529.

Mechanics/electronics

Supply voltage

10 V DC ... 30 V DC

```
^{1)} Of V<sub>S</sub>.
```

 $^{^{2)}}$ At I_a max.

³⁾ Of Sr.

 $^{^{4)}}$ UB = 20 V DC ... 30 V DC, TA = 23 °C \pm 5 °C.

INDUCTIVE PROXIMITY SENSORS

Ripple	< 20 % ¹⁾
Voltage drop	$\leq 2 V^{2}$
Time delay before availability	≤ 40 ms
Hysteresis	1 % 15 %
Reproducibility	$\leq 5 \%^{(3)(4)}$
Temperature drift (of S _r)	≤ 10 %
EMC	According to EN 60947-5-2
Continuous current l _a	≤ 200 mA
Short-circuit protection	✓
Power-up pulse protection	\checkmark
Shock and vibration resistance	30 g, 11 ms / 10 55 Hz, 1 mm
Shock and vibration resistance Ambient operating temperature	30 g, 11 ms / 10 55 Hz, 1 mm -25 °C +85 °C
Ambient operating temperature	-25 °C +85 °C
Ambient operating temperature Housing material	-25 °C +85 °C Stainless steel V4A, DIN 1.4404 / AISI 316L
Ambient operating temperature Housing material Sensing face material	-25 °C +85 °C Stainless steel V4A, DIN 1.4404 / AISI 316L Stainless steel V4A, DIN 1.4404 / AISI 316L
Ambient operating temperature Housing material Sensing face material Housing length	-25 °C +85 °C Stainless steel V4A, DIN 1.4404 / AISI 316L Stainless steel V4A, DIN 1.4404 / AISI 316L 63.5 mm
Ambient operating temperature Housing material Sensing face material Housing length Thread length	-25 °C +85 °C Stainless steel V4A, DIN 1.4404 / AISI 316L Stainless steel V4A, DIN 1.4404 / AISI 316L 63.5 mm 32 mm

 $^{1)}$ Of V_S.

²⁾ At I_a max.

³⁾ Of Sr.

⁴⁾ UB = 20 V DC ... 30 V DC, TA = 23 °C \pm 5 °C.

Safety-related parameters

MTTFD	16 years
DC _{avg}	0%
T _M (mission time)	20 years

Reduction factors

Note	The values are reference values which may vary
St37 steel (Fe)	Approx. 1
Aluminum (Al)	Approx. 1
Copper (Cu)	Approx. 0.9
Brass (Br)	Approx. 1.2

Installation note


Remark	Associated graphic see "Installation"
A	75 mm
В	270 mm
c	30 mm
D	120 mm
E	Aluminium: 34 mm, Steel: 18 mm, Brass: 34 mm, Stainless steel: 18 mm

INDUCTIVE PROXIMITY SENSORS

F	400 mm	
Classifications		
ECLASS 5.0	27270101	
ECLASS 5.1.4	27270101	
ECLASS 6.0	27270101	
ECLASS 6.2	27270101	
ECLASS 7.0	27270101	
ECLASS 8.0	27270101	
ECLASS 8.1	27270101	
ECLASS 9.0	27270101	
ECLASS 10.0	27270101	
ECLASS 11.0	27270101	
ECLASS 12.0	27274001	
ETIM 5.0	EC002714	
ETIM 6.0	EC002714	
ETIM 7.0	EC002714	
ETIM 8.0	EC002714	
UNSPSC 16.0901	39122230	


Installation note

Non-flush installation




Connection diagram

Cd-007




Response diagram



All dimensions in mm (inch)

Dimensional drawing (Dimensions in mm (inch))

IM30 Inox, non flush



① Connection ② Display LED

③ Fastening nuts (2x); width across 24, metal

Recommended accessories

Other models and accessories -> www.sick.com/IMI

	Brief description	Туре	Part no.	
Mounting brackets and plates				
	Mounting plate for M30 sensors, steel, zinc coated, without mounting hardware	BEF-WG-M30	5321871	

INDUCTIVE PROXIMITY SENSORS

	Brief description	Туре	Part no.
-	Mounting bracket for M30 sensors, steel, zinc coated, without mounting hardware	BEF-WN-M30	5308445
Oth a m			
Others	 Connection type head A: Female connector, M12, 4-pin, straight Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Connection systems: Flying leads Note: This product is generally resistant to chemical cleaning agents (see ECOLAB). Please do not use cleaning agents of any other Kind., Not resistant against lactic acid & hydrogen peroxide (H2O2) Application: Hygienic and washdown zones 	DOL-1204-G02MNI	6052613
~	 Connection type head A: Female connector, M12, 4-pin, straight Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Connection systems: Flying leads Note: This product is generally resistant to chemical cleaning agents (see ECOLAB). Please do not use cleaning agents of any other Kind., Not resistant against lactic acid & hydrogen peroxide (H2O2) Application: Hygienic and washdown zones 	DOL-1204-G05MNI	6052615
	 Connection type head A: Female connector, M12, 4-pin, angled Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Connection systems: Flying leads Note: This product is generally resistant to chemical cleaning agents (see ECOLAB). Please do not use cleaning agents of any other Kind., Not resistant against lactic acid & hydrogen peroxide (H2O2) Application: Hygienic and washdown zones 	DOL-1204-W02MNI	6052614
2	 Connection type head A: Female connector, M12, 4-pin, angled Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Connection systems: Flying leads Note: This product is generally resistant to chemical cleaning agents (see ECOLAB). Please do not use cleaning agents of any other Kind., Not resistant against lactic acid & hydrogen peroxide (H2O2) Application: Hygienic and washdown zones 	DOL-1204-W05MNI	6052616
2	 Connection type head A: Female connector, M12, 4-pin, angled Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded, LED function display Connection systems: Flying leads Note: This product is generally resistant to chemical cleaning agents (see ECOLAB). Please do not use cleaning agents of any other Kind., Not resistant against lactic acid & hydrogen peroxide (H2O2), only suitable for PNP sensors Application: Hygienic and washdown zones 	DOL-1204-L02MNI	6052621

IM30-40NNS-NC1 | IMI INDUCTIVE PROXIMITY SENSORS

	Brief description	Туре	Part no.
	 Connection type head A: Female connector, M12, 4-pin, angled Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded, LED function display Connection systems: Flying leads Note: This product is generally resistant to chemical cleaning agents (see ECOLAB). Please do not use cleaning agents of any other Kind., Not resistant against lactic acid & hydrogen peroxide (H2O2), only suitable for PNP sensors Application: Hygienic and washdown zones 	DOL-1204-L05MNI	6052622
6	 Connection type head A: Female connector, M12, 4-pin, straight Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 4-wire, PP Description: Sensor/actuator cable, unshielded Connection systems: Flying leads Note: This product is generally resistant to chemical cleaning agents (see ECOLAB) and other chemical compounds such as H202 and CH202. Before permanent installation is carried out, the material's resistance to the cleaning agent being used must be checked., Resistant against lactic acid & hydrogen peroxide (H202) Application: Hygienic and washdown zones, Drag chain operation 	DOL-1204-G02MRN	6058291
6	 Connection type head A: Female connector, M12, 4-pin, straight Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PP Description: Sensor/actuator cable, unshielded Connection systems: Flying leads Note: This product is generally resistant to chemical cleaning agents (see ECOLAB) and other chemical compounds such as H2O2 and CH2O2. Before permanent installation is carried out, the material's resistance to the cleaning agent being used must be checked., Resistant against lactic acid & hydrogen peroxide (H2O2) Application: Hygienic and washdown zones, Drag chain operation 	DOL-1204-G05MRN	6058476
	 Connection type head A: Female connector, M12, 4-pin, angled Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 4-wire, PP Description: Sensor/actuator cable, unshielded Connection systems: Flying leads Note: This product is generally resistant to chemical cleaning agents (see ECOLAB) and other chemical compounds such as H202 and CH202. Before permanent installation is carried out, the material's resistance to the cleaning agent being used must be checked., Resistant against lactic acid & hydrogen peroxide (H202) Application: Hygienic and washdown zones, Drag chain operation 	DOL-1204-W02MRN	6058474
	 Connection type head A: Female connector, M12, 4-pin, angled Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PP Description: Sensor/actuator cable, unshielded Connection systems: Flying leads Note: This product is generally resistant to chemical cleaning agents (see ECOLAB) and other chemical compounds such as H202 and CH202. Before permanent installation is carried out, the material's resistance to the cleaning agent being used must be checked., Resistant against lactic acid & hydrogen peroxide (H202) Application: Hygienic and washdown zones, Drag chain operation 	DOL-1204-W05MRN	6058477

INDUCTIVE PROXIMITY SENSORS

	Brief description	Туре	Part no.
	 Connection type head A: Female connector, M12, 4-pin, angled Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 4-wire, PP Description: Sensor/actuator cable, unshielded, LED function display Connection systems: Flying leads Note: This product is generally resistant to chemical cleaning agents (see ECOLAB) and other chemical compounds such as H2O2 and CH2O2. Before permanent installation is carried out, the material's resistance to the cleaning agent being used must be checked., Resistant against lactic acid & hydrogen peroxide (H2O2), only suitable for PNP sensors Application: Hygienic and washdown zones, Drag chain operation 	D0I-1204-L02MRN	6058482
6	 Connection type head A: Female connector, M12, 4-pin, angled Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PP Description: Sensor/actuator cable, unshielded, LED function display Connection systems: Flying leads Note: This product is generally resistant to chemical cleaning agents (see ECOLAB) and other chemical compounds such as H2O2 and CH2O2. Before permanent installation is carried out, the material's resistance to the cleaning agent being used must be checked., Resistant against lactic acid & hydrogen peroxide (H2O2), only suitable for PNP sensors Application: Hygienic and washdown zones, Drag chain operation 	DOL-1204-L05MRN	6058483
~	 Connection type head A: Female connector, M12, 5-pin, straight Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 5-wire, PP Description: Sensor/actuator cable, unshielded Connection systems: Flying leads Note: This product is generally resistant to chemical cleaning agents (see ECOLAB) and other chemical compounds such as H2O2 and CH2O2. Before permanent installation is carried out, the material's resistance to the cleaning agent being used must be checked., Resistant against lactic acid & hydrogen peroxide (H2O2) Application: Hygienic and washdown zones, Drag chain operation 	DOL-1205-G02MRN	6058494
~	 Connection type head A: Female connector, M12, 5-pin, straight Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 5-wire, PP Description: Sensor/actuator cable, unshielded Connection systems: Flying leads Note: This product is generally resistant to chemical cleaning agents (see ECOLAB) and other chemical compounds such as H2O2 and CH2O2. Before permanent installation is carried out, the material's resistance to the cleaning agent being used must be checked., Resistant against lactic acid & hydrogen peroxide (H2O2) Application: Hygienic and washdown zones, Drag chain operation 	DOL-1205-G05MRN	6058495

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

