



CDM420-0108

Connection Device Modular

4DPROCONNECTIVITY


SICK
Sensor Intelligence.



Ordering information

Type	Part no.
CDM420-0108	1064248

Other models and accessories → www.sick.com/Connection_Device_Modular



Detailed technical data

Features

Brief description	Kit: modular connection module for one sensor, 2 A fuse, Host and AUX interface available on face plate, power supply CMP490, US power cord
Supported products	CLV69x RFU63x Lector65x RFU65x
Cloning module support (CMC)	Yes (depending on sensor connected)
Supports display module (CMD)	No
Supports power supply module (CMP)	Yes (on board)
Supports fieldbus gateway (CMF)	No

Mechanics/electronics

Power consumption	Power consumption of the sensor + 0.5 W
Housing	Polycarbonate
Housing color	Blue (RAL 5012)
Enclosure rating	IP20 ¹⁾
Protection class	III
Weight	+ 1,428 g
Dimensions (L x W x H)	192 mm x 167 mm x 70 mm
Scanner connection	15-pin D-Sub HD female connector
Service plug	9-pin D-Sub plug (internal)

¹⁾ When using a standard connection cable for scanners by SICK.

Interfaces

Serial	✓, RS-232, RS-422, RS-485
Remark	Depending on sensor connected
CAN	✓
Remark	Depending on sensor connected
Digital inputs	Depending on sensor connected
Digital outputs	Depending on sensor connected
Optical indicators	5 LED

Configuration software	SOPAS ET
-------------------------------	----------

Ambient data



Ambient operating temperature	-35 °C ... +40 °C
Storage temperature	-20 °C ... +70 °C
Permissible relative humidity	< 90 %, Non-condensing

Classifications

ECLASS 5.0	27242208
ECLASS 5.1.4	27242608
ECLASS 6.0	27242608
ECLASS 6.2	27242608
ECLASS 7.0	27242608
ECLASS 8.0	27242608
ECLASS 8.1	27242608
ECLASS 9.0	27242608
ECLASS 10.0	27242608
ECLASS 11.0	27242608
ECLASS 12.0	27242608
ETIM 5.0	EC001604
ETIM 6.0	EC001604
ETIM 7.0	EC001604
ETIM 8.0	EC001604
UNSPSC 16.0901	32151705

Recommended accessories

Other models and accessories → www.sick.com/Connection_Device_Modular

	Brief description	Type	Part no.
Cloning modules			
	External parameter memory for integration in CDB620/CDB650/CDM42x	CMC600-101	1042259
	<ul style="list-style-type: none"> • Connection type head A: Female connector, D-Sub, 9-pin, straight • Connection type head B: Female connector, D-Sub, 9-pin, straight • Signal type: Serial • Cable: 3 m • Description: Serial, unshielded • Note: For PC connection 	YFHDA9-030XXXFHDA9	2103279

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com