

# DFS25A-A2AAE002500

DFS2x

**INCREMENTAL ENCODERS** 





## Ordering information

Туре	Part no.
DFS25A-A2AAE002500	1076161

Other models and accessories → www.sick.com/DFS2x

Illustration may differ



#### Detailed technical data

#### Performance

Pulses per revolution	2,500
Measuring step	± 90°, electric/pulses per revolution
Measuring step deviation	± 0.008° pulses 100 10,000
Error limits	± 0.03°

#### Interfaces

Communication interface	Incremental
Communication Interface detail	TTL / RS-422
Number of signal channels	6-channel
0-set function via hardware pin	✓
0-SET function	H-active, $L = 0 - 3 \text{ V}$ , $H = 4.0 - U_s \text{ V}$
Initialization time	40 ms <sup>1)</sup>
Output frequency	820 kHz
Load current	30 mA
Operating current	50 mA (without load)

 $<sup>^{1)}</sup>$  Valid positional data can be read once this time has elapsed.

#### Electrical data

Connection type	Male connector, MS, 7-pin, radial
Supply voltage	4.5 5.5 V
Reference signal, number	1
Reference signal, position	180°, Degree Marker Gated with BN2
Reverse polarity protection	✓
Short-circuit protection of the outputs	<b>✓</b> <sup>1)</sup>

 $<sup>^{1)}\,\</sup>mathrm{Short}\text{-}\mathrm{circuit}$  opposite to another channel or GND permissable for maximum 30 s.

<sup>&</sup>lt;sup>2)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of components, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

#### MTTFd: mean time to dangerous failure

330 years (EN ISO 13849-1) 2)

#### Mechanical data

Mechanical design	Solid shaft, Square flange
Shaft diameter	3/8"
Shaft length	19 mm
Weight	$+ 0.4  \text{kg}^{ 1)}$
Shaft material	Stainless steel 1,4305
Flange material	Aluminum
Housing material	Aluminum
Start up torque	0.5 Ncm (+20 °C)
Operating torque	0.3 Ncm (+20 °C)
Permissible shaft loading	80 N (radial) 40 N (axial)
Operating speed	≤ 9,000 min <sup>-1</sup>
Moment of inertia of the rotor	15 gcm <sup>2</sup>
Bearing lifetime	3.6 x 10 <sup>9</sup> revolutions
Angular acceleration	≤ 500,000 rad/s²

 $<sup>^{1)}</sup>$  Based on encoder with MS male connector.

#### Ambient data

EMC	According to EN 61000-6-2 and EN 61000-6-3
Enclosure rating	IP65, shaft side (IEC 60529) IP67, housing side (IEC 60529)
Permissible relative humidity	90 % (Condensation not permitted)
Operating temperature range	-30 °C +85 °C
Storage temperature range	-40 °C +100 °C, without package
Resistance to shocks	100 g, 11 ms (EN 60068-2-27)
Resistance to vibration	30 g, 10 Hz 2,000 Hz (EN 60068-2-6)

#### Classifications

ECLASS 5.0	27270501
ECLASS 5.1.4	27270501
ECLASS 6.0	27270590
ECLASS 6.2	27270590
ECLASS 7.0	27270501
ECLASS 8.0	27270501
ECLASS 8.1	27270501
ECLASS 9.0	27270501
ECLASS 10.0	27270501
ECLASS 11.0	27270501


 $<sup>^{1)}\,\</sup>mbox{Short-circuit}$  opposite to another channel or GND permissable for maximum 30 s.

<sup>2)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of components, average ambient temperature 40°C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

ECLASS 12.0	27270501
ETIM 5.0	EC001486
ETIM 6.0	EC001486
ETIM 7.0	EC001486
ETIM 8.0	EC001486
UNSPSC 16.0901	41112113

## Dimensional drawing (Dimensions in mm (inch))

DFS25 square flange mount, radial connector outlet M12 and MS, cable outlet



Туре	Shaft diameter A
DFS2x-x1xxxxxxxxx	1/4"
DFS2x-x2xxxxxxxx DFS2x-xCxxxxxxxxx	3/8"
DFS2x-xFxxxxxxxxx	1/2"
DFS2x-x3xxxxxxxx	6 mm
DFS2x-x4xxxxxxxx	10 mm

# PIN assignment


View of MS male device connector on encoder




M12, 8-pin	MS, 10-pin	MS, 7-pin	MS, 6-pin	Cable, 9-wire	Signal	Description
1	Н	-	-	Brown	-A	Signal wire
2	Α	Α	E	White	A	Signal wire
3	1	-	17	Black	_В	Signal wire
4	В	В	D	Pink	В	Signal wire
5	J	-	1=	Yellow	_Z	Signal wire
6	С	С	С	Purple	Z	Signal wire
7	F	F	Α	Blue	GND	GND
8	D	D	В	Red	Us	Supply voltage
-	E	E	-	Orange	0-SET	Input signal
-	G	G	F	-	Housing	Electrically con- nected to the housing poten- tial
-	-	-	-	Blank	Drain wire	Bare wire paral- lel to the braided screen
-	-	-	-	Screen	Screen	Screen connect- ed to housing on encoder side

## **Diagrams**

Maximum revolution range




Signal Outputs with Counter Clock-wise Counting Direction Option Selected (B leads A for clock-wise rotation). Complement signals AN, BN and ZN are not shown.



Cw with view on the encoder shaft in direction "A", compare dimensional drawing.

Signal Outputs with Clock-wise Counting Direction Option Selected (A leads B for clock-wise rotation). Complement signals AN, BN and ZN are not shown.



Cw with view on the encoder shaft in direction "A", compare dimensional drawing.

#### Recommended accessories

Other models and accessories → www.sick.com/DFS2x

Brief description	Туре	Part no.
Others		
<ul> <li>Connection type head A: Female connector, MS/07, 7-pin, straight</li> <li>Connection type head B: Flying leads</li> <li>Cable: 3 m, 11-wire</li> <li>Description: Shielded</li> </ul>	DOL-MS07- G03MMA2	7102145
<ul> <li>Connection type head A: Female connector, MS/07, 7-pin, straight</li> <li>Connection type head B: Flying leads</li> <li>Cable: 5 m, 11-wire</li> <li>Description: Shielded</li> </ul>	DOL-MS07- G05MMA2	7102146
<ul> <li>Connection type head A: Female connector, MS/07, 7-pin, straight</li> <li>Connection type head B: Flying leads</li> <li>Cable: 1.5 m, 11-wire</li> <li>Description: Shielded</li> </ul>	DOL-MS07- G1M5MA2	7102144
<ul> <li>Connection type head A: Female connector, MS/07, 7-pin, straight</li> <li>Connection type head B: Flying leads</li> <li>Cable: 10 m, 11-wire</li> <li>Description: Shielded</li> </ul>	DOL-MS07- G10MMA2	7102147
<ul> <li>Connection type head A: Female connector, MS/07, 7-pin, straight</li> <li>Connection type head B: Flying leads</li> <li>Cable: 20 m, 11-wire</li> <li>Description: Shielded</li> </ul>	DOL-MS07- G20MMA2	7102148
<ul> <li>Connection type head A: Female connector, MS/07, 7-pin, straight</li> <li>Connection type head B: Flying leads</li> <li>Cable: 30 m, 11-wire</li> <li>Description: Shielded</li> </ul>	DOL-MS07- G30MMA2	7102149
<ul> <li>Connection type head A: Female connector, MS/07, 7-pin, straight, A-coded</li> <li>Description: Unshielded</li> </ul>	DOS-MS07-G	7102143

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

