

SRS50-HPA0-K21

SRS/SRM50

MOTOR FEEDBACK SYSTEMS



Ordering information

Туре	Part no.
SRS50-HPA0-K21	7127312

Other models and accessories → www.sick.com/SRS_SRM50

Illustration may differ



Detailed technical data

Safety-related parameters

MTTF _D (mean time to dangerous failure)	005 (EN 100 400 40) 1)
Will II b (lineall time to dangerous familie)	235 years (EN ISO 13849) ¹⁾

¹⁾ This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of components, average ambient temperature 60 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

Performance

Sine/cosine periods per revolution	1,024
Number of the absolute ascertainable revolutions	1
Total number of steps	32,768
Measuring step	$0.3{\rm ''}$ For interpolation of the sine/cosine signals with, e. g., 12 bits
Integral non-linearity	Typ. \pm 45 $^{\prime\prime}$, Error limits for evaluating sine/cosine period
Differential non-linearity	± 7 "
Operating speed	\leq 3,000 min ⁻¹ , up to which the absolute position can be reliably produced
Available memory area	128 Byte
System accuracy	± 52 "

Interfaces

Type of code for the absolute value	Binary
Code sequence	Increasing, when turning the shaft For clockwise rotation, looking in direction "A" (see dimensional drawing), For clockwise shaft rotation, looking in direction "A" (see dimensional drawing)
Communication interface	HIPERFACE [®]

Electrical data

Connection type	Male connector, MS, 10-pin, radial
Supply voltage	7 V DC 12 V DC
Recommended supply voltage	8 V DC
Current consumption	80 mA ¹⁾

¹⁾ Without load.

≤ 200 kHz

Mechanical data

Shaft version	Blind hollow shaft
Flange type / stator coupling	Stator coupling
Dimensions	See dimensional drawing
Weight	≤ 0.2 kg
Moment of inertia of the rotor	50 gcm ²
Operating speed	≤ 6,000 min ⁻¹
Angular acceleration	$\leq 500,000 \text{ rad/s}^2$
Operating torque	1.8 Ncm
Start up torque	+ 2.6 Ncm
Permissible movement static	± 0.3 mm radial ± 0.1 mm axial
Permissible movement dynamic	± 0.1 mm radial ± 0.2 mm axial

Ambient data

Operating temperature range	≤ +75 °C
Storage temperature range	-40 °C +85 °C, without package
Relative humidity/condensation	90 %, Condensation not permitted
Resistance to shocks	100 g, 10 ms, 10 ms (according to EN 60068-2-27)
Frequency range of resistance to vibrations	20 g, 10 Hz 2,000 Hz (EN 60068-2-6)
EMC	According to EN 61000-6-2 and EN 61000-6-3 1)
Enclosure rating	IP65, with mating connector inserted (IEC 60529)

¹⁾ The EMC according to the standards quoted is achieved when the motor feedback system is mounted in an electrically conductive housing, which is connected to the central earthing point of the motor controller via a cable screen. The GND-(0 V) connection of the supply voltage is also grounded here. If other shielding concepts are used, users must perform their own tests.


Classifications

ECLASS 5.0	27270590
ECLASS 5.1.4	27270590
ECLASS 6.0	27270590
ECLASS 6.2	27270590
ECLASS 7.0	27270590
ECLASS 8.0	27270590
ECLASS 8.1	27270590
ECLASS 9.0	27270590
ECLASS 10.0	27273805
ECLASS 11.0	27273901
ECLASS 12.0	27273901
ETIM 5.0	EC001486
ETIM 6.0	EC001486
ETIM 7.0	EC001486

¹⁾ Without load.

ETIM 8.0	EC001486
UNSPSC 16.0901	41112113

Dimensional drawing (Dimensions in mm (inch))



PIN assignment




PIN	Signal	Wire colors (cable connection)	Explanation
1	REFCOS	Black	Process data channel
2	Data +	Gray or yellow	Parameter channel RS 485
3	N.C.	-	N.C.
4	N.C.	r	N.C.
5	SIN	White	Process data channel
6	REFSIN	Brown	Process data channel


PIN	Signal	Wire colors (cable connection)	Explanation
7	Data -	Green or purple	Parameter channel RS 485
8	COS	Pink	Process data channel
9	N.C.	-	N.C.
10	GND	Blue	Ground connection
11	N.C.	-	N.C.
12	Us	Red	Supply voltage: 7 V 12 V

Diagrams

Signal specification of the process channel



Signal diagram for clockwise rotation of the shaft looking in direction "A" (see dimensional drawing)1 period = 360° : 1024° Signal diagram for clockwise rotation of the shaft looking in direction "A" (see dimensional drawing)1 period = 360° : 1024°



Operation note

Model-specific settings

Type-specific settings	SRS	SRM
Model ID (command 52h)	22h	27h
Free E ² PROM [bytes]	128/1.792	128/1.792
Address	40h	40h
Mode_485	E4h	E4h
Codes 0 to 3	55h	55h
Counter	0	0

Overview of status messages for $\mathsf{HIPERFACE}^{\circledast}$

	Status code	Description	SRS	SRM
Error type	00h	The encoder has not detected any faults		
Initialization	01h	Incorrect alignment data	•	
	02h	Incorrect internal angular offset		
	03h	Data field partitioning table destroyed	•	
	04h	Analog limit values not available	•	
	05h	Internal I2C bus inoperative		
	06h	Internal checksum error	•	•
Protocol	07h	Encoder reset occurred as a result of program monitoring	•	•
	09h	Parity error		
	0Ah	Checksum of transmitted data is incorrect	-	
	0Bh	Unknown command code		
	0Ch	Number of transmitted data is incorrect	-	-
	0Dh	Transmitted command argument is not allowed	-	-
Data	0Eh	The selected data field may not be written to		
	0Fh	Incorrect access code		
	10h	Size of specified data field cannot be changed		
	11h	Specified word address lies outside the data field		
	12h	Access to non-existent data field		
Position	01h	Analog signals outside specification		
	1Fh	Speed too high, no position formation possible	•	-
	20h	Singleturn position unreliable	•	
	21h	Multiturn position error		
	22h	Multiturn position error		
	23h	Multiturn position error		
Other	1Ch	Value monitoring of the analog signals (process data)	•	
	1Dh	Transmitter current critical or P2RAM-Error		
	1Eh	Encoder temperature critical		
	08h	Counter overflow		
Fo	or more informati	on on the interface see HIPERFACE® - description, part no. 8010)701	

Overview of supported commands for HIPERFACE®

			SRS	SRM
Command byte	Function	Code 0 ¹⁾	Comments	Comments
42h	Read position		15 bit	27 bit
43h	Set position			
44h	Read analog value		Channel number F0H 48h	Channel number F0H 48h
			Temperature [°C]	Temperature [°C]
46h	Read counter			
47h	Increment Counter			
49h	Delete counter	-		
4Ah	Read data			
4Bh	Store data			
4Ch	Determine status of a data field			
4Dh	Create data field			
4Eh	Determine available memory area			
4Fh	Change access code			
50h	Read encoder status			
52h	Read out type label		Encoder type = 22h	Encoder type = 27h
53h	Encoder reset			
55h	Allocate encoder address	-		
56h	Read serial number and program version			
57h	Configure serial interface	-		

¹⁾ The commands thus marked include the parameter "Code 0". Code 0 is a byte inserted into the protocol to provide additional protection of vital system parameters against accidental overwriting. When the device is supplied, "Code 0" = 55h.

Charactersitics applicable to all permissible environmental conditions

Signal	Values/unit
Signal peak, peak V _{SS} of SIN, COS	0.9 V 1.1 V
Signal offset REFSIN, REFCOS	2.2 V 2.8 V

Recommended accessories

Other models and accessories \rightarrow www.sick.com/SRS_SRM50

	Brief description	Туре	Part no.	
Programming	Programming and configuration tools			
(co 3)	SVip® LAN programming tool for all motor feedback systems	PGT-11-S LAN	1057324	
Spare parts	Spare parts			
	BEF-MK-S02	BEF-MK-S02	2074582	
Others				
	 Connection type head A: Female connector, MS/10, 10-pin, straight, A-coded Description: Unshielded 	DOS-MS10-G	7102129	

SRS50-HPA0-K21 | SRS/SRM50 MOTOR FEEDBACK SYSTEMS

Brief description	Туре	Part no.
 Connection type head A: Female connector, MS/10, 10-pin, straight Connection type head B: Flying leads Cable: 3 m, 8-wire Description: Shielded 	DOL-MS10- G03MMA3	7102161
 Connection type head A: Female connector, MS/10, 10-pin, straight Connection type head B: Flying leads Cable: 5 m, 8-wire Description: Shielded 	DOL-MS10- G05MMA3	7102162
 Connection type head A: Female connector, MS/10, 10-pin, straight Connection type head B: Flying leads Cable: 1.5 m, 8-wire Description: Shielded 	DOL-MS10- G1M5MA3	7102160
 Connection type head A: Female connector, MS/10, 10-pin, straight Connection type head B: Flying leads Cable: 10 m, 8-wire Description: Shielded 	DOL-MS10- G10MMA3	7102163
 Connection type head A: Female connector, MS/10, 10-pin, straight Connection type head B: Flying leads Cable: 20 m, 8-wire Description: Shielded 	DOL-MS10- G20MMA3	7102164
 Connection type head A: Female connector, MS/10, 10-pin, straight Connection type head B: Flying leads Cable: 30 m, 8-wire Description: Shielded 	DOL-MS10- G30MMA3	7102165

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

