

SICK Sensor Intelligence.

CONTRAST SENSORS

Ordering information

Type KTX-WN91342252ZZZZ

Other models and accessories -> www.sick.com/KTX

CONTRAST SENSORS



Illustration may differ



Detailed technical data

Features

	Observations of the second sec
Special applications	Standard
Device type	Standard
Dimensions (W x H x D)	30 mm x 53 mm x 78.5 mm
Sensing distance	≤ 40 mm
Sensing distance tolerance	± 3 mm
Housing design	Large
Light source	LED, RGB ⁽¹⁾
Wave length	470 nm, 525 nm, 625 nm
Light emission	Short device side
Light spot size	3.9 mm x 0.9 mm
Light spot direction	Vertical ²⁾
Receiving filters	None
Teach-in mode	1-point teach-in, 2-point teach-in, teach-in dynamic, auto mode
Output function	Light/dark switching
Delay time	Adjustable
Special features	Long sensing distance
Delivery status	2-point teach-in
Parameter presettings	None
Setting the key lock	Standard

 $^{1)}$ Average service life: 100,000 h at T_{U} = +25 °C.

 $^{2)}$ In relation to long side of housing.

Part no.

1078133

Mechanics/electronics

Supply voltage10.8 V D C 28.8 V DC ¹ Ripple25 Vpp ² Current consumption5 0 kHz ^{41 5} Switching frequency50 kHz ^{41 5} Response time10 μs ^{61 71} Itter5 μs ⁸ Switching outputNPNSwitching output (voltage)NPNOutput current I _{max} .100 mA ⁹¹ Input, teach-in (ET)Teach: U < 2 V		
Current consumption< 100 mA ³)Switching frequency50 kHz ^{41 5})Response time10 µs ^{6) 7})Jitter5 µs ⁸)Switching outputNPNSwitching output (voltage)NPN: HIGH = V _S / LOW ≤ 3 VOutput current I _{max} 100 mA ⁹)Input, teach-in (ET)Teach: U < 2 V	Supply voltage	10.8 V DC 28.8 V DC ¹⁾
Switching frequencySo kHz ^{4 5} Switching frequency50 kHz ^{4 5} Response time10 µs ^{6) 7)} Jitter5 µs ⁸⁾ Switching outputNPNSwitching output (voltage)NPN: HIGH = Vs / LOW ≤ 3 VOutput current Imax.100 mA ⁹⁾ Input, teach-in (ET)Teach: U < 2 V	Ripple	\leq 5 V _{pp} ²⁾
Response time10 μs 6) 7Jitter5 μs 8)Switching outputNPNSwitching output (voltage)NPN: HIGH = Vs / LOW ≤ 3 VOutput current Imax.100 mA 9)Input, teach-in (ET)Teach: U < 2 V	Current consumption	< 100 mA ³⁾
Jitter5 µs ⁸ Switching outputNPNSwitching output (voltage)NPN: HIGH = V _S / LOW ≤ 3 VOutput current I _{max} .100 mA ⁹ Input, teach-in (ET)Each: U < 2 V	Switching frequency	50 kHz ^{4) 5)}
Switching outputNPNSwitching output (voltage)NPN: HIGH = Vs / LOW < 3 VOutput current Imax.100 mA 9Input, teach-in (ET)Teach: U < 2 VInput, fine/coarse (F/C)Blanked: U < 2 VInput, fine/coarse (F/C)Coarse: U < 2 VInput, light/dark (L/D)Light: U < 2 VRetention time (ET)25 ms, non-volatile memoryProtection classIIIConnection typeNuVu connectors, reverse polarity protected Output cytocher (Protection)Vu connectors, reverse polarity protected Output gestionsProtection1967Weight94 g	Response time	10 µs ^{6) 7)}
Switching output (voltage)NPN: HIGH = V _S / LOW ≤ 3 VOutput current I _{max.} 100 mA ⁹ Input, teach-in (ET)Teach: U < 2 V	Jitter	5 μs ⁸⁾
Output current Imax.100 mA 9Input, teach-in (ET)Teach: U < 2 V	Switching output	NPN
Input, teach-in (ET)Teach: U < 2V	Switching output (voltage)	NPN: HIGH = $V_S / LOW \le 3 V$
Input, blanking input (AT)Blanked: U < 2 V	Output current I _{max.}	100 mA ⁹⁾
Input, fine/coarse (F/C)Coarse: U < 2 V	Input, teach-in (ET)	Teach: U < 2 V
Input, light/dark (L/D)Light: U < 2 V	Input, blanking input (AT)	Blanked: U < 2 V
Retention time (ET)25 ms, non-volatile memoryConnection typeMale connector M12, 5-pinProtection classIIICircuit protectionUv connections, reverse polarity protected Output Q short-circuit protected niterference pulse suppressionEnclosure ratingIP67Weight94 g	Input, fine/coarse (F/C)	Coarse: U < 2 V
Connection typeMale connector M12, 5-pinProtection classIIICircuit protectionUv connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppressionEnclosure ratingIP67Weight94 g	Input, light/dark (L/D)	Light: U < 2 V
Protection classIIICircuit protectionUv connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppressionEnclosure ratingIP67Weight94 g	Retention time (ET)	25 ms, non-volatile memory
Circuit protectionUv connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppressionEnclosure ratingIP67Weight94 g	Connection type	Male connector M12, 5-pin
Enclosure rating Dutput Q short-circuit protected Interference pulse suppression Weight 94 g	Protection class	III
Weight 94 g	Circuit protection	Output Q short-circuit protected
	Enclosure rating	IP67
Housing material VISTAL®	Weight	94 g
	Housing material	VISTAL®

 $^{(1)}$ Limit values: DC 12 V (–10 %) ... DC 24 V (+20 %). Operation in short-circuit protected network max. 8 A.

 $^{2)}\,\mbox{May}$ not fall below or exceed \mbox{U}_{V} tolerances.

³⁾ Without load.

⁴⁾ With light/dark ratio 1:1.

⁵⁾ 1-point teach-in (color mode): 16 kHz.

⁶⁾ Signal transit time with resistive load.

 $^{7)}$ 1-point teach-in (color mode): 30 $\mu s.$

 $^{8)}$ 1-point teach-in (color mode): 15 $\mu s.$

⁹⁾ Total current of all Outputs.

Ambient data

Ambient operating temperature	-20 °C +60 °C
Ambient temperature, storage	-25 °C +75 °C
Shock load	According to IEC 60068-2-27 (30 g/11 ms)
UL File No.	E181493


Classifications


ECLASS 5.0	27270906
ECLASS 5.1.4	27270906
ECLASS 6.0	27270906
ECLASS 6.2	27270906
ECLASS 7.0	27270906


CONTRAST SENSORS

ECLASS 8.0	27270906
ECLASS 8.1	27270906
ECLASS 9.0	27270906
ECLASS 10.0	27270906
ECLASS 11.0	27270906
ECLASS 12.0	27270906
ETIM 5.0	EC001820
ETIM 6.0	EC001820
ETIM 7.0	EC001820
ETIM 8.0	EC001820
UNSPSC 16.0901	39121528

Dimensional drawing (Dimensions in mm (inch))








① Optical axis

- ② Threaded mounting hole M5
- ③ M12 male connector, delivery state
- ④ M12 male connector, end stop right
- ⑤ M12 male connector, end stop left
- 6 Display and adjustment elements

CONTRAST SENSORS

Adjustments

Display and adjustment elements




① LED status indicator

② Display

③ Navigation buttons

Connection diagram

Cd-382





Concept of operation

KTS/KTX Prime - setting the switching threshold (2-point teach-in)


Suitable for manual positioning of the object to be detected, e.g. marks and background.

1. Position mark





When setting the contrasts to be detected, "1st" flashes. Press set button.





When setting the contrasts to be detected, "2nd" flashes. Press set button. The Quality of Teach is displayed.


KTS/KTX Prime - Setting the switching threshold (teach-in dynamic)

Suitable for teaching in moving objects.

- 1. Position background
- 2. Move at least the mark and background using the light spot








Press the Set pushbutton to start the teach-in process.

The display lights up during repeat length detection (---).

Press the Set pushbutton to end the teach-in process. The Quality of Teach is displayed.



Switching characteristics

The optimum emitted light is selected automatically (at RGB variants).

Static teach-in: light/dark setting is defined using teach-in sequence.

Dynamic teach-in: switching output active on mark, if background is longer in the field of view during the teach-in. The switching threshold is set in the center between the background and the mark.


Keylock (activation and deactivation): Press and hold the "+" pushbutton > 10 s.

The Q-LED (yellow) flashes and the "Err" error message appears on the display.

CONTRAST SENSORS

Sensing distance

Sensing distance 40 mm



Recommended accessories

Other models and accessories → www.sick.com/KTX

	Brief description	Туре	Part no.	
Universal bar clamp systems				
4	Plate G for universal clamp bracket, steel, zinc coated, Universal clamp (2022726), mounting hardware	BEF-KHS-G01	2022464	
	Mounting bar, straight, 200 mm, steel, steel, zinc coated, without mounting hardware	BEF-MS12G-A	4056054	
\langle	Mounting bar, L-shaped, 150 mm x 150 mm, steel, steel, zinc coated, without mounting hardware	BEF-MS12L-A	4056052	
Others				
N.O.	 Connection type head A: Female connector, M12, 5-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 5-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF2A15- 050VB5XLEAX	2096240	
	 Connection type head A: Male connector, M12, 5-pin, straight, A-coded Description: Unshielded, Head A: male connector, M12, 5-pin, straight, unshielded, for cable diameter 4 mm 6 mm Head B: - Connection systems: Screw-type terminals Permitted cross-section: < 0.75 mm² Note: For field bus technology 	STE-1205-G	6022083	

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

