

IMI12-04BNSVU2S

IMI

INDUCTIVE PROXIMITY SENSORS



Ordering information

| Туре | Part no. |
|-----------------|----------|
| IMI12-04BNSVU2S | 1093895 |

Included in delivery: BEF-MU-M12N (1)

Other models and accessories → www.sick.com/IMI

Illustration may differ



Detailed technical data

Features

| Housing | Metric |
|-----------------------------------|--|
| Thread size | M12 x 1 |
| Diameter | Ø 12 mm |
| Sensing range S _n | 4 mm |
| Safe sensing range S _a | 3.24 mm |
| Installation type | Flush |
| Switching frequency | 75 Hz |
| Connection type | Cable, 3-wire, 2 m |
| Switching output | NPN |
| Output function | NO |
| Electrical wiring | DC 3-wire |
| Enclosure rating | IP68, IP69K ¹⁾ |
| Special features | Sensing face made of stainless steel V2A, Resistant against coolant lubricants |
| Special applications | Zones with coolants and lubricants, Difficult application conditions |
| Items supplied | Mounting nut, V2A stainless steel, with locking teeth (2x) |

 $^{^{1)}}$ According to EN 60529.

Mechanics/electronics

| Supply voltage | 10 V DC 30 V DC |
|--------------------------------|----------------------|
| Ripple | ≤ 10 % ¹⁾ |
| Voltage drop | ≤ 2 V ²⁾ |
| Time delay before availability | ≤ 300 ms |
| Hysteresis | 1 % 20 % |

 $^{^{1)}}$ Of V_{S} .

²⁾ With I max.

³⁾ Of Sr.

| Reproducibility | ≤ 2 % ³⁾ |
|--|---|
| Temperature drift (of S _r) | ≤ 10 % |
| EMC | According to EN 60947-5-2 |
| Continuous current I _a | ≤ 200 mA |
| No load current | ≤ 10 mA |
| Cable material | PUR |
| Conductor size | 0.34 mm ² |
| Cable diameter | Ø 4.5 mm |
| Short-circuit protection | ✓ |
| Power-up pulse protection | ✓ |
| Shock and vibration resistance | $100\mathrm{g}/5\mathrm{ms}/1000$ cycles; $150\mathrm{g}/1$ Mio cycles; $10\mathrm{Hz}55\mathrm{Hz}, 1\mathrm{mm}/55\mathrm{Hz}500\mathrm{Hz}/60\mathrm{g}$ |
| Ambient operating temperature | -25 °C +75 °C |
| Housing material | Stainless steel V2A, DIN 1.4305 / AISI 303 |
| Sensing face material | Stainless steel V2A, DIN 1.4305 / AISI 303 |
| Housing length | 58.8 mm |
| Thread length | 54.7 mm |
| Tightening torque, max. | ≤ 32 Nm |
| Protection class | III |
| UL File No. | E181493 |

 $^{^{1)}}$ Of V_{S} .

Safety-related parameters

| MTTF _D | 1,892 years |
|--------------------------|-------------|
| DC _{avg} | 0 % |

Reduction factors

| Note | The values are reference values which may vary | |
|----------------------------|--|--|
| St37 steel (Fe) | Approx. 1 | |
| Stainless steel (V2A, 304) | Approx. 0.67 | |
| Aluminum (AI) | Approx. 0.71 | |
| Copper (Cu) | Approx. 0.51 | |
| Brass (Br) | Approx. 0.8 | |

Installation note

| Remark | Associated graphic see "Installation" |
|--------|---------------------------------------|
| В | 12 mm |
| C | 12 mm |
| D | 25 mm |
| F | 32 mm |

Classifications

| ECLASS 5.0 | 27270101 |
|------------|----------|
|------------|----------|

²⁾ With I max.

³⁾ Of Sr.


IMI12-04BNSVU2S | IMI


INDUCTIVE PROXIMITY SENSORS

| ECLASS 5.1.4 | 27270101 |
|----------------|----------|
| ECLASS 6.0 | 27270101 |
| ECLASS 6.2 | 27270101 |
| ECLASS 7.0 | 27270101 |
| ECLASS 8.0 | 27270101 |
| ECLASS 8.1 | 27270101 |
| ECLASS 9.0 | 27270101 |
| ECLASS 10.0 | 27270101 |
| ECLASS 11.0 | 27270101 |
| ECLASS 12.0 | 27274001 |
| ETIM 5.0 | EC002714 |
| ETIM 6.0 | EC002714 |
| ETIM 7.0 | EC002714 |
| ETIM 8.0 | EC002714 |
| UNSPSC 16.0901 | 39122230 |

Installation note


Flush installation






Connection diagram

Cd-001



Response diagram




Distance of target edge to center of active face in mm (inch)

All dimensions in mm (inch)

Dimensional drawing (Dimensions in mm (inch))

IM12 Inox, flush



- ① Connection
- ② Display LED
- ③ Fastening nuts (2 x); width across 17, stainless steel V2A

Recommended accessories

Other models and accessories → www.sick.com/IMI

| | Brief description | Туре | Part no. |
|--------|--|-------------|----------|
| Others | | | |
| | Connection type head A: Male connector, M12, 4-pin, straight, A-coded Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: ≤ 0.75 mm² Application: Hygienic and washdown zones | STE-1204-GN | 6028359 |
| | Connection type head A: Male connector, M12, 4-pin, straight, A-coded Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: ≤ 0.75 mm² Note: For 2 cable connections Application: Hygienic and washdown zones | STE-1204-TN | 6028360 |
| | Connection type head A: Female connector, M12, 4-pin, straight, A-coded Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: ≤ 0.75 mm² Application: Hygienic and washdown zones | DOS-1204-GN | 6028357 |
| | Connection type head A: Female connector, M12, 4-pin, angled, A-coded Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: ≤ 0.75 mm² Application: Hygienic and washdown zones | DOS-1204-WN | 6028358 |

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

