

# IMB08-02BPOVQDK

IMB

**INDUCTIVE PROXIMITY SENSORS** 



## INDUCTIVE PROXIMITY SENSORS

## Ordering information

Туре	Part no.
IMB08-02BP0VQDK	1111805

Included in delivery: BEF-MU-M08N (1)

Other models and accessories → www.sick.com/IMB

Illustration may differ



## Detailed technical data

#### **Features**

reatures		
Housing	Metric	
Housing	Short-body	
Thread size	M8 x 1	
Diameter	Ø 8 mm	
Sensing range S <sub>n</sub>	2 mm	
Safe sensing range S <sub>a</sub>	1.62 mm	
Installation type	Flush	
Switching frequency	4,000 Hz	
Connection type	Cable with connector M12, 3-pin, 600 mm	
Switching output	PNP	
Output function	NC	
Electrical wiring	DC 3-wire	
Enclosure rating	IP68 <sup>1)</sup> IP69K <sup>2)</sup>	
Special features	Resistant against coolant lubricants, Visual adjustment indicator	
Special applications	Zones with coolants and lubricants, Mobile machines, Difficult application conditions	
Items supplied	Mounting nut, V2A stainless steel, with locking teeth (2x)	

<sup>&</sup>lt;sup>1)</sup> According to EN 60529.

## Mechanics/electronics

Supply voltage	10 V DC 30 V DC
Ripple	≤ 10 %

 $<sup>^{1)}</sup>$  At I $_{\rm a}$  max.

<sup>&</sup>lt;sup>2)</sup> According to ISO 20653:2013-03.

 $<sup>^{\</sup>rm 2)}$  Supply voltage  $\rm U_B$  and constant ambient temperature Ta.

<sup>3)</sup> Of St

 $<sup>^{</sup>m 4)}$  When using the non-toothed side of the nut.

 $<sup>^{5)}\,\</sup>mbox{Valid}$  if toothed side of nut is used.

Voltage drop	$\leq$ 2 V $^{1)}$
Hysteresis	3 % 20 %
Reproducibility	≤ 2 % <sup>2) 3)</sup>
Temperature drift (of S <sub>r</sub> )	± 10 %
EMC	According to EN 60947-5-2
Continuous current I <sub>a</sub>	≤ 200 mA
No load current	≤ 10 mA
Cable material	PUR
Short-circuit protection	✓
Power-up pulse protection	✓
Shock and vibration resistance	$100~{\rm g}/$ 11 ms / $1000$ cycles; 150 g / 1 Mio cycles; 10 Hz 55 Hz, 1 mm / 55 Hz 500 Hz / 15 g
Ambient operating temperature	-40 °C +80 °C
Ambient operating temperature	
Housing material	Stainless steel V2A, DIN 1.4305 / AISI 303
Housing material	Stainless steel V2A, DIN 1.4305 / AISI 303
Housing material Sensing face material	Stainless steel V2A, DIN 1.4305 / AISI 303 Plastic, LCP
Housing material Sensing face material Housing length	Stainless steel V2A, DIN 1.4305 / AISI 303 Plastic, LCP 32 mm
Housing material Sensing face material Housing length Thread length	Stainless steel V2A, DIN 1.4305 / AISI 303  Plastic, LCP  32 mm  28 mm  Typ. 7 Nm 4)

<sup>&</sup>lt;sup>1)</sup> At I<sub>a</sub> max.

## Safety-related parameters

MTTF <sub>D</sub>	1,971 years
<b>DC</b> <sub>avg</sub>	0 %
T <sub>M</sub> (mission time)	20 years

## Reduction factors

Note	The values are reference values which may vary
St37 steel (Fe)	1
Stainless steel (V2A, 304)	Approx. 0.74
Aluminum (AI)	Approx. 0.43
Copper (Cu)	Approx. 0.33
Brass (Br)	Approx. 0.46

## Installation note

Remark	Associated graphic see "Installation"
В	6.5 mm
c	8 mm

 $<sup>^{\</sup>rm 2)}$  Supply voltage  $\rm U_B$  and constant ambient temperature Ta.

<sup>3)</sup> Of Sr.

<sup>4)</sup> When using the non-toothed side of the nut.

<sup>5)</sup> Valid if toothed side of nut is used.

## IMB08-02BPOVQDK | IMB

## INDUCTIVE PROXIMITY SENSORS


D	6 mm
F	16 mm


## Classifications

ECLASS 5.0	27270101
ECLASS 5.1.4	27270101
ECLASS 6.0	27270101
ECLASS 6.2	27270101
ECLASS 7.0	27270101
ECLASS 8.0	27270101
ECLASS 8.1	27270101
ECLASS 9.0	27270101
ECLASS 10.0	27270101
ECLASS 11.0	27270101
ECLASS 12.0	27274001
ETIM 5.0	EC002714
ETIM 6.0	EC002714
ETIM 7.0	EC002714
ETIM 8.0	EC002714
UNSPSC 16.0901	39122230

## Installation note

Flush installation






## Connection diagram

Cd-004

## Response diagram


#### Response diagram

#### Distance in mm (inch)




## Functional principle

#### Installation aid



## Dimensional drawing (Dimensions in mm (inch))



- ① Connection
- ② Fastening nuts (2 x); width across 13, stainless steel V2A

## IMB08-02BPOVQDK | IMB

## INDUCTIVE PROXIMITY SENSORS

## Recommended accessories

Other models and accessories → www.sick.com/IMB

	Brief description	Туре	Part no.
Mounting brackets and plates			
	Mounting plate for M8 sensors, steel, zinc coated, without mounting hardware	BEF-WG-M08	5321722
	Mounting bracket for M8 sensors, steel, zinc coated, without mounting hardware	BEF-WN-M08	5321721

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

## **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

